

[All Products](#) / [Optics](#) / [Optical Filters](#) / [Neutral Density \(ND\) Filters](#)

TECHSPEC®

Reflective Neutral Density (ND) Filters



- Spectrally Flat
- Maximum Accuracy and Neutrality at Moderate Price
- Use Stacks to Create Intermediate Density Values

Common Specifications

General

Note:		Optical density values are average over specified blocking wavelength range.	
Physical & Mechanical Properties			
Thickness (mm):		1.60 Nominal	
Dimensional Tolerance (mm):		±0.5	Clear Aperture (%): 80
Optical Properties			
Angle of Incidence (°):		0	Substrate: Float Glass
Coating:		Surface 1: Inconel	Surface Quality: 80-50
Blocking Wavelength Range (nm):		400 - 700	Surface Flatness (P-V): 4 - 6λ

Technical Information

Products

Dia. (mm)	Dimensions (mm)	Optical Density OD (Average)	Thickness (mm)	Transmission (%)	Stock Number	Price	Buy
12.50	-	0.1	1.60	79.49	#64-125	₹2,647 Volume Pricing	20+ In Stock
12.50	-	0.15	1.60	70.79	#64-126	₹2,647 Volume Pricing	20+ In Stock
12.50	-	0.2	1.60	63.10	#64-127	₹2,647 Volume Pricing	20+ In Stock
12.50	-	0.3	1.60	50.00	#46-131	₹2,647 Volume Pricing	20+ In Stock
12.50	-	0.4	1.60	40.00	#64-128	₹2,647 Volume Pricing	20+ In Stock
12.50	-	0.5	1.60	32.00	#46-132	₹2,647 Volume Pricing	20+ In Stock
12.50	-	0.6	1.60	25.00	#49-071	₹2,647 Volume Pricing	1 In Stock
12.50	-	0.7	1.60	20.00	#64-130	₹2,647 Volume Pricing	20+ In Stock
12.50	-	0.9	1.60	12.5	#49-074	₹2,647 Volume Pricing	20+ In Stock
12.50	-	1.0	1.60	10.00	#46-133	₹2,647 Volume Pricing	20+ In Stock
12.50	-	2.0	1.60	1.00	#46-136	₹2,647 Volume Pricing	20+ In Stock
12.50	-	2.5	1.60	0.3	#46-137	₹2,647 Volume Pricing	20+ In Stock
12.50	-	3.0	1.60	0.1	#46-138	₹2,647 Volume Pricing	4 In Stock
25.00	-	0.1	1.60	79.49	#64-131	₹3,893 Volume Pricing	20+ In Stock
25.00	-	0.2	1.60	63.10	#64-133	₹3,893 Volume Pricing	14 In Stock
25.00	-	0.3	1.60	50.00	#30-933	₹3,893 Volume Pricing	20+ In Stock

[#64-136 Clearance](#)



Clearance

Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.

25.00	-	0.7	1.60	20.00		₹3,236	17 In Stock
-------	---	-----	------	-------	--	--------	-------------

25.00	-	1.0	1.60	10.00	#30-935	₹3,893 Volume Pricing	20+ In Stock
-------	---	-----	------	-------	-------------------------	--	--------------

25.00	-	1.3	1.60	5.00	#30-936	₹3,893 Volume Pricing	Contact Us
-------	---	-----	------	------	-------------------------	--	------------

25.00	-	2.0	1.60	1.00	#30-938	₹3,893 Volume Pricing	20+ In Stock
-------	---	-----	------	------	-------------------------	--	--------------

[#43-812 Clearance](#)



Clearance

Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.

25.00	-	3.0	1.60	0.1		₹3,236	Contact Us
-------	---	-----	------	-----	--	--------	------------

[#64-139 Clearance](#)



Clearance

Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.

-	50.0 x 50.0	0.2	1.60	63.10		₹4,586	7 In Stock
---	-------------	-----	------	-------	--	--------	------------

-	50.0 x 50.0	0.3	1.60	50.00	#43-813	₹5,605 Volume Pricing	5 In Stock
---	-------------	-----	------	-------	-------------------------	--	------------

-	50.0 x 50.0	1.0	1.60	10.00	#43-815	₹5,605 Volume Pricing	20+ In Stock
---	-------------	-----	------	-------	-------------------------	--	--------------

-	50.0 x 50.0	1.3	1.60	5.00	#46-123	₹5,605 Volume Pricing	14 In Stock
---	-------------	-----	------	------	-------------------------	--	-------------

-	50.0 x 50.0	2.0	1.60	1.00	#43-816	₹5,605 Volume Pricing	Contact Us
---	-------------	-----	------	------	-------------------------	--	------------

-	50.0 x 50.0	3.0	1.60	0.1	#46-126	₹5,605 Volume Pricing	20+ In Stock
---	-------------	-----	------	-----	-------------------------	--	--------------

