

[All Products](#) / [Optics](#) / [Windows and Diffusers](#) / [Visible Windows](#)

TECHSPEC® $\lambda/4$ N-BK7 Precision Windows



- Circular and Rectangular Sizes from 2mm to 200mm
- 8 Broadband Anti-Reflection Coating Options Available
- World's Largest Selection of Standard N-BK7 Windows
- Also Available with [Ultra-Thin N-BK7 Windows](#)

Common Specifications

Physical & Mechanical Properties

Bevel:	Protective as needed	Clear Aperture (%):	90
Edges:	Fine Ground	Knoop Hardness (kg/mm²):	610.00
Parallelism (arcmin):	<1	Poisson's Ratio:	0.21
Young's Modulus (GPa):	82		

Optical Properties

Abbe Number (v_d):	64.17		
Index of Refraction (n_d):	1.516	Surface Quality:	60-40

Material Properties

Density (g/cm³):	2.51
------------------------------------	------

Technical Information

Products

Dia. (mm)	Dimensions (mm)	Thickness (mm)	Coating	Stock Number	Price	Buy
2.00	-	1.00	Uncoated	#27-674	₹2,971 Volume Pricing	20+ In Stock
2.50	-	1.00	Uncoated	#27-675	₹3,172 Volume Pricing	4 In Stock
3.00	-	1.00	Uncoated	#27-719	₹3,374 Volume Pricing	8 In Stock
4.00	-	1.00	Uncoated	#27-815	₹3,778 Volume Pricing	20+ In Stock
5.00	-	1.00	Uncoated	#20-464	₹4,401 Volume Pricing	20+ In Stock
5.00	-	1.00	MgF ₂ (400-700nm)	#23-355	₹5,281 Volume Pricing	8 In Stock
5.00	-	1.00	VIS-EXT (350-700nm)	#23-443	₹6,381 Volume Pricing	1 In Stock
5.00	-	1.00	VIS-NIR (400-1000nm)	#23-399	₹6,381 Volume Pricing	1 In Stock
5.00	-	1.00	VIS 0° (425-675nm)	#23-377	₹6,125 Volume Pricing	6 In Stock
5.00	-	1.00	YAG-BBAR (500-1100nm)	#23-465	₹6,381 Volume Pricing	11 In Stock
5.00	-	1.00	NIR I (600-1050nm)	#23-421	₹6,125 Volume Pricing	2 In Stock
5.00	-	1.00	NIR II (750-1550nm)	#25-783	₹6,125 Volume Pricing	5 In Stock
5.00	-	2.00	Uncoated	#45-573	₹4,401 Volume Pricing	5 In Stock
5.00	-	2.00	MgF ₂ (400-700nm)	#45-574	₹5,281 Volume Pricing	20+ In Stock
5.00	-	2.00	VIS-EXT (350-700nm)	#13-286	₹6,381 Volume Pricing	10 In Stock

5.00	-	2.00	VIS-NIR (400-1000nm)	#48-448	₹6,381 Volume Pricing	Contact Us
5.00	-	2.00	VIS 0° (425-675nm)	#47-515	₹6,125 Volume Pricing	9 In Stock
5.00	-	2.00	YAG-BBAR (500-1100nm)	#13-308	₹6,381 Volume Pricing	16 In Stock
5.00	-	2.00	NIR I (600-1050nm)	#83-464	₹6,125 Volume Pricing	20+ In Stock
5.00	-	2.00	NIR II (750-1550nm)	#25-784	₹6,125 Volume Pricing	20+ In Stock
-	6.00 x 6.00	2.00	Uncoated	#29-300	₹4,401 Volume Pricing	17 In Stock
9.00	-	1.00	Uncoated	#20-472	₹4,401 Volume Pricing	3 In Stock
9.00	-	1.00	MgF ₂ (400-700nm)	#23-356	₹5,281 Volume Pricing	1 In Stock
9.00	-	1.00	VIS-EXT (350-700nm)	#23-444	₹6,381 Volume Pricing	5 In Stock
9.00	-	1.00	VIS-NIR (400-1000nm)	#23-400	₹6,381 Volume Pricing	Contact Us
9.00	-	1.00	VIS 0° (425-675nm)	#23-378	₹6,125 Volume Pricing	1 In Stock
9.00	-	1.00	YAG-BBAR (500-1100nm)	#23-466	₹6,381 Volume Pricing	5 In Stock
9.00	-	1.00	NIR I (600-1050nm)	#23-422	₹6,125 Volume Pricing	20+ In Stock
9.00	-	1.00	NIR II (750-1550nm)	#25-785	₹6,125 Volume Pricing	5 In Stock
9.00	-	2.00	Uncoated	#49-121	₹4,401 Volume Pricing	20+ In Stock
9.00	-	2.00	MgF ₂ (400-700nm)	#49-122	₹5,281 Volume Pricing	20+ In Stock
9.00	-	2.00	VIS-EXT (350-700nm)	#13-287	₹6,381 Volume Pricing	5 In Stock

9.00	-	2.00	VIS-NIR (400-1000nm)	#49-124	₹6,381 Volume Pricing	20+ In Stock
9.00	-	2.00	VIS 0° (425-675nm)	#49-123	₹6,125 Volume Pricing	20+ In Stock
9.00	-	2.00	YAG-BBAR (500-1100nm)	#13-309	₹6,381 Volume Pricing	8 In Stock
9.00	-	2.00	NIR I (600-1050nm)	#83-465	₹6,125 Volume Pricing	7 In Stock
9.00	-	2.00	NIR II (750-1550nm)	#25-786	₹6,125 Volume Pricing	4 In Stock
10.00	-	1.00	Uncoated	#20-480	₹4,401 Volume Pricing	20+ In Stock
10.00	-	1.00	MgF ₂ (400-700nm)	#23-357	₹5,281 Volume Pricing	7 In Stock
10.00	-	1.00	VIS-EXT (350-700nm)	#23-445	₹6,381 Volume Pricing	6 In Stock
10.00	-	1.00	VIS-NIR (400-1000nm)	#23-401	₹6,381 Volume Pricing	Contact Us
10.00	-	1.00	VIS 0° (425-675nm)	#23-379	₹6,125 Volume Pricing	3 In Stock
10.00	-	1.00	YAG-BBAR (500-1100nm)	#23-467	₹6,381 Volume Pricing	7 In Stock
10.00	-	1.00	NIR I (600-1050nm)	#23-423	₹6,125 Volume Pricing	2 In Stock
10.00	-	1.00	NIR II (750-1550nm)	#25-787	₹6,125 Volume Pricing	20+ In Stock
-	10.00 x 10.00	1.00	Uncoated	#20-539	₹4,401 Volume Pricing	5 In Stock
-	10.00 x 10.00	1.00	MgF ₂ (400-700nm)	#23-369	₹5,281 Volume Pricing	Contact Us
-	10.00 x 10.00	1.00	VIS-EXT (350-700nm)	#23-457	₹6,381 Volume Pricing	5 In Stock
-	10.00 x 10.00	1.00	VIS-NIR (400-1000nm)	#23-413	₹6,381 Volume Pricing	1 In Stock

-	10.00 x 10.00	1.00	VIS 0° (425-675nm)	#23-391	₹6,125 Volume Pricing	Contact Us
-	10.00 x 10.00	1.00	YAG-BBAR (500-1100nm)	#23-479	₹6,381 Volume Pricing	Contact Us
-	10.00 x 10.00	1.00	NIR I (600-1050nm)	#23-435	₹6,125 Volume Pricing	1 In Stock
-	10.00 x 10.00	1.00	NIR II (750-1550nm)	#25-788	₹6,125 Volume Pricing	1 In Stock
10.00	-	2.00	Uncoated	#45-074	₹4,401 Volume Pricing	20+ In Stock
10.00	-	2.00	MgF ₂ (400-700nm)	#45-256	₹5,281 Volume Pricing	20+ In Stock
10.00	-	2.00	VIS-EXT (350-700nm)	#13-288	₹6,381 Volume Pricing	8 In Stock
10.00	-	2.00	VIS-NIR (400-1000nm)	#45-657	₹6,381 Volume Pricing	20+ In Stock
10.00	-	2.00	VIS 0° (425-675nm)	#47-516	₹6,125 Volume Pricing	Contact Us
10.00	-	2.00	YAG-BBAR (500-1100nm)	#13-310	₹6,381 Volume Pricing	6 In Stock
10.00	-	2.00	NIR I (600-1050nm)	#83-466	₹6,125 Volume Pricing	15 In Stock
10.00	-	2.00	NIR II (750-1550nm)	#25-789	₹6,125 Volume Pricing	5 In Stock
-	10.00 x 10.00	2.00	Uncoated	#49-620	₹4,401 Volume Pricing	20+ In Stock
-	10.00 x 10.00	2.00	MgF ₂ (400-700nm)	#49-623	₹5,281 Volume Pricing	20+ In Stock
-	10.00 x 10.00	2.00	VIS-EXT (350-700nm)	#13-289	₹6,381 Volume Pricing	8 In Stock
-	10.00 x 10.00	2.00	VIS-NIR (400-1000nm)	#49-631	₹6,381 Volume Pricing	6 In Stock
-	10.00 x 10.00	2.00	VIS 0° (425-675nm)	#49-627	₹6,125 Volume Pricing	Contact Us

-	10.00 x 10.00	2.00	YAG-BBAR (500-1100nm)	#13-311	₹6,381 Volume Pricing	5 In Stock
-	10.00 x 10.00	2.00	NIR I (600-1050nm)	#83-467	₹6,125 Volume Pricing	1 In Stock
-	10.00 x 10.00	2.00	NIR II (750-1550nm)	#25-790	₹6,125 Volume Pricing	4 In Stock
12.50	-	1.00	Uncoated	#20-491	₹4,401 Volume Pricing	20+ In Stock
12.50	-	1.00	MgF ₂ (400-700nm)	#23-358	₹5,281 Volume Pricing	Contact Us
12.50	-	1.00	VIS-EXT (350-700nm)	#23-446	₹6,381 Volume Pricing	6 In Stock
12.50	-	1.00	VIS-NIR (400-1000nm)	#23-402	₹6,381 Volume Pricing	20+ In Stock
12.50	-	1.00	VIS 0° (425-675nm)	#23-380	₹6,125 Volume Pricing	3 In Stock
12.50	-	1.00	YAG-BBAR (500-1100nm)	#23-468	₹6,381 Volume Pricing	1 In Stock
12.50	-	1.00	NIR I (600-1050nm)	#23-424	₹6,125 Volume Pricing	3 In Stock
12.50	-	1.00	NIR II (750-1550nm)	#25-791	₹6,125 Volume Pricing	6 In Stock
12.50	-	1.00	BBAR (1650-3000nm)	#70-280	₹7,152 Volume Pricing	4 In Stock
12.50	-	2.00	Uncoated	#20-495	₹4,401 Volume Pricing	10 In Stock
12.50	-	2.00	MgF ₂ (400-700nm)	#23-359	₹5,281 Volume Pricing	Contact Us
12.50	-	2.00	VIS-EXT (350-700nm)	#23-447	₹6,381 Volume Pricing	2 In Stock
12.50	-	2.00	VIS-NIR (400-1000nm)	#23-403	₹6,381 Volume Pricing	5 In Stock
12.50	-	2.00	VIS 0° (425-675nm)	#23-381	₹6,125 Volume Pricing	2 In Stock

12.50	-	2.00	YAG-BBAR (500-1100nm)	#23-469	₹6,381 Volume Pricing	Contact Us
12.50	-	2.00	NIR I (600-1050nm)	#23-425	₹6,125 Volume Pricing	1 In Stock
12.50	-	2.00	NIR II (750-1550nm)	#25-792	₹6,125 Volume Pricing	5 In Stock
12.50	-	3.00	Uncoated	#45-075	₹4,401 Volume Pricing	20+ In Stock
12.50	-	3.00	MgF ₂ (400-700nm)	#45-257	₹5,281 Volume Pricing	Contact Us
12.50	-	3.00	VIS-EXT (350-700nm)	#13-290	₹6,381 Volume Pricing	7 In Stock
12.50	-	3.00	VIS-NIR (400-1000nm)	#45-658	₹6,381 Volume Pricing	20+ In Stock
12.50	-	3.00	VIS 0° (425-675nm)	#47-517	₹6,125 Volume Pricing	20+ In Stock
12.50	-	3.00	YAG-BBAR (500-1100nm)	#13-312	₹6,381 Volume Pricing	11 In Stock
12.50	-	3.00	NIR I (600-1050nm)	#83-468	₹6,125 Volume Pricing	14 In Stock
12.50	-	3.00	NIR II (750-1550nm)	#25-793	₹6,125 Volume Pricing	11 In Stock
-	12.50 x 12.50	3.00	Uncoated	#49-621	₹4,401 Volume Pricing	20+ In Stock
-	12.50 x 12.50	3.00	MgF ₂ (400-700nm)	#49-624	₹5,281 Volume Pricing	20+ In Stock
-	12.50 x 12.50	3.00	VIS-EXT (350-700nm)	#13-291	₹6,381 Volume Pricing	7 In Stock
-	12.50 x 12.50	3.00	VIS-NIR (400-1000nm)	#49-632	₹6,381 Volume Pricing	5 In Stock
-	12.50 x 12.50	3.00	VIS 0° (425-675nm)	#49-628	₹6,125 Volume Pricing	2 In Stock
-	12.50 x 12.50	3.00	YAG-BBAR (500-1100nm)	#13-313	₹6,381 Volume Pricing	4 In Stock

-	12.50 x 12.50	3.00	NIR I (600-1050nm)	#83-469	₹6,125 Volume Pricing	5 In Stock
-	12.50 x 12.50	3.00	NIR II (750-1550nm)	#25-794	₹6,125 Volume Pricing	2 In Stock
12.70	-	3.00	Uncoated	#15-423	₹4,401 Volume Pricing	20+ In Stock
12.70	-	3.00	MgF ₂ (400-700nm)	#15-427	₹5,281 Volume Pricing	5 In Stock
12.70	-	3.00	VIS-EXT (350-700nm)	#15-787	₹6,381 Volume Pricing	Contact Us
12.70	-	3.00	VIS-NIR (400-1000nm)	#15-435	₹6,381 Volume Pricing	20+ In Stock
12.70	-	3.00	VIS 0° (425-675nm)	#15-431	₹6,125 Volume Pricing	3 In Stock
12.70	-	3.00	YAG-BBAR (500-1100nm)	#15-791	₹6,381 Volume Pricing	11 In Stock
12.70	-	3.00	NIR I (600-1050nm)	#15-439	₹6,125 Volume Pricing	7 In Stock
12.70	-	3.00	NIR II (750-1550nm)	#25-795	₹6,125 Volume Pricing	2 In Stock
15.00	-	1.00	Uncoated	#20-503	₹4,548 Volume Pricing	Contact Us
15.00	-	1.00	MgF ₂ (400-700nm)	#23-360	₹5,355 Volume Pricing	1 In Stock
15.00	-	1.00	VIS-EXT (350-700nm)	#23-448	₹6,491 Volume Pricing	4 In Stock
15.00	-	1.00	VIS-NIR (400-1000nm)	#23-404	₹6,491 Volume Pricing	Contact Us
15.00	-	1.00	VIS 0° (425-675nm)	#23-382	₹6,235 Volume Pricing	5 In Stock
15.00	-	1.00	YAG-BBAR (500-1100nm)	#23-470	₹6,491 Volume Pricing	4 In Stock
15.00	-	1.00	NIR I (600-1050nm)	#23-426	₹6,235 Volume Pricing	2 In Stock

15.00	-	1.00	NIR II (750-1550nm)	#25-796	₹6,235 Volume Pricing	5 In Stock
15.00	-	3.00	Uncoated	#45-575	₹4,548 Volume Pricing	20+ In Stock
15.00	-	3.00	MgF ₂ (400-700nm)	#45-576	₹5,355 Volume Pricing	20+ In Stock
15.00	-	3.00	VIS-EXT (350-700nm)	#13-292	₹6,491 Volume Pricing	6 In Stock
15.00	-	3.00	VIS-NIR (400-1000nm)	#45-659	₹6,491 Volume Pricing	Contact Us
15.00	-	3.00	VIS 0° (425-675nm)	#47-518	₹6,235 Volume Pricing	20+ In Stock
15.00	-	3.00	YAG-BBAR (500-1100nm)	#13-314	₹6,491 Volume Pricing	7 In Stock
15.00	-	3.00	NIR I (600-1050nm)	#83-470	₹6,235 Volume Pricing	9 In Stock
15.00	-	3.00	NIR II (750-1550nm)	#25-797	₹6,235 Volume Pricing	5 In Stock
20.00	-	1.00	Uncoated	#20-504	₹4,841 Volume Pricing	20+ In Stock
20.00	-	1.00	MgF ₂ (400-700nm)	#23-361	₹5,721 Volume Pricing	1 In Stock
20.00	-	1.00	VIS-EXT (350-700nm)	#23-449	₹6,858 Volume Pricing	4 In Stock
20.00	-	1.00	VIS-NIR (400-1000nm)	#23-405	₹6,858 Volume Pricing	5 In Stock
20.00	-	1.00	VIS 0° (425-675nm)	#23-383	₹6,675 Volume Pricing	3 In Stock
20.00	-	1.00	YAG-BBAR (500-1100nm)	#23-471	₹6,858 Volume Pricing	4 In Stock
20.00	-	1.00	NIR I (600-1050nm)	#23-427	₹6,675 Volume Pricing	5 In Stock
20.00	-	1.00	NIR II (750-1550nm)	#25-798	₹6,675 Volume Pricing	1 In Stock

20.00	-	2.00	Uncoated	#20-507	₹4,841 Volume Pricing	20+ In Stock
20.00	-	2.00	MgF ₂ (400-700nm)	#23-362	₹5,721 Volume Pricing	5 In Stock
20.00	-	2.00	VIS-EXT (350-700nm)	#23-450	₹6,858 Volume Pricing	4 In Stock
20.00	-	2.00	VIS-NIR (400-1000nm)	#23-406	₹6,858 Volume Pricing	10 In Stock
20.00	-	2.00	VIS 0° (425-675nm)	#23-384	₹6,675 Volume Pricing	6 In Stock
20.00	-	2.00	YAG-BBAR (500-1100nm)	#23-472	₹6,858 Volume Pricing	8 In Stock
20.00	-	2.00	NIR I (600-1050nm)	#23-428	₹6,675 Volume Pricing	1 In Stock
20.00	-	2.00	NIR II (750-1550nm)	#25-799	₹6,675 Volume Pricing	3 In Stock
20.00	-	3.00	Uncoated	#45-577	₹4,841 Volume Pricing	20+ In Stock
20.00	-	3.00	MgF ₂ (400-700nm)	#45-578	₹5,721 Volume Pricing	3 In Stock
20.00	-	3.00	VIS-EXT (350-700nm)	#13-293	₹6,858 Volume Pricing	2 In Stock
20.00	-	3.00	VIS-NIR (400-1000nm)	#45-660	₹6,858 Volume Pricing	20+ In Stock
20.00	-	3.00	VIS 0° (425-675nm)	#47-519	₹6,675 Volume Pricing	20+ In Stock
20.00	-	3.00	YAG-BBAR (500-1100nm)	#13-315	₹6,858 Volume Pricing	4 In Stock
20.00	-	3.00	NIR I (600-1050nm)	#83-471	₹6,675 Volume Pricing	20+ In Stock
20.00	-	3.00	NIR II (750-1550nm)	#25-800	₹6,675 Volume Pricing	1 In Stock
25.00	-	1.00	Uncoated	#36-991	₹5,135 Volume Pricing	20+ In Stock

25.00	-	1.00	MgF ₂ (400-700nm)	#36-994	₹6,051 Volume Pricing	5 In Stock
25.00	-	1.00	VIS-EXT (350-700nm)	#13-294	₹7,152 Volume Pricing	14 In Stock
25.00	-	1.00	VIS-NIR (400-1000nm)	#36-997	₹7,152 Volume Pricing	13 In Stock
25.00	-	1.00	VIS 0° (425-675nm)	#36-996	₹6,932 Volume Pricing	5 In Stock
25.00	-	1.00	YAG-BBAR (500-1100nm)	#13-316	₹7,152 Volume Pricing	1 In Stock
25.00	-	1.00	NIR I (600-1050nm)	#36-995	₹6,932 Volume Pricing	20+ In Stock
25.00	-	1.00	NIR II (750-1550nm)	#25-801	₹6,932 Volume Pricing	2 In Stock
25.00	-	1.00	BBAR (1650-3000nm)	#70-281	₹7,775 Volume Pricing	3 In Stock
-	25.00 x 25.00	1.00	Uncoated	#20-556	₹5,135 Volume Pricing	20+ In Stock
-	25.00 x 25.00	1.00	MgF ₂ (400-700nm)	#23-370	₹6,051 Volume Pricing	4 In Stock
-	25.00 x 25.00	1.00	VIS-EXT (350-700nm)	#23-458	₹7,152 Volume Pricing	2 In Stock
-	25.00 x 25.00	1.00	VIS-NIR (400-1000nm)	#23-414	₹7,152 Volume Pricing	6 In Stock
-	25.00 x 25.00	1.00	VIS 0° (425-675nm)	#23-392	₹6,932 Volume Pricing	1 In Stock
-	25.00 x 25.00	1.00	YAG-BBAR (500-1100nm)	#23-480	₹7,152 Volume Pricing	1 In Stock
-	25.00 x 25.00	1.00	NIR I (600-1050nm)	#23-436	₹6,932 Volume Pricing	5 In Stock
-	25.00 x 25.00	1.00	NIR II (750-1550nm)	#25-802	₹6,932 Volume Pricing	7 In Stock
25.00	-	2.00	Uncoated	#36-992	₹5,135 Volume Pricing	20+ In Stock

25.00	-	2.00	MgF ₂ (400-700nm)	#36-998	₹6,051 Volume Pricing	20+ In Stock
25.00	-	2.00	VIS-EXT (350-700nm)	#13-295	₹7,152 Volume Pricing	10 In Stock
25.00	-	2.00	VIS-NIR (400-1000nm)	#37-002	₹7,152 Volume Pricing	5 In Stock
25.00	-	2.00	VIS 0° (425-675nm)	#37-001	₹6,932 Volume Pricing	5 In Stock
25.00	-	2.00	YAG-BBAR (500-1100nm)	#13-317	₹7,152 Volume Pricing	6 In Stock
25.00	-	2.00	NIR I (600-1050nm)	#36-999	₹6,932 Volume Pricing	10 In Stock
25.00	-	2.00	NIR II (750-1550nm)	#25-803	₹6,932 Volume Pricing	1 In Stock
-	25.00 x 25.00	2.00	Uncoated	#20-573	₹5,135 Volume Pricing	1 In Stock
-	25.00 x 25.00	2.00	MgF ₂ (400-700nm)	#23-371	₹6,051 Volume Pricing	1 In Stock
-	25.00 x 25.00	2.00	VIS-EXT (350-700nm)	#23-459	₹7,152 Volume Pricing	Contact Us
-	25.00 x 25.00	2.00	VIS-NIR (400-1000nm)	#23-415	₹7,152 Volume Pricing	4 In Stock
-	25.00 x 25.00	2.00	VIS 0° (425-675nm)	#23-393	₹6,932 Volume Pricing	4 In Stock
-	25.00 x 25.00	2.00	YAG-BBAR (500-1100nm)	#23-481	₹7,152 Volume Pricing	13 In Stock
-	25.00 x 25.00	2.00	NIR I (600-1050nm)	#23-437	₹6,932 Volume Pricing	1 In Stock
-	25.00 x 25.00	2.00	NIR II (750-1550nm)	#25-804	₹6,932 Volume Pricing	2 In Stock
25.00	-	3.00	Uncoated	#36-993	₹5,135 Volume Pricing	20+ In Stock
25.00	-	3.00	MgF ₂ (400-700nm)	#37-003	₹6,051 Volume Pricing	1 In Stock

25.00	-	3.00	VIS-EXT (350-700nm)	#13-296	₹7,152 Volume Pricing	Contact Us
25.00	-	3.00	VIS-NIR (400-1000nm)	#37-006	₹7,152 Volume Pricing	3 In Stock
25.00	-	3.00	VIS 0° (425-675nm)	#37-005	₹6,932 Volume Pricing	20+ In Stock
25.00	-	3.00	YAG-BBAR (500-1100nm)	#13-318	₹7,152 Volume Pricing	4 In Stock
25.00	-	3.00	NIR I (600-1050nm)	#37-004	₹6,932 Volume Pricing	2 In Stock
25.00	-	3.00	NIR II (750-1550nm)	#25-805	₹6,932 Volume Pricing	8 In Stock
25.00	-	3.00	BBAR (1650-3000nm)	#70-282	₹7,775 Volume Pricing	3 In Stock
25.00	-	4.00	Uncoated	#45-076	₹5,135 Volume Pricing	20+ In Stock
25.00	-	4.00	MgF ₂ (400-700nm)	#45-258	₹6,051 Volume Pricing	2 In Stock
25.00	-	4.00	VIS-EXT (350-700nm)	#13-297	₹7,152 Volume Pricing	4 In Stock
25.00	-	4.00	VIS-NIR (400-1000nm)	#45-661	₹7,152 Volume Pricing	15 In Stock
25.00	-	4.00	VIS 0° (425-675nm)	#47-520	₹6,932 Volume Pricing	20+ In Stock
25.00	-	4.00	YAG-BBAR (500-1100nm)	#13-319	₹7,152 Volume Pricing	12 In Stock
25.00	-	4.00	NIR I (600-1050nm)	#83-472	₹6,932 Volume Pricing	20+ In Stock
25.00	-	4.00	NIR II (750-1550nm)	#25-806	₹6,932 Volume Pricing	3 In Stock
-	25.00 x 25.00	4.00	Uncoated	#49-622	₹5,135 Volume Pricing	20+ In Stock
-	25.00 x 25.00	4.00	MgF ₂ (400-700nm)	#49-625	₹6,051 Volume Pricing	1 In Stock

-	25.00 x 25.00	4.00	VIS-EXT (350-700nm)	#13-298	₹7,152 Volume Pricing	5 In Stock
-	25.00 x 25.00	4.00	VIS-NIR (400-1000nm)	#49-633	₹7,152 Volume Pricing	3 In Stock
-	25.00 x 25.00	4.00	VIS 0° (425-675nm)	#49-629	₹6,932 Volume Pricing	20+ In Stock
-	25.00 x 25.00	4.00	YAG-BBAR (500-1100nm)	#13-320	₹7,152 Volume Pricing	6 In Stock
-	25.00 x 25.00	4.00	NIR I (600-1050nm)	#83-473	₹6,932 Volume Pricing	Contact Us
-	25.00 x 25.00	4.00	NIR II (750-1550nm)	#25-807	₹6,932 Volume Pricing	6 In Stock
-	25.00 x 35.00	3.00	Uncoated	#29-301	₹5,355 Volume Pricing	17 In Stock
-	25.20 x 35.60	1.00	Uncoated	#29-302	₹5,355 Volume Pricing	20+ In Stock
25.40	-	1.00	Uncoated	#20-512	₹5,135 Volume Pricing	Contact Us
25.40	-	1.00	MgF ₂ (400-700nm)	#23-363	₹6,051 Volume Pricing	3 In Stock
25.40	-	1.00	VIS-EXT (350-700nm)	#23-451	₹7,152 Volume Pricing	Contact Us
25.40	-	1.00	VIS-NIR (400-1000nm)	#23-407	₹7,152 Volume Pricing	Contact Us
25.40	-	1.00	VIS 0° (425-675nm)	#23-385	₹6,932 Volume Pricing	1 In Stock
25.40	-	1.00	YAG-BBAR (500-1100nm)	#23-473	₹7,152 Volume Pricing	9 In Stock
25.40	-	1.00	NIR I (600-1050nm)	#23-429	₹6,932 Volume Pricing	5 In Stock
25.40	-	1.00	NIR II (750-1550nm)	#25-808	₹6,932 Volume Pricing	1 In Stock
25.40	-	2.00	Uncoated	#15-424	₹5,135 Volume Pricing	20+ In Stock

25.40	-	2.00	MgF ₂ (400-700nm)	#15-428	₹6,051 Volume Pricing	1 In Stock
25.40	-	2.00	VIS-EXT (350-700nm)	#15-788	₹7,152 Volume Pricing	Contact Us
25.40	-	2.00	VIS-NIR (400-1000nm)	#15-436	₹7,152 Volume Pricing	6 In Stock
25.40	-	2.00	VIS 0° (425-675nm)	#15-432	₹6,932 Volume Pricing	Contact Us
25.40	-	2.00	YAG-BBAR (500-1100nm)	#15-792	₹7,152 Volume Pricing	8 In Stock
25.40	-	2.00	NIR I (600-1050nm)	#15-440	₹6,932 Volume Pricing	9 In Stock
25.40	-	2.00	NIR II (750-1550nm)	#25-809	₹6,932 Volume Pricing	Contact Us
25.40	-	4.00	Uncoated	#15-425	₹5,135 Volume Pricing	20+ In Stock
25.40	-	4.00	MgF ₂ (400-700nm)	#15-429	₹6,051 Volume Pricing	3 In Stock
25.40	-	4.00	VIS-EXT (350-700nm)	#15-789	₹7,152 Volume Pricing	5 In Stock
25.40	-	4.00	VIS-NIR (400-1000nm)	#15-437	₹7,152 Volume Pricing	6 In Stock
25.40	-	4.00	VIS 0° (425-675nm)	#15-433	₹6,932 Volume Pricing	3 In Stock
25.40	-	4.00	YAG-BBAR (500-1100nm)	#15-793	₹7,152 Volume Pricing	3 In Stock
25.40	-	4.00	NIR I (600-1050nm)	#15-441	₹6,932 Volume Pricing	4 In Stock
25.40	-	4.00	NIR II (750-1550nm)	#25-810	₹6,932 Volume Pricing	5 In Stock
30.00	-	1.00	Uncoated	#20-528	₹5,355 Volume Pricing	20+ In Stock
30.00	-	1.00	MgF ₂ (400-700nm)	#23-364	₹6,785 Volume Pricing	1 In Stock

30.00	-	1.00	VIS-EXT (350-700nm)	#23-452	₹8,362 Volume Pricing	4 In Stock
30.00	-	1.00	VIS-NIR (400-1000nm)	#23-408	₹8,362 Volume Pricing	20+ In Stock
30.00	-	1.00	VIS 0° (425-675nm)	#23-386	₹8,069 Volume Pricing	3 In Stock
30.00	-	1.00	YAG-BBAR (500-1100nm)	#23-474	₹8,362 Volume Pricing	4 In Stock
30.00	-	1.00	NIR I (600-1050nm)	#23-430	₹8,069 Volume Pricing	9 In Stock
30.00	-	1.00	NIR II (750-1550nm)	#25-811	₹8,069 Volume Pricing	1 In Stock
30.00	-	2.00	Uncoated	#20-530	₹5,355 Volume Pricing	20+ In Stock
30.00	-	2.00	MgF ₂ (400-700nm)	#23-365	₹6,785 Volume Pricing	4 In Stock
30.00	-	2.00	VIS-EXT (350-700nm)	#23-453	₹8,362 Volume Pricing	1 In Stock
30.00	-	2.00	VIS-NIR (400-1000nm)	#23-409	₹8,362 Volume Pricing	10 In Stock
30.00	-	2.00	VIS 0° (425-675nm)	#23-387	₹8,069 Volume Pricing	8 In Stock
30.00	-	2.00	YAG-BBAR (500-1100nm)	#23-475	₹8,362 Volume Pricing	2 In Stock
30.00	-	2.00	NIR I (600-1050nm)	#23-431	₹8,069 Volume Pricing	5 In Stock
30.00	-	2.00	NIR II (750-1550nm)	#25-812	₹8,069 Volume Pricing	7 In Stock
30.00	-	4.00	Uncoated	#45-579	₹5,355 Volume Pricing	20+ In Stock
30.00	-	4.00	MgF ₂ (400-700nm)	#45-580	₹6,785 Volume Pricing	14 In Stock
30.00	-	4.00	VIS-EXT (350-700nm)	#13-299	₹8,362 Volume Pricing	13 In Stock

30.00	-	4.00	VIS-NIR (400-1000nm)	#48-445	₹8,362 Volume Pricing	20+ In Stock
30.00	-	4.00	VIS 0° (425-675nm)	#47-521	₹8,069 Volume Pricing	20+ In Stock
30.00	-	4.00	YAG-BBAR (500-1100nm)	#13-321	₹8,362 Volume Pricing	20+ In Stock
30.00	-	4.00	NIR I (600-1050nm)	#83-474	₹8,069 Volume Pricing	13 In Stock
30.00	-	4.00	NIR II (750-1550nm)	#25-813	₹8,069 Volume Pricing	5 In Stock
-	35.00 x 35.00	1.00	Uncoated	#20-584	₹5,978 Volume Pricing	8 In Stock
-	35.00 x 35.00	1.00	MgF ₂ (400-700nm)	#23-372	₹7,335 Volume Pricing	Contact Us
-	35.00 x 35.00	1.00	VIS-EXT (350-700nm)	#23-460	₹8,729 Volume Pricing	5 In Stock
-	35.00 x 35.00	1.00	VIS-NIR (400-1000nm)	#23-416	₹8,729 Volume Pricing	1 In Stock
-	35.00 x 35.00	1.00	VIS 0° (425-675nm)	#23-394	₹8,582 Volume Pricing	9 In Stock
-	35.00 x 35.00	1.00	YAG-BBAR (500-1100nm)	#23-482	₹8,729 Volume Pricing	3 In Stock
-	35.00 x 35.00	1.00	NIR I (600-1050nm)	#23-438	₹8,582 Volume Pricing	1 In Stock
-	35.00 x 35.00	1.00	NIR II (750-1550nm)	#25-814	₹8,582 Volume Pricing	5 In Stock
-	35.00 x 35.00	2.00	Uncoated	#20-586	₹5,978 Volume Pricing	7 In Stock
-	35.00 x 35.00	2.00	MgF ₂ (400-700nm)	#23-373	₹7,335 Volume Pricing	3 In Stock
-	35.00 x 35.00	2.00	VIS-EXT (350-700nm)	#23-461	₹8,729 Volume Pricing	11 In Stock
-	35.00 x 35.00	2.00	VIS-NIR (400-1000nm)	#23-417	₹8,729 Volume Pricing	Contact Us

-	35.00 x 35.00	2.00	VIS 0° (425-675nm)	#23-395	₹8,582 Volume Pricing	2 In Stock
-	35.00 x 35.00	2.00	YAG-BBAR (500-1100nm)	#23-483	₹8,729 Volume Pricing	5 In Stock
-	35.00 x 35.00	2.00	NIR I (600-1050nm)	#23-439	₹8,582 Volume Pricing	2 In Stock
-	35.00 x 35.00	2.00	NIR II (750-1550nm)	#25-815	₹8,582 Volume Pricing	3 In Stock
-	35.00 x 35.00	3.00	Uncoated	#49-470	₹5,978 Volume Pricing	20+ In Stock
-	35.00 x 35.00	3.00	MgF ₂ (400-700nm)	#49-626	₹7,335 Volume Pricing	20+ In Stock
-	35.00 x 35.00	3.00	VIS-EXT (350-700nm)	#13-300	₹8,729 Volume Pricing	Contact Us
-	35.00 x 35.00	3.00	VIS-NIR (400-1000nm)	#49-634	₹8,729 Volume Pricing	14 In Stock
-	35.00 x 35.00	3.00	VIS 0° (425-675nm)	#49-630	₹8,582 Volume Pricing	20+ In Stock
-	35.00 x 35.00	3.00	YAG-BBAR (500-1100nm)	#13-322	₹8,729 Volume Pricing	6 In Stock
-	35.00 x 35.00	3.00	NIR I (600-1050nm)	#83-475	₹8,582 Volume Pricing	20+ In Stock
-	35.00 x 35.00	3.00	NIR II (750-1550nm)	#25-816	₹8,582 Volume Pricing	4 In Stock
40.00	-	1.00	Uncoated	#20-532	₹6,602 Volume Pricing	20+ In Stock
40.00	-	1.00	MgF ₂ (400-700nm)	#23-366	₹7,848 Volume Pricing	5 In Stock
40.00	-	1.00	VIS-EXT (350-700nm)	#23-454	₹9,242 Volume Pricing	6 In Stock
40.00	-	1.00	VIS-NIR (400-1000nm)	#23-410	₹9,242 Volume Pricing	4 In Stock
40.00	-	1.00	VIS 0° (425-675nm)	#23-388	₹9,095 Volume Pricing	8 In Stock

40.00	-	1.00	YAG-BBAR (500-1100nm)	#23-476	₹9,242 Volume Pricing	3 In Stock
40.00	-	1.00	NIR I (600-1050nm)	#23-432	₹9,095 Volume Pricing	1 In Stock
40.00	-	1.00	NIR II (750-1550nm)	#25-817	₹9,095 Volume Pricing	4 In Stock
40.00	-	2.00	Uncoated	#20-536	₹6,602 Volume Pricing	20+ In Stock
40.00	-	2.00	MgF ₂ (400-700nm)	#23-367	₹7,848 Volume Pricing	5 In Stock
40.00	-	2.00	VIS-EXT (350-700nm)	#23-455	₹9,242 Volume Pricing	1 In Stock
40.00	-	2.00	VIS-NIR (400-1000nm)	#23-411	₹9,242 Volume Pricing	Contact Us
40.00	-	2.00	VIS 0° (425-675nm)	#23-389	₹9,095 Volume Pricing	1 In Stock
40.00	-	2.00	YAG-BBAR (500-1100nm)	#23-477	₹9,242 Volume Pricing	Contact Us
40.00	-	2.00	NIR I (600-1050nm)	#23-433	₹9,095 Volume Pricing	1 In Stock
40.00	-	2.00	NIR II (750-1550nm)	#25-818	₹9,095 Volume Pricing	4 In Stock
40.00	-	4.00	Uncoated	#45-581	₹6,602 Volume Pricing	20+ In Stock
40.00	-	4.00	MgF ₂ (400-700nm)	#45-582	₹7,848 Volume Pricing	20+ In Stock
40.00	-	4.00	VIS-EXT (350-700nm)	#13-301	₹9,242 Volume Pricing	1 In Stock
40.00	-	4.00	VIS-NIR (400-1000nm)	#48-446	₹9,242 Volume Pricing	20+ In Stock
40.00	-	4.00	VIS 0° (425-675nm)	#47-522	₹9,095 Volume Pricing	20+ In Stock
40.00	-	4.00	YAG-BBAR (500-1100nm)	#13-323	₹9,242 Volume Pricing	13 In Stock

40.00	-	4.00	NIR I (600-1050nm)	#83-476	₹9,095 Volume Pricing	7 In Stock
40.00	-	4.00	NIR II (750-1550nm)	#25-819	₹9,095 Volume Pricing	5 In Stock
50.00	-	1.00	Uncoated	#34-427	₹6,968 Volume Pricing	10 In Stock
50.00	-	1.00	MgF ₂ (400-700nm)	#37-007	₹8,435 Volume Pricing	Contact Us
50.00	-	1.00	VIS-EXT (350-700nm)	#13-302	₹9,609 Volume Pricing	3 In Stock
50.00	-	1.00	VIS-NIR (400-1000nm)	#37-010	₹9,609 Volume Pricing	20+ In Stock
50.00	-	1.00	VIS 0° (425-675nm)	#37-009	₹9,462 Volume Pricing	4 In Stock
50.00	-	1.00	YAG-BBAR (500-1100nm)	#13-324	₹9,609 Volume Pricing	5 In Stock
50.00	-	1.00	NIR I (600-1050nm)	#37-008	₹9,462 Volume Pricing	3 In Stock
50.00	-	1.00	NIR II (750-1550nm)	#25-820	₹9,462 Volume Pricing	2 In Stock
50.00	-	3.00	BBAR (1650-3000nm)	#70-283	₹9,829 Volume Pricing	4 In Stock
-	50.00 x 50.00	1.00	Uncoated	#20-592	₹6,968 Volume Pricing	20+ In Stock
-	50.00 x 50.00	1.00	MgF ₂ (400-700nm)	#23-374	₹8,435 Volume Pricing	5 In Stock
-	50.00 x 50.00	1.00	VIS-EXT (350-700nm)	#23-462	₹9,609 Volume Pricing	7 In Stock
-	50.00 x 50.00	1.00	VIS-NIR (400-1000nm)	#23-418	₹9,609 Volume Pricing	2 In Stock
-	50.00 x 50.00	1.00	VIS 0° (425-675nm)	#23-396	₹9,462 Volume Pricing	5 In Stock
-	50.00 x 50.00	1.00	YAG-BBAR (500-1100nm)	#23-484	₹9,609 Volume Pricing	4 In Stock

-	50.00 x 50.00	1.00	NIR I (600-1050nm)	#23-440	₹9,462 Volume Pricing	3 In Stock
-	50.00 x 50.00	1.00	NIR II (750-1550nm)	#25-821	₹9,462 Volume Pricing	3 In Stock
50.00	-	2.00	Uncoated	#34-428	₹6,968 Volume Pricing	20+ In Stock
50.00	-	2.00	MgF ₂ (400-700nm)	#37-011	₹8,435 Volume Pricing	2 In Stock
50.00	-	2.00	VIS-EXT (350-700nm)	#13-303	₹9,609 Volume Pricing	2 In Stock
50.00	-	2.00	VIS-NIR (400-1000nm)	#37-014	₹9,609 Volume Pricing	20+ In Stock
50.00	-	2.00	VIS 0° (425-675nm)	#37-013	₹9,462 Volume Pricing	6 In Stock
50.00	-	2.00	YAG-BBAR (500-1100nm)	#13-325	₹9,609 Volume Pricing	4 In Stock
50.00	-	2.00	NIR I (600-1050nm)	#37-012	₹9,462 Volume Pricing	1 In Stock
50.00	-	2.00	NIR II (750-1550nm)	#25-822	₹9,462 Volume Pricing	3 In Stock
-	50.00 x 50.00	2.00	Uncoated	#20-596	₹6,968 Volume Pricing	20+ In Stock
-	50.00 x 50.00	2.00	MgF ₂ (400-700nm)	#23-375	₹8,435 Volume Pricing	2 In Stock
-	50.00 x 50.00	2.00	VIS-EXT (350-700nm)	#23-463	₹9,609 Volume Pricing	20+ In Stock
-	50.00 x 50.00	2.00	VIS-NIR (400-1000nm)	#23-419	₹9,609 Volume Pricing	4 In Stock
-	50.00 x 50.00	2.00	VIS 0° (425-675nm)	#23-397	₹9,462 Volume Pricing	3 In Stock
-	50.00 x 50.00	2.00	YAG-BBAR (500-1100nm)	#23-485	₹9,609 Volume Pricing	5 In Stock
-	50.00 x 50.00	2.00	NIR I (600-1050nm)	#23-441	₹9,462 Volume Pricing	5 In Stock

-	50.00 x 50.00	2.00	NIR II (750-1550nm)	#25-823	₹9,462 Volume Pricing	11 In Stock
50.00	-	3.00	Uncoated	#34-429	₹6,968 Volume Pricing	20+ In Stock
50.00	-	3.00	MgF ₂ (400-700nm)	#37-015	₹8,435 Volume Pricing	2 In Stock
50.00	-	3.00	VIS-EXT (350-700nm)	#13-304	₹9,609 Volume Pricing	9 In Stock
50.00	-	3.00	VIS-NIR (400-1000nm)	#37-018	₹9,609 Volume Pricing	13 In Stock
50.00	-	3.00	VIS 0° (425-675nm)	#37-017	₹9,462 Volume Pricing	10 In Stock
50.00	-	3.00	YAG-BBAR (500-1100nm)	#13-326	₹9,609 Volume Pricing	1 In Stock
50.00	-	3.00	NIR I (600-1050nm)	#37-016	₹9,462 Volume Pricing	9 In Stock
50.00	-	3.00	NIR II (750-1550nm)	#25-824	₹9,462 Volume Pricing	6 In Stock
50.00	-	4.00	Uncoated	#45-583	₹6,968 Volume Pricing	20+ In Stock
50.00	-	4.00	MgF ₂ (400-700nm)	#45-584	₹8,435 Volume Pricing	20+ In Stock
50.00	-	4.00	VIS-EXT (350-700nm)	#13-305	₹9,609 Volume Pricing	Contact Us
50.00	-	4.00	VIS-NIR (400-1000nm)	#48-447	₹9,609 Volume Pricing	20+ In Stock
50.00	-	4.00	VIS 0° (425-675nm)	#47-523	₹9,462 Volume Pricing	20+ In Stock
50.00	-	4.00	YAG-BBAR (500-1100nm)	#13-327	₹9,609 Volume Pricing	6 In Stock
50.00	-	4.00	NIR I (600-1050nm)	#83-477	₹9,462 Volume Pricing	8 In Stock
50.00	-	4.00	NIR II (750-1550nm)	#25-825	₹9,462 Volume Pricing	20+ In Stock

-	50.00 x 50.00	4.00	Uncoated	#47-944	₹6,968 Volume Pricing	20+ In Stock
-	50.00 x 50.00	4.00	MgF ₂ (400-700nm)	#47-945	₹8,435 Volume Pricing	1 In Stock
-	50.00 x 50.00	4.00	VIS-EXT (350-700nm)	#13-307	₹9,609 Volume Pricing	8 In Stock
-	50.00 x 50.00	4.00	VIS-NIR (400-1000nm)	#47-947	₹9,609 Volume Pricing	16 In Stock
-	50.00 x 50.00	4.00	VIS 0° (425-675nm)	#47-946	₹9,462 Volume Pricing	8 In Stock
-	50.00 x 50.00	4.00	YAG-BBAR (500-1100nm)	#13-329	₹9,609 Volume Pricing	11 In Stock
-	50.00 x 50.00	4.00	NIR I (600-1050nm)	#83-478	₹9,462 Volume Pricing	14 In Stock
-	50.00 x 50.00	4.00	NIR II (750-1550nm)	#25-826	₹9,462 Volume Pricing	2 In Stock
50.00	-	6.00	Uncoated	#34-430	₹6,968 Volume Pricing	20+ In Stock
50.00	-	6.00	MgF ₂ (400-700nm)	#37-019	₹8,435 Volume Pricing	6 In Stock
50.00	-	6.00	VIS-EXT (350-700nm)	#13-306	₹9,609 Volume Pricing	5 In Stock
50.00	-	6.00	VIS-NIR (400-1000nm)	#37-022	₹9,609 Volume Pricing	8 In Stock
50.00	-	6.00	VIS 0° (425-675nm)	#37-021	₹9,462 Volume Pricing	2 In Stock
50.00	-	6.00	YAG-BBAR (500-1100nm)	#13-328	₹9,609 Volume Pricing	11 In Stock
50.00	-	6.00	NIR I (600-1050nm)	#37-020	₹9,462 Volume Pricing	5 In Stock
50.00	-	6.00	NIR II (750-1550nm)	#25-827	₹9,462 Volume Pricing	4 In Stock
50.80	-	4.00	Uncoated	#15-426	₹6,968 Volume Pricing	14 In Stock

50.80	-	4.00	MgF ₂ (400-700nm)	#15-430	₹8,435 Volume Pricing	1 In Stock
50.80	-	4.00	VIS-EXT (350-700nm)	#15-790	₹9,609 Volume Pricing	6 In Stock
50.80	-	4.00	VIS-NIR (400-1000nm)	#15-438	₹9,609 Volume Pricing	5 In Stock
50.80	-	4.00	VIS 0° (425-675nm)	#15-434	₹9,462 Volume Pricing	16 In Stock
50.80	-	4.00	YAG-BBAR (500-1100nm)	#15-794	₹9,609 Volume Pricing	3 In Stock
50.80	-	4.00	NIR I (600-1050nm)	#15-442	₹9,462 Volume Pricing	6 In Stock
50.80	-	4.00	NIR II (750-1550nm)	#25-828	₹9,462 Volume Pricing	2 In Stock
75.00	-	4.00	BBAR (1650-3000nm)	#70-284	₹17,384 Volume Pricing	4 In Stock
75.00	-	2.00	Uncoated	#20-538	₹10,782 Volume Pricing	20+ In Stock
75.00	-	2.00	MgF ₂ (400-700nm)	#23-368	₹12,543 Volume Pricing	20+ In Stock
75.00	-	2.00	VIS-EXT (350-700nm)	#23-456	₹15,404 Volume Pricing	7 In Stock
75.00	-	2.00	VIS-NIR (400-1000nm)	#23-412	₹15,404 Volume Pricing	Contact Us
75.00	-	2.00	VIS 0° (425-675nm)	#23-390	₹15,037 Volume Pricing	Contact Us
75.00	-	2.00	YAG-BBAR (500-1100nm)	#23-478	₹15,404 Volume Pricing	15 In Stock
75.00	-	2.00	NIR I (600-1050nm)	#23-434	₹15,037 Volume Pricing	3 In Stock
75.00	-	2.00	NIR II (750-1550nm)	#25-829	₹15,037 Volume Pricing	20+ In Stock
-	75.00 x 75.00	2.00	Uncoated	#20-598	₹10,782 Volume Pricing	20+ In Stock

-	75.00 x 75.00	2.00	MgF ₂ (400-700nm)	#23-376	₹12,543 Volume Pricing	5 In Stock
-	75.00 x 75.00	2.00	VIS-EXT (350-700nm)	#23-464	₹15,404 Volume Pricing	5 In Stock
-	75.00 x 75.00	2.00	VIS-NIR (400-1000nm)	#23-420	₹15,404 Volume Pricing	20+ In Stock
-	75.00 x 75.00	2.00	VIS 0° (425-675nm)	#23-398	₹15,037 Volume Pricing	12 In Stock
-	75.00 x 75.00	2.00	YAG-BBAR (500-1100nm)	#23-486	₹15,404 Volume Pricing	15 In Stock
-	75.00 x 75.00	2.00	NIR I (600-1050nm)	#23-442	₹15,037 Volume Pricing	2 In Stock
-	75.00 x 75.00	2.00	NIR II (750-1550nm)	#25-830	₹15,037 Volume Pricing	7 In Stock
75.00	-	4.00	Uncoated	#62-606	₹10,782 Volume Pricing	20+ In Stock
75.00	-	4.00	MgF ₂ (400-700nm)	#62-608	₹12,543 Volume Pricing	20+ In Stock
75.00	-	4.00	VIS-EXT (350-700nm)	#15-795	₹15,404 Volume Pricing	10 In Stock
75.00	-	4.00	VIS-NIR (400-1000nm)	#84-359	₹15,404 Volume Pricing	20+ In Stock
75.00	-	4.00	VIS 0° (425-675nm)	#37-070	₹15,037 Volume Pricing	5 In Stock
75.00	-	4.00	YAG-BBAR (500-1100nm)	#15-797	₹15,404 Volume Pricing	Contact Us
75.00	-	4.00	NIR I (600-1050nm)	#37-073	₹15,037 Volume Pricing	3 In Stock
75.00	-	4.00	NIR II (750-1550nm)	#25-831	₹15,037 Volume Pricing	20+ In Stock
-	75.00 x 75.00	4.00	Uncoated	#62-607	₹10,782 Volume Pricing	14 In Stock
-	75.00 x 75.00	4.00	MgF ₂ (400-700nm)	#62-609	₹12,543 Volume Pricing	20+ In Stock

-	75.00 x 75.00	4.00	VIS-EXT (350-700nm)	#15-796	₹15,404 Volume Pricing	20+ In Stock
-	75.00 x 75.00	4.00	VIS-NIR (400-1000nm)	#37-072	₹15,404 Volume Pricing	9 In Stock
-	75.00 x 75.00	4.00	VIS 0° (425-675nm)	#37-071	₹15,037 Volume Pricing	Contact Us
-	75.00 x 75.00	4.00	YAG-BBAR (500-1100nm)	#15-798	₹15,404 Volume Pricing	5 In Stock
-	75.00 x 75.00	4.00	NIR I (600-1050nm)	#37-074	₹15,037 Volume Pricing	1 In Stock
-	75.00 x 75.00	4.00	NIR II (750-1550nm)	#25-832	₹15,037 Volume Pricing	5 In Stock
100.00	-	6.00	Uncoated	#11-856	₹15,844 Volume Pricing	20+ In Stock
-	100 x 100	6.00	Uncoated	#70-699	₹15,844 Volume Pricing	Contact Us
100.00	-	6.00	MgF ₂ (400-700nm)	#11-859	₹28,533 Volume Pricing	5 In Stock
100.00	-	6.00	VIS-NIR (400-1000nm)	#26-675	₹38,509 Volume Pricing	Contact Us
100.00	-	6.00	VIS 0° (425-675nm)	#17-298	₹37,042 Volume Pricing	7 In Stock
100.00	-	6.00	VIS-EXT (350-700nm)	#29-590	₹39,242 Volume Pricing	3 In Stock
100.00	-	6.00	NIR I (600-1050nm)	#17-295	₹37,042 Volume Pricing	3 In Stock
100.00	-	6.00	NIR II (750-1550nm)	#29-589	₹39,242 Volume Pricing	3 In Stock
100.00	-	6.00	YAG-BBAR (500-1100nm)	#29-591	₹39,242 Volume Pricing	1 In Stock
125.00	-	8.00	Uncoated	#11-857	₹23,545 Volume Pricing	20+ In Stock
125.00	-	8.00	MgF ₂ (400-700nm)	#11-860	₹36,235 Volume Pricing	6 In Stock

125.00	-	8.00	VIS-NIR (400-1000nm)	#26-676	₹46,211 Volume Pricing	3 In Stock
125.00	-	8.00	VIS 0° (425-675nm)	#17-299	₹44,744 Volume Pricing	13 In Stock
125.00	-	8.00	VIS-EXT (350-700nm)	#29-593	₹47,311 Volume Pricing	Contact Us
125.00	-	8.00	NIR I (600-1050nm)	#17-296	₹44,744 Volume Pricing	2 In Stock
125.00	-	8.00	NIR II (750-1550nm)	#29-592	₹45,844 Volume Pricing	3 In Stock
125.00	-	8.00	YAG-BBAR (500-1100nm)	#29-594	₹47,311 Volume Pricing	1 In Stock
150.00	-	10.00	Uncoated	#11-858	₹33,521 Volume Pricing	Contact Us
150.00	-	10.00	MgF ₂ (400-700nm)	#11-861	₹46,211 Volume Pricing	3 In Stock
150.00	-	10.00	VIS-NIR (400-1000nm)	#26-677	₹56,480 Volume Pricing	Contact Us
150.00	-	10.00	VIS 0° (425-675nm)	#17-300	₹55,013 Volume Pricing	3 In Stock
150.00	-	10.00	VIS-EXT (350-700nm)	#29-596	₹57,580 Volume Pricing	1 In Stock
150.00	-	10.00	NIR I (600-1050nm)	#17-297	₹55,013 Volume Pricing	8 In Stock
150.00	-	10.00	NIR II (750-1550nm)	#29-595	₹55,746 Volume Pricing	Contact Us
150.00	-	10.00	YAG-BBAR (500-1100nm)	#29-597	₹57,580 Volume Pricing	2 In Stock
200.00	-	10.00	Uncoated	#26-475	₹48,411 Volume Pricing	8 In Stock
200.00	-	10.00	MgF ₂ (400-700nm)	#29-598	₹78,485 Volume Pricing	Contact Us
200.00	-	10.00	VIS 0° (425-675nm)	#26-679	₹73,350 Volume Pricing	1 In Stock

200.00	-	10.00	VIS-EXT (350-700nm)	#29-601	₹90,587 Volume Pricing	Contact Us
200.00	-	10.00	VIS-NIR (400-1000nm)	#29-602	₹90,587 Volume Pricing	Contact Us
200.00	-	10.00	NIR I (600-1050nm)	#29-599	₹86,553 Volume Pricing	3 In Stock
200.00	-	10.00	NIR II (750-1550nm)	#29-600	₹86,553 Volume Pricing	3 In Stock
200.00	-	10.00	YAG-BBAR (500-1100nm)	#29-603	₹90,587 Volume Pricing	2 In Stock
250.00	-	12.50	Uncoated	#29-936	₹1,07,458 Volume Pricing	5 In Stock
300.00	-	15.00	Uncoated	#29-937	₹1,27,262 Volume Pricing	4 In Stock



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038

Phone: 1-800-363-1992 :

www.edmundoptics.com