

[All Products](#) / [Optics](#) / [Optical Mirrors](#) / [Flat Mirrors](#) / [Precision Polished Metal Coatings](#)

TECHSPEC®

λ/4 First Surface Mirrors



- Available in a Wide Range of Sizes and Shapes
- Precision Metallic Mirror Coatings
- [Contact Us](#) for Custom Sizes

Common Specifications

Physical & Mechanical Properties

Bevel:	Protective as needed	Edges:	Fine Ground
--------	----------------------	--------	-------------

Optical Properties

Surface Flatness (P-V):	λ/4	Substrate:	BOROFLOAT®
Surface Quality:	60-40	Coating Type:	Metal

Technical Information

Products

Dia. (mm)	Surface Flatness (P-V)	Dimensions (mm)	Coating Specification	Coating	Thickness (mm)	Stock Number	Price	Buy
5.00	$\lambda/4$	-	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	2.00	#48-404	₹4,087 Volume Pricing	20+ In Stock
5.00	$\lambda/4$	-	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	2.00	#48-407	₹4,087 Volume Pricing	Contact Us
5.00	$\lambda/4$	-	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	2.00	#48-410	₹5,333 Volume Pricing	20+ In Stock
5.00	$\lambda/4$	-	$R_{avg} > 98\% @ 450 - 800nm$ $R_{avg} > 98.5\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	2.00	#49-186	₹4,905 Volume Pricing	1 In Stock
-	$\lambda/4$	5.0 x 5.0	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	2.00	#48-405	₹4,087 Volume Pricing	20+ In Stock
-	$\lambda/4$	5.0 x 5.0	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	2.00	#48-408	₹4,087 Volume Pricing	8 In Stock
-	$\lambda/4$	5.0 x 5.0	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	2.00	#48-411	₹5,333 Volume Pricing	8 In Stock
-	$\lambda/4$	5.0 x 5.0	$R_{avg} > 98\% @ 450 - 800nm$ $R_{avg} > 98.5\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	2.00	#49-187	₹4,905 Volume Pricing	1 In Stock
10.00	$\lambda/4$	-	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	2.00	#45-598	₹4,087 Volume Pricing	20+ In Stock
10.00	$\lambda/4$	-	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	2.00	#45-599	₹4,087 Volume Pricing	14 In Stock

10.00	$\lambda/4$	-	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	2.00	#45-600	₹5,333 Volume Pricing	Contact Us
10.00	$\lambda/4$	-	$R_{avg} > 98\% @ 450 - 800nm$ $R_{avg} > 98.5\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	2.00	#49-188	₹4,905 Volume Pricing	20+ In Stock
-	$\lambda/4$	10.0 x 10.0	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	2.00	#45-722	₹4,087 Volume Pricing	6 In Stock
-	$\lambda/4$	10.0 x 10.0	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	2.00	#45-723	₹4,087 Volume Pricing	20+ In Stock
-	$\lambda/4$	10.0 x 10.0	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	2.00	#45-724	₹5,333 Volume Pricing	20+ In Stock
-	$\lambda/4$	10.0 x 10.0	$R_{avg} > 98\% @ 450 - 800nm$ $R_{avg} > 98.5\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	2.00	#49-189	₹4,905 Volume Pricing	Contact Us
12.50	$\lambda/4$	-	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	2.00	#45-601	₹4,087 Volume Pricing	20+ In Stock
12.50	$\lambda/4$	-	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	2.00	#45-602	₹4,087 Volume Pricing	20+ In Stock
12.50	$\lambda/4$	-	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	2.00	#45-603	₹5,333 Volume Pricing	5 In Stock
12.50	$\lambda/4$	-	$R_{avg} > 98\% @ 450 - 800nm$ $R_{avg} > 98.5\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	2.00	#49-190	₹4,905 Volume Pricing	Contact Us
-	$\lambda/4$	12.5 x 12.5	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	2.00	#48-406	₹4,087 Volume Pricing	Contact Us

-	$\lambda/4$	12.5 x 12.5	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	2.00	#48-409	₹4,087 Volume Pricing	5 In Stock
-	$\lambda/4$	12.5 x 12.5	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	2.00	#48-412	₹5,333 Volume Pricing	5 In Stock
-	$\lambda/4$	12.5 x 12.5	$R_{avg} > 98\% @ 450 - 800nm$ $R_{avg} > 98.5\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	2.00	#49-191	₹4,905 Volume Pricing	5 In Stock
-	$\lambda/4$	12.5 x 17.5	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	3.00	#25-746	₹4,282 Volume Pricing	Contact Us
-	$\lambda/4$	12.5 x 17.5	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	3.00	#25-747	₹4,282 Volume Pricing	4 In Stock
-	$\lambda/4$	12.5 x 17.5	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	3.00	#25-748	₹5,722 Volume Pricing	Contact Us
-	$\lambda/4$	12.5 x 17.5	$R_{avg} > 98\% @ 450 - 2000nm$ $R_{avg} > 98\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	3.00	#25-749	₹5,333 Volume Pricing	4 In Stock
12.70	$\lambda/4$	-	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	2.00	#25-730	₹4,087 Volume Pricing	Contact Us
12.70	$\lambda/4$	-	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	2.00	#25-731	₹4,087 Volume Pricing	6 In Stock
12.70	$\lambda/4$	-	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	2.00	#25-732	₹5,333 Volume Pricing	1 In Stock
12.70	$\lambda/4$	-	$R_{avg} > 98\% @ 450 - 2000nm$ $R_{avg} > 98\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	2.00	#25-733	₹4,905 Volume Pricing	Contact Us

15.00	$\lambda/4$	-	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	2.00	#63-162	₹4,282 Volume Pricing	20+ In Stock
15.00	$\lambda/4$	-	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	2.00	#63-168	₹4,282 Volume Pricing	Contact Us
15.00	$\lambda/4$	-	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	2.00	#63-174	₹5,722 Volume Pricing	20+ In Stock
15.00	$\lambda/4$	-	$R_{avg} > 98\% @ 450 - 2000nm$ $R_{avg} > 98\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	2.00	#88-535	₹5,333 Volume Pricing	5 In Stock
-	$\lambda/4$	15.0 x 15.0	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	2.00	#45-725	₹4,282 Volume Pricing	20+ In Stock
-	$\lambda/4$	15.0 x 15.0	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	2.00	#45-726	₹4,282 Volume Pricing	Contact Us
-	$\lambda/4$	15.0 x 15.0	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	2.00	#45-727	₹5,722 Volume Pricing	20+ In Stock
-	$\lambda/4$	15.0 x 15.0	$R_{avg} > 98\% @ 450 - 800nm$ $R_{avg} > 98.5\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	2.00	#49-192	₹5,333 Volume Pricing	20+ In Stock
-	$\lambda/4$	16.0 x 23.0	$R_{avg} > 85\% @ 400 - 700nm$ $R_{avg} > 90\% @ 400 - 2000nm$	Protected Aluminum (400-2000nm)	5.00	#30-875	₹3,698 Volume Pricing	20+ In Stock
-	$\lambda/4$	16.0 x 23.0	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	5.00	#43-506	₹4,282 Volume Pricing	7 In Stock
-	$\lambda/4$	16.0 x 23.0	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	5.00	#46-716	₹4,282 Volume Pricing	11 In Stock

-	$\lambda/4$	16.0 x 23.0	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	5.00	#32-432	₹5,722 Volume Pricing	16 In Stock
-	$\lambda/4$	16.0 x 23.0	$R_{avg} > 98\% @ 450 - 2000nm$ $R_{avg} > 98\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	5.00	#46-721	₹5,333 Volume Pricing	20+ In Stock
20.00	$\lambda/4$	-	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	3.00	#63-163	₹4,515 Volume Pricing	20+ In Stock
20.00	$\lambda/4$	-	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	3.00	#63-169	₹4,515 Volume Pricing	Contact Us
20.00	$\lambda/4$	-	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	3.00	#63-175	₹5,917 Volume Pricing	2 In Stock
20.00	$\lambda/4$	-	$R_{avg} > 98\% @ 450 - 2000nm$ $R_{avg} > 98\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	3.00	#88-536	₹5,527 Volume Pricing	16 In Stock
-	$\lambda/4$	20.0 x 20.0	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	2.00	#45-728	₹4,515 Volume Pricing	Contact Us
-	$\lambda/4$	20.0 x 20.0	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	2.00	#45-729	₹4,515 Volume Pricing	7 In Stock
-	$\lambda/4$	20.0 x 20.0	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	2.00	#45-730	₹5,917 Volume Pricing	20+ In Stock
-	$\lambda/4$	20.0 x 20.0	$R_{avg} > 98\% @ 450 - 800nm$ $R_{avg} > 98.5\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	2.00	#49-193	₹5,527 Volume Pricing	17 In Stock
-	$\lambda/4$	21.0 x 30.0	$R_{avg} > 85\% @ 400 - 700nm$ $R_{avg} > 90\% @ 400 - 2000nm$	Protected Aluminum (400-2000nm)	5.00	#32-454	₹3,893 Volume Pricing	Contact Us

-	$\lambda/4$	21.0 x 30.0	$R_{avg} > 95\% @$ 450 - 650nm	Enhanced Aluminum (450- 650nm)	5.00	#43-507	₹4,515 Volume Pricing	20+ In Stock
-	$\lambda/4$	21.0 x 30.0	$R_{avg} > 89\% @$ 250 - 450nm $R_{avg} > 85\% @$ 250 - 700nm	Enhanced Aluminum (250- 700nm)	5.00	#46-717	₹4,515 Volume Pricing	1 In Stock
-	$\lambda/4$	21.0 x 30.0	$R_{avg} > 96\% @$ 700 - 2000nm $R_{avg} > 96\% @$ 2000 - 10,000nm	Protected Gold (700- 10000nm)	5.00	#32-742	₹5,917 Volume Pricing	20+ In Stock
-	$\lambda/4$	21.0 x 30.0	$R_{avg} > 98\% @$ 450 - 2000nm $R_{avg} > 98\% @$ 2000 - 10,000nm	Protected Silver (450- 10000nm)	5.00	#46-722	₹5,527 Volume Pricing	20+ In Stock
-	$\lambda/4$	22.0 x 22.0	$R_{avg} > 85\% @$ 400 - 700nm $R_{avg} > 90\% @$ 400 - 2000nm	Protected Aluminum (400- 2000nm)	5.00	#33-510	₹3,893 Volume Pricing	9 In Stock
-	$\lambda/4$	22.0 x 22.0	$R_{avg} > 95\% @$ 450 - 650nm	Enhanced Aluminum (450- 650nm)	5.00	#32-516	₹4,515 Volume Pricing	20+ In Stock
-	$\lambda/4$	22.0 x 22.0	$R_{avg} > 89\% @$ 250 - 450nm $R_{avg} > 85\% @$ 250 - 700nm	Enhanced Aluminum (250- 700nm)	5.00	#46-718	₹4,515 Volume Pricing	Contact Us
-	$\lambda/4$	22.0 x 22.0	$R_{avg} > 96\% @$ 700 - 2000nm $R_{avg} > 96\% @$ 2000 - 10,000nm	Protected Gold (700- 10000nm)	5.00	#32-433	₹5,917 Volume Pricing	20+ In Stock
-	$\lambda/4$	22.0 x 22.0	$R_{avg} > 98\% @$ 450 - 2000nm $R_{avg} > 98\% @$ 2000 - 10,000nm	Protected Silver (450- 10000nm)	5.00	#46-723	₹5,527 Volume Pricing	15 In Stock
25.00	$\lambda/4$	-	$R_{avg} > 95\% @$ 450 - 650nm	Enhanced Aluminum (450- 650nm)	3.00	#45-604	₹5,099 Volume Pricing	20+ In Stock
25.00	$\lambda/4$	-	$R_{avg} > 89\% @$ 250 - 450nm $R_{avg} > 85\% @$ 250 - 700nm	Enhanced Aluminum (250- 700nm)	3.00	#45-605	₹5,099 Volume Pricing	5 In Stock

25.00	$\lambda/4$	-	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	3.00	#45-606	₹7,357 Volume Pricing	5 In Stock
25.00	$\lambda/4$	-	$R_{avg} > 98\% @ 450 - 800nm$ $R_{avg} > 98.5\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	3.00	#49-194	₹6,150 Volume Pricing	20+ In Stock
-	$\lambda/4$	25.0 x 35.0	$R_{avg} > 85\% @ 400 - 700nm$ $R_{avg} > 90\% @ 400 - 2000nm$	Protected Aluminum (400-2000nm)	5.00	#30-286	₹4,282 Volume Pricing	20+ In Stock
-	$\lambda/4$	25.0 x 25.0	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	6.00	#45-333	₹5,099 Volume Pricing	20+ In Stock
-	$\lambda/4$	25.0 x 25.0	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	6.00	#45-334	₹5,099 Volume Pricing	20+ In Stock
-	$\lambda/4$	25.0 x 25.0	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	6.00	#45-335	₹7,357 Volume Pricing	20+ In Stock
-	$\lambda/4$	25.0 x 25.0	$R_{avg} > 98\% @ 450 - 800nm$ $R_{avg} > 98.5\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	6.00	#49-195	₹6,150 Volume Pricing	3 In Stock
-	$\lambda/4$	25.0 x 35.0	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	5.00	#32-513	₹5,099 Volume Pricing	Contact Us
-	$\lambda/4$	25.0 x 35.0	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	5.00	#46-719	₹5,099 Volume Pricing	17 In Stock
-	$\lambda/4$	25.0 x 35.0	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	5.00	#32-434	₹7,357 Volume Pricing	20+ In Stock
-	$\lambda/4$	25.0 x 35.0	$R_{avg} > 98\% @ 450 - 2000nm$ $R_{avg} > 98\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	5.00	#46-724	₹6,150 Volume Pricing	20+ In Stock

25.40	$\lambda/4$	-	$R_{avg} > 95\% @$ 450 - 650nm	Enhanced Aluminum (450- 650nm)	3.00	#25-734	₹5,099 Volume Pricing	Contact Us
25.40	$\lambda/4$	-	$R_{avg} > 89\% @$ 250 - 450nm $R_{avg} > 85\% @$ 250 - 700nm	Enhanced Aluminum (250- 700nm)	3.00	#25-735	₹5,099 Volume Pricing	Contact Us
25.40	$\lambda/4$	-	$R_{avg} > 96\% @$ 700 - 2000nm $R_{avg} > 96\% @$ 2000 - 10,000nm	Protected Gold (700- 10000nm)	3.00	#25-736	₹7,357 Volume Pricing	Contact Us
25.40	$\lambda/4$	-	$R_{avg} > 98\% @$ 450 - 2000nm $R_{avg} > 98\% @$ 2000 - 10,000nm	Protected Silver (450- 10000nm)	3.00	#25-737	₹6,150 Volume Pricing	6 In Stock
30.00	$\lambda/4$	-	$R_{avg} > 95\% @$ 450 - 650nm	Enhanced Aluminum (450- 650nm)	3.00	#63-164	₹6,345 Volume Pricing	Contact Us
30.00	$\lambda/4$	-	$R_{avg} > 89\% @$ 250 - 450nm $R_{avg} > 85\% @$ 250 - 700nm	Enhanced Aluminum (250- 700nm)	3.00	#63-170	₹6,345 Volume Pricing	5 In Stock
30.00	$\lambda/4$	-	$R_{avg} > 96\% @$ 700 - 2000nm $R_{avg} > 96\% @$ 2000 - 10,000nm	Protected Gold (700- 10000nm)	3.00	#63-176	₹8,564 Volume Pricing	20+ In Stock
30.00	$\lambda/4$	-	$R_{avg} > 98\% @$ 450 - 2000nm $R_{avg} > 98\% @$ 2000 - 10,000nm	Protected Silver (450- 10000nm)	3.00	#88-537	₹7,162 Volume Pricing	4 In Stock
-	$\lambda/4$	30.0 x 30.0	$R_{avg} > 95\% @$ 450 - 650nm	Enhanced Aluminum (450- 650nm)	5.00	#63-165	₹6,345 Volume Pricing	5 In Stock
-	$\lambda/4$	30.0 x 30.0	$R_{avg} > 89\% @$ 250 - 450nm $R_{avg} > 85\% @$ 250 - 700nm	Enhanced Aluminum (250- 700nm)	5.00	#63-171	₹6,345 Volume Pricing	20+ In Stock
-	$\lambda/4$	30.0 x 30.0	$R_{avg} > 96\% @$ 700 - 2000nm $R_{avg} > 96\% @$ 2000 - 10,000nm	Protected Gold (700- 10000nm)	5.00	#63-177	₹8,564 Volume Pricing	5 In Stock

-	$\lambda/4$	30.0 x 30.0	R _{avg} >98% @ 450 - 2000nm R _{avg} >98% @ 2000 - 10,000nm	Protected Silver (450- 10000nm)	5.00	#88-538	₹7,162 Volume Pricing	20+ In Stock
-	$\lambda/4$	35.0 x 50.0	R _{avg} >95% @ 450 - 650nm	Enhanced Aluminum (450- 650nm)	5.00	#25-750	₹7,941 Volume Pricing	Contact Us
-	$\lambda/4$	35.0 x 50.0	R _{avg} >89% @ 250 - 450nm R _{avg} >85% @ 250 - 700nm	Enhanced Aluminum (250- 700nm)	5.00	#25-751	₹7,941 Volume Pricing	5 In Stock
-	$\lambda/4$	35.0 x 50.0	R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm	Protected Gold (700- 10000nm)	5.00	#25-752	₹11,444 Volume Pricing	1 In Stock
-	$\lambda/4$	35.0 x 50.0	R _{avg} >98% @ 450 - 2000nm R _{avg} >98% @ 2000 - 10,000nm	Protected Silver (450- 10000nm)	5.00	#25-753	₹9,420 Volume Pricing	7 In Stock
40.00	$\lambda/4$	-	R _{avg} >95% @ 450 - 650nm	Enhanced Aluminum (450- 650nm)	4.00	#63-166	₹7,551 Volume Pricing	20+ In Stock
40.00	$\lambda/4$	-	R _{avg} >89% @ 250 - 450nm R _{avg} >85% @ 250 - 700nm	Enhanced Aluminum (250- 700nm)	4.00	#63-172	₹7,551 Volume Pricing	Contact Us
40.00	$\lambda/4$	-	R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm	Protected Gold (700- 10000nm)	4.00	#63-178	₹10,432 Volume Pricing	5 In Stock
40.00	$\lambda/4$	-	R _{avg} >98% @ 450 - 2000nm R _{avg} >98% @ 2000 - 10,000nm	Protected Silver (450- 10000nm)	4.00	#88-539	₹8,408 Volume Pricing	20+ In Stock
-	$\lambda/4$	40.0 x 40.0	R _{avg} >95% @ 450 - 650nm	Enhanced Aluminum (450- 650nm)	5.00	#63-167	₹7,551 Volume Pricing	20+ In Stock
-	$\lambda/4$	40.0 x 40.0	R _{avg} >89% @ 250 - 450nm R _{avg} >85% @ 250 - 700nm	Enhanced Aluminum (250- 700nm)	5.00	#63-173	₹7,551 Volume Pricing	20+ In Stock

-	$\lambda/4$	40.0 x 40.0	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	5.00	#63-179	₹10,432 Volume Pricing	20+ In Stock
-	$\lambda/4$	40.0 x 40.0	$R_{avg} > 98\% @ 450 - 2000nm$ $R_{avg} > 98\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	5.00	#88-540	₹8,408 Volume Pricing	20+ In Stock
50.00	$\lambda/4$	-	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	4.00	#45-607	₹8,564 Volume Pricing	14 In Stock
50.00	$\lambda/4$	-	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	4.00	#45-608	₹8,564 Volume Pricing	20+ In Stock
50.00	$\lambda/4$	-	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	4.00	#45-609	₹12,456 Volume Pricing	Contact Us
50.00	$\lambda/4$	-	$R_{avg} > 98\% @ 450 - 800nm$ $R_{avg} > 98.5\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	4.00	#49-196	₹10,432 Volume Pricing	20+ In Stock
-	$\lambda/4$	50.0 x 50.0	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	10.00	#45-336	₹8,564 Volume Pricing	9 In Stock
-	$\lambda/4$	50.0 x 50.0	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	Enhanced Aluminum (250-700nm)	10.00	#45-337	₹8,564 Volume Pricing	8 In Stock
-	$\lambda/4$	50.0 x 50.0	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	Protected Gold (700-10000nm)	10.00	#45-338	₹12,456 Volume Pricing	4 In Stock
-	$\lambda/4$	50.0 x 50.0	$R_{avg} > 98\% @ 450 - 800nm$ $R_{avg} > 98.5\% @ 2000 - 10,000nm$	Protected Silver (450-10000nm)	10.00	#49-197	₹10,432 Volume Pricing	7 In Stock
50.80	$\lambda/4$	-	$R_{avg} > 95\% @ 450 - 650nm$	Enhanced Aluminum (450-650nm)	4.00	#25-738	₹8,564 Volume Pricing	Contact Us

50.80	$\lambda/4$	-	$R_{avg} > 89\% @$ 250 - 450nm $R_{avg} > 85\% @$ 250 - 700nm	Enhanced Aluminum (250- 700nm)	4.00	#25-739	₹8,564 Volume Pricing	4 In Stock
50.80	$\lambda/4$	-	$R_{avg} > 96\% @$ 700 - 2000nm $R_{avg} > 96\% @$ 2000 - 10,000nm	Protected Gold (700- 10000nm)	4.00	#25-740	₹12,456 Volume Pricing	7 In Stock
50.80	$\lambda/4$	-	$R_{avg} > 98\% @$ 450 - 2000nm $R_{avg} > 98\% @$ 2000 - 10,000nm	Protected Silver (450- 10000nm)	4.00	#25-741	₹10,432 Volume Pricing	8 In Stock
51.00	$\lambda/4$	-	$R_{avg} > 85\% @$ 400 - 700nm $R_{avg} > 90\% @$ 400 - 2000nm	Protected Aluminum (400- 2000nm)	13.00	#33-511	₹4,905 Volume Pricing	Contact Us
51.00	$\lambda/4$	-	$R_{avg} > 95\% @$ 450 - 650nm	Enhanced Aluminum (450- 650nm)	13.00	#32-514	₹8,564 Volume Pricing	2 In Stock
51.00	$\lambda/4$	-	$R_{avg} > 89\% @$ 250 - 450nm $R_{avg} > 85\% @$ 250 - 700nm	Enhanced Aluminum (250- 700nm)	13.00	#46-720	₹8,564 Volume Pricing	2 In Stock
51.00	$\lambda/4$	-	$R_{avg} > 96\% @$ 700 - 2000nm $R_{avg} > 96\% @$ 2000 - 10,000nm	Protected Gold (700- 10000nm)	13.00	#32-435	₹12,456 Volume Pricing	20+ In Stock
51.00	$\lambda/4$	-	$R_{avg} > 98\% @$ 450 - 2000nm $R_{avg} > 98\% @$ 2000 - 10,000nm	Protected Silver (450- 10000nm)	13.00	#46-725	₹10,432 Volume Pricing	3 In Stock
-	$\lambda/4$	75.0 x 75.0	$R_{avg} > 95\% @$ 450 - 650nm	Enhanced Aluminum (450- 650nm)	12.00	#45-339	₹16,582 Volume Pricing	12 In Stock
-	$\lambda/4$	75.0 x 75.0	$R_{avg} > 89\% @$ 250 - 450nm $R_{avg} > 85\% @$ 250 - 700nm	Enhanced Aluminum (250- 700nm)	12.00	#45-340	₹16,582 Volume Pricing	Contact Us
-	$\lambda/4$	75.0 x 75.0	$R_{avg} > 96\% @$ 700 - 2000nm $R_{avg} > 96\% @$ 2000 - 10,000nm	Protected Gold (700- 10000nm)	12.00	#45-341	₹22,265 Volume Pricing	4 In Stock

-	$\lambda/4$	75.0 x 75.0	$R_{avg} > 98\% @$ 450 - 2000nm $R_{avg} > 98\% @$ 2000 - 10,000nm	Protected Silver (450- 10000nm)	12.00	#88-541	₹19,229 Volume Pricing	20+ In Stock
-	$\lambda/4$	100.0 x 100.0	$R_{avg} > 95\% @$ 450 - 650nm	Enhanced Aluminum (450- 650nm)	15.00	#45-342	₹26,547 Volume Pricing	20+ In Stock
-	$\lambda/4$	100.0 x 100.0	$R_{avg} > 89\% @$ 250 - 450nm $R_{avg} > 85\% @$ 250 - 700nm	Enhanced Aluminum (250- 700nm)	15.00	#45-343	₹26,547 Volume Pricing	20+ In Stock
-	$\lambda/4$	100.0 x 100.0	$R_{avg} > 96\% @$ 700 - 2000nm $R_{avg} > 96\% @$ 2000 - 10,000nm	Protected Gold (700- 10000nm)	15.00	#45-344	₹36,590 Volume Pricing	4 In Stock

	Edmund optics worldwide	$R_{avg} > 98\% @$ 450 - 2000nm $R_{avg} > 98\% @$ 2000 - 10,000nm	Protected Silver (450- 10000nm)	15.00	#88-542	₹28,182 Volume Pricing	7 In Stock
--	-------------------------------------	--	--	-------	-------------------------	---	------------

Copyright 2023, Edmund Optics India Pvt. Ltd., #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038
Phone: 1-800-363-1992 :
www.edmundoptics.com