


[All Products](#) / [Optics](#) / [Beamsplitters](#) / [Plate Beamsplitters](#)

TECHSPEC® UV Plate Beamsplitters



- Multiple Transmission/Reflection Ratios Available
- BBAR Coated Second Surface
- Fused Silica Substrate

Common Specifications

Physical & Mechanical Properties

Clear Aperture (%):	>85	Construction:	Plate
Parallelism (arcmin):	<5		

Optical Properties

Angle of Incidence (°):	45		
Substrate:	Fused Silica (Corning 7980)	Surface Flatness (P-V):	1λ
Surface Quality:	60-40	Wavelength Range (nm):	250 - 450

Technical Information

Products

Dia. (mm)	Dimensions (mm)	Substrate	Reflection/Transmission Ratio (R/T)	Wavelength Range (nm)	Thickness (mm)	Stock Number	Price	Buy
10.00	-	Fused Silica	30/70	250 - 450	1.00	#65-922	₹10,260 Volume Pricing	1 In Stock
12.50	-	Fused Silica	30/70	250 - 450	2.00	#48-194	₹10,440 Volume Pricing	20+ In Stock
-	12.5 x 12.5	Fused Silica	30/70	250 - 450	2.00	#48-195	₹10,440 Volume Pricing	20+ In Stock
20.00	-	Fused Silica	30/70	250 - 450	2.00	#65-924	₹11,610 Volume Pricing	16 In Stock
25.00	-	Fused Silica	30/70	250 - 450	2.00	#48-196	₹12,600 Volume Pricing	6 In Stock
-	25.0 x 25.0	Fused Silica	30/70	250 - 450	2.00	#48-197	₹12,600 Volume Pricing	15 In Stock
30.00	-	Fused Silica	30/70	250 - 450	3.00	#65-926	₹14,490 Volume Pricing	5 In Stock
40.00	-	Fused Silica	30/70	250 - 450	4.00	#65-928	₹18,810 Volume Pricing	11 In Stock
50.00	-	Fused Silica	30/70	250 - 450	4.00	#48-198	₹20,970 Volume Pricing	11 In Stock
-	50.0 x 50.0	Fused Silica	30/70	250 - 450	4.00	#48-199	₹20,970 Volume Pricing	12 In Stock
10.00	-	Fused Silica	50/50	250 - 450	1.00	#65-921	₹10,260 Volume Pricing	20+ In Stock
12.50	-	Fused Silica	50/50	250 - 450	2.00	#48-188	₹10,440 Volume Pricing	13 In Stock
-	12.5 x 12.5	Fused Silica	50/50	250 - 450	2.00	#48-189	₹10,440 Volume Pricing	12 In Stock
-	12.50 x 17.50	Fused Silica	50/50	250 - 450	2.00	#72-249	₹10,980 Volume Pricing	4 In Stock
20.00	-	Fused Silica	50/50	250 - 450	2.00	#65-923	₹11,610 Volume Pricing	16 In Stock
25.00	-	Fused Silica	50/50	250 - 450	2.00	#48-190	₹12,600 Volume Pricing	Contact Us
-	25.0 x 25.0	Fused Silica	50/50	250 - 450	2.00	#48-191	₹12,600 Volume Pricing	Contact Us
-	25.00 x 35.00	Fused Silica	50/50	250 - 450	3.00	#72-250	₹13,860 Volume Pricing	Contact Us
30.00	-	Fused Silica	50/50	250 - 450	3.00	#65-925	₹14,490 Volume Pricing	8 In Stock
40.00	-	Fused Silica	50/50	250 - 450	4.00	#65-927	₹18,810 Volume Pricing	2 In Stock
50.00	-	Fused Silica	50/50	250 - 450	4.00	#48-192	₹20,970 Volume Pricing	3 In Stock

-	35.00 x 50.00	Fused Silica	50/50	250 - 450	4.00	#72-251	₹19,530 Volume Pricing	1 In Stock
-	50.0 x 50.0	Fused Silica	50/50	250 - 450	4.00	#48-193	₹20,970 Volume Pricing	5 In Stock
10.00	-	Fused Silica	70/30	250 - 450	1.00	#84-483	₹10,260 Volume Pricing	10 In Stock
12.50	-	Fused Silica	70/30	250 - 450	2.00	#84-484	₹10,440 Volume Pricing	12 In Stock
-	12.5 x 12.5	Fused Silica	70/30	250 - 450	2.00	#84-485	₹10,440 Volume Pricing	16 In Stock
20.00	-	Fused Silica	70/30	250 - 450	2.00	#84-486	₹11,610 Volume Pricing	11 In Stock
25.00	-	Fused Silica	70/30	250 - 450	2.00	#84-487	₹12,600 Volume Pricing	Contact Us
30.00	-	Fused Silica	70/30	250 - 450	3.00	#84-489	₹14,490 Volume Pricing	12 In Stock
40.00	-	Fused Silica	70/30	250 - 450	4.00	#84-490	₹18,810 Volume Pricing	5 In Stock
50.00	-	Fused Silica	70/30	250 - 450	4.00	#84-491	₹20,970 Volume Pricing	1 In Stock
-	50.0 x 50.0	Fused Silica	70/30	250 - 450	4.00	#84-492	₹20,970 Volume Pricing	Contact Us



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038
Phone: 1-800-363-1992 :
www.edmundoptics.com