

[All Products](#) / [Optics](#) / [Optical Mirrors](#) / [Flat Mirrors](#) / [Precision Polished Metal Coatings](#)

TECHSPEC® $\lambda/10$ First Surface Mirrors



- Precision Fused Silica Substrate
- Variety of Sizes and Coating Options Available
- Low Coefficient of Thermal Expansion

Common Specifications

Physical & Mechanical Properties

Back Surface:	Commercial Polish	Bevel:	Protective as needed
Clear Aperture (%):	90	Edges:	Ground

Optical Properties

Surface Flatness (P-V):	$\lambda/10$	Surface Quality:	20-10
--------------------------------	--------------	-------------------------	-------

Technical Information

Products

Dia. (mm)	Surface Flatness (P-V)	Dimensions (mm)	Thickness (mm)	Coating	Coating Specification	Stock Number	Price	Buy
5.00	λ/10	-	2.00	Enhanced Aluminum (450- 650nm)	R _{avg} >95% @ 450 - 650nm	#64-007	₹6,189 Volume Pricing	1 In Stock
5.00	λ/10	-	2.00	Enhanced Aluminum (250- 700nm)	R _{avg} >89% @ 250 - 450nm R _{avg} >85% @ 250 - 700nm	#68-307	₹6,189 Volume Pricing	5 In Stock
5.00	λ/10	-	2.00	Protected Gold (700- 10000nm)	R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm	#64-021	₹7,707 Volume Pricing	Contact Us
5.00	λ/10	-	2.00	Protected Silver (450- 10000nm)	R _{avg} >98% @ 450 - 800nm R _{avg} >98.5% @ 2000 - 10,000nm	#68-321	₹7,396 Volume Pricing	16 In Stock
5.00	λ/10	-	2.00	Ultrafast- Enhanced Silver (600- 1000nm)	R _{avg} >99% @ 600 - 1000nm, 0° R _s >99% @ 540 - 1000nm, 45° R _p >98.5% @ ~730 - 870nm, 45°	#21-976	₹7,590 Volume Pricing	14 In Stock
5.00	λ/10	-	2.00	Ultrafast- Enhanced Silver (800- 1150nm)	R _{avg} >99% @ 850 - 1150nm, 0° R _s >99% @ 800 - 1150nm, 45° R _p >98.5% @ ~850 - 1100nm, 45°	#22-006	₹7,590 Volume Pricing	7 In Stock
-	λ/10	5.0 x 5.0	2.00	Enhanced Aluminum (450- 650nm)	R _{avg} >95% @ 450 - 650nm	#64-008	₹6,189 Volume Pricing	20+ In Stock
-	λ/10	5.0 x 5.0	2.00	Enhanced Aluminum (250- 700nm)	R _{avg} >89% @ 250 - 450nm R _{avg} >85% @ 250 - 700nm	#68-308	₹6,189 Volume Pricing	3 In Stock

-	$\lambda/10$	5.0 x 5.0	2.00	Protected Gold (700-10000nm)	$R_{avg} > 96\%$ @ 700 - 2000nm $R_{avg} > 96\%$ @ 2000 - 10,000nm	#64-022	₹7,707 Volume Pricing	1 In Stock
-	$\lambda/10$	5.0 x 5.0	2.00	Protected Silver (450-10000nm)	$R_{avg} > 98\%$ @ 450 - 800nm $R_{avg} > 98.5\%$ @ 2000 - 10,000nm	#68-322	₹7,396 Volume Pricing	Contact Us
-	$\lambda/10$	5.0 x 5.0	2.00	Ultrafast-Enhanced Silver (600-1000nm)	$R_{avg} > 99\%$ @ 600 - 1000nm, 0° $R_s > 99\%$ @ 540 - 1000nm, 45° $R_p > 98.5\%$ @ ~730 - 870nm, 45°	#21-977	₹7,590 Volume Pricing	7 In Stock
-	$\lambda/10$	5.0 x 5.0	2.00	Ultrafast-Enhanced Silver (800-1150nm)	$R_{avg} > 99\%$ @ 850 - 1150nm, 0° $R_s > 99\%$ @ 800 - 1150nm, 45° $R_p > 98.5\%$ @ ~850 - 1100nm, 45°	#22-007	₹7,590 Volume Pricing	2 In Stock
6.35	$\lambda/10$	-	4.00	Enhanced Aluminum (450-650nm)	$R_{avg} > 95\%$ @ 450 - 650nm	#39-189	₹6,189 Volume Pricing	3 In Stock
6.35	$\lambda/10$	-	4.00	Enhanced Aluminum (250-700nm)	$R_{avg} > 89\%$ @ 250 - 450nm $R_{avg} > 85\%$ @ 250 - 700nm	#39-188	₹6,189 Volume Pricing	3 In Stock
6.35	$\lambda/10$	-	4.00	Protected Gold (700-10000nm)	$R_{avg} > 96\%$ @ 700 - 2000nm $R_{avg} > 96\%$ @ 2000 - 10,000nm	#39-186	₹7,707 Volume Pricing	Contact Us
6.35	$\lambda/10$	-	4.00	Protected Silver (450-10000nm)	$R_{avg} > 98\%$ @ 450 - 800nm $R_{avg} > 98.5\%$ @ 2000 - 10,000nm	#39-187	₹7,396 Volume Pricing	2 In Stock
10.00	$\lambda/10$	-	2.00	Enhanced Aluminum (450-650nm)	$R_{avg} > 95\%$ @ 450 - 650nm	#64-009	₹6,189 Volume Pricing	20+ In Stock

10.00	$\lambda/10$	-	2.00	Enhanced Aluminum (250-700nm)	$R_{avg} > 89\%$ @ 250 - 450nm $R_{avg} > 85\%$ @ 250 - 700nm	#68-309	₹6,189 Volume Pricing	2 In Stock
10.00	$\lambda/10$	-	2.00	Protected Gold (700-10000nm)	$R_{avg} > 96\%$ @ 700 - 2000nm $R_{avg} > 96\%$ @ 2000 - 10,000nm	#64-023	₹7,707 Volume Pricing	Contact Us
10.00	$\lambda/10$	-	2.00	Protected Silver (450-10000nm)	$R_{avg} > 98\%$ @ 450 - 800nm $R_{avg} > 98.5\%$ @ 2000 - 10,000nm	#68-323	₹7,396 Volume Pricing	15 In Stock
10.00	$\lambda/10$	-	2.00	UV Enhanced Silver (350 - 3,000nm)	$R_{avg} > 90\%$ @ 350 - 400nm $R_{avg} > 96\%$ @ 400 - 3,000nm	#70-233	₹7,707 Volume Pricing	17 In Stock
10.00	$\lambda/10$	-	2.00	Ultrafast-Enhanced Silver (600-1000nm)	$R_{avg} > 99\%$ @ 600 - 1000nm, 0° $R_s > 99\%$ @ 540 - 1000nm, 45° $R_p > 98.5\%$ @ ~730 - 870nm, 45°	#21-979	₹7,590 Volume Pricing	4 In Stock
10.00	$\lambda/10$	-	2.00	Ultrafast-Enhanced Silver (800-1150nm)	$R_{avg} > 99\%$ @ 850 - 1150nm, 0° $R_s > 99\%$ @ 800 - 1150nm, 45° $R_p > 98.5\%$ @ ~850 - 1100nm, 45°	#22-009	₹7,590 Volume Pricing	3 In Stock
-	$\lambda/10$	10.0 x 10.0	2.00	Enhanced Aluminum (450-650nm)	$R_{avg} > 95\%$ @ 450 - 650nm	#64-010	₹6,189 Volume Pricing	15 In Stock
-	$\lambda/10$	10.0 x 10.0	2.00	Enhanced Aluminum (250-700nm)	$R_{avg} > 89\%$ @ 250 - 450nm $R_{avg} > 85\%$ @ 250 - 700nm	#68-310	₹6,189 Volume Pricing	14 In Stock
-	$\lambda/10$	10.0 x 10.0	2.00	Protected Gold (700-10000nm)	$R_{avg} > 96\%$ @ 700 - 2000nm $R_{avg} > 96\%$ @ 2000 - 10,000nm	#64-024	₹7,707 Volume Pricing	15 In Stock

-	$\lambda/10$	10.0 x 10.0	2.00	Protected Silver (450-10000nm)	$R_{avg} > 98\%$ @ 450 - 800nm $R_{avg} > 98.5\%$ @ 2000 - 10,000nm	#68-324	₹7,396 Volume Pricing	Contact Us
12.50	$\lambda/10$	-	3.00	Enhanced Aluminum (450-650nm)	$R_{avg} > 95\%$ @ 450 - 650nm	#84-409	₹6,189 Volume Pricing	20+ In Stock
12.50	$\lambda/10$	-	3.00	Enhanced Aluminum (250-700nm)	$R_{avg} > 89\%$ @ 250 - 450nm $R_{avg} > 85\%$ @ 250 - 700nm	#84-419	₹6,189 Volume Pricing	9 In Stock
12.50	$\lambda/10$	-	3.00	Protected Gold (700-10000nm)	$R_{avg} > 96\%$ @ 700 - 2000nm $R_{avg} > 96\%$ @ 2000 - 10,000nm	#84-429	₹7,707 Volume Pricing	20+ In Stock
12.50	$\lambda/10$	-	3.00	Protected Silver (450-10000nm)	$R_{avg} > 98\%$ @ 450 - 800nm $R_{avg} > 98.5\%$ @ 2000 - 10,000nm	#84-439	₹7,396 Volume Pricing	9 In Stock
12.50	$\lambda/10$	-	3.00	UV Enhanced Silver (350 - 3,000nm)	$R_{avg} > 90\%$ @ 350 - 400nm $R_{avg} > 96\%$ @ 400 - 3,000nm	#70-234	₹7,707 Volume Pricing	5 In Stock
12.50	$\lambda/10$	-	3.00	Ultrafast-Enhanced Silver (600-1000nm)	$R_{avg} > 99\%$ @ 600 - 1000nm, 0° $R_s > 99\%$ @ 540 - 1000nm, 45° $R_p > 98.5\%$ @ ~730 - 870nm, 45°	#21-980	₹7,590 Volume Pricing	9 In Stock
12.50	$\lambda/10$	-	3.00	Ultrafast-Enhanced Silver (800-1150nm)	$R_{avg} > 99\%$ @ 850 - 1150nm, 0° $R_s > 99\%$ @ 800 - 1150nm, 45° $R_p > 98.5\%$ @ ~850 - 1100nm, 45°	#22-010	₹7,590 Volume Pricing	3 In Stock
-	$\lambda/10$	12.5 x 12.5	3.00	Enhanced Aluminum (450-650nm)	$R_{avg} > 95\%$ @ 450 - 650nm	#84-410	₹6,189 Volume Pricing	3 In Stock
-	$\lambda/10$	12.5 x 12.5	3.00	Enhanced Aluminum (250-700nm)	$R_{avg} > 89\%$ @ 250 - 450nm $R_{avg} > 85\%$ @ 250 - 700nm	#84-420	₹6,189 Volume Pricing	Contact Us

-	$\lambda/10$	12.5 x 12.5	3.00	Protected Gold (700-10000nm)	$R_{avg} >96\%$ @ 700 - 2000nm $R_{avg} >96\%$ @ 2000 - 10,000nm	#84-430	₹7,707 Volume Pricing	13 In Stock
-	$\lambda/10$	12.5 x 12.5	3.00	Protected Silver (450-10000nm)	$R_{avg} >98\%$ @ 450 - 800nm $R_{avg} >98.5\%$ @ 2000 - 10,000nm	#84-440	₹7,396 Volume Pricing	5 In Stock
12.70	$\lambda/10$	-	6.35	Enhanced Aluminum (450-650nm)	$R_{avg} >95\%$ @ 450 - 650nm	#39-196	₹6,189 Volume Pricing	1 In Stock
12.70	$\lambda/10$	-	6.35	Enhanced Aluminum (250-700nm)	$R_{avg} >89\%$ @ 250 - 450nm $R_{avg} >85\%$ @ 250 - 700nm	#39-195	₹6,189 Volume Pricing	Contact Us
12.70	$\lambda/10$	-	6.35	Protected Gold (700-10000nm)	$R_{avg} >96\%$ @ 700 - 2000nm $R_{avg} >96\%$ @ 2000 - 10,000nm	#39-193	₹7,707 Volume Pricing	1 In Stock
12.70	$\lambda/10$	-	6.35	Protected Silver (450-10000nm)	$R_{avg} >98\%$ @ 450 - 800nm $R_{avg} >98.5\%$ @ 2000 - 10,000nm	#39-194	₹7,396 Volume Pricing	11 In Stock
15.00	$\lambda/10$	-	3.00	Enhanced Aluminum (450-650nm)	$R_{avg} >95\%$ @ 450 - 650nm	#64-011	₹6,656 Volume Pricing	7 In Stock
15.00	$\lambda/10$	-	3.00	Enhanced Aluminum (250-700nm)	$R_{avg} >89\%$ @ 250 - 450nm $R_{avg} >85\%$ @ 250 - 700nm	#68-311	₹6,656 Volume Pricing	4 In Stock
15.00	$\lambda/10$	-	3.00	Protected Gold (700-10000nm)	$R_{avg} >96\%$ @ 700 - 2000nm $R_{avg} >96\%$ @ 2000 - 10,000nm	#64-025	₹8,174 Volume Pricing	2 In Stock
15.00	$\lambda/10$	-	3.00	Protected Silver (450-10000nm)	$R_{avg} >98\%$ @ 450 - 800nm $R_{avg} >98.5\%$ @ 2000 - 10,000nm	#68-325	₹7,980 Volume Pricing	20+ In Stock
15.00	$\lambda/10$	-	3.00	UV Enhanced Silver (350 - 3,000nm)	$R_{avg} >90\%$ @ 350 - 400nm $R_{avg} >96\%$ @ 400 - 3,000nm	#70-235	₹8,953 Volume Pricing	1 In Stock

15.00	$\lambda/10$	-	3.00	Ultrafast-Enhanced Silver (600-1000nm)	$R_{avg} > 99\%$ @ 600 - 1000nm, 0° $R_s > 99\%$ @ 540 - 1000nm, 45° $R_p > 98.5\%$ @ ~730 - 870nm, 45°	#21-982	₹8,174 Volume Pricing	5 In Stock
15.00	$\lambda/10$	-	3.00	Ultrafast-Enhanced Silver (800-1150nm)	$R_{avg} > 99\%$ @ 850 - 1150nm, 0° $R_s > 99\%$ @ 800 - 1150nm, 45° $R_p > 98.5\%$ @ ~850 - 1100nm, 45°	#22-012	₹8,174 Volume Pricing	7 In Stock
-	$\lambda/10$	15.0 x 15.0	3.00	Enhanced Aluminum (450-650nm)	$R_{avg} > 95\%$ @ 450 - 650nm	#64-012	₹6,656 Volume Pricing	12 In Stock
-	$\lambda/10$	15.0 x 15.0	3.00	Enhanced Aluminum (250-700nm)	$R_{avg} > 89\%$ @ 250 - 450nm $R_{avg} > 85\%$ @ 250 - 700nm	#68-312	₹7,201 Volume Pricing	Contact Us
-	$\lambda/10$	15.0 x 15.0	3.00	Protected Gold (700-10000nm)	$R_{avg} > 96\%$ @ 700 - 2000nm $R_{avg} > 96\%$ @ 2000 - 10,000nm	#64-026	₹8,174 Volume Pricing	Contact Us
-	$\lambda/10$	15.0 x 15.0	3.00	Protected Silver (450-10000nm)	$R_{avg} > 98\%$ @ 450 - 800nm $R_{avg} > 98.5\%$ @ 2000 - 10,000nm	#68-326	₹7,980 Volume Pricing	20+ In Stock
-	$\lambda/10$	15.0 x 15.0	3.00	Ultrafast-Enhanced Silver (600-1000nm)	$R_{avg} > 99\%$ @ 600 - 1000nm, 0° $R_s > 99\%$ @ 540 - 1000nm, 45° $R_p > 98.5\%$ @ ~730 - 870nm, 45°	#21-997	₹8,174 Volume Pricing	6 In Stock
19.10	$\lambda/10$	-	6.35	Enhanced Aluminum (450-650nm)	$R_{avg} > 95\%$ @ 450 - 650nm	#39-203	₹7,201 Volume Pricing	5 In Stock
19.10	$\lambda/10$	-	6.35	Enhanced Aluminum (250-700nm)	$R_{avg} > 89\%$ @ 250 - 450nm $R_{avg} > 85\%$ @ 250 - 700nm	#39-202	₹7,201 Volume Pricing	3 In Stock

19.10	$\lambda/10$	-	6.35	Protected Gold (700-10000nm)	$R_{avg} >96\%$ @ 700 - 2000nm $R_{avg} >96\%$ @ 2000 - 10,000nm	#39-200	₹8,953 Volume Pricing	1 In Stock
19.10	$\lambda/10$	-	6.35	Protected Silver (450-10000nm)	$R_{avg} >98\%$ @ 450 - 800nm $R_{avg} >98.5\%$ @ 2000 - 10,000nm	#39-201	₹8,369 Volume Pricing	1 In Stock
20.00	$\lambda/10$	-	3.00	Enhanced Aluminum (450-650nm)	$R_{avg} >95\%$ @ 450 - 650nm	#64-013	₹7,201 Volume Pricing	20+ In Stock
20.00	$\lambda/10$	-	3.00	Enhanced Aluminum (250-700nm)	$R_{avg} >89\%$ @ 250 - 450nm $R_{avg} >85\%$ @ 250 - 700nm	#68-313	₹7,201 Volume Pricing	5 In Stock
20.00	$\lambda/10$	-	3.00	Protected Gold (700-10000nm)	$R_{avg} >96\%$ @ 700 - 2000nm $R_{avg} >96\%$ @ 2000 - 10,000nm	#64-027	₹8,953 Volume Pricing	15 In Stock
20.00	$\lambda/10$	-	3.00	Protected Silver (450-10000nm)	$R_{avg} >98\%$ @ 450 - 800nm $R_{avg} >98.5\%$ @ 2000 - 10,000nm	#68-327	₹8,369 Volume Pricing	20+ In Stock
20.00	$\lambda/10$	-	3.00	UV Enhanced Silver (350 - 3,000nm)	$R_{avg} >90\%$ @ 350 - 400nm $R_{avg} >96\%$ @ 400 - 3,000nm	#70-236	₹8,953 Volume Pricing	7 In Stock
20.00	$\lambda/10$	-	3.00	Ultrafast-Enhanced Silver (600-1000nm)	$R_{avg} >99\%$ @ 600 - 1000nm, 0° $R_s >99\%$ @ 540 - 1000nm, 45° $R_p >98.5\%$ @ ~730 - 870nm, 45°	#21-984	₹8,758 Volume Pricing	10 In Stock
20.00	$\lambda/10$	-	3.00	Ultrafast-Enhanced Silver (800-1150nm)	$R_{avg} >99\%$ @ 850 - 1150nm, 0° $R_s >99\%$ @ 800 - 1150nm, 45° $R_p >98.5\%$ @ ~850 - 1100nm, 45°	#22-014	₹8,758 Volume Pricing	2 In Stock

-	$\lambda/10$	20.0 x 20.0	3.00	Enhanced Aluminum (450-650nm)	$R_{avg} >95\%$ @ 450 - 650nm	#64-014	₹7,201 Volume Pricing	Contact Us
-	$\lambda/10$	20.0 x 20.0	3.00	Enhanced Aluminum (250-700nm)	$R_{avg} >89\%$ @ 250 - 450nm $R_{avg} >85\%$ @ 250 - 700nm	#68-314	₹7,201 Volume Pricing	20+ In Stock
-	$\lambda/10$	20.0 x 20.0	3.00	Protected Gold (700-10000nm)	$R_{avg} >96\%$ @ 700 - 2000nm $R_{avg} >96\%$ @ 2000 - 10,000nm	#64-028	₹8,953 Volume Pricing	Contact Us
-	$\lambda/10$	20.0 x 20.0	3.00	Protected Silver (450-10000nm)	$R_{avg} >98\%$ @ 450 - 800nm $R_{avg} >98.5\%$ @ 2000 - 10,000nm	#68-328	₹8,369 Volume Pricing	20+ In Stock
-	$\lambda/10$	20.0 x 20.0	3.00	Ultrafast-Enhanced Silver (600-1000nm)	$R_{avg} >99\%$ @ 600 - 1000nm, 0° $R_s >99\%$ @ 540 - 1000nm, 45° $R_p >98.5\%$ @ ~730 - 870nm, 45°	#21-998	₹8,758 Volume Pricing	1 In Stock
25.00	$\lambda/10$	-	4.00	Enhanced Aluminum (450-650nm)	$R_{avg} >95\%$ @ 450 - 650nm	#64-015	₹7,590 Volume Pricing	20+ In Stock
25.00	$\lambda/10$	-	4.00	Enhanced Aluminum (250-700nm)	$R_{avg} >89\%$ @ 250 - 450nm $R_{avg} >85\%$ @ 250 - 700nm	#68-315	₹7,590 Volume Pricing	20+ In Stock
25.00	$\lambda/10$	-	4.00	Protected Gold (700-10000nm)	$R_{avg} >96\%$ @ 700 - 2000nm $R_{avg} >96\%$ @ 2000 - 10,000nm	#64-029	₹10,510 Volume Pricing	20+ In Stock
25.00	$\lambda/10$	-	4.00	Protected Silver (450-10000nm)	$R_{avg} >98\%$ @ 450 - 800nm $R_{avg} >98.5\%$ @ 2000 - 10,000nm	#68-329	₹9,731 Volume Pricing	17 In Stock
25.00	$\lambda/10$	-	4.00	UV Enhanced Silver (350 - 3,000nm)	$R_{avg} >90\%$ @ 350 - 400nm $R_{avg} >96\%$ @ 400 - 3,000nm	#70-237	₹10,043 Volume Pricing	Contact Us

25.00	$\lambda/10$	-	4.00	Ultrafast-Enhanced Silver (600-1000nm)	$R_{avg} > 99\%$ @ 600 - 1000nm, 0° $R_s > 99\%$ @ 540 - 1000nm, 45° $R_p > 98.5\%$ @ ~730 - 870nm, 45°	#21-985	₹10,043 Volume Pricing	12 In Stock
25.00	$\lambda/10$	-	4.00	Ultrafast-Enhanced Silver (800-1150nm)	$R_{avg} > 99\%$ @ 850 - 1150nm, 0° $R_s > 99\%$ @ 800 - 1150nm, 45° $R_p > 98.5\%$ @ ~850 - 1100nm, 45°	#22-015	₹10,043 Volume Pricing	14 In Stock
-	$\lambda/10$	25.0 x 25.0	4.00	Enhanced Aluminum (450-650nm)	$R_{avg} > 95\%$ @ 450 - 650nm	#64-016	₹7,590 Volume Pricing	20+ In Stock
-	$\lambda/10$	25.0 x 25.0	4.00	Enhanced Aluminum (250-700nm)	$R_{avg} > 89\%$ @ 250 - 450nm $R_{avg} > 85\%$ @ 250 - 700nm	#68-316	₹7,590 Volume Pricing	20+ In Stock
-	$\lambda/10$	25.0 x 25.0	4.00	Protected Gold (700-10000nm)	$R_{avg} > 96\%$ @ 700 - 2000nm $R_{avg} > 96\%$ @ 2000 - 10,000nm	#64-030	₹10,510 Volume Pricing	1 In Stock
-	$\lambda/10$	25.0 x 25.0	4.00	Protected Silver (450-10000nm)	$R_{avg} > 98\%$ @ 450 - 800nm $R_{avg} > 98.5\%$ @ 2000 - 10,000nm	#68-330	₹9,731 Volume Pricing	16 In Stock
-	$\lambda/10$	25.0 x 35.0	5.00	Protected Silver (450-10000nm)	$R_{avg} > 98\%$ @ 450 - 800nm $R_{avg} > 98.5\%$ @ 2000 - 10,000nm	#25-549	₹12,845 Volume Pricing	9 In Stock
-	$\lambda/10$	25.0 x 25.0	4.00	Ultrafast-Enhanced Silver (600-1000nm)	$R_{avg} > 99\%$ @ 600 - 1000nm, 0° $R_s > 99\%$ @ 540 - 1000nm, 45° $R_p > 98.5\%$ @ ~730 - 870nm, 45°	#21-999	₹10,043 Volume Pricing	4 In Stock
25.40	$\lambda/10$	-	6.35	Enhanced Aluminum (450-650nm)	$R_{avg} > 95\%$ @ 450 - 650nm	#39-210	₹7,590 Volume Pricing	8 In Stock

25.40	$\lambda/10$	-	6.35	Enhanced Aluminum (250-700nm)	$R_{avg} > 89\%$ @ 250 - 450nm $R_{avg} > 85\%$ @ 250 - 700nm	#39-209	₹7,590 Volume Pricing	Contact Us
25.40	$\lambda/10$	-	6.35	Protected Gold (700-10000nm)	$R_{avg} > 96\%$ @ 700 - 2000nm $R_{avg} > 96\%$ @ 2000 - 10,000nm	#39-207	₹10,510 Volume Pricing	14 In Stock
25.40	$\lambda/10$	-	6.35	Protected Silver (450-10000nm)	$R_{avg} > 98\%$ @ 450 - 800nm $R_{avg} > 98.5\%$ @ 2000 - 10,000nm	#39-208	₹9,731 Volume Pricing	17 In Stock
30.00	$\lambda/10$	-	5.00	Enhanced Aluminum (450-650nm)	$R_{avg} > 95\%$ @ 450 - 650nm	#84-411	₹9,731 Volume Pricing	Contact Us
30.00	$\lambda/10$	-	5.00	Enhanced Aluminum (250-700nm)	$R_{avg} > 89\%$ @ 250 - 450nm $R_{avg} > 85\%$ @ 250 - 700nm	#84-421	₹9,731 Volume Pricing	5 In Stock
30.00	$\lambda/10$	-	5.00	Protected Gold (700-10000nm)	$R_{avg} > 96\%$ @ 700 - 2000nm $R_{avg} > 96\%$ @ 2000 - 10,000nm	#84-431	₹13,235 Volume Pricing	14 In Stock
30.00	$\lambda/10$	-	5.00	Protected Silver (450-10000nm)	$R_{avg} > 98\%$ @ 450 - 800nm $R_{avg} > 98.5\%$ @ 2000 - 10,000nm	#84-441	₹10,510 Volume Pricing	Contact Us
30.00	$\lambda/10$	-	5.00	UV Enhanced Silver (350 - 3,000nm)	$R_{avg} > 90\%$ @ 350 - 400nm $R_{avg} > 96\%$ @ 400 - 3,000nm	#70-238	₹11,288 Volume Pricing	13 In Stock
30.00	$\lambda/10$	-	5.00	Ultrafast-Enhanced Silver (600-1000nm)	$R_{avg} > 99\%$ @ 600 - 1000nm, 0° $R_s > 99\%$ @ 540 - 1000nm, 45° $R_p > 98.5\%$ @ ~730 - 870nm, 45°	#21-987	₹11,288 Volume Pricing	3 In Stock

30.00	$\lambda/10$	-	5.00	Ultrafast-Enhanced Silver (800-1150nm)	$R_{avg} > 99\% @ 850 - 1150nm, 0^\circ$ $R_s > 99\% @ 800 - 1150nm, 45^\circ$ $R_p > 98.5\% @ \sim 850 - 1100nm, 45^\circ$	#22-017	₹11,288 Volume Pricing	2 In Stock
-	$\lambda/10$	30.0 x 30.0	5.00	Enhanced Aluminum (450-650nm)	$R_{avg} > 95\% @ 450 - 650nm$	#84-412	₹9,731 Volume Pricing	20+ In Stock
-	$\lambda/10$	30.0 x 30.0	5.00	Enhanced Aluminum (250-700nm)	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	#84-422	₹9,731 Volume Pricing	Contact Us
-	$\lambda/10$	30.0 x 30.0	5.00	Protected Gold (700-10000nm)	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	#84-432	₹13,235 Volume Pricing	2 In Stock
-	$\lambda/10$	30.0 x 30.0	5.00	Protected Silver (450-10000nm)	$R_{avg} > 98\% @ 450 - 800nm$ $R_{avg} > 98.5\% @ 2000 - 10,000nm$	#84-442	₹10,510 Volume Pricing	1 In Stock
-	$\lambda/10$	30.0 x 30.0	5.00	Ultrafast-Enhanced Silver (600-1000nm)	$R_{avg} > 99\% @ 600 - 1000nm, 0^\circ$ $R_s > 99\% @ 540 - 1000nm, 45^\circ$ $R_p > 98.5\% @ \sim 730 - 870nm, 45^\circ$	#22-000	₹11,288 Volume Pricing	1 In Stock
35.00	$\lambda/10$	-	5.00	Enhanced Aluminum (450-650nm)	$R_{avg} > 95\% @ 450 - 650nm$	#84-413	₹10,899 Volume Pricing	5 In Stock
35.00	$\lambda/10$	-	5.00	Enhanced Aluminum (250-700nm)	$R_{avg} > 89\% @ 250 - 450nm$ $R_{avg} > 85\% @ 250 - 700nm$	#84-423	₹10,899 Volume Pricing	5 In Stock
35.00	$\lambda/10$	-	5.00	Protected Gold (700-10000nm)	$R_{avg} > 96\% @ 700 - 2000nm$ $R_{avg} > 96\% @ 2000 - 10,000nm$	#84-433	₹14,013 Volume Pricing	Contact Us

35.00	$\lambda/10$	-	5.00	Protected Silver (450-10000nm)	$R_{avg} > 98\%$ @ 450 - 800nm $R_{avg} > 98.5\%$ @ 2000 - 10,000nm	#84-443	₹12,845 Volume Pricing	10 In Stock
35.00	$\lambda/10$	-	5.00	UV Enhanced Silver (350 - 3,000nm)	$R_{avg} > 90\%$ @ 350 - 400nm $R_{avg} > 96\%$ @ 400 - 3,000nm	#70-239	₹13,624 Volume Pricing	10 In Stock
35.00	$\lambda/10$	-	5.00	Ultrafast-Enhanced Silver (600-1000nm)	$R_{avg} > 99\%$ @ 600 - 1000nm, 0° $R_s > 99\%$ @ 540 - 1000nm, 45° $R_p > 98.5\%$ @ ~730 - 870nm, 45°	#21-988	₹13,235 Volume Pricing	7 In Stock
-	$\lambda/10$	25.0 x 35.0	5.00	Enhanced Aluminum (450-650nm)	$R_{avg} > 95\%$ @ 450 - 650nm	#25-546	₹10,899 Volume Pricing	4 In Stock
-	$\lambda/10$	25.0 x 35.0	5.00	Enhanced Aluminum (250-700nm)	$R_{avg} > 89\%$ @ 250 - 450nm $R_{avg} > 85\%$ @ 250 - 700nm	#25-547	₹10,899 Volume Pricing	1 In Stock
-	$\lambda/10$	25.0 x 35.0	5.00	Protected Gold (700-10000nm)	$R_{avg} > 96\%$ @ 700 - 2000nm $R_{avg} > 96\%$ @ 2000 - 10,000nm	#25-548	₹14,013 Volume Pricing	14 In Stock
-	$\lambda/10$	35.0 x 35.0	5.00	Ultrafast-Enhanced Silver (800-1150nm)	$R_{avg} > 99\%$ @ 850 - 1150nm, 0° $R_s > 99\%$ @ 800 - 1150nm, 45° $R_p > 98.5\%$ @ ~850 - 1100nm, 45°	#22-031	₹13,235 Volume Pricing	5 In Stock
35.00	$\lambda/10$	-	5.00	Ultrafast-Enhanced Silver (800-1150nm)	$R_{avg} > 99\%$ @ 850 - 1150nm, 0° $R_s > 99\%$ @ 800 - 1150nm, 45° $R_p > 98.5\%$ @ ~850 - 1100nm, 45°	#22-018	₹13,235 Volume Pricing	4 In Stock
-	$\lambda/10$	35.0 x 35.0	5.00	Enhanced Aluminum (450-650nm)	$R_{avg} > 95\%$ @ 450 - 650nm	#84-414	₹10,899 Volume Pricing	14 In Stock

-	$\lambda/10$	35.0 x 35.0	5.00	Enhanced Aluminum (250-700nm)	$R_{avg} > 89\%$ @ 250 - 450nm $R_{avg} > 85\%$ @ 250 - 700nm	#84-424	₹10,899 Volume Pricing	8 In Stock
-	$\lambda/10$	35.0 x 35.0	5.00	Protected Gold (700-10000nm)	$R_{avg} > 96\%$ @ 700 - 2000nm $R_{avg} > 96\%$ @ 2000 - 10,000nm	#84-434	₹14,013 Volume Pricing	1 In Stock
-	$\lambda/10$	35.0 x 35.0	5.00	Protected Silver (450-10000nm)	$R_{avg} > 98\%$ @ 450 - 800nm $R_{avg} > 98.5\%$ @ 2000 - 10,000nm	#84-444	₹12,845 Volume Pricing	20+ In Stock
-	$\lambda/10$	35.0 x 35.0	5.00	Ultrafast-Enhanced Silver (600-1000nm)	$R_{avg} > 99\%$ @ 600 - 1000nm, 0° $R_s > 99\%$ @ 540 - 1000nm, 45° $R_p > 98.5\%$ @ ~730 - 870nm, 45°	#22-001	₹13,235 Volume Pricing	4 In Stock
38.10	$\lambda/10$	-	6.35	Enhanced Aluminum (450-650nm)	$R_{avg} > 95\%$ @ 450 - 650nm	#39-217	₹11,678 Volume Pricing	3 In Stock
38.10	$\lambda/10$	-	6.35	Enhanced Aluminum (250-700nm)	$R_{avg} > 89\%$ @ 250 - 450nm $R_{avg} > 85\%$ @ 250 - 700nm	#39-216	₹11,678 Volume Pricing	20+ In Stock
38.10	$\lambda/10$	-	6.35	Protected Gold (700-10000nm)	$R_{avg} > 96\%$ @ 700 - 2000nm $R_{avg} > 96\%$ @ 2000 - 10,000nm	#39-214	₹15,492 Volume Pricing	1 In Stock
38.10	$\lambda/10$	-	6.35	Protected Silver (450-10000nm)	$R_{avg} > 98\%$ @ 450 - 800nm $R_{avg} > 98.5\%$ @ 2000 - 10,000nm	#39-215	₹14,402 Volume Pricing	3 In Stock
40.00	$\lambda/10$	-	5.00	Enhanced Aluminum (450-650nm)	$R_{avg} > 95\%$ @ 450 - 650nm	#64-017	₹11,678 Volume Pricing	20+ In Stock
40.00	$\lambda/10$	-	5.00	Enhanced Aluminum (250-700nm)	$R_{avg} > 89\%$ @ 250 - 450nm $R_{avg} > 85\%$ @ 250 - 700nm	#68-317	₹11,678 Volume Pricing	5 In Stock

40.00	$\lambda/10$	-	5.00	Protected Gold (700-10000nm)	$R_{avg} > 96\%$ @ 700 - 2000nm $R_{avg} > 96\%$ @ 2000 - 10,000nm	#64-031	₹15,492 Volume Pricing	1 In Stock
40.00	$\lambda/10$	-	5.00	Protected Silver (450-10000nm)	$R_{avg} > 98\%$ @ 450 - 800nm $R_{avg} > 98.5\%$ @ 2000 - 10,000nm	#68-331	₹14,402 Volume Pricing	20+ In Stock
40.00	$\lambda/10$	-	5.00	UV Enhanced Silver (350 - 3,000nm)	$R_{avg} > 90\%$ @ 350 - 400nm $R_{avg} > 96\%$ @ 400 - 3,000nm	#70-240	₹15,570 Volume Pricing	12 In Stock
40.00	$\lambda/10$	-	5.00	Ultrafast-Enhanced Silver (600-1000nm)	$R_{avg} > 99\%$ @ 600 - 1000nm, 0° $R_s > 99\%$ @ 540 - 1000nm, 45° $R_p > 98.5\%$ @ ~730 - 870nm, 45°	#21-990	₹14,792 Volume Pricing	5 In Stock
40.00	$\lambda/10$	-	5.00	Ultrafast-Enhanced Silver (800-1150nm)	$R_{avg} > 99\%$ @ 850 - 1150nm, 0° $R_s > 99\%$ @ 800 - 1150nm, 45° $R_p > 98.5\%$ @ ~850 - 1100nm, 45°	#22-020	₹14,792 Volume Pricing	3 In Stock
-	$\lambda/10$	40.0 x 40.0	5.00	Enhanced Aluminum (450-650nm)	$R_{avg} > 95\%$ @ 450 - 650nm	#64-018	₹11,678 Volume Pricing	9 In Stock
-	$\lambda/10$	40.0 x 40.0	5.00	Enhanced Aluminum (250-700nm)	$R_{avg} > 89\%$ @ 250 - 450nm $R_{avg} > 85\%$ @ 250 - 700nm	#68-318	₹11,678 Volume Pricing	2 In Stock
-	$\lambda/10$	40.0 x 40.0	5.00	Protected Gold (700-10000nm)	$R_{avg} > 96\%$ @ 700 - 2000nm $R_{avg} > 96\%$ @ 2000 - 10,000nm	#64-032	₹15,492 Volume Pricing	11 In Stock
-	$\lambda/10$	40.0 x 40.0	5.00	Protected Silver (450-10000nm)	$R_{avg} > 98\%$ @ 450 - 800nm $R_{avg} > 98.5\%$ @ 2000 - 10,000nm	#68-332	₹14,402 Volume Pricing	12 In Stock

50.00	$\lambda/10$	-	5.00	Enhanced Aluminum (450-650nm)	$R_{avg} > 95\%$ @ 450 - 650nm	#64-019	₹12,845 Volume Pricing	20+ In Stock
50.00	$\lambda/10$	-	5.00	Enhanced Aluminum (250-700nm)	$R_{avg} > 89\%$ @ 250 - 450nm $R_{avg} > 85\%$ @ 250 - 700nm	#68-319	₹12,845 Volume Pricing	Contact Us
50.00	$\lambda/10$	-	5.00	Protected Gold (700-10000nm)	$R_{avg} > 96\%$ @ 700 - 2000nm $R_{avg} > 96\%$ @ 2000 - 10,000nm	#64-033	₹17,127 Volume Pricing	2 In Stock
50.00	$\lambda/10$	-	5.00	Protected Silver (450-10000nm)	$R_{avg} > 98\%$ @ 450 - 800nm $R_{avg} > 98.5\%$ @ 2000 - 10,000nm	#68-333	₹15,959 Volume Pricing	20+ In Stock
50.00	$\lambda/10$	-	5.00	UV Enhanced Silver (350 - 3,000nm)	$R_{avg} > 90\%$ @ 350 - 400nm $R_{avg} > 96\%$ @ 400 - 3,000nm	#70-241	₹18,295 Volume Pricing	14 In Stock
50.00	$\lambda/10$	-	5.00	Ultrafast-Enhanced Silver (600-1000nm)	$R_{avg} > 99\%$ @ 600 - 1000nm, 0° $R_s > 99\%$ @ 540 - 1000nm, 45° $R_p > 98.5\%$ @ ~730 - 870nm, 45°	#21-991	₹16,349 Volume Pricing	8 In Stock
50.00	$\lambda/10$	-	5.00	Ultrafast-Enhanced Silver (800-1150nm)	$R_{avg} > 99\%$ @ 850 - 1150nm, 0° $R_s > 99\%$ @ 800 - 1150nm, 45° $R_p > 98.5\%$ @ ~850 - 1100nm, 45°	#22-021	₹16,349 Volume Pricing	5 In Stock
-	$\lambda/10$	50.0 x 50.0	5.00	Enhanced Aluminum (450-650nm)	$R_{avg} > 95\%$ @ 450 - 650nm	#64-020	₹12,845 Volume Pricing	13 In Stock
-	$\lambda/10$	50.0 x 50.0	5.00	Enhanced Aluminum (250-700nm)	$R_{avg} > 89\%$ @ 250 - 450nm $R_{avg} > 85\%$ @ 250 - 700nm	#68-320	₹12,845 Volume Pricing	20+ In Stock
-	$\lambda/10$	50.0 x 50.0	5.00	Protected Gold (700-10000nm)	$R_{avg} > 96\%$ @ 700 - 2000nm $R_{avg} > 96\%$ @ 2000 - 10,000nm	#64-034	₹17,127 Volume Pricing	6 In Stock

-	$\lambda/10$	50.0 x 50.0	5.00	Protected Silver (450-10000nm)	$R_{avg} >98\%$ @ 450 - 800nm $R_{avg} >98.5\%$ @ 2000 - 10,000nm	#68-334	₹15,959 Volume Pricing	9 In Stock
50.80	$\lambda/10$	-	9.53	Enhanced Aluminum (450-650nm)	$R_{avg} >95\%$ @ 450 - 650nm	#39-224	₹12,845 Volume Pricing	5 In Stock
50.80	$\lambda/10$	-	9.53	Enhanced Aluminum (250-700nm)	$R_{avg} >89\%$ @ 250 - 450nm $R_{avg} >85\%$ @ 250 - 700nm	#39-223	₹12,845 Volume Pricing	7 In Stock
50.80	$\lambda/10$	-	9.53	Protected Gold (700-10000nm)	$R_{avg} >96\%$ @ 700 - 2000nm $R_{avg} >96\%$ @ 2000 - 10,000nm	#39-221	₹17,127 Volume Pricing	3 In Stock
50.80	$\lambda/10$	-	9.53	Protected Silver (450-10000nm)	$R_{avg} >98\%$ @ 450 - 800nm $R_{avg} >98.5\%$ @ 2000 - 10,000nm	#39-222	₹15,959 Volume Pricing	Contact Us
75.00	$\lambda/10$	-	7.50	Enhanced Aluminum (450-650nm)	$R_{avg} >95\%$ @ 450 - 650nm	#84-415	₹26,469 Volume Pricing	8 In Stock
75.00	$\lambda/10$	-	7.50	Enhanced Aluminum (250-700nm)	$R_{avg} >89\%$ @ 250 - 450nm $R_{avg} >85\%$ @ 250 - 700nm	#84-425	₹26,469 Volume Pricing	15 In Stock
75.00	$\lambda/10$	-	7.50	Protected Gold (700-10000nm)	$R_{avg} >96\%$ @ 700 - 2000nm $R_{avg} >96\%$ @ 2000 - 10,000nm	#84-435	₹34,254 Volume Pricing	8 In Stock
75.00	$\lambda/10$	-	7.50	Protected Silver (450-10000nm)	$R_{avg} >98\%$ @ 450 - 800nm $R_{avg} >98.5\%$ @ 2000 - 10,000nm	#84-445	₹31,919 Volume Pricing	20+ In Stock
-	$\lambda/10$	75.0 x 75.0	7.50	Enhanced Aluminum (450-650nm)	$R_{avg} >95\%$ @ 450 - 650nm	#84-416	₹26,469 Volume Pricing	20+ In Stock
-	$\lambda/10$	75.0 x 75.0	7.50	Enhanced Aluminum (250-700nm)	$R_{avg} >89\%$ @ 250 - 450nm $R_{avg} >85\%$ @ 250 - 700nm	#84-426	₹26,469 Volume Pricing	7 In Stock

-	$\lambda/10$	75.0 x 75.0	7.50	Protected Gold (700-10000nm)	$R_{avg} >96\%$ @ 700 - 2000nm $R_{avg} >96\%$ @ 2000 - 10,000nm	#84-436	₹34,254 Volume Pricing	2 In Stock
-	$\lambda/10$	75.0 x 75.0	7.50	Protected Silver (450-10000nm)	$R_{avg} >98\%$ @ 450 - 800nm $R_{avg} >98.5\%$ @ 2000 - 10,000nm	#84-446	₹31,919 Volume Pricing	10 In Stock
100.00	$\lambda/10$	-	10.00	Enhanced Aluminum (450-650nm)	$R_{avg} >95\%$ @ 450 - 650nm	#84-417	₹38,847 Volume Pricing	9 In Stock
100.00	$\lambda/10$	-	10.00	Enhanced Aluminum (250-700nm)	$R_{avg} >89\%$ @ 250 - 450nm $R_{avg} >85\%$ @ 250 - 700nm	#84-427	₹38,847 Volume Pricing	13 In Stock
100.00	$\lambda/10$	-	10.00	Protected Gold (700-10000nm)	$R_{avg} >96\%$ @ 700 - 2000nm $R_{avg} >96\%$ @ 2000 - 10,000nm	#84-437	₹56,052 Volume Pricing	20+ In Stock
100.00	$\lambda/10$	-	10.00	Protected Silver (450-10000nm)	$R_{avg} >98\%$ @ 450 - 800nm $R_{avg} >98.5\%$ @ 2000 - 10,000nm	#84-447	₹50,603 Volume Pricing	10 In Stock
-	$\lambda/10$	100.0 x 100.0	10.00	Enhanced Aluminum (450-650nm)	$R_{avg} >95\%$ @ 450 - 650nm	#84-418	₹38,847 Volume Pricing	4 In Stock
-	$\lambda/10$	100.0 x 100.0	10.00	Enhanced Aluminum (250-700nm)	$R_{avg} >89\%$ @ 250 - 450nm $R_{avg} >85\%$ @ 250 - 700nm	#84-428	₹38,847 Volume Pricing	5 In Stock
-	$\lambda/10$	100.0 x 100.0	10.00	Protected Gold (700-10000nm)	$R_{avg} >96\%$ @ 700 - 2000nm $R_{avg} >96\%$ @ 2000 - 10,000nm	#84-438	₹56,052 Volume Pricing	4 In Stock
-	$\lambda/10$	100.0 x 100.0	10.00	Protected Silver (450-10000nm)	$R_{avg} >98\%$ @ 450 - 800nm $R_{avg} >98.5\%$ @ 2000 - 10,000nm	#84-448	₹50,603 Volume Pricing	20+ In Stock
5.00	$\lambda/10$	-	1.00	Enhanced Aluminum (450-650nm)	$R_{avg} >95\%$ @ 450 - 650nm	#26-094	₹6,189 Volume Pricing	Contact Us

5.00	$\lambda/10$	-	1.00	Enhanced Aluminum (250-700nm)	Ravg >89% @ 250 - 450nm Ravg >85% @ 250 - 700nm	#26-098	₹6,189 Volume Pricing	2 In Stock
5.00	$\lambda/10$	-	1.00	Protected Gold (700-10000nm)	Ravg >96% @ 700 - 2000nm Ravg >96% @ 2000 - 10,000nm	#26-099	₹7,707 Volume Pricing	3 In Stock
5.00	$\lambda/10$	-	1.00	Protected Silver (450-10000nm)	Ravg >98% @ 450 - 2000nm Ravg >98% @ 2000 - 10,000nm	#26-100	₹7,396 Volume Pricing	Contact Us
10.00	$\lambda/10$	-	1.00	Enhanced Aluminum (450-650nm)	Ravg >95% @ 450 - 650nm	#26-101	₹6,189 Volume Pricing	1 In Stock
10.00	$\lambda/10$	-	1.00	Enhanced Aluminum (250-700nm)	Ravg >89% @ 250 - 450nm Ravg >85% @ 250 - 700nm	#26-102	₹6,189 Volume Pricing	6 In Stock
10.00	$\lambda/10$	-	1.00	Protected Gold (700-10000nm)	Ravg >96% @ 700 - 2000nm Ravg >96% @ 2000 - 10,000nm	#26-103	₹7,707 Volume Pricing	4 In Stock
10.00	$\lambda/10$	-	1.00	Protected Silver (450-10000nm)	Ravg >98% @ 450 - 2000nm Ravg >98% @ 2000 - 10,000nm	#26-104	₹7,396 Volume Pricing	5 In Stock
12.50	$\lambda/10$	-	1.50	Enhanced Aluminum (450-650nm)	Ravg >95% @ 450 - 650nm	#26-105	₹6,189 Volume Pricing	1 In Stock
12.50	$\lambda/10$	-	1.50	Enhanced Aluminum (250-700nm)	Ravg >89% @ 250 - 450nm Ravg >85% @ 250 - 700nm	#26-364	₹6,189 Volume Pricing	4 In Stock
12.50	$\lambda/10$	-	1.50	Protected Gold (700-10000nm)	Ravg >96% @ 700 - 2000nm Ravg >96% @ 2000 - 10,000nm	#26-365	₹7,707 Volume Pricing	13 In Stock
12.50	$\lambda/10$	-	1.50	Protected Silver (450-10000nm)	Ravg >98% @ 450 - 2000nm Ravg >98% @ 2000 - 10,000nm	#26-366	₹7,396 Volume Pricing	Contact Us
15.00	$\lambda/10$	-	1.50	Enhanced Aluminum (450-650nm)	Ravg >95% @ 450 - 650nm	#26-367	₹6,656 Volume Pricing	5 In Stock

15.00	λ/10	-	1.50	Enhanced Aluminum (250-700nm)	Ravg >89% @ 250 - 450nm Ravg >85% @ 250 - 700nm	#26-368	₹6,656 Volume Pricing	Contact Us
15.00	λ/10	-	1.50	Protected Gold (700-10000nm)	Ravg >96% @ 700 - 2000nm Ravg >96% @ 2000 - 10,000nm	#26-369	₹8,174 Volume Pricing	2 In Stock
15.00	λ/10	-	1.50	Protected Silver (450-10000nm)	Ravg >98% @ 450 - 2000nm Ravg >98% @ 2000 - 10,000nm	#26-370	₹7,980 Volume Pricing	Contact Us
20.00	λ/10	-	2.00	Enhanced Aluminum (450-650nm)	Ravg >95% @ 450 - 650nm	#26-371	₹7,201 Volume Pricing	1 In Stock
20.00	λ/10	-	2.00	Enhanced Aluminum (250-700nm)	Ravg >89% @ 250 - 450nm Ravg >85% @ 250 - 700nm	#26-372	₹7,201 Volume Pricing	1 In Stock
20.00	λ/10	-	2.00	Protected Gold (700-10000nm)	Ravg >96% @ 700 - 2000nm Ravg >96% @ 2000 - 10,000nm	#26-373	₹8,953 Volume Pricing	5 In Stock
20.00	λ/10	-	2.00	Protected Silver (450-10000nm)	Ravg >98% @ 450 - 2000nm Ravg >98% @ 2000 - 10,000nm	#26-374	₹8,369 Volume Pricing	Contact Us
25.00	λ/10	-	3.00	Enhanced Aluminum (450-650nm)	Ravg >95% @ 450 - 650nm	#26-375	₹7,590 Volume Pricing	1 In Stock
25.00	λ/10	-	3.00	Enhanced Aluminum (250-700nm)	Ravg >89% @ 250 - 450nm Ravg >85% @ 250 - 700nm	#26-376	₹7,590 Volume Pricing	5 In Stock
25.00	λ/10	-	3.00	Protected Gold (700-10000nm)	Ravg >96% @ 700 - 2000nm Ravg >96% @ 2000 - 10,000nm	#26-377	₹10,510 Volume Pricing	2 In Stock
25.00	λ/10	-	3.00	Protected Silver (450-10000nm)	Ravg >98% @ 450 - 2000nm Ravg >98% @ 2000 - 10,000nm	#26-378	₹9,731 Volume Pricing	2 In Stock
30.00	λ/10	-	3.00	Enhanced Aluminum (450-650nm)	Ravg >95% @ 450 - 650nm	#26-379	₹9,731 Volume Pricing	1 In Stock

30.00	$\lambda/10$	-	3.00	Enhanced Aluminum (250-700nm)	R _{avg} >89% @ 250 - 450nm R _{avg} >85% @ 250 - 700nm	#26-380	₹9,731 Volume Pricing	4 In Stock
30.00	$\lambda/10$	-	3.00	Protected Gold (700-10000nm)	R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm	#26-381	₹13,235 Volume Pricing	3 In Stock
30.00	$\lambda/10$	-	3.00	Protected Silver (450-10000nm)	R _{avg} >98% @ 450 - 2000nm R _{avg} >98% @ 2000 - 10,000nm	#26-382	₹10,510 Volume Pricing	3 In Stock
125.00	$\lambda/10$	-	12.50	Enhanced Aluminum (450-650nm)	R _{avg} >95% @ 450 - 650nm	#70-924	₹66,173 Volume Pricing	Contact Us
125.00	$\lambda/10$	-	12.50	Enhanced Aluminum (250-700nm)	R _{avg} >89% @ 250 - 450nm R _{avg} >85% @ 250 - 700nm	#70-925	₹66,173 Volume Pricing	2 In Stock
125.00	$\lambda/10$	-	12.50	Protected Gold (700-10000nm)	R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm	#70-926	₹75,904 Volume Pricing	1 In Stock
125.00	$\lambda/10$	-	12.50	Protected Silver (450-10000nm)	R _{avg} >98% @ 450 - 2000nm R _{avg} >98% @ 2000 - 10,000nm	#70-927	₹72,011 Volume Pricing	2 In Stock
-	$\lambda/10$	125 x 125	12.50	Enhanced Aluminum (450-650nm)	R _{avg} >95% @ 450 - 650nm	#70-928	₹66,173 Volume Pricing	3 In Stock
-	$\lambda/10$	125 x 125	12.50	Enhanced Aluminum (250-700nm)	R _{avg} >89% @ 250 - 450nm R _{avg} >85% @ 250 - 700nm	#70-929	₹66,173 Volume Pricing	1 In Stock
-	$\lambda/10$	125 x 125	12.50	Protected Gold (700-10000nm)	R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm	#70-930	₹75,904 Volume Pricing	4 In Stock
-	$\lambda/10$	125 x 125	12.50	Protected Silver (450-10000nm)	R _{avg} >98% @ 450 - 2000nm R _{avg} >98% @ 2000 - 10,000nm	#70-931	₹72,011 Volume Pricing	8 In Stock

150.00	$\lambda/10$	-	15.00	Enhanced Aluminum (450-650nm)	$R_{avg} > 95\%$ @ 450 - 650nm	#70-932	₹1,01,205 Volume Pricing	2 In Stock
150.00	$\lambda/10$	-	15.00	Enhanced Aluminum (250-700nm)	$R_{avg} > 89\%$ @ 250 - 450nm $R_{avg} > 85\%$ @ 250 - 700nm	#70-933	₹1,01,205 Volume Pricing	5 In Stock
150.00	$\lambda/10$	-	15.00	Protected Gold (700-10000nm)	$R_{avg} > 96\%$ @ 700 - 2000nm $R_{avg} > 96\%$ @ 2000 - 10,000nm	#70-934	₹1,16,775 Volume Pricing	3 In Stock
150.00	$\lambda/10$	-	15.00	Protected Silver (450-10000nm)	$R_{avg} > 98\%$ @ 450 - 2000nm $R_{avg} > 98\%$ @ 2000 - 10,000nm	#70-935	₹1,08,990 Volume Pricing	Contact Us
-	$\lambda/10$	150 x 150	15.00	Enhanced Aluminum (450-650nm)	$R_{avg} > 95\%$ @ 450 - 650nm	#70-936	₹1,01,205 Volume Pricing	3 In Stock
-	$\lambda/10$	150 x 150	15.00	Enhanced Aluminum (250-700nm)	$R_{avg} > 89\%$ @ 250 - 450nm $R_{avg} > 85\%$ @ 250 - 700nm	#70-937	₹1,01,205 Volume Pricing	1 In Stock
-	$\lambda/10$	150 x 150	15.00	Protected Gold (700-10000nm)	$R_{avg} > 96\%$ @ 700 - 2000nm $R_{avg} > 96\%$ @ 2000 - 10,000nm	#70-938	₹1,16,775 Volume Pricing	1 In Stock
-	$\lambda/10$	150 x 150	15.00	Protected Silver (450-10000nm)	$R_{avg} > 98\%$ @ 450 - 2000nm $R_{avg} > 98\%$ @ 2000 - 10,000nm	#70-939	₹1,08,990 Volume Pricing	Contact Us



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038

Phone: 1-800-363-1992 :

www.edmundoptics.com