

[All Products](#) / [Lights and Illumination](#) / [Machine Vision Lighting](#) / [Inline Lights](#)

Advanced Illumination In-Line Lights See More by [Advanced Illumination](#)



- Compatible with 8mm or 1/4" (0.312") Fiber Illumination Ports
- Multiple Versions Offered

Common Specifications

General			
LED Lifetime (hours):	50,000	Number of LEDs:	1 High Brightness
Type of Illumination:	LED Illuminator	Manufacturer:	Advanced Illumination
Geometry:	Spot Light		

Physical & Mechanical Properties	
Weight (g):	42.5

Optical Properties	
Light Distribution (%):	±10

Hardware & Interface Connectivity			
Connector:	Flying Leads		
Power Supply:	Power Supply Required and Sold Separately: USA: #66-855 Europe: #66-855 Japan: #89-513 Korea: #33-773 China: #66-855	Length of Cable (m):	1.5

Environmental & Durability Factors	
Operating Temperature (°C):	0 to 60

Technical Information

Products

Color	Wavelength (nm)	Stock Number	Price	Buy
White	-	#66-861	₹47,700	5 In Stock
White	-	#83-302	₹59,400	Contact Us
Blue	470.00	#66-862	₹47,700	1 In Stock
Blue	470.00	#83-303	₹59,400	Contact Us
Green	530.00	#66-863	₹47,700	1 In Stock
Green	530.00	#83-304	₹59,400	Contact Us
Yellow	590.00	#66-864	₹47,700	Contact Us
Yellow	590.00	#83-305	₹59,400	Contact Us
Red	625.00	#66-865	₹47,700	1 In Stock
Red	625.00	#83-306	₹59,400	Contact Us



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038

Phone: 1-800-363-1992 :

www.edmundoptics.com