

[All Products](#) /
 [Optics](#) /
 [Polarization Optics](#) /
 [Linear Polarizers](#) /
 [Thin Film Polarizers](#)

TECHSPEC® Thin Film Laser Line Polarizers



- High Extinction Ratio of 10,000:1
- 45° Angle of Incidence
- Available for Nd:YAG Harmonics and HeNe Wavelengths

Common Specifications

Physical & Mechanical Properties

Thickness (mm):	6.00 ±0.25	Dimensional Tolerance (mm):	+0.00/-0.25
Construction:	Thin Film Dielectric	Clear Aperture (%):	90

Optical Properties

Angle of Incidence (°):	45 ±2	Extinction Ratio:	10,000:1
Substrate:	Fused Silica (Corning 7980)	Surface Quality:	40-20
Transmission (%):	>98 (P-Polarization)	Transmitted Wavefront, P-V:	λ/4 @ 633nm
Damage Threshold, By Design:	2 J/cm ² @ 532nm, 10ns, S or P Polarization		

Technical Information

Products

DWL (nm)	Extinction Ratio	CA (mm)	Surface Quality	Dia. (mm)	CA (%)	Stock Number	Price	Buy
355	10,000:1	22.5	40-20	25.00	90	#86-707	₹40,482 Volume Pricing	13 In Stock
355	10,000:1	45.00	40-20	50.00	90	#86-708	₹78,629 Volume Pricing	3 In Stock
532	10,000:1	11.25	40-20	12.50	90	#86-709	₹23,744 Volume Pricing	1 In Stock
532	10,000:1	22.50	40-20	25.00	90	#86-710	₹40,482 Volume Pricing	2 In Stock
532	10,000:1	45.00	40-20	50.00	90	#86-711	₹78,629 Volume Pricing	5 In Stock
633	10,000:1	22.50	40-20	25.00	90	#86-713	₹40,482 Volume Pricing	5 In Stock
633	10,000:1	45.00	40-20	50.00	90	#86-714	₹78,629 Volume Pricing	1 In Stock
1064	10,000:1	22.50	40-20	25.00	90	#86-716	₹40,482 Volume Pricing	Contact Us
1064	10,000:1	45.00	40-20	50.00	90	#86-717	₹78,629 Volume Pricing	3 In Stock



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038

Phone: 1-800-363-1992 :

www.edmundoptics.com