

[All Products](#) / [Optics](#) / [Optical Filters](#) / [Bandpass Filters](#)

TECHSPEC®

Multi-Band Fluorescence Bandpass Filters



- Multiple Pass Bands on a Single Filter
- High Peak Transmission, Excellent Blocking
- Ideal for Simultaneous Viewing of Multiple Fluorophores
- For Optimal Performance Pair with [Multi-Edge Fluorescence Dichroic Filters](#)

Common Specifications

Physical & Mechanical Properties				
Construction:		Mounted in Black Anodized Ring	Physical Durability:	Adhesion per MIL-PRF-13830B, Section C.4.5.12 Moderate abrasion per MIL-PRF-13830B, Section C.4.5.11 Cleaning per MIL-C-48497A Section 4.5.4.2
Substrate Thickness (mm):		2.00 ±0.25		
Optical Properties				
Angle of Incidence (°):		0		
Optical Density OD (Average):		≥6.0	Substrate:	Fused Silica (Corning 7980)
Coating:		Hard Coated	Surface Quality:	60-40
Transmission (%):		>90	Blocking Wavelength Range (nm):	250 - 1100
Threading & Mounting				
Mount Thickness (mm):		3.5 ±0.1		
Environmental & Durability Factors				
Environmental Durability:			Humidity per MIL-STD-810H, Section 507.6 Temperature per MIL-STD-810H, Section 501.7 and 502.7	

Technical Information



All mounted TECHSPEC® Optical Filters have an arrow on the side of the mount that points to the filter-coated surface for quick reference. Filter oriented such that arrow points to filter coated surface S1. Anti-reflective (AR) coating is applied to S2.

Products

Dia. (mm)	Multi-Band Center Wavelengths (nm)	Minimum Transmission (%)	Compatible Fluorophore	Blocking Wavelength Range (nm)	Substrate Thickness (mm)	Stock Number	Price	Buy
12.50	433, 530	-	DAPI & FITC Emission	250 - 1100	2.00	#87-232	₹25,613 Volume Pricing	14 In Stock
25.00	433, 530	-	DAPI & FITC Emission	250 - 1100	2.00	#87-240	₹33,476 Volume Pricing	Contact Us
50.00	433, 530	-	DAPI & FITC Emission	250 - 1100	2.00	#87-248	₹78,473 Volume Pricing	5 In Stock
12.50	512, 630	-	GFP & TRITC Emission	250 - 1100	2.00	#87-233	₹25,613 Volume Pricing	1 In Stock
25.00	512, 630	-	GFP & TRITC Emission	250 - 1100	2.00	#87-241	₹33,476 Volume Pricing	1 In Stock
50.00	512, 630	-	GFP & TRITC Emission	250 - 1100	2.00	#87-249	₹78,473 Volume Pricing	1 In Stock
12.50	432, 517, 615	-	DAPI/FITC/TRITC Emission	250 - 1100	2.00	#87-236	₹27,248 Volume Pricing	1 In Stock
25.00	432, 517, 615	-	DAPI/FITC/TRITC Emission	250 - 1100	2.00	#87-244	₹36,745 Volume Pricing	1 In Stock
50.00	432, 517, 615	-	DAPI/FITC/TRITC Emission	250 - 1100	2.00	#87-252	₹87,581 Volume Pricing	3 In Stock
12.50	457, 530, 628	-	DAPI/FITC/Texas Red Emission	250 - 1100	2.00	#87-237	₹27,248 Volume Pricing	1 In Stock
25.00	457, 530, 628	-	DAPI/FITC/Texas Red Emission	250 - 1100	2.00	#87-245	₹36,745 Volume Pricing	7 In Stock
50.00	457, 530, 628	-	DAPI/FITC/Texas Red Emission	250 - 1100	2.00	#87-253	₹87,581 Volume Pricing	1 In Stock
12.50	464, 542, 639	-	CFP/YFP/Texas Red Emission	250 - 1100	2.00	#87-238	₹27,248 Volume Pricing	1 In Stock
25.00	464, 542, 639	-	CFP/YFP/Texas Red Emission	250 - 1100	2.00	#87-246	₹36,745 Volume Pricing	3 In Stock
50.00	464, 542, 639	-	CFP/YFP/Texas Red Emission	250 - 1100	2.00	#87-254	₹87,581 Volume Pricing	1 In Stock
12.50	440, 521, 607, 700	-	DAPI/FITC/TRITC/CY5 Emission	250 - 1100	2.00	#87-239	₹30,673 Volume Pricing	2 In Stock
25.00	440, 521, 607, 700	-	DAPI/FITC/TRITC/CY5 Emission	250 - 1100	2.00	#87-247	₹41,261 Volume Pricing	3 In Stock
50.00	440, 521, 607, 700	-	DAPI/FITC/TRITC/CY5 Emission	250 - 1100	2.00	#87-255	₹99,103 Volume Pricing	1 In Stock
12.50	577, 690	-	CY3 & CY5 Emission	250 - 1100	2.00	#87-235	₹25,613 Volume Pricing	10 In Stock
25.00	577, 690	-	CY3 & CY5 Emission	250 - 1100	2.00	#87-243	₹33,476 Volume Pricing	3 In Stock



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038

Phone: 1-800-363-1992 :

www.edmundoptics.com