

[All Products](#) / [Lasers](#) / [Laser Sources](#) / [Industrial and Pointing Lasers](#)

DPSS Pointing Lasers



- TTL Modulation up to 10kHz
- Transverse Mode TEM₀₀
- Blue, Green, Yellow, and IR Output Wavelengths
- TEC or Heatsink Required for Operation ([Sold Separately](#))



Common Specifications

Optical Properties

Spatial Mode: TEM₀₀

Environmental & Durability Factors

Operating Temperature (°C): 23 to 27

Technical Information

Products

Wavelength (nm)	Output Power (mW)	Beam Diameter (mm)	Beam Divergence (mrad)	Stock Number	Price	Buy
473.00	10	1.5	<1.5	#19-469	₹1,17,450 Volume Pricing	2 In Stock
520.00	1	3.5	<1	#29-130	₹30,330 Volume Pricing	2 In Stock
520.00	5	3.5	<1	#29-131	₹31,950 Volume Pricing	2 In Stock
520.00	25	3.5	<1	#29-133	₹48,150 Volume Pricing	1 In Stock
520.00	50	3.5	<1	#29-134	₹63,450 Volume Pricing	2 In Stock
532.00	1	1.0	<1	#37-026	₹30,330 Volume Pricing	16 In Stock
532.00	5	1.0	<1	#37-027	₹31,950 Volume Pricing	10 In Stock
532.00	10	1.0	<1	#37-028	₹33,390 Volume Pricing	1 In Stock
532.00	25	1.5	<1.5	#19-470	₹48,150 Volume Pricing	10 In Stock
532.00	80	1.5	<1.5	#19-471	₹63,450 Volume Pricing	7 In Stock
589.00	10	1.5	<1.5	#19-472	₹1,47,150 Volume Pricing	4 In Stock



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038

Phone: 1-800-363-1992 :

www.edmundoptics.com