

[All Products](#) / [Imaging Lenses](#) / [M12 Lenses \(S-Mount Lenses\)](#)

TECHSPEC® Liquid Lens M12 Lenses



- Up to 1/1.8", S-Mount Lens
- Up to 5 MegaPixels, 2.8 μ m Pixel Size Sensors
- Liquid Lens Provides Quick Autofocus
- 6mm to 16mm Focal Length

Common Specifications

General

Note: Separate driver not included. Electronic development kit [#28-773](#) recommended. When using a Maxim driver board (#12-247, #12-248, or #17-172) the jumper at ST2 **must** be removed before use to ensure optimal performance and product lifetime. Watch this [video](#) for more information.

Integrated Liquid Lens Model:

Corning® Varioptic® A-39N0

IR Cut Filter: No

Physical & Mechanical Properties

Iris Option: Fixed

Flange Distance (mm): 14.025

Optical Properties

Wavelength Range (nm): 400 - 700

Aperture (f/#): f/2.4

Coating Specification: $\lambda/4$ MgF₂ @ 550nm

Threading & Mounting

Mount: M12 x 0.5 (S-Mount)

Technical Information

Products

FL (mm)	Aperture (f/#)	Max. Sensor Format	WD (mm)	IR Cut Filter	Stock Number	Price	Buy
6.00	f/2.4	1/2"	100 - ∞	No	#37-521	₹26,796	10 to 12 days
8.00	f/2.4	1/2"	150 - ∞	No	#37-522	₹26,796	10 to 12 days
12.00	f/2.4	1/2"	150 - ∞	No	#37-523	₹26,796	Contact Us
16.00	f/2.4	1/1.8"	220 - ∞	No	#37-524	₹26,796	10 to 12 days



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038

Phone: 1-800-363-1992 :

www.edmundoptics.com