

[All Products](#) / [Optics](#) / [IBS \(Ion Beam Sputtering\) Coated Optics](#)

TECHSPEC® High Performance Nd:YAG Laser Line Mirrors



- Up to 99.98% Reflectivity
- Certified High Laser Damage Threshold at DWL up to 15 J/cm² @ 1064nm
- [Superpolished](#) Substrates Available with Parts per Million Level Scattering Performance
- Additional Sizes Coming Soon

Common Specifications

Physical & Mechanical Properties

Back Surface: Commercial Polish

Optical Properties

Coating Type: Dielectric

Substrate: [Fused Silica](#) (Corning 7980)

Technical Information

Products

Wavelength Range (nm)	DWL (nm)	Dia. (mm)	Thickness (mm)	AOI (°)	Stock Number	Price	Buy
-	355	25.40	6.35	45	#34-838	₹13,468 Volume Pricing	5 In Stock
-	532	25.40	6.35	45	#34-842	₹13,468 Volume Pricing	Contact Us
-	1064	6.35	4.00	45	#12-525	₹11,288 Volume Pricing	13 In Stock
-	1064	12.70	6.35	45	#34-843	₹11,288 Volume Pricing	20+ In Stock
-	1064	25.40	6.35	45	#34-845	₹12,145 Volume Pricing	20+ In Stock
-	1064	50.80	9.53	45	#12-550	₹34,176 Volume Pricing	8 In Stock
343 - 355	355	25.40	5.00	45	#89-450	₹19,696 Volume Pricing	1 In Stock
515 - 532	532	25.40	5.00	45	#89-451	₹16,115 Volume Pricing	Contact Us
1030 - 1064	1064	25.40	5.00	0	#89-452	₹16,115 Volume Pricing	Contact Us
1030 - 1064	1064	25.40	5.00	45	#89-453	₹16,115 Volume Pricing	Contact Us



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038

Phone: 1-800-363-1992 :

www.edmundoptics.com