

[All Products](#) / [Lasers](#) / [Laser Mechanics](#)

Optotune Fast Steering Mirrors See More by [Optotune](#)



- $\pm 50^\circ$ of Optical Scanning
- Protected Gold or Silver, and VIS Dielectric Coated Mirror Options
- Compact 45mm Diameter Housing Footprint
- Control via USB, SPI, or Analog Input

Common Specifications

General

Note:

Do not connect or disconnect the mirror head while the base unit is connected to power as this will damage the mirror driver.

Physical & Mechanical Properties

Diameter (mm): 15.00

Mechanical Tilt ($^\circ$): ± 25

Repeatability (μrad): 30 - 100 RMS

Optical Properties

Surface Quality: 60-40


Environmental & Durability Factors

Operating Temperature ($^\circ\text{C}$): 0 to +40

Storage Temperature ($^\circ\text{C}$): -40 to +85

Technical Information

Products

Title	Stock Number	Price	Buy
#14-574 Clearance			
15mm Dia. Mirror, Protected Silver, Optotune Dual Axis Fast Steering Mirror with Position Feedback			
	Clearance Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.	₹1,77,911	2 In Stock
15mm Dia. Mirror, Protected Gold, Optotune Dual Axis Fast Steering Mirror with Position Feedback	#73-039	₹2,25,000	3 In Stock
15mm Dia. Mirror, Protected Silver, Optotune Dual Axis Fast Steering Mirror with Position Feedback	#73-042	₹2,25,000	3 In Stock
15mm Dia. Mirror, VIS Dielectric, Optotune Dual Axis Fast Steering Mirror with Position Feedback	#73-043	₹2,25,000	Contact Us



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038

Phone: 1-800-363-1992 :

www.edmundoptics.com