

[All Products](#) / [Microscopy](#) / [Infinity Corrected Objectives](#)

Olympus X-Line Extended Apochromat Infinity Corrected Objectives

 See More by [Olympus](#)


- High Numerical Aperture (NA) up to 1.45
- Chromatic Aberration Correction from 400 - 1000nm
- Uniform Image Flatness over Large FOVs

Common Specifications

General

Compatible Tube Lens Focal Length (mm):

Focal Length: 180mm

Manufacturer:

Olympus

Optical Properties

Wavelength Range (nm):

400 - 1000

Field Number (mm):

26.5

Threading & Mounting

Mounting Threads:

RMS / 20.32mm x 36 TPI

Technical Information

Products

Magnification	NA	Field Number (mm)	FL (mm)	Model Number	WD (mm)	Stock Number	Price	Buy
4X	0.16	26.5	45.00	UPLXAPO4X	13.0	#14-905	₹1,96,650	5 In Stock
10X	0.40	26.5	18.00	UPLXAPO10X	3.1	#14-906	₹2,69,100	Contact Us
20X	0.80	26.5	9.00	UPLXAPO20X	0.61	#14-907	₹3,50,100	3 In Stock
40X	0.95	26.5	4.50	UPLXAPO40X	0.18	#14-908	₹4,54,500	1 In Stock
40X	1.40	26.5	4.50	UPLXAPO40XO	0.13	#73-283	₹6,82,200	1 In Stock
#74-022 New								
New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!								
60X	1.20	26.5	3.00	UPLXAPO60XW	0.28		₹6,85,560	1 In Stock
60X	1.42	26.5	3.00	UPLXAPO60XO	0.15	#14-909	₹7,27,200	4 In Stock
100X	1.45	26.5	1.80	UPLXAPO100XO	0.135	#14-910	₹7,38,900	Contact Us

