

[All Products](#) / 
 [Optics](#) / 
 [Optical Lenses](#) / 
 [Aspheric Lenses](#) / 
 [Glass Polished](#)

## TECHSPEC® Precision Aspheric Lenses



- Improved Versions of Our Aspheric Lenses
- Precision Grade Aspheric Surfaces
- High Numerical Apertures to Maximize Throughput

### Common Specifications

#### Physical & Mechanical Properties

|                        |       |        |                      |
|------------------------|-------|--------|----------------------|
| Centering (arcmin):    | <3    | Bevel: | Protective as needed |
| Shape of Back Surface: | Plano |        |                      |

#### Optical Properties

|                                      |       |                     |          |
|--------------------------------------|-------|---------------------|----------|
| Asphere Figure Error, RMS @ 632.8nm: | 0.4λ  |                     |          |
| Surface Quality:                     | 40-20 | Conjugate Distance: | Infinite |

## Technical Information

## Products

| Dia.<br>(mm) | EFL<br>(mm) | NA   | Coating              | Stock<br>Number         | Price                                     | Buy         |
|--------------|-------------|------|----------------------|-------------------------|-------------------------------------------|-------------|
| 6.00         | 7.50        | 0.40 | Uncoated             | <a href="#">#29-960</a> | ₹27,559<br><a href="#">Volume Pricing</a> | 6 In Stock  |
| 6.00         | 7.50        | 0.40 | VIS-EXT+ (350-700nm) | <a href="#">#70-058</a> | ₹30,751<br><a href="#">Volume Pricing</a> | 4 In Stock  |
| 6.00         | 7.50        | 0.40 | NIR+ (600-1050nm)    | <a href="#">#70-070</a> | ₹30,751<br><a href="#">Volume Pricing</a> | 1 In Stock  |
| 6.00         | 7.50        | 0.40 | SWIR+ (900-1700nm)   | <a href="#">#70-082</a> | ₹30,751<br><a href="#">Volume Pricing</a> | 5 In Stock  |
| 6.00         | 6.00        | 0.50 | Uncoated             | <a href="#">#29-959</a> | ₹27,559<br><a href="#">Volume Pricing</a> | 3 In Stock  |
| 6.00         | 6.00        | 0.50 | VIS-EXT+ (350-700nm) | <a href="#">#70-057</a> | ₹30,751<br><a href="#">Volume Pricing</a> | 1 In Stock  |
| 6.00         | 6.00        | 0.50 | NIR+ (600-1050nm)    | <a href="#">#70-069</a> | ₹30,751<br><a href="#">Volume Pricing</a> | 5 In Stock  |
| 6.00         | 6.00        | 0.50 | SWIR+ (900-1700nm)   | <a href="#">#70-081</a> | ₹30,751<br><a href="#">Volume Pricing</a> | 5 In Stock  |
| 6.00         | 4.50        | 0.66 | Uncoated             | <a href="#">#29-958</a> | ₹29,583<br><a href="#">Volume Pricing</a> | 5 In Stock  |
| 6.00         | 4.50        | 0.66 | VIS-EXT+ (350-700nm) | <a href="#">#70-056</a> | ₹32,775<br><a href="#">Volume Pricing</a> | 1 In Stock  |
| 6.00         | 4.50        | 0.66 | NIR+ (600-1050nm)    | <a href="#">#70-068</a> | ₹32,775<br><a href="#">Volume Pricing</a> | 1 In Stock  |
| 6.00         | 4.50        | 0.66 | SWIR+ (900-1700nm)   | <a href="#">#70-080</a> | ₹32,775<br><a href="#">Volume Pricing</a> | 10 In Stock |
| 9.00         | 11.25       | 0.33 | Uncoated             | <a href="#">#29-963</a> | ₹25,535<br><a href="#">Volume Pricing</a> | 3 In Stock  |
| 9.00         | 11.25       | 0.33 | VIS-EXT+ (350-700nm) | <a href="#">#70-061</a> | ₹28,727<br><a href="#">Volume Pricing</a> | 7 In Stock  |
| 9.00         | 11.25       | 0.33 | NIR+ (600-1050nm)    | <a href="#">#70-073</a> | ₹28,727<br><a href="#">Volume Pricing</a> | 5 In Stock  |
| 9.00         | 11.25       | 0.33 | SWIR+ (900-1700nm)   | <a href="#">#70-085</a> | ₹28,727<br><a href="#">Volume Pricing</a> | 1 In Stock  |
| 9.00         | 9.00        | 0.41 | Uncoated             | <a href="#">#29-962</a> | ₹25,535<br><a href="#">Volume Pricing</a> | 3 In Stock  |

|       |       |      |                      |                         |                                           |              |
|-------|-------|------|----------------------|-------------------------|-------------------------------------------|--------------|
| 9.00  | 9.00  | 0.41 | VIS-EXT+ (350-700nm) | <a href="#">#70-060</a> | ₹28,727<br><a href="#">Volume Pricing</a> | 5 In Stock   |
| 9.00  | 9.00  | 0.41 | NIR+ (600-1050nm)    | <a href="#">#70-072</a> | ₹28,727<br><a href="#">Volume Pricing</a> | 5 In Stock   |
| 9.00  | 9.00  | 0.41 | SWIR+ (900-1700nm)   | <a href="#">#70-084</a> | ₹28,727<br><a href="#">Volume Pricing</a> | Contact Us   |
| 9.00  | 6.00  | 0.62 | Uncoated             | <a href="#">#29-961</a> | ₹27,559<br><a href="#">Volume Pricing</a> | 6 In Stock   |
| 9.00  | 6.00  | 0.62 | VIS-EXT+ (350-700nm) | <a href="#">#70-059</a> | ₹30,751<br><a href="#">Volume Pricing</a> | 5 In Stock   |
| 9.00  | 6.00  | 0.62 | NIR+ (600-1050nm)    | <a href="#">#70-071</a> | ₹30,751<br><a href="#">Volume Pricing</a> | 5 In Stock   |
| 9.00  | 6.00  | 0.62 | SWIR+ (900-1700nm)   | <a href="#">#70-083</a> | ₹30,751<br><a href="#">Volume Pricing</a> | 4 In Stock   |
| 10.00 | 10.00 | 0.50 | Uncoated             | <a href="#">#37-415</a> | ₹16,193<br><a href="#">Volume Pricing</a> | 9 In Stock   |
| 10.00 | 10.00 | 0.50 | VIS-EXT+ (350-700nm) | <a href="#">#16-951</a> | ₹19,463<br><a href="#">Volume Pricing</a> | 4 In Stock   |
| 10.00 | 10.00 | 0.50 | NIR+ (600-1050nm)    | <a href="#">#16-971</a> | ₹19,463<br><a href="#">Volume Pricing</a> | 2 In Stock   |
| 10.00 | 10.00 | 0.50 | SWIR+ (900-1700nm)   | <a href="#">#16-991</a> | ₹19,463<br><a href="#">Volume Pricing</a> | 20+ In Stock |
| 10.00 | 7.50  | 0.67 | Uncoated             | <a href="#">#37-414</a> | ₹16,582<br><a href="#">Volume Pricing</a> | 20+ In Stock |
| 10.00 | 7.50  | 0.67 | VIS-EXT+ (350-700nm) | <a href="#">#22-989</a> | ₹19,463<br><a href="#">Volume Pricing</a> | 8 In Stock   |
| 10.00 | 7.50  | 0.67 | NIR+ (600-1050nm)    | <a href="#">#22-990</a> | ₹19,463<br><a href="#">Volume Pricing</a> | 4 In Stock   |
| 10.00 | 7.50  | 0.67 | SWIR+ (900-1700nm)   | <a href="#">#22-991</a> | ₹19,463<br><a href="#">Volume Pricing</a> | 4 In Stock   |
| 12.50 | 12.50 | 0.50 | Uncoated             | <a href="#">#37-417</a> | ₹18,217<br><a href="#">Volume Pricing</a> | 14 In Stock  |
| 12.50 | 12.50 | 0.50 | VIS-EXT+ (350-700nm) | <a href="#">#16-952</a> | ₹21,487<br><a href="#">Volume Pricing</a> | 5 In Stock   |
| 12.50 | 12.50 | 0.50 | NIR+ (600-1050nm)    | <a href="#">#16-972</a> | ₹21,487<br><a href="#">Volume Pricing</a> | 11 In Stock  |
| 12.50 | 12.50 | 0.50 | SWIR+ (900-1700nm)   | <a href="#">#16-992</a> | ₹21,487<br><a href="#">Volume Pricing</a> | 9 In Stock   |

|       |       |      |                      |                         |                                           |              |
|-------|-------|------|----------------------|-------------------------|-------------------------------------------|--------------|
| 12.50 | 9.50  | 0.66 | Uncoated             | <a href="#">#37-416</a> | ₹18,606<br><a href="#">Volume Pricing</a> | 5 In Stock   |
| 12.50 | 9.50  | 0.66 | VIS-EXT+ (350-700nm) | <a href="#">#22-754</a> | ₹21,876<br><a href="#">Volume Pricing</a> | 11 In Stock  |
| 12.50 | 9.50  | 0.66 | NIR+ (600-1050nm)    | <a href="#">#22-755</a> | ₹21,876<br><a href="#">Volume Pricing</a> | 7 In Stock   |
| 12.50 | 9.50  | 0.66 | SWIR+ (900-1700nm)   | <a href="#">#22-756</a> | ₹21,876<br><a href="#">Volume Pricing</a> | 5 In Stock   |
| 15.00 | 11.25 | 0.66 | Uncoated             | <a href="#">#37-419</a> | ₹22,265<br><a href="#">Volume Pricing</a> | 20+ In Stock |
| 15.00 | 11.25 | 0.66 | VIS-EXT+ (350-700nm) | <a href="#">#16-954</a> | ₹25,535<br><a href="#">Volume Pricing</a> | 20+ In Stock |
| 15.00 | 11.25 | 0.66 | NIR+ (600-1050nm)    | <a href="#">#16-974</a> | ₹23,900<br><a href="#">Volume Pricing</a> | 7 In Stock   |
| 15.00 | 11.25 | 0.66 | SWIR+ (900-1700nm)   | <a href="#">#16-994</a> | ₹25,535<br><a href="#">Volume Pricing</a> | 14 In Stock  |
| 15.00 | 15.00 | 0.50 | Uncoated             | <a href="#">#37-420</a> | ₹20,630<br><a href="#">Volume Pricing</a> | 11 In Stock  |
| 15.00 | 15.00 | 0.50 | VIS-EXT+ (350-700nm) | <a href="#">#16-953</a> | ₹23,900<br><a href="#">Volume Pricing</a> | 20+ In Stock |
| 15.00 | 15.00 | 0.50 | NIR+ (600-1050nm)    | <a href="#">#16-973</a> | ₹23,900<br><a href="#">Volume Pricing</a> | 1 In Stock   |
| 15.00 | 15.00 | 0.50 | SWIR+ (900-1700nm)   | <a href="#">#16-993</a> | ₹23,900<br><a href="#">Volume Pricing</a> | 20+ In Stock |
| 15.00 | 18.75 | 0.40 | Uncoated             | <a href="#">#37-421</a> | ₹23,900<br><a href="#">Volume Pricing</a> | 20+ In Stock |
| 15.00 | 18.75 | 0.40 | VIS-EXT+ (350-700nm) | <a href="#">#22-992</a> | ₹23,900<br><a href="#">Volume Pricing</a> | 9 In Stock   |
| 15.00 | 18.75 | 0.40 | NIR+ (600-1050nm)    | <a href="#">#22-993</a> | ₹23,900<br><a href="#">Volume Pricing</a> | Contact Us   |
| 15.00 | 18.75 | 0.40 | SWIR+ (900-1700nm)   | <a href="#">#22-994</a> | ₹23,900<br><a href="#">Volume Pricing</a> | 17 In Stock  |
| 15.00 | 22.50 | 0.33 | Uncoated             | <a href="#">#37-422</a> | ₹20,630<br><a href="#">Volume Pricing</a> | 6 In Stock   |
| 15.00 | 22.50 | 0.33 | VIS-EXT+ (350-700nm) | <a href="#">#22-995</a> | ₹23,900<br><a href="#">Volume Pricing</a> | 6 In Stock   |
| 15.00 | 22.50 | 0.33 | NIR+ (600-1050nm)    | <a href="#">#22-996</a> | ₹23,900<br><a href="#">Volume Pricing</a> | 20+ In Stock |

|       |       |      |                      |                         |                                           |              |
|-------|-------|------|----------------------|-------------------------|-------------------------------------------|--------------|
| 15.00 | 22.50 | 0.33 | SWIR+ (900-1700nm)   | <a href="#">#22-997</a> | ₹23,900<br><a href="#">Volume Pricing</a> | 2 In Stock   |
| 15.00 | 9.00  | 0.83 | Uncoated             | <a href="#">#37-418</a> | ₹28,337<br><a href="#">Volume Pricing</a> | 20+ In Stock |
| 15.00 | 9.00  | 0.83 | VIS-EXT+ (350-700nm) | <a href="#">#22-757</a> | ₹31,607<br><a href="#">Volume Pricing</a> | 20+ In Stock |
| 15.00 | 9.00  | 0.83 | NIR+ (600-1050nm)    | <a href="#">#22-758</a> | ₹31,607<br><a href="#">Volume Pricing</a> | 7 In Stock   |
| 15.00 | 9.00  | 0.83 | SWIR+ (900-1700nm)   | <a href="#">#22-759</a> | ₹31,607<br><a href="#">Volume Pricing</a> | 11 In Stock  |
| 20.00 | 12.50 | 0.80 | Uncoated             | <a href="#">#37-423</a> | ₹30,751<br><a href="#">Volume Pricing</a> | 14 In Stock  |
| 20.00 | 12.50 | 0.80 | VIS-EXT+ (350-700nm) | <a href="#">#16-956</a> | ₹34,020<br><a href="#">Volume Pricing</a> | 20+ In Stock |
| 20.00 | 12.50 | 0.80 | NIR+ (600-1050nm)    | <a href="#">#16-976</a> | ₹34,020<br><a href="#">Volume Pricing</a> | Contact Us   |
| 20.00 | 12.50 | 0.80 | SWIR+ (900-1700nm)   | <a href="#">#16-996</a> | ₹34,020<br><a href="#">Volume Pricing</a> | 4 In Stock   |
| 20.00 | 15.00 | 0.67 | Uncoated             | <a href="#">#37-424</a> | ₹23,044<br><a href="#">Volume Pricing</a> | 4 In Stock   |
| 20.00 | 15.00 | 0.67 | VIS-EXT+ (350-700nm) | <a href="#">#22-998</a> | ₹26,313<br><a href="#">Volume Pricing</a> | 5 In Stock   |
| 20.00 | 15.00 | 0.67 | NIR+ (600-1050nm)    | <a href="#">#22-999</a> | ₹26,313<br><a href="#">Volume Pricing</a> | 10 In Stock  |
| 20.00 | 15.00 | 0.67 | SWIR+ (900-1700nm)   | <a href="#">#23-013</a> | ₹26,313<br><a href="#">Volume Pricing</a> | 12 In Stock  |
| 20.00 | 20.00 | 0.50 | Uncoated             | <a href="#">#37-425</a> | ₹23,044<br><a href="#">Volume Pricing</a> | 14 In Stock  |
| 20.00 | 20.00 | 0.50 | VIS-EXT+ (350-700nm) | <a href="#">#16-955</a> | ₹26,313<br><a href="#">Volume Pricing</a> | 5 In Stock   |
| 20.00 | 20.00 | 0.50 | NIR+ (600-1050nm)    | <a href="#">#16-975</a> | ₹26,313<br><a href="#">Volume Pricing</a> | 20+ In Stock |
| 20.00 | 20.00 | 0.50 | SWIR+ (900-1700nm)   | <a href="#">#16-995</a> | ₹26,313<br><a href="#">Volume Pricing</a> | 5 In Stock   |
| 25.00 | 15.00 | 0.83 | Uncoated             | <a href="#">#37-426</a> | ₹31,996<br><a href="#">Volume Pricing</a> | 14 In Stock  |
| 25.00 | 15.00 | 0.83 | VIS-EXT+ (350-700nm) | <a href="#">#16-962</a> | ₹36,823<br><a href="#">Volume Pricing</a> | 13 In Stock  |

|       |       |      |                      |                         |                                           |              |
|-------|-------|------|----------------------|-------------------------|-------------------------------------------|--------------|
| 25.00 | 15.00 | 0.83 | NIR+ (600-1050nm)    | <a href="#">#16-982</a> | ₹36,823<br><a href="#">Volume Pricing</a> | 13 In Stock  |
| 25.00 | 15.00 | 0.83 | SWIR+ (900-1700nm)   | <a href="#">#17-002</a> | ₹28,727<br><a href="#">Volume Pricing</a> | 14 In Stock  |
| 25.00 | 18.75 | 0.66 | Uncoated             | <a href="#">#37-427</a> | ₹25,068<br><a href="#">Volume Pricing</a> | 9 In Stock   |
| 25.00 | 18.75 | 0.66 | VIS-EXT+ (350-700nm) | <a href="#">#16-961</a> | ₹29,972<br><a href="#">Volume Pricing</a> | 14 In Stock  |
| 25.00 | 18.75 | 0.66 | NIR+ (600-1050nm)    | <a href="#">#16-981</a> | ₹29,972<br><a href="#">Volume Pricing</a> | 8 In Stock   |
| 25.00 | 18.75 | 0.66 | SWIR+ (900-1700nm)   | <a href="#">#17-001</a> | ₹30,362<br><a href="#">Volume Pricing</a> | 20+ In Stock |
| 25.00 | 25.00 | 0.50 | Uncoated             | <a href="#">#37-428</a> | ₹23,900<br><a href="#">Volume Pricing</a> | 1 In Stock   |
| 25.00 | 25.00 | 0.50 | VIS-EXT+ (350-700nm) | <a href="#">#16-960</a> | ₹28,727<br><a href="#">Volume Pricing</a> | 9 In Stock   |
| 25.00 | 25.00 | 0.50 | NIR+ (600-1050nm)    | <a href="#">#16-980</a> | ₹28,727<br><a href="#">Volume Pricing</a> | 20+ In Stock |
| 25.00 | 25.00 | 0.50 | SWIR+ (900-1700nm)   | <a href="#">#17-000</a> | ₹28,727<br><a href="#">Volume Pricing</a> | Contact Us   |
| 25.00 | 31.25 | 0.40 | Uncoated             | <a href="#">#37-429</a> | ₹23,900<br><a href="#">Volume Pricing</a> | 5 In Stock   |
| 25.00 | 31.25 | 0.40 | VIS-EXT+ (350-700nm) | <a href="#">#16-959</a> | ₹28,727<br><a href="#">Volume Pricing</a> | 14 In Stock  |
| 25.00 | 31.25 | 0.40 | NIR+ (600-1050nm)    | <a href="#">#16-979</a> | ₹28,727<br><a href="#">Volume Pricing</a> | 9 In Stock   |
| 25.00 | 31.25 | 0.40 | SWIR+ (900-1700nm)   | <a href="#">#16-999</a> | ₹28,727<br><a href="#">Volume Pricing</a> | Contact Us   |
| 25.00 | 37.50 | 0.33 | Uncoated             | <a href="#">#37-430</a> | ₹23,900<br><a href="#">Volume Pricing</a> | 8 In Stock   |
| 25.00 | 37.50 | 0.33 | VIS-EXT+ (350-700nm) | <a href="#">#16-958</a> | ₹28,727<br><a href="#">Volume Pricing</a> | 12 In Stock  |
| 25.00 | 37.50 | 0.33 | NIR+ (600-1050nm)    | <a href="#">#16-978</a> | ₹28,727<br><a href="#">Volume Pricing</a> | 5 In Stock   |
| 25.00 | 37.50 | 0.33 | SWIR+ (900-1700nm)   | <a href="#">#16-998</a> | ₹28,727<br><a href="#">Volume Pricing</a> | 3 In Stock   |
| 25.00 | 50.00 | 0.25 | Uncoated             | <a href="#">#37-431</a> | ₹23,900<br><a href="#">Volume Pricing</a> | Contact Us   |

|       |       |      |                      |                         |                                           |             |
|-------|-------|------|----------------------|-------------------------|-------------------------------------------|-------------|
| 25.00 | 50.00 | 0.25 | VIS-EXT+ (350-700nm) | <a href="#">#16-957</a> | ₹28,727<br><a href="#">Volume Pricing</a> | 9 In Stock  |
| 25.00 | 50.00 | 0.25 | NIR+ (600-1050nm)    | <a href="#">#16-977</a> | ₹28,727<br><a href="#">Volume Pricing</a> | Contact Us  |
| 25.00 | 50.00 | 0.25 | SWIR+ (900-1700nm)   | <a href="#">#16-997</a> | ₹28,727<br><a href="#">Volume Pricing</a> | 5 In Stock  |
| 30.00 | 17.50 | 0.86 | Uncoated             | <a href="#">#37-432</a> | ₹36,434<br><a href="#">Volume Pricing</a> | 4 In Stock  |
| 30.00 | 17.50 | 0.86 | VIS-EXT+ (350-700nm) | <a href="#">#16-965</a> | ₹42,039<br><a href="#">Volume Pricing</a> | 10 In Stock |
| 30.00 | 17.50 | 0.86 | NIR+ (600-1050nm)    | <a href="#">#16-985</a> | ₹42,039<br><a href="#">Volume Pricing</a> | 2 In Stock  |
| 30.00 | 17.50 | 0.86 | SWIR+ (900-1700nm)   | <a href="#">#17-005</a> | ₹42,039<br><a href="#">Volume Pricing</a> | 5 In Stock  |
| 30.00 | 22.50 | 0.66 | Uncoated             | <a href="#">#37-433</a> | ₹30,362<br><a href="#">Volume Pricing</a> | 14 In Stock |
| 30.00 | 22.50 | 0.66 | VIS-EXT+ (350-700nm) | <a href="#">#16-964</a> | ₹35,188<br><a href="#">Volume Pricing</a> | 12 In Stock |
| 30.00 | 22.50 | 0.66 | NIR+ (600-1050nm)    | <a href="#">#16-984</a> | ₹34,020<br><a href="#">Volume Pricing</a> | 13 In Stock |
| 30.00 | 22.50 | 0.66 | SWIR+ (900-1700nm)   | <a href="#">#17-004</a> | ₹35,188<br><a href="#">Volume Pricing</a> | 5 In Stock  |
| 30.00 | 30.00 | 0.50 | Uncoated             | <a href="#">#37-434</a> | ₹29,116<br><a href="#">Volume Pricing</a> | 16 In Stock |
| 30.00 | 30.00 | 0.50 | VIS-EXT+ (350-700nm) | <a href="#">#16-963</a> | ₹34,020<br><a href="#">Volume Pricing</a> | 4 In Stock  |
| 30.00 | 30.00 | 0.50 | NIR+ (600-1050nm)    | <a href="#">#16-983</a> | ₹34,020<br><a href="#">Volume Pricing</a> | 1 In Stock  |
| 30.00 | 30.00 | 0.50 | SWIR+ (900-1700nm)   | <a href="#">#17-003</a> | ₹34,020<br><a href="#">Volume Pricing</a> | Contact Us  |
| 40.00 | 25.00 | 0.80 | Uncoated             | <a href="#">#37-435</a> | ₹46,710<br><a href="#">Volume Pricing</a> | 2 In Stock  |
| 40.00 | 25.00 | 0.80 | VIS-EXT+ (350-700nm) | <a href="#">#16-968</a> | ₹51,381<br><a href="#">Volume Pricing</a> | 9 In Stock  |
| 40.00 | 25.00 | 0.80 | NIR+ (600-1050nm)    | <a href="#">#16-988</a> | ₹51,381<br><a href="#">Volume Pricing</a> | 8 In Stock  |
| 40.00 | 25.00 | 0.80 | SWIR+ (900-1700nm)   | <a href="#">#17-010</a> | ₹51,381<br><a href="#">Volume Pricing</a> | 5 In Stock  |



|       |       |      |                      |                         |                                           |              |
|-------|-------|------|----------------------|-------------------------|-------------------------------------------|--------------|
| 40.00 | 30.00 | 0.66 | Uncoated             | <a href="#">#37-436</a> | ₹38,458<br><a href="#">Volume Pricing</a> | 13 In Stock  |
| 40.00 | 30.00 | 0.66 | VIS-EXT+ (350-700nm) | <a href="#">#16-967</a> | ₹43,207<br><a href="#">Volume Pricing</a> | 17 In Stock  |
| 40.00 | 30.00 | 0.66 | NIR+ (600-1050nm)    | <a href="#">#16-987</a> | ₹42,039<br><a href="#">Volume Pricing</a> | 14 In Stock  |
| 40.00 | 30.00 | 0.66 | SWIR+ (900-1700nm)   | <a href="#">#17-009</a> | ₹43,207<br><a href="#">Volume Pricing</a> | 10 In Stock  |
| 40.00 | 40.00 | 0.50 | Uncoated             | <a href="#">#37-437</a> | ₹37,212<br><a href="#">Volume Pricing</a> | 20+ In Stock |
| 40.00 | 40.00 | 0.50 | VIS-EXT+ (350-700nm) | <a href="#">#16-966</a> | ₹42,039<br><a href="#">Volume Pricing</a> | 5 In Stock   |
| 40.00 | 40.00 | 0.50 | NIR+ (600-1050nm)    | <a href="#">#16-986</a> | ₹42,039<br><a href="#">Volume Pricing</a> | 4 In Stock   |
| 40.00 | 40.00 | 0.50 | SWIR+ (900-1700nm)   | <a href="#">#17-008</a> | ₹42,039<br><a href="#">Volume Pricing</a> | 6 In Stock   |
| 50.00 | 30.00 | 0.83 | Uncoated             | <a href="#">#37-438</a> | ₹59,166<br><a href="#">Volume Pricing</a> | 20+ In Stock |
| 50.00 | 30.00 | 0.83 | VIS-EXT+ (350-700nm) | <a href="#">#16-970</a> | ₹63,837<br><a href="#">Volume Pricing</a> | 3 In Stock   |
| 50.00 | 30.00 | 0.83 | NIR+ (600-1050nm)    | <a href="#">#16-990</a> | ₹64,616<br><a href="#">Volume Pricing</a> | 8 In Stock   |
| 50.00 | 30.00 | 0.83 | SWIR+ (900-1700nm)   | <a href="#">#17-012</a> | ₹63,837<br><a href="#">Volume Pricing</a> | 4 In Stock   |
| 50.00 | 37.50 | 0.66 | Uncoated             | <a href="#">#37-439</a> | ₹45,153<br><a href="#">Volume Pricing</a> | 20+ In Stock |
| 50.00 | 37.50 | 0.66 | VIS-EXT+ (350-700nm) | <a href="#">#16-969</a> | ₹50,213<br><a href="#">Volume Pricing</a> | 14 In Stock  |
| 50.00 | 37.50 | 0.66 | NIR+ (600-1050nm)    | <a href="#">#16-989</a> | ₹50,213<br><a href="#">Volume Pricing</a> | 13 In Stock  |
| 50.00 | 37.50 | 0.66 | SWIR+ (900-1700nm)   | <a href="#">#17-011</a> | ₹50,213<br><a href="#">Volume Pricing</a> | 4 In Stock   |
| 50.00 | 50.00 | 0.50 | Uncoated             | <a href="#">#37-440</a> | ₹45,153<br><a href="#">Volume Pricing</a> | 8 In Stock   |
| 50.00 | 50.00 | 0.50 | VIS-EXT+ (350-700nm) | <a href="#">#23-021</a> | ₹50,213<br><a href="#">Volume Pricing</a> | 5 In Stock   |
| 50.00 | 50.00 | 0.50 | NIR+ (600-1050nm)    | <a href="#">#23-022</a> | ₹50,213<br><a href="#">Volume Pricing</a> | Contact Us   |

|       |       |      |                    |                         |                                           |            |
|-------|-------|------|--------------------|-------------------------|-------------------------------------------|------------|
| 50.00 | 50.00 | 0.50 | SWIR+ (900-1700nm) | <a href="#">#23-023</a> | ₹50,213<br><a href="#">Volume Pricing</a> | 4 In Stock |
|-------|-------|------|--------------------|-------------------------|-------------------------------------------|------------|

---



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038

Phone: 1-800-363-1992 :

[www.edmundoptics.com](http://www.edmundoptics.com)