

[All Products](#) / [Optics](#) / [Optical Filters](#) / [Neutral Density \(ND\) Filters](#)

Variable Neutral Density (ND) Machine Vision Filters



- Continuous Attenuation of Illumination Intensity
- Ideal for the Visible Spectrum
- Variety of Common Machine Vision Threads Available
- [Mounted Absorptive Neutral Density \(ND\) Filters](#) Also Available

Common Specifications

General

Note: AR Coated

Optical Properties

Optical Density OD (Average): 0.5 - 4.0 @ 550 - 650nm

Substrate: Polymer Film XP42

Blocking Wavelength Range (nm): 400 - 700

Coating Specification: $R_{avg} \leq 2\% @ 400 - 700\text{nm}$

Threading & Mounting

Mount Thickness (mm): 5.85

Mount Thickness Including Threads (mm): 7.85

Technical Information

Products

Filter Thread	Optical Density OD (Average)	Stock Number	Price	Buy
M58 x 0.75	0.5 - 4.0 @ 550 - 650nm	#16-079	₹12,300 Volume Pricing	4 In Stock
M67 x 0.75	0.5 - 4.0 @ 550 - 650nm	#16-080	₹13,468 Volume Pricing	6 In Stock
M77 x 0.75	0.5 - 4.0 @ 550 - 650nm	#16-081	₹14,792 Volume Pricing	2 In Stock
M82 x 0.75	0.5 - 4.0 @ 550 - 650nm	#16-082	₹15,959 Volume Pricing	3 In Stock



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038

Phone: 1-800-363-1992 :

www.edmundoptics.com