

[All Products](#) / [Optics](#) / [Optical Filters](#) / [Machine Vision Filters](#) / [Color Filters](#)

Mounted Machine Vision Filters



- Optimized for Use with Popular LEDs
- Multiple Mounting Sizes and Threads Available to Ease System Compatibility
- $\geq 85\%$ Transmission
- [TECHSPEC® High Performance Mounted Machine Vision Filters](#) and [Mounted Color Filters](#) Also Available

Common Specifications

Physical & Mechanical Properties

Construction:

Mounted in Black Anodized Ring

Technical Information

Products

Filter Thread	Color	CWL (nm)	FWHM (nm)	Stock Number	Price	Buy
M77 x 0.75	NUV	324.00	105.00	#21-400	₹33,476 Volume Pricing	1 In Stock
-	NUV	324.00	105.00	#70-534	₹8,797 Volume Pricing	6 In Stock
-	Blue	470.00	85.00	#70-535	₹8,797 Volume Pricing	6 In Stock
-	Cyan	505.00	90.00	#70-536	₹8,797 Volume Pricing	5 In Stock
-	Green	525.00	80.00	#70-537	₹8,797 Volume Pricing	7 In Stock
-	-	530.00	120.00	#70-538	₹8,797 Volume Pricing	Contact Us
-	VIS	550.00	300.00	#70-539	₹8,096 Volume Pricing	Contact Us
-	Orange	590.00	70.00	#70-540	₹8,797 Volume Pricing	5 In Stock
-	Light Red	635.00	60.00	#70-541	₹8,096 Volume Pricing	3 In Stock
-	Dark Red	660.00	70.00	#70-542	₹8,096 Volume Pricing	9 In Stock
-	NIR-IR	800.00	315.00	#70-543	₹8,096 Volume Pricing	1 In Stock
-	SWIR	1,000.00	150.00	#70-544	₹17,205 Volume Pricing	5 In Stock
-	SWIR	1,550.00	190.00	#70-545	₹26,625 Volume Pricing	5 In Stock
M77 x 0.75	Blue	470.00	85.00	#21-401	₹33,476 Volume Pricing	1 In Stock
M77 x 0.75	Cyan	505.00	90.00	#21-402	₹33,476 Volume Pricing	1 In Stock
M77 x 0.75	Green	525.00	80.00	#21-403	₹33,476 Volume Pricing	1 In Stock
M77 x 0.75	Vis	550.00	300.00	#21-404	₹30,128 Volume Pricing	1 In Stock

M77 x 0.75	Orange	590.00	75.00	#21-405	₹33,476 Volume Pricing	1 In Stock
M77 x 0.75	Light Red	635.00	60.00	#21-406	₹30,128 Volume Pricing	1 In Stock
M77 x 0.75	Dark Red	660.00	60.00	#21-407	₹30,128 Volume Pricing	1 In Stock
M77 x 0.75	IR	850.00	160.00	#21-408	₹30,128 Volume Pricing	1 In Stock
M39 x 0.50	NUV	324.00	105.00	#21-417	₹14,402 Volume Pricing	1 In Stock
M39 x 0.50	Blue	470.00	85.00	#21-418	₹14,402 Volume Pricing	2 In Stock
M39 x 0.50	Cyan	505.00	90.00	#21-419	₹14,402 Volume Pricing	1 In Stock
M39 x 0.50	Green	525.00	80.00	#21-420	₹14,402 Volume Pricing	2 In Stock
M39 x 0.50	Vis	550.00	300.00	#21-421	₹13,001 Volume Pricing	1 In Stock
M39 x 0.50	Orange	590.00	75.00	#21-422	₹14,402 Volume Pricing	2 In Stock
M39 x 0.50	Light Red	635.00	60.00	#21-423	₹13,001 Volume Pricing	2 In Stock
M39 x 0.50	Dark Red	660.00	60.00	#21-424	₹13,001 Volume Pricing	1 In Stock
M39 x 0.50	IR	850.00	160.00	#21-425	₹13,001 Volume Pricing	Contact Us
M49 x 0.75	NUV	324.00	105.00	#21-434	₹16,271 Volume Pricing	1 In Stock
M49 x 0.75	Blue	470.00	85.00	#21-435	₹16,271 Volume Pricing	3 In Stock
M49 x 0.75	Cyan	505.00	90.00	#21-436	₹16,271 Volume Pricing	1 In Stock
M49 x 0.75	Green	525.00	80.00	#21-437	₹16,271 Volume Pricing	Contact Us
M49 x 0.75	Vis	550.00	300.00	#21-438	₹14,636 Volume Pricing	1 In Stock
M49 x 0.75	Orange	590.00	75.00	#21-439	₹16,271 Volume Pricing	1 In Stock
M49 x 0.75	Light Red	635.00	60.00	#21-440	₹14,636 Volume Pricing	2 In Stock

M49 x 0.75	Dark Red	660.00	60.00	#21-441	₹14,636 Volume Pricing	5 In Stock
M49 x 0.75	IR	850.00	160.00	#21-442	₹14,636 Volume Pricing	1 In Stock
M67 x 0.75	NUV	324.00	105.00	#21-451	₹26,158 Volume Pricing	1 In Stock
M67 x 0.75	Blue	470.00	85.00	#21-452	₹26,158 Volume Pricing	1 In Stock
M67 x 0.75	Cyan	505.00	90.00	#21-453	₹26,158 Volume Pricing	1 In Stock
M67 x 0.75	Green	525.00	80.00	#21-454	₹26,158 Volume Pricing	1 In Stock
M67 x 0.75	Vis	550.00	300.00	#21-455	₹23,511 Volume Pricing	1 In Stock
M67 x 0.75	Orange	590.00	75.00	#21-456	₹26,158 Volume Pricing	1 In Stock
M67 x 0.75	Light Red	635.00	60.00	#21-457	₹23,511 Volume Pricing	1 In Stock
M67 x 0.75	Dark Red	660.00	60.00	#21-458	₹23,511 Volume Pricing	1 In Stock
M67 x 0.75	IR	850.00	160.00	#21-459	₹23,511 Volume Pricing	1 In Stock
M52 x 0.75	NUV	324.00	105.00	#21-468	₹16,738 Volume Pricing	1 In Stock
M52 x 0.75	Blue	470.00	85.00	#21-469	₹16,738 Volume Pricing	3 In Stock
M52 x 0.75	Cyan	505.00	90.00	#21-470	₹16,738 Volume Pricing	Contact Us
M52 x 0.75	Green	525.00	80.00	#21-471	₹16,738 Volume Pricing	Contact Us
M52 x 0.75	Vis	550.00	300.00	#21-472	₹15,103 Volume Pricing	2 In Stock
M52 x 0.75	Orange	590.00	75.00	#21-473	₹16,738 Volume Pricing	1 In Stock
M52 x 0.75	Light Red	635.00	60.00	#21-474	₹15,103 Volume Pricing	1 In Stock

M52 x 0.75	Dark Red	660.00	60.00	#21-475	₹15,103 Volume Pricing	1 In Stock
M52 x 0.75	IR	850.00	160.00	#21-476	₹15,103 Volume Pricing	1 In Stock
M55 x 0.75	NUV	324.00	105.00	#21-485	₹17,516 Volume Pricing	1 In Stock
M55 x 0.75	Blue	470.00	85.00	#21-486	₹17,516 Volume Pricing	1 In Stock
M55 x 0.75	Cyan	505.00	90.00	#21-487	₹17,516 Volume Pricing	1 In Stock
M55 x 0.75	Green	525.00	80.00	#21-488	₹17,516 Volume Pricing	1 In Stock
M55 x 0.75	Vis	550.00	300.00	#21-489	₹15,804 Volume Pricing	1 In Stock
M55 x 0.75	Orange	590.00	75.00	#21-490	₹17,516 Volume Pricing	1 In Stock
M55 x 0.75	Light Red	635.00	60.00	#21-491	₹15,804 Volume Pricing	Contact Us
M55 x 0.75	Dark Red	660.00	60.00	#21-492	₹15,804 Volume Pricing	Contact Us
M55 x 0.75	IR	850.00	160.00	#21-493	₹15,804 Volume Pricing	2 In Stock
M55 x 0.75	SWIR	940.00	55.00	#28-794	₹20,864	1 In Stock
M55 x 0.75	SWIR	1,000.00	150.00	#28-805	₹36,045	1 In Stock
M55 x 0.75	SWIR	1,070.00	-	#28-860	₹28,337	1 In Stock
M55 x 0.75	SWIR	1,300.00	35.00	#28-827	₹38,847	1 In Stock
M55 x 0.75	SWIR	1,450.00	35.00	#28-838	₹38,847	1 In Stock
M55 x 0.75	SWIR	1,475.00	-	#28-871	₹28,337	1 In Stock
M55 x 0.75	SWIR	1,550.00	190.00	#28-816	₹36,045	1 In Stock
M55 x 0.75	SWIR	1,550.00	35.00	#28-849	₹38,847	1 In Stock
M86 x 0.75	NUV	324.00	105.00	#21-502	₹45,231 Volume Pricing	1 In Stock
M86 x 0.75	Blue	470.00	85.00	#21-503	₹45,231 Volume Pricing	1 In Stock
M86 x 0.75	Cyan	505.00	90.00	#21-504	₹45,231 Volume Pricing	1 In Stock

M86 x 0.75	Green	525.00	80.00	#21-505	₹45,231 Volume Pricing	1 In Stock
M86 x 0.75	Vis	550.00	300.00	#21-506	₹40,716 Volume Pricing	1 In Stock
M86 x 0.75	Orange	590.00	75.00	#21-507	₹45,231 Volume Pricing	1 In Stock
M86 x 0.75	Light Red	635.00	60.00	#21-508	₹40,716 Volume Pricing	1 In Stock
M86 x 0.75	Dark Red	660.00	60.00	#21-509	₹40,716 Volume Pricing	1 In Stock
M86 x 0.75	IR	850.00	160.00	#21-510	₹40,716 Volume Pricing	1 In Stock
M22 x 0.75	NUV	324.00	105.00	#21-519	₹13,079 Volume Pricing	1 In Stock
M22 x 0.75	Blue	470.00	85.00	#21-520	₹13,079 Volume Pricing	1 In Stock
M22 x 0.75	Cyan	505.00	90.00	#21-521	₹13,079 Volume Pricing	1 In Stock
M22 x 0.75	Green	525.00	80.00	#21-522	₹13,079 Volume Pricing	1 In Stock
M22 x 0.75	Vis	550.00	300.00	#21-523	₹11,989 Volume Pricing	1 In Stock
M22 x 0.75	Orange	590.00	75.00	#21-524	₹13,079 Volume Pricing	1 In Stock
M22 x 0.75	Light Red	635.00	60.00	#21-525	₹11,989 Volume Pricing	1 In Stock
M22 x 0.75	Dark Red	660.00	60.00	#21-526	₹11,989 Volume Pricing	1 In Stock
M22 x 0.75	IR	850.00	160.00	#21-527	₹11,989 Volume Pricing	1 In Stock
M22.5 x 0.50	NUV	324.00	105.00	#21-536	₹10,510 Volume Pricing	1 In Stock
M22.5 x 0.50	Blue	470.00	85.00	#21-537	₹10,510 Volume Pricing	Contact Us
M22.5 x 0.50	Cyan	505.00	90.00	#21-538	₹10,510 Volume Pricing	1 In Stock
M22.5 x 0.50	Green	525.00	80.00	#21-539	₹10,510 Volume Pricing	1 In Stock
M22.5 x 0.50	Vis	550.00	300.00	#21-540	₹9,420 Volume Pricing	Contact Us

M22.5 x 0.50	Orange	590.00	75.00	#21-541	₹10,510 Volume Pricing	1 In Stock
M22.5 x 0.50	Light Red	635.00	60.00	#21-542	₹9,420 Volume Pricing	2 In Stock
M22.5 x 0.50	Dark Red	660.00	60.00	#21-543	₹9,420 Volume Pricing	2 In Stock
M22.5 x 0.50	IR	850.00	160.00	#21-544	₹9,420 Volume Pricing	1 In Stock
M37 x 0.75	NUV	324.00	105.00	#21-553	₹13,079 Volume Pricing	1 In Stock
M37 x 0.75	Blue	470.00	85.00	#21-554	₹13,079 Volume Pricing	1 In Stock
M37 x 0.75	Cyan	505.00	90.00	#21-555	₹13,079 Volume Pricing	1 In Stock
M37 x 0.75	Green	525.00	80.00	#21-556	₹13,079 Volume Pricing	2 In Stock
M37 x 0.75	Vis	550.00	300.00	#21-557	₹11,755 Volume Pricing	1 In Stock
M37 x 0.75	Orange	590.00	75.00	#21-558	₹13,079 Volume Pricing	1 In Stock
M37 x 0.75	Light Red	635.00	60.00	#21-559	₹11,755 Volume Pricing	3 In Stock
M37 x 0.75	Dark Red	660.00	60.00	#21-560	₹11,755 Volume Pricing	Contact Us
M37 x 0.75	IR	850.00	160.00	#21-561	₹11,755 Volume Pricing	5 In Stock
M37 x 0.75	SWIR	940.00	55.00	#28-790	₹15,570	Contact Us
M37 x 0.75	SWIR	1,000.00	150.00	#28-801	₹27,948	1 In Stock
M37 x 0.75	SWIR	1,070.00	-	#28-856	₹19,307	1 In Stock
M37 x 0.75	SWIR	1,300.00	35.00	#28-823	₹27,559	1 In Stock
M37 x 0.75	SWIR	1,450.00	35.00	#28-834	₹27,559	1 In Stock
M37 x 0.75	SWIR	1,475.00	-	#28-867	₹18,995	1 In Stock
M37 x 0.75	SWIR	1,550.00	190.00	#28-812	₹27,948	1 In Stock
M37 x 0.75	SWIR	1,550.00	35.00	#28-845	₹27,559	2 In Stock
M35.5 x 0.50	NUV	324.00	105.00	#21-570	₹12,300 Volume Pricing	1 In Stock

M35.5 x 0.50	Blue	470.00	85.00	#21-571	₹12,300 Volume Pricing	1 In Stock
M35.5 x 0.50	Cyan	505.00	90.00	#21-572	₹12,300 Volume Pricing	1 In Stock
M35.5 x 0.50	Green	525.00	80.00	#21-573	₹12,300 Volume Pricing	1 In Stock
M35.5 x 0.50	Vis	550.00	300.00	#21-574	₹11,055 Volume Pricing	1 In Stock
M35.5 x 0.50	Orange	590.00	75.00	#21-575	₹12,300 Volume Pricing	5 In Stock
M35.5 x 0.50	Light Red	635.00	60.00	#21-576	₹11,055 Volume Pricing	1 In Stock
M35.5 x 0.50	Dark Red	660.00	60.00	#21-577	₹11,055 Volume Pricing	1 In Stock
M35.5 x 0.50	IR	850.00	160.00	#21-578	₹11,055 Volume Pricing	1 In Stock
M35.5 x 0.50	SWIR	940.00	55.00	#28-789	₹14,636	1 In Stock
M35.5 x 0.50	SWIR	1,000.00	150.00	#28-800	₹25,691	1 In Stock
M35.5 x 0.50	SWIR	1,070.00	-	#28-855	₹17,438	1 In Stock
M35.5 x 0.50	SWIR	1,300.00	35.00	#28-822	₹26,703	1 In Stock
M35.5 x 0.50	SWIR	1,450.00	35.00	#28-833	₹26,703	1 In Stock
M35.5 x 0.50	SWIR	1,475.00	-	#28-866	₹17,438	Contact Us
M35.5 x 0.50	SWIR	1,550.00	190.00	#28-811	₹25,691	1 In Stock
M35.5 x 0.50	SWIR	1,550.00	35.00	#28-844	₹26,703	1 In Stock
M72 x 0.75	NUV	324.00	105.00	#21-587	₹29,272 Volume Pricing	1 In Stock
M72 x 0.75	Blue	470.00	85.00	#21-588	₹29,272 Volume Pricing	1 In Stock
M72 x 0.75	Cyan	505.00	90.00	#21-589	₹29,272 Volume Pricing	1 In Stock
M72 x 0.75	Green	525.00	80.00	#21-590	₹29,272 Volume Pricing	Contact Us
M72 x 0.75	Vis	550.00	300.00	#21-591	₹26,391 Volume Pricing	1 In Stock
M72 x 0.75	Orange	590.00	75.00	#21-592	₹29,272 Volume Pricing	1 In Stock

M72 x 0.75	Light Red	635.00	60.00	#21-593	₹26,391 Volume Pricing	2 In Stock
M72 x 0.75	Dark Red	660.00	60.00	#21-594	₹26,391 Volume Pricing	1 In Stock
M72 x 0.75	IR	850.00	160.00	#21-595	₹26,391 Volume Pricing	2 In Stock
M72 x 0.75	SWIR	940.00	55.00	#28-796	₹34,877	1 In Stock
M72 x 0.75	SWIR	1,000.00	150.00	#28-807	₹50,603	Contact Us
M72 x 0.75	SWIR	1,070.00	-	#28-862	₹55,663	1 In Stock
M72 x 0.75	SWIR	1,300.00	35.00	#28-829	₹58,777	1 In Stock
M72 x 0.75	SWIR	1,450.00	35.00	#28-840	₹58,777	1 In Stock
M72 x 0.75	SWIR	1,475.00	-	#28-873	₹54,884	2 In Stock
M72 x 0.75	SWIR	1,550.00	190.00	#28-818	₹50,603	1 In Stock
M72 x 0.75	SWIR	1,550.00	35.00	#28-851	₹58,777	Contact Us
M105 x 1.00	NUV	324.00	105.00	#21-604	₹68,508 Volume Pricing	1 In Stock
M105 x 1.00	Blue	470.00	85.00	#21-605	₹68,508 Volume Pricing	1 In Stock
M105 x 1.00	Cyan	505.00	90.00	#21-606	₹68,508 Volume Pricing	1 In Stock
M105 x 1.00	Green	525.00	80.00	#21-607	₹68,508 Volume Pricing	1 In Stock
M105 x 1.00	Vis	550.00	300.00	#21-608	₹61,657 Volume Pricing	Contact Us
M105 x 1.00	Orange	590.00	75.00	#21-609	₹68,508 Volume Pricing	1 In Stock
M105 x 1.00	Light Red	635.00	60.00	#21-610	₹61,657 Volume Pricing	1 In Stock
M105 x 1.00	Dark Red	660.00	60.00	#21-611	₹61,657 Volume Pricing	1 In Stock
M105 x 1.00	IR	850.00	160.00	#21-612	₹61,657 Volume Pricing	1 In Stock
M62 x 0.75	NUV	324.00	105.00	#21-621	₹22,810 Volume Pricing	1 In Stock

M62 x 0.75	Blue	470.00	85.00	#21-622	₹22,810 Volume Pricing	1 In Stock
M62 x 0.75	Cyan	505.00	90.00	#21-623	₹22,810 Volume Pricing	1 In Stock
M62 x 0.75	Green	525.00	80.00	#21-624	₹22,810 Volume Pricing	1 In Stock
M62 x 0.75	Vis	550.00	300.00	#21-625	₹20,475 Volume Pricing	1 In Stock
M62 x 0.75	Orange	590.00	75.00	#21-626	₹22,810 Volume Pricing	1 In Stock
M62 x 0.75	Light Red	635.00	60.00	#21-627	₹20,475 Volume Pricing	1 In Stock
M62 x 0.75	Dark Red	660.00	60.00	#21-628	₹20,475 Volume Pricing	1 In Stock
M62 x 0.75	IR	850.00	160.00	#21-629	₹20,475 Volume Pricing	1 In Stock
M46 x 0.75	NUV	324.00	105.00	#21-638	₹15,726 Volume Pricing	1 In Stock
M46 x 0.75	Blue	470.00	85.00	#21-639	₹15,726 Volume Pricing	1 In Stock
M46 x 0.75	Cyan	505.00	90.00	#21-640	₹15,726 Volume Pricing	1 In Stock
M46 x 0.75	Green	525.00	80.00	#21-641	₹15,726 Volume Pricing	1 In Stock
M46 x 0.75	Vis	550.00	300.00	#21-642	₹14,169 Volume Pricing	3 In Stock
M46 x 0.75	Orange	590.00	75.00	#21-643	₹15,726 Volume Pricing	1 In Stock
M46 x 0.75	Light Red	635.00	60.00	#21-644	₹14,169 Volume Pricing	1 In Stock
M46 x 0.75	Dark Red	660.00	60.00	#21-645	₹14,169 Volume Pricing	Contact Us
M46 x 0.75	IR	850.00	160.00	#21-646	₹14,169 Volume Pricing	Contact Us
M46 x 0.75	SWIR	940.00	55.00	#28-793	₹18,684	1 In Stock
M46 x 0.75	SWIR	1,000.00	150.00	#28-804	₹33,709	Contact Us
M46 x 0.75	SWIR	1,070.00	-	#28-859	₹25,223	1 In Stock

M46 x 0.75	SWIR	1,300.00	35.00	#28-826	₹32,386	Contact Us
M46 x 0.75	SWIR	1,450.00	35.00	#28-837	₹32,386	1 In Stock
M46 x 0.75	SWIR	1,475.00	-	#28-870	₹25,068	1 In Stock
M46 x 0.75	SWIR	1,550.00	190.00	#28-815	₹33,787	1 In Stock
M46 x 0.75	SWIR	1,550.00	35.00	#28-848	₹32,386	1 In Stock
M40.5 x 0.50	NUV	324.00	105.00	#21-655	₹14,402 Volume Pricing	1 In Stock
M40.5 x 0.50	Blue	470.00	85.00	#21-656	₹14,402 Volume Pricing	1 In Stock
M40.5 x 0.50	Cyan	505.00	90.00	#21-657	₹14,402 Volume Pricing	1 In Stock
M40.5 x 0.50	Green	525.00	80.00	#21-658	₹14,402 Volume Pricing	1 In Stock
M40.5 x 0.50	Vis	550.00	300.00	#21-659	₹13,001 Volume Pricing	3 In Stock
M40.5 x 0.50	Orange	590.00	75.00	#21-660	₹14,402 Volume Pricing	1 In Stock
M40.5 x 0.50	Light Red	635.00	60.00	#21-661	₹13,001 Volume Pricing	1 In Stock
M40.5 x 0.50	Dark Red	660.00	60.00	#21-662	₹13,001 Volume Pricing	1 In Stock
M40.5 x 0.50	IR	850.00	160.00	#21-663	₹13,001 Volume Pricing	1 In Stock
M40.5 x 0.50	SWIR	940.00	55.00	#28-791	₹17,127	1 In Stock
M40.5 x 0.50	SWIR	1,000.00	150.00	#28-802	₹30,595	1 In Stock
M40.5 x 0.50	SWIR	1,070.00	-	#28-857	₹21,175	1 In Stock
M40.5 x 0.50	SWIR	1,300.00	35.00	#28-824	₹31,607	1 In Stock
M40.5 x 0.50	SWIR	1,450.00	35.00	#28-835	₹31,607	1 In Stock
M40.5 x 0.50	SWIR	1,475.00	-	#28-868	₹21,487	1 In Stock
M40.5 x 0.50	SWIR	1,550.00	190.00	#28-813	₹30,595	1 In Stock
M40.5 x 0.50	SWIR	1,550.00	35.00	#28-846	₹31,607	1 In Stock
M37.5 x 0.50	NUV	324.00	105.00	#21-672	₹13,079 Volume Pricing	1 In Stock

M37.5 x 0.50	Blue	470.00	85.00	#21-673	₹13,079 Volume Pricing	1 In Stock
M37.5 x 0.50	Cyan	505.00	90.00	#21-674	₹13,079 Volume Pricing	1 In Stock
M37.5 x 0.50	Green	525.00	80.00	#21-675	₹13,079 Volume Pricing	1 In Stock
M37.5 x 0.50	Vis	550.00	300.00	#21-676	₹11,755 Volume Pricing	2 In Stock
M37.5 x 0.50	Orange	590.00	75.00	#21-677	₹13,079 Volume Pricing	1 In Stock
M37.5 x 0.50	Light Red	635.00	60.00	#21-678	₹11,755 Volume Pricing	1 In Stock
M37.5 x 0.50	Dark Red	660.00	60.00	#21-679	₹11,755 Volume Pricing	1 In Stock
M37.5 x 0.50	IR	850.00	160.00	#21-680	₹11,755 Volume Pricing	2 In Stock
M43 x 0.75	NUV	324.00	105.00	#21-689	₹14,402 Volume Pricing	2 In Stock
M43 x 0.75	Blue	470.00	85.00	#21-690	₹14,402 Volume Pricing	1 In Stock
M43 x 0.75	Cyan	505.00	90.00	#21-691	₹14,402 Volume Pricing	1 In Stock
M43 x 0.75	Green	525.00	80.00	#21-692	₹14,402 Volume Pricing	1 In Stock
M43 x 0.75	Vis	550.00	300.00	#21-693	₹13,001 Volume Pricing	1 In Stock
M43 x 0.75	Orange	590.00	75.00	#21-694	₹14,402 Volume Pricing	1 In Stock
M43 x 0.75	Light Red	635.00	60.00	#21-695	₹13,001 Volume Pricing	1 In Stock
M43 x 0.75	Dark Red	660.00	60.00	#21-696	₹13,001 Volume Pricing	1 In Stock
M43 x 0.75	IR	850.00	160.00	#21-697	₹13,001 Volume Pricing	6 In Stock
M43 x 0.75	SWIR	940.00	55.00	#28-792	₹17,127	1 In Stock
M43 x 0.75	SWIR	1,000.00	150.00	#28-803	₹30,595	1 In Stock
M43 x 0.75	SWIR	1,070.00	-	#28-858	₹23,355	1 In Stock
M43 x 0.75	SWIR	1,300.00	35.00	#28-825	₹32,386	Contact Us

M43 x 0.75	SWIR	1,450.00	35.00	#28-836	₹32,386	Contact Us
M43 x 0.75	SWIR	1,475.00	-	#28-869	₹23,044	1 In Stock
M43 x 0.75	SWIR	1,550.00	190.00	#28-814	₹30,595	1 In Stock
M43 x 0.75	SWIR	1,550.00	35.00	#28-847	₹32,386	1 In Stock
M34 x 0.50	NUV	324.00	105.00	#21-706	₹12,300 Volume Pricing	1 In Stock
M34 x 0.50	Blue	470.00	85.00	#21-707	₹12,300 Volume Pricing	Contact Us
M34 x 0.50	Cyan	505.00	90.00	#21-708	₹12,300 Volume Pricing	1 In Stock
M34 x 0.50	Green	525.00	80.00	#21-709	₹12,300 Volume Pricing	2 In Stock
M34 x 0.50	Vis	550.00	300.00	#21-710	₹11,055 Volume Pricing	2 In Stock
M34 x 0.50	Orange	590.00	75.00	#21-711	₹12,300 Volume Pricing	1 In Stock
M34 x 0.50	Light Red	635.00	60.00	#21-712	₹11,055 Volume Pricing	1 In Stock
M34 x 0.50	Dark Red	660.00	60.00	#21-713	₹11,055 Volume Pricing	1 In Stock
M34 x 0.50	IR	850.00	160.00	#21-714	₹11,055 Volume Pricing	3 In Stock
M34 x 0.50	SWIR	940.00	55.00	#28-788	₹14,636	1 In Stock
M34 x 0.50	SWIR	1,000.00	150.00	#28-799	₹25,691	1 In Stock
M34 x 0.50	SWIR	1,070.00	-	#28-854	₹17,438	Contact Us
M34 x 0.50	SWIR	1,300.00	35.00	#28-821	₹26,703	Contact Us
M34 x 0.50	SWIR	1,450.00	35.00	#28-832	₹26,703	Contact Us
M34 x 0.50	SWIR	1,475.00	-	#28-865	₹17,438	1 In Stock
M34 x 0.50	SWIR	1,550.00	190.00	#28-810	₹25,691	Contact Us
M34 x 0.50	SWIR	1,550.00	35.00	#28-843	₹26,703	1 In Stock

M58 x 0.75	NUV	324.00	105.00	#21-723	₹18,295 Volume Pricing	1 In Stock
M58 x 0.75	Blue	470.00	85.00	#21-724	₹18,295 Volume Pricing	Contact Us
M58 x 0.75	Cyan	505.00	90.00	#21-725	₹18,295 Volume Pricing	1 In Stock
M58 x 0.75	Green	525.00	80.00	#21-726	₹18,295 Volume Pricing	1 In Stock
M58 x 0.75	Vis	550.00	300.00	#21-727	₹16,504 Volume Pricing	1 In Stock
M58 x 0.75	Orange	590.00	75.00	#21-728	₹18,295 Volume Pricing	1 In Stock
M58 x 0.75	Light Red	635.00	60.00	#21-729	₹16,504 Volume Pricing	Contact Us
M58 x 0.75	Dark Red	660.00	60.00	#21-730	₹16,504 Volume Pricing	1 In Stock
M58 x 0.75	IR	850.00	160.00	#21-731	₹16,504 Volume Pricing	7 In Stock
M58 x 0.75	SWIR	940.00	55.00	#28-795	₹21,798	1 In Stock
M58 x 0.75	SWIR	1,000.00	150.00	#28-806	₹37,368	1 In Stock
M58 x 0.75	SWIR	1,070.00	-	#28-861	₹28,337	1 In Stock
M58 x 0.75	SWIR	1,300.00	35.00	#28-828	₹38,847	Contact Us
M58 x 0.75	SWIR	1,450.00	35.00	#28-839	₹38,847	1 In Stock
M58 x 0.75	SWIR	1,475.00	-	#28-872	₹28,337	1 In Stock
M58 x 0.75	SWIR	1,550.00	190.00	#28-817	₹37,368	1 In Stock
M58 x 0.75	SWIR	1,550.00	35.00	#28-850	₹38,847	1 In Stock
M25.5 x 0.50	NUV	324.00	105.00	#21-740	₹10,510 Volume Pricing	1 In Stock
M25.5 x 0.50	Blue	470.00	85.00	#21-741	₹10,510 Volume Pricing	Contact Us
M25.5 x 0.50	Cyan	505.00	90.00	#21-742	₹10,510 Volume Pricing	1 In Stock
M25.5 x 0.50	Green	525.00	80.00	#21-743	₹10,510 Volume Pricing	2 In Stock

M25.5 x 0.50	Vis	550.00	300.00	#21-744	₹9,420 Volume Pricing	2 In Stock
M25.5 x 0.50	Orange	590.00	75.00	#21-745	₹10,510 Volume Pricing	1 In Stock
M25.5 x 0.50	Light Red	635.00	60.00	#21-746	₹9,420 Volume Pricing	Contact Us
M25.5 x 0.50	Dark Red	660.00	60.00	#21-747	₹9,420 Volume Pricing	Contact Us
M25.5 x 0.50	IR	850.00	160.00	#21-748	₹9,420 Volume Pricing	5 In Stock
M25.5 x 0.50	SWIR	940.00	55.00	#28-786	₹12,456	Contact Us
M25.5 x 0.50	SWIR	1,000.00	150.00	#28-797	₹22,499	1 In Stock
M25.5 x 0.50	SWIR	1,070.00	-	#28-852	₹15,103	1 In Stock
M25.5 x 0.50	SWIR	1,300.00	35.00	#28-819	₹22,265	1 In Stock
M25.5 x 0.50	SWIR	1,450.00	35.00	#28-830	₹22,265	1 In Stock
M25.5 x 0.50	SWIR	1,475.00	-	#28-863	₹14,947	2 In Stock
M25.5 x 0.50	SWIR	1,550.00	190.00	#28-808	₹22,265	3 In Stock
M25.5 x 0.50	SWIR	1,550.00	35.00	#28-841	₹22,265	Contact Us
M30.5 x 0.50	NUV	324.00	105.00	#21-757	₹11,288 Volume Pricing	1 In Stock
M30.5 x 0.50	Blue	470.00	85.00	#21-758	₹11,288 Volume Pricing	1 In Stock
M30.5 x 0.50	Cyan	505.00	90.00	#21-759	₹11,288 Volume Pricing	1 In Stock
M30.5 x 0.50	Green	525.00	80.00	#21-760	₹11,288 Volume Pricing	Contact Us
M30.5 x 0.50	Vis	550.00	300.00	#21-761	₹10,121 Volume Pricing	Contact Us
M30.5 x 0.50	Orange	590.00	75.00	#21-762	₹11,288 Volume Pricing	1 In Stock
M30.5 x 0.50	Light Red	635.00	60.00	#21-763	₹10,121 Volume Pricing	1 In Stock
M30.5 x 0.50	Dark Red	660.00	60.00	#21-764	₹10,121 Volume Pricing	2 In Stock

M30.5 x 0.50	IR	850.00	160.00	#21-765	₹10,121 Volume Pricing	1 In Stock
M30.5 x 0.50	SWIR	940.00	55.00	#28-787	₹13,390	1 In Stock
M30.5 x 0.50	SWIR	1,000.00	150.00	#28-798	₹23,900	1 In Stock
M30.5 x 0.50	SWIR	1,070.00	-	#28-853	₹16,193	1 In Stock
M30.5 x 0.50	SWIR	1,300.00	35.00	#28-820	₹24,289	1 In Stock
M30.5 x 0.50	SWIR	1,450.00	35.00	#28-831	₹24,289	1 In Stock
M30.5 x 0.50	SWIR	1,475.00	-	#28-864	₹16,193	1 In Stock
M30.5 x 0.50	SWIR	1,550.00	190.00	#28-809	₹23,900	1 In Stock
M30.5 x 0.50	SWIR	1,550.00	35.00	#28-842	₹24,289	1 In Stock



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038

Phone: 1-800-363-1992 :

www.edmundoptics.com