

[All Products](#) / [Lights and Illumination](#) / [Machine Vision Lighting](#) / [Ring Lights](#)

Effilux SWIR LED Ring Lights



- Full Range of SWIR Wavelengths Available
- High Intensity and Uniform Lighting
- Adjustable Illumination Angles

Common Specifications

General

Number of LEDs:	-	Type of Illumination:	LED Illuminator
Uniformity (%):	>90%	Manufacturer:	Effilux
Geometry:	Ring Light	Illumination Mode:	Strobed or Constant

Physical & Mechanical Properties

Inner Diameter (mm):	58.0	Dimensions (mm):	151.0 W x 117.0 L x 40.0 H
Weight (g):	400	Active Area (mm):	100 x 100

Optical Properties

Color:	SWIR
---------------	------

Hardware & Interface Connectivity

Connector:	M12, 5 pins
Input Voltage (V):	24V DC

Threading & Mounting

Mount:	M4 (x4) and 3.5mm Thru (x4)
Environmental & Durability Factors	
Operating Temperature (°C):	-10 to 50

Technical Information

Products

Title	Stock Number	Price	Buy
SWIR 1050nm Adjustable Ring Light	#28-622	₹3,59,910	Contact Us
SWIR 1200nm Adjustable Ring Light	#28-623	₹3,59,910	Contact Us
SWIR 1300nm Adjustable Ring Light	#28-624	₹3,59,910	Contact Us
SWIR 1450nm Adjustable Ring Light	#28-625	₹3,59,910	2 In Stock
SWIR 1550nm Adjustable Ring Light	#28-626	₹3,59,910	Contact Us
SWIR 1650nm Adjustable Ring Light	#28-627	₹3,59,910	1 In Stock



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038

Phone: 1-800-363-1992 :

www.edmundoptics.com