

[All Products](#) / [Imaging Lenses](#) / [Fixed Focal Length Lenses](#)

TECHSPEC® HP+ Series Fixed Focal Length Lenses



- 1.2", C-Mount Lenses
- Up to 24.5 MegaPixels, 2.74µm Pixel Size Sensors
- 16mm to 35mm Focal Length

Common Specifications

General

Imaging Lens Type:	High Performance Lens
--------------------	-----------------------

Physical & Mechanical Properties

Iris Option:	Variable
--------------	----------

Optical Properties

Maximum Image Circle (mm):	19.30	Coating:	$\lambda/4$ MgF ₂
----------------------------	-------	----------	------------------------------

Coating Specification:	$\lambda/4$ MgF ₂
------------------------	------------------------------

Sensor

Maximum Sensor Format:	1.2"
------------------------	------

Threading & Mounting

Mount:	C-Mount
--------	---------

Environmental & Durability Factors

Storage Temperature (°C):	-20 to +60 For questions regarding operating temperature please contact our support team
---------------------------	--

Technical Information

Products

FL (mm)	Max. Sensor Format	Aperture (f/#)	WD (mm)	Mount	Stock Number	Price	Buy
#20-224 New							
12.00	1.2"	f/2.8 – 16	100mm to ∞	C- Mount		New	
Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!							
12.00	1.2"	f/2.8 – 16	100mm to ∞	C- Mount	#20-224	₹46,719	Contact Us
1 In Stock							
16.00	1.2"	f/2.8 – 16	100 - ∞	C- Mount	#20-225	₹74,385	1 In Stock
3 In Stock							
25.00	1.2"	f/2.8 – 22	200 - ∞	C- Mount	#20-226	₹70,079	3 In Stock
4 In Stock							
35.00	1.2"	f/2.8 – 16	200 - ∞	C- Mount	#20-227	₹70,079	4 In Stock



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038

Phone: 1-800-363-1992 :

www.edmundoptics.com