

[All Products](#) / [Cameras](#) / [Gigabit Ethernet Cameras](#)

Teledyne Imaging DALSA Linea Lite GigE Line Scan Cameras

See More by [Teledyne DALSA](#)



- Compact 46 x 46mm Form Factor
- Line Rates from 12.5 – 50kHz
- 2k, 4k, or 8k Resolution Options Available
- Simple Integration with Gigabit Ethernet Connectivity
- Teledyne TurboDrive™ Enabled
- Monochrome and Color Options Available

Common Specifications

General			
Manufacturer:	Teledyne DALSA	Camera Series:	LINEA™ LITE
Physical & Mechanical Properties			
Dimensions (mm):	46 x 46 x 37 (excludes connectors and lens mount)	Weight (g):	111
Housing:	Full		
Sensor			
Type of Sensor:	DALSA Line Scan CMOS		
Dynamic Range (dB):	72.00	Machine Vision Standard:	GigE Vision
Read Noise (e ⁻):	8.5		
Hardware & Interface Connectivity			
Interface:	GigE (PoE)		
Connector:	GigE, RJ45 with Screw Locks	Power Supply:	+12 to +24V DC HD15 Connector or 48V POE
Interface Port Orientation:	Back Panel	GPIO Connector Type:	HD15 (High Density)
Threading & Mounting			
Mount:	M42-Mount		
Environmental & Durability Factors			
Operating Temperature (°C):	-10 to +65		

Technical Information

Products

Type	Model Number	Resolution (Pixels)	Mount	Stock Number	Price	Buy
Monochrome Camera	L2-GM-02K05B-00-A	2048.00	M42-Mount	#71-774	₹63,945	Contact Us
Monochrome Camera	L2-GM-04K02B-00-A	4096.00	M42-Mount	#71-775	₹73,080	1 In Stock
Monochrome Camera	L2-GM-08k02S-00-A	8192.00	M42-Mount	#71-776	₹99,615	2 In Stock
Color Camera	L2-GC-02K02B-00-A	2048 x 2	M42-Mount	#71-777	₹67,164	1 In Stock
Color Camera	L2-GC-04K01B-00-A	4096 x 2	M42-Mount	#71-778	₹76,734	Contact Us



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038

Phone: 1-800-363-1992 :

www.edmundoptics.com