


1" x 1" (30 lp/mm), Ronchi Ruling



Stock #66-347 CLEARANCE **1 In Stock**

₹20,340

ADD TO CART

Volume Pricing	
Qty 1-4	₹20,340 each
Qty 5+	₹19,386 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Metric Type:

Physical & Mechanical Properties

Dimensional Tolerance (inches):

±0.02

Dimensions (inches):

1 x 1

Thickness (mm):

1.50

Dimensional Tolerance (mm):

± 0.02

Line to Line Parallelism (arcsec):

≤2

Parallelism of Pattern to Substrate (°):

±1

Optical Properties

Coating:

Vacuum Deposited Chrome, OD >3.0

Frequency (lp/mm):

30

Substrate:

Float Glass

Optical Density OD (Average):

3.00

Surface Quality:

20-10

Surface Flatness (P-V):

1λ

Regulatory Compliance

RoHS 2015:

[Compliant](#)

Certificate of Conformance:

[View](#)

Reach 240:

[Compliant](#)

PRODUCT DETAILS

- Chrome on Glass
- High Tolerance
- Superior to Etched and Filled Rulings
- Lines Parallel to Edge
- English and Metric Versions Available

High Precision Ronchi Rulings are excellent for evaluating resolution, field distortion, and parfocal stability. The glass targets are coated with vacuum-deposited chrome and have a float glass substrate. English and Metric version are available with various Linepairs Per Inch (LPI) and Linepairs Per Millimeter (lp/mm) measurements. High Precision Ronchi Rulings are offered in 0.5", 1", 2", and 4" squares.