

2" x 2" Green Advanced Illumination Side-Fired Backlight

See More by [Advanced Illumination](#)



Stock **#88-502** CLEARANCE **2 In Stock**

-

1

+

₹34,883

ADD TO CART

Volume Pricing	
Qty 1+	₹34,883 each
Need More?	Request Quote

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

SPECIFICATIONS

General

	Model Number:
BX0202-530-IC	
	LED Lifetime (hours):
50,000	

1.00	Number of Channels:
LED Illuminator	Type of Illumination:
Advanced Illumination	Manufacturer:
Backlight	Geometry:
Constant	Illumination Mode:

Physical & Mechanical Properties

115.1 L x 115.1 W x 20.1 D	Dimensions (mm):
2 x 2	Active Area (inches):

Optical Properties

Green	Color:
530.00	Wavelength (nm):

Hardware & Interface Connectivity

Power Supply Required and Sold Separately: USA: #66-855 Europe: #66-855 Japan: #89-513 Korea: #33-773 China: #66-855	Power Supply:
---	---------------

Environmental & Durability Factors

0 to 60	Operating Temperature (°C):
---------	-----------------------------

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	Reach 233:

PRODUCT DETAILS

- 30% Brighter than Comparable Surface Mount Light
 - Uniform, Low Heat Illumination
- Advanced Illumination Side-Fired LED Backlights are high performance alternatives to surface mount lights. Advanced Illumination Side-Fired LED Backlights provide uniform, low heat illumination that is 30% brighter than surface mount lights of equal size. To simplify system integration, these backlights include mounting brackets and mounting channels for M6 nuts.
- Note:** Required 24V power supply [#66-855](#). [Accessories for Advanced Illumination products](#) are available and sold separately. Units cannot be intensity controlled.