

[All Products](#) / [Lasers](#) / [Laser Safety](#) / [Laser Safety Glasses and Goggles](#)

Laser Safety Glasses and Goggles



- CE Certified Laser Radiation Protection
- Designs for Ultraviolet, Visible, and Infrared Lasers
- Available in Goggles, Glasses, or Comfort Glasses Styles

Technical Information

Products

Filter	Optical Density OD (Average)	Visible Light Transmission VLT (%)	Style	Stock Number	Price	Buy
LS01	>7 @ 190 - 398nm >7 @ 9000 - 11,000nm	93	Adjustable Temples Wrap Around	#12-730	₹11,223	7 In Stock
LS02	>7 @ 180 - 532nm	48	Adjustable Temples Wrap Around	#12-731	₹12,267	Contact Us
#75-528 New						
						
LS02	>7 @ 180 - 532nm	48	Rx Flip Up	New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	₹9,135	1 In Stock

[#75-550 New](#)



New

Launched
on our
website
before
appearing
in our
latest print
catalogs.
Be the
first to buy
before
anyone
else!

LS02	>7 @ 180 - 532nm	48	Vented Fit Over		₹9,135	Contact Us
------	---------------------	----	--------------------	--	--------	------------

LS03	>6 @ 190 - 400nm, 532nm, 561nm	19	Adjustable Temples Wrap Around	#12-732	₹21,600 Volume Pricing	5 In Stock
------	---	----	---	-------------------------	---	------------

LS04	>5 @ 190 - 400nm >4 @ 625 - 850nm >5 @ 633nm >5 @ 662 - 835nm	14	Adjustable Temples Wrap Around	#12-733	₹15,660	5 In Stock
------	--	----	---	-------------------------	---------	------------

LS05	>6 @ 190 - 400nm >3 @ 615 - 720nm >4 @ 651 - 670nm >5 @ 671 - 715nm >6 @ 680 - 710nm >7 @ 690 - 700nm	35	Adjustable Temples Wrap Around	#12-734	₹18,531	3 In Stock
------	--	----	---	-------------------------	---------	------------

LS06	>6 @ 190 - 400nm >7 @ 720 - 810nm >5 @ 810 - 830nm	33	Adjustable Temples Wrap Around	#12-735	₹20,358	4 In Stock
------	---	----	---	-------------------------	---------	------------

LS07	>5 @ 190 - 435nm >1 @ 650 - 680nm >2 @ 680 - 720nm >5 @ 730 - 1085nm >6 @ 745 - 765nm >7 @ 755, 1064nm	36	Adjustable Temples Wrap Around	#12-736	₹15,660	Contact Us
LS08	>5 @ 190 - 400nm >5 @ 800 - 830nm >7 @ 805 - 825nm	69	Adjustable Temples Wrap Around	#12-737	₹17,400	Contact Us
LS09	>6 @ 190 - 450nm >1 @ 700 - 770nm >2 @ 770 - 1840nm >3 @ 820 - 1720nm >4 @ 870 - 1600nm >5 @ 940 - 1070nm >1 @ 1840 - 1950nm	19	Adjustable Temples Wrap Around	#12-738	₹20,358	2 In Stock
LS10	>5 @ 190 - 400nm >2 @ 1450 - 1650nm >3 @ 1650 - 1775nm >4 @ 1775 - 3000nm >5 @ 1980 - 2550nm >5 @ 5,200 - 11,000nm >6 @ 9,000 - 10,600nm	41	Adjustable Temples Wrap Around	#12-739	₹15,660	1 In Stock

LS11	>5 @ 190 - 420nm >5 @ 765 - 1100nm >6 @ 775 - 1085nm >7 @ 790 - 1080nm	45	Adjustable Temples Wrap Around	#12-740	₹17,400	5 In Stock
LS12	>5 @ 190 - 400nm >5 @ 1025 - 1075nm >6 @ 1035 - 1070nm >7 @ 1045 - 1065nm	55	Adjustable Temples Wrap Around	#12-741	₹25,200 Volume Pricing	2 In Stock
LS13	>5 @ 190 - 400nm >4 @ 808 - 840nm >5 @ 840 - 950nm >7 @ 950 - 1080nm >5 @ 1080 - 1090nm	59	Adjustable Temples Wrap Around	#12-742	₹17,400	1 In Stock
LS14	>7 @ 190 - 534nm >5 @ 850 - 925nm >6 @ 925 - 1070nm >7 @ 960 - 1064nm	35	Adjustable Temples Wrap Around	#12-743	₹19,575	3 In Stock
LS15	>7 @ 180 - 534nm >5 @ 720 - 770nm >7 @ 750 - 760nm >4 @ 770 - 850nm >5 @ 850 - 1080nm >7 @ 980 - 1064nm	22	Adjustable Temples Wrap Around	#12-744	₹28,620 Volume Pricing	1 In Stock

LS16	>0.5 @ 500 - 770nm >5 @ 770 - 810nm >7 @ 810 - 1100nm >1.5 @ 1100 - 1800nm	26	Adjustable Temples Wrap Around	#12-745	₹25,200 Volume Pricing	1 In Stock
LS17	>3 @ 850 - 2800nm >4 @ 900 - 2600nm >5 @ 950 - 1010nm >7 @ 1010 - 1500nm >5 @ 1500 - 2350nm >5 @ 2800 - 10,600nm	75	Adjustable Temples Wrap Around	#12-746	₹30,450	Contact Us
LS01	>7 @ 190 - 398nm >7 @ 9000 - 11,000nm	93	Fit Over Rx Glasses	#12-713	₹11,223	5 In Stock
LS02	>7 @ 180 - 532nm	48	Fit Over Rx Glasses	#12-714	₹12,267	5 In Stock
LS03	>6 @ 190 - 400nm, 532nm, 561nm	19	Fit Over Rx Glasses	#12-715	₹21,600 Volume Pricing	3 In Stock
LS04	>5 @ 190 - 400nm >4 @ 625 - 850nm >5 @ 633nm >5 @ 662 - 835nm	14	Fit Over Rx Glasses	#12-716	₹16,530	2 In Stock

LS05	>6 @ 190 - 400nm >3 @ 615 - 720nm >4 @ 651 - 670nm >5 @ 671 - 715nm >6 @ 680 - 710nm >7 @ 690 - 700nm	35	Fit Over Rx Glasses	#12-717	₹18,531	1 In Stock
LS06	>6 @ 190 - 400nm >7 @ 720 - 810nm >5 @ 810 - 830nm	33	Fit Over Rx Glasses	#12-718	₹19,575	2 In Stock
LS07	>5 @ 190 - 435nm >1 @ 650 - 680nm >2 @ 680 - 720nm >5 @ 730 - 1085nm >6 @ 745 - 765nm >7 @ 755, 1064nm	36	Fit Over Rx Glasses	#12-719	₹15,660	2 In Stock
LS08	>5 @ 190 - 400nm >5 @ 800 - 830nm >7 @ 805 - 825nm	69	Fit Over Rx Glasses	#12-720	₹22,320 Volume Pricing	2 In Stock
LS09	>6 @ 190 - 450nm >1 @ 700 - 770nm >2 @ 770 - 1840nm >3 @ 820 - 1720nm >4 @ 870 - 1600nm >5 @ 940 - 1070nm >1 @ 1840 - 1950nm	19	Fit Over Rx Glasses	#12-721	₹20,358	3 In Stock

LS10	>5 @ 190 - 400nm >2 @ 1450 - 1650nm >3 @ 1650 - 1775nm >4 @ 1775 - 3000nm >5 @ 1980 - 2550nm >5 @ 5,200 - 11,000nm >6 @ 9,000 - 10,600nm	41	Fit Over Rx Glasses	#12-722	₹15,660	3 In Stock
LS11	>5 @ 190 - 420nm >5 @ 765 - 1100nm >6 @ 775 - 1085nm >7 @ 790 - 1080nm	45	Fit Over Rx Glasses	#12-723	₹17,400	8 In Stock
LS12	>5 @ 190 - 400nm >5 @ 1025 - 1075nm >6 @ 1035 - 1070nm >7 @ 1045 - 1065nm	55	Fit Over Rx Glasses	#12-724	₹17,835	2 In Stock
LS13	>5 @ 190 - 400nm >4 @ 808 - 840nm >5 @ 840 - 950nm >7 @ 950 - 1080nm >5 @ 1080 - 1090nm	59	Fit Over Rx Glasses	#12-725	₹17,400	Contact Us

LS14	>7 @ 190 - 534nm >5 @ 850 - 925nm >6 @ 925 - 1070nm >7 @ 960 - 1064nm	35	Fit Over Rx Glasses	#12-726	₹19,575	1 In Stock
LS15	>7 @ 180 - 534nm >5 @ 720 - 770nm >7 @ 750 - 760nm >4 @ 770 - 850nm >5 @ 850 - 1080nm >7 @ 980 - 1064nm	22	Fit Over Rx Glasses	#12-727	₹28,620 Volume Pricing	4 In Stock
LS16	>0.5 @ 500 - 770nm >5 @ 770 - 810nm >7 @ 810 - 1100nm >1.5 @ 1100 - 1800nm	26	Fit Over Rx Glasses	#12-728	₹25,200 Volume Pricing	Contact Us
LS17	>3 @ 850 - 2800nm >4 @ 900 - 2600nm >5 @ 950 - 1010nm >7 @ 1010 - 1500nm >5 @ 1500 - 2350nm >5 @ 2800 - 10,600nm	75	Fit Over Rx Glasses	#12-729	₹30,450	Contact Us
LS01	>7 @ 190 - 398nm >7 @ 9000 - 11,000nm	93	Goggles	#12-696	₹11,223	2 In Stock
LS02	>7 @ 180 - 532nm	48	Goggles	#12-697	₹12,267	Contact Us

LS03	>6 @ 190 - 400nm, 532nm, 561nm	19	Goggles	#12-698	₹21,600 Volume Pricing	2 In Stock
LS04	>5 @ 190 - 400nm >4 @ 625 - 850nm >5 @ 633nm >5 @ 662 - 835nm	14	Goggles	#12-699	₹16,530	Contact Us
LS05	>6 @ 190 - 400nm >3 @ 615 - 720nm >4 @ 651 - 670nm >5 @ 671 - 715nm >6 @ 680 - 710nm >7 @ 690 - 700nm	35	Goggles	#12-700	₹18,531	2 In Stock
LS06	>6 @ 190 - 400nm >7 @ 720 - 810nm >5 @ 810 - 830nm	33	Goggles	#12-701	₹19,575	1 In Stock
LS07	>5 @ 190 - 435nm >1 @ 650 - 680nm >2 @ 680 - 720nm >5 @ 730 - 1085nm >6 @ 745 - 765nm >7 @ 755, 1064nm	36	Goggles	#12-702	₹15,660	2 In Stock
LS08	>5 @ 190 - 400nm >5 @ 800 - 830nm >7 @ 805 - 825nm	69	Goggles	#12-703	₹17,400	2 In Stock

LS09	>6 @ 190 - 450nm >1 @ 700 - 770nm >2 @ 770 - 1840nm >3 @ 820 - 1720nm >4 @ 870 - 1600nm >5 @ 940 - 1070nm >1 @ 1840 - 1950nm	19	Goggles	#12-704	₹15,660	3 In Stock
LS10	>5 @ 190 - 400nm >2 @ 1450 - 1650nm >3 @ 1650 - 1775nm >4 @ 1775 - 3000nm >5 @ 1980 - 2550nm >5 @ 5,200 - 11,000nm >6 @ 9,000 - 10,600nm	41	Goggles	#12-705	₹15,660	3 In Stock
LS11	>5 @ 190 - 420nm >5 @ 765 - 1100nm >6 @ 775 - 1085nm >7 @ 790 - 1080nm	45	Goggles	#12-706	₹17,400	2 In Stock
LS12	>5 @ 190 - 400nm >5 @ 1025 - 1075nm >6 @ 1035 - 1070nm >7 @ 1045 - 1065nm	55	Goggles	#12-707	₹25,200 Volume Pricing	1 In Stock

LS13	>5 @ 190 - 400nm >4 @ 808 - 840nm >5 @ 840 - 950nm >7 @ 950 - 1080nm >5 @ 1080 - 1090nm	59	Goggles	#12-708	₹17,400	3 In Stock
LS14	>7 @ 190 - 534nm >5 @ 850 - 925nm >6 @ 925 - 1070nm >7 @ 960 - 1064nm	35	Goggles	#12-709	₹19,575	Contact Us
LS15	>7 @ 180 - 534nm >5 @ 720 - 770nm >7 @ 750 - 760nm >4 @ 770 - 850nm >5 @ 850 - 1080nm >7 @ 980 - 1064nm	22	Goggles	#12-710	₹28,620 Volume Pricing	1 In Stock
LS16	>0.5 @ 500 - 770nm >5 @ 770 - 810nm >7 @ 810 - 1100nm >1.5 @ 1100 - 1800nm	26	Goggles	#12-711	₹25,200 Volume Pricing	6 In Stock
LS01	>7 @ 190 - 398nm >7 @ 9000 - 11,000nm	93	Adjustable Bridge Wrap Around	#18-346	₹11,223	1 In Stock
LS02	>7 @ 180 - 532nm	48	Adjustable Bridge Wrap Around	#18-347	₹12,267	Contact Us

LS03	>6 @ 190 - 400nm, 532nm, 561nm	19	Adjustable Bridge Wrap Around	#18-348	₹21,600 Volume Pricing	2 In Stock
LS04	>5 @ 190 - 400nm >4 @ 625 - 850nm >5 @ 633nm >5 @ 662 - 835nm	14	Adjustable Bridge Wrap Around	#18-349	₹16,530	4 In Stock
LS05	>6 @ 190 - 400nm >3 @ 615 - 720nm >4 @ 651 - 670nm >5 @ 671 - 715nm >6 @ 680 - 710nm >7 @ 690 - 700nm	35	Adjustable Bridge Wrap Around	#18-350	₹18,531	2 In Stock
LS06	>6 @ 190 - 400nm >7 @ 720 - 810nm >5 @ 810 - 830nm	33	Adjustable Bridge Wrap Around	#18-351	₹20,184	3 In Stock
LS07	>5 @ 190 - 435nm >1 @ 650 - 680nm >2 @ 680 - 720nm >5 @ 730 - 1085nm >6 @ 745 - 765nm >7 @ 755, 1064nm	36	Adjustable Bridge Wrap Around	#18-352	₹15,660	1 In Stock
LS08	>5 @ 190 - 400nm >5 @ 800 - 830nm >7 @ 805 - 825nm	69	Adjustable Bridge Wrap Around	#18-353	₹17,400	3 In Stock

LS09	>6 @ 190 - 450nm >1 @ 700 - 770nm >2 @ 770 - 1840nm >3 @ 820 - 1720nm >4 @ 870 - 1600nm >5 @ 940 - 1070nm >1 @ 1840 - 1950nm	19	Adjustable Bridge Wrap Around	#18-354	₹20,358	1 In Stock
LS10	>5 @ 190 - 400nm >2 @ 1450 - 1650nm >3 @ 1650 - 1775nm >4 @ 1775 - 3000nm >5 @ 1980 - 2550nm >5 @ 5,200 - 11,000nm >6 @ 9,000 - 10,600nm	41	Adjustable Bridge Wrap Around	#18-355	₹17,400	1 In Stock
LS11	>5 @ 190 - 420nm >5 @ 765 - 1100nm >6 @ 775 - 1085nm >7 @ 790 - 1080nm	45	Adjustable Bridge Wrap Around	#18-356	₹17,400	3 In Stock
LS12	>5 @ 190 - 400nm >5 @ 1025 - 1075nm >6 @ 1035 - 1070nm >7 @ 1045 - 1065nm	55	Adjustable Bridge Wrap Around	#18-357	₹23,850 Volume Pricing	3 In Stock

LS13	>5 @ 190 - 400nm >4 @ 808 - 840nm >5 @ 840 - 950nm >7 @ 950 - 1080nm >5 @ 1080 - 1090nm	59	Adjustable Bridge Wrap Around	#18-358	₹17,400	2 In Stock
LS14	>7 @ 190 - 534nm >5 @ 850 - 925nm >6 @ 925 - 1070nm >7 @ 960 - 1064nm	35	Adjustable Bridge Wrap Around	#18-359	₹19,575	Contact Us
LS15	>7 @ 180 - 534nm >5 @ 720 - 770nm >7 @ 750 - 760nm >4 @ 770 - 850nm >5 @ 850 - 1080nm >7 @ 980 - 1064nm	22	Adjustable Bridge Wrap Around	#18-360	₹28,620 Volume Pricing	5 In Stock
LS16	>0.5 @ 500 - 770nm >5 @ 770 - 810nm >7 @ 810 - 1100nm >1.5 @ 1100 - 1800nm	26	Adjustable Bridge Wrap Around	#18-361	₹25,200 Volume Pricing	4 In Stock

[#75-523 New](#)



LS17 and LS02	>3 @ 850 - 2800nm >4 @ 900 - 2600nm >5 @ 950 - 1010nm >7 @ 1010 - 1500nm >5 @ 1500 - 2350nm >5 @ 2800 - 10,600nm >7 @ 180 - 532nm	75 and 48	1 + 1 Flip Up	New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	₹33,495	1 In Stock
---------------------	---	-----------	------------------	---	---------	------------

LS18	>7 @ 190 - 534nm >5 @ 760 - 1090nm >7 @ 790 - 850nm >6 @ 851 - 960nm >7 @ 961 - 1070nm	22	Adjustable Temples Wrap Around	#17-641	₹21,750	1 In Stock
------	---	----	---	-------------------------	---------	------------

LS18	>7 @ 190 - 534nm >5 @ 760 - 1090nm >7 @ 790 - 850nm >6 @ 851 - 960nm >7 @ 961 - 1070nm	22	Fit Over Rx Glasses	#17-645	₹21,750	2 In Stock
------	---	----	---------------------------	-------------------------	---------	------------

LS18	>7 @ 190 - 534nm >5 @ 760 - 1090nm >7 @ 790 - 850nm >6 @ 851 - 960nm >7 @ 961 - 1070nm	22	Adjustable Bridge Wrap Around	#17-649	₹21,750	3 In Stock
------	---	----	--	-------------------------	---------	------------

LS19	>5 @ 1025 - 1075nm >6 @ 1035 - 1070nm >7 @ 1045 - 1065nm >2 @ 1450 - 1650nm >3 @ 1651 - 1775nm >4 @ 1776 - 3000nm >5 @ 1980 - 2550nm >5 @ 5200 - 11,000nm >6 @ 9000 - 10,600nm	23	Adjustable Temples Wrap Around	#17-639	₹24,480 Volume Pricing	1 In Stock
LS19	>5 @ 1025 - 1075nm >6 @ 1035 - 1070nm >7 @ 1045 - 1065nm >2 @ 1450 - 1650nm >3 @ 1651 - 1775nm >4 @ 1776 - 3000nm >5 @ 1980 - 2550nm >5 @ 5200 - 11,000nm >6 @ 9000 - 10,600nm	23	Fit Over Rx Glasses	#17-643	₹24,480 Volume Pricing	2 In Stock

LS19	>5 @ 1025 - 1075nm >6 @ 1035 - 1070nm >7 @ 1045 - 1065nm >2 @ 1450 - 1650nm >3 @ 1651 - 1775nm >4 @ 1776 - 3000nm >5 @ 1980 - 2550nm >5 @ 5200 - 11,000nm >6 @ 9000 - 10,600nm	23	Adjustable Bridge Wrap Around	#17-647	₹24,480 Volume Pricing	1 In Stock
LS20	>8 @ 190 - 532nm >5 @ 730 - 1110nm >7 @ 745 - 1100nm >9 @ 753 - 765nm >10 @ 765 - 800nm >8 @ 801 - 980nm >10 @ 981 - 1065nm	13	Adjustable Temples Wrap Around	#17-640	₹25,230	1 In Stock

LS20	>8 @ 190 - 532nm >5 @ 730 - 1110nm >7 @ 745 - 1100nm >9 @ 753 - 765nm >10 @ 765 - 800nm >8 @ 801 - 980nm >10 @ 981 - 1065nm	13	Fit Over Rx Glasses	#17-644	₹25,230	5 In Stock
LS20	>8 @ 190 - 532nm >5 @ 730 - 1110nm >7 @ 745 - 1100nm >9 @ 753 - 765nm >10 @ 765 - 800nm >8 @ 801 - 980nm >10 @ 981 - 1065nm	13	Adjustable Bridge Wrap Around	#17-648	₹25,230	2 In Stock
LS21	>6 @ 180 - 400nm >5 @ 720 - 1090nm >7 @ 750 - 1064nm	25	Adjustable Temples Wrap Around	#17-642	₹19,575	3 In Stock
LS21	>6 @ 180 - 400nm >5 @ 720 - 1090nm >7 @ 750 - 1064nm	25	Fit Over Rx Glasses	#17-646	₹19,140	2 In Stock
LS21	>6 @ 180 - 400nm >5 @ 720 - 1090nm >7 @ 750 - 1064nm	25	Adjustable Bridge Wrap Around	#17-650	₹19,575	4 In Stock

[#74-518 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

LS01	>7 @ 190 - 398nm >7 @ 9000 - 11,000nm	93	Vented Adjustable Temples	₹7,308 Volume Pricing	2 In Stock
------	--	----	---------------------------	--	------------

[#74-512 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

LS02	>7 @ 180 - 532nm	48	Vented Adjustable Temples	₹8,091 Volume Pricing	9 In Stock
------	------------------	----	---------------------------	--	------------

[#74-522 New](#)



LS05	>6 @ 190 - 400nm >3 @ 615 - 720nm >4 @ 651 - 670nm >5 @ 671 - 715nm >6 @ 680 - 710nm >7 @ 690 - 700nm	35	Vented Adjustable Temples	New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	₹12,702 Volume Pricing	Contact Us
------	--	----	---------------------------------	---	---	------------

[#90-857 New](#)



LS06	>6 @ 190 - 400nm >7 @ 720 - 810nm >5 @ 810 - 830nm	33	Vented Adjustable Temples	New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	₹15,660	2 In Stock
------	---	----	---------------------------------	---	---------	------------

[#90-864 New](#)



New

LS08	>5 @ 190 - 400nm >5 @ 800 - 830nm >7 @ 805 - 825nm	69	Vented Adjustable Temples	Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	₹16,530	2 In Stock
------	---	----	---------------------------------	--	---------	------------

[#74-526 New](#)



New

LS09	>6 @ 190 - 450nm >1 @ 700 - 770nm >2 @ 770 - 1840nm >3 @ 820 - 1720nm >4 @ 870 - 1600nm >5 @ 940 - 1070nm >1 @ 1840 - 1950nm	19	Vented Adjustable Temples	Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	₹13,920 Volume Pricing	1 In Stock
------	--	----	---------------------------------	--	---	------------

[#90-867 New](#)

LS10	>5 @ 190 - 400nm >2 @ 1450 - 1650nm >3 @ 1650 - 1775nm >4 @ 1775 - 3000nm >5 @ 1980 - 2550nm >5 @ 5,200 - 11,000nm >6 @ 9,000 - 10,600nm	41	Vented Adjustable Temples	 New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	₹15,225	2 In Stock
------	--	----	---------------------------	--	---------	------------

[#90-868 New](#)

LS12	>5 @ 190 - 400nm >5 @ 1025 - 1075nm >6 @ 1035 - 1070nm >7 @ 1045 - 1065nm	55	Vented Adjustable Temples	 New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	₹17,835	2 In Stock
------	--	----	---------------------------	--	---------	------------

[#74-527 New](#)



LS13	>5 @ 190 - 400nm >4 @ 808 - 840nm >5 @ 840 - 950nm >7 @ 950 - 1080nm >5 @ 1080 - 1090nm	59	Vented Adjustable Temples	New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	₹13,920 Volume Pricing	1 In Stock
------	---	----	---------------------------------	---	---	------------

[#74-521 New](#)



LS14	>7 @ 190 - 534nm >5 @ 850 - 925nm >6 @ 925 - 1070nm >7 @ 960 - 1064nm	35	Vented Adjustable Temples	New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	₹17,400 Volume Pricing	1 In Stock
------	--	----	---------------------------------	---	---	------------

[#90-833 New](#)



New

LS03	>6 @ 190 - 400nm, 532nm, 561nm	19	Vented Fit Over	Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	₹16,095	2 In Stock
------	---	----	--------------------	--	---------	------------

[#90-834 New](#)



New

LS04	>5 @ 190 - 400nm >4 @ 625 - 850nm >5 @ 633nm >5 @ 662 - 835nm	14	Vented Fit Over	Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	₹14,355	Contact Us
------	--	----	--------------------	--	---------	------------

[#90-835 New](#)



LS05	>6 @ 190 - 400nm >3 @ 615 - 720nm >4 @ 651 - 670nm >5 @ 671 - 715nm >6 @ 680 - 710nm >7 @ 690 - 700nm	35	Vented Fit Over	New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	₹14,355	2 In Stock
------	--	----	--------------------	---	---------	------------

[#90-836 New](#)



LS06	>6 @ 190 - 400nm >7 @ 720 - 810nm >5 @ 810 - 830nm	33	Vented Fit Over	New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	₹15,660	2 In Stock
------	---	----	--------------------	---	---------	------------

[#90-838 New](#)



LS07	>5 @ 190 - 435nm >1 @ 650 - 680nm >2 @ 680 - 720nm >5 @ 730 - 1085nm >6 @ 745 - 765nm >7 @ 755, 1064nm	36	Vented Fit Over	New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	₹15,660	2 In Stock
------	---	----	--------------------	---	---------	------------

[#90-839 New](#)



LS08	>5 @ 190 - 400nm >5 @ 800 - 830nm >7 @ 805 - 825nm	69	Vented Fit Over	New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	₹16,530	2 In Stock
------	---	----	--------------------	---	---------	------------

[#90-841 New](#)

LS09	>6 @ 190	19	Vented Fit Over	 New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	₹15,660	2 In Stock
	- 450nm					
	>1 @ 700					
	- 770nm					
	>2 @ 770					
	- 1840nm					
	>3 @ 820					
	- 1720nm					
	>4 @ 870					
	- 1600nm					
	>5 @ 940					
	- 1070nm					
	>1 @					
	1840 - 1950nm					

[#90-843 New](#)

LS10	>5 @ 190	41	Vented Fit Over	 New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	₹15,225	2 In Stock
	- 400nm					
	>2 @					
	1450 -					
	1650nm					
	>3 @					
	1650 -					
	1775nm					
	>4 @					
	1775 -					
	3000nm					
	>5 @					
	1980 -					
	2550nm					
	>5 @					
	5,200 -					
	11,000nm					
	>6 @					
	9,000 -					
	10,600nm					

[#90-844 New](#)



New

LS11	>5 @ 190 - 420nm >5 @ 765 - 1100nm >6 @ 775 - 1085nm >7 @ 790 - 1080nm	45	Vented Fit Over	Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	₹17,400	2 In Stock
------	---	----	--------------------	--	---------	------------

[#90-845 New](#)



New

LS12	>5 @ 190 - 400nm >5 @ 1025 - 1075nm >6 @ 1035 - 1070nm >7 @ 1045 - 1065nm	55	Vented Fit Over	Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	₹17,835	2 In Stock
------	---	----	--------------------	--	---------	------------

[#90-847 New](#)



LS13	>5 @ 190 - 400nm >4 @ 808 - 840nm >5 @ 840 - 950nm >7 @ 950 - 1080nm >5 @ 1080 - 1090nm	59	Vented Fit Over	New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	₹15,660	2 In Stock
------	---	----	--------------------	---	---------	------------

[#90-848 New](#)



LS14	>7 @ 190 - 534nm >5 @ 850 - 925nm >6 @ 925 - 1070nm >7 @ 960 - 1064nm	35	Vented Fit Over	New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	₹19,575	1 In Stock
------	--	----	--------------------	---	---------	------------

[#90-851 New](#)



LS15	>7 @ 180 - 534nm >5 @ 720 - 770nm >7 @ 750 - 760nm >4 @ 770 - 850nm >5 @ 850 - 1080nm >7 @ 980 - 1064nm	22	Vented Fit Over	New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	₹20,880	1 In Stock
------	--	----	--------------------	---	---------	------------

[#90-852 New](#)



LS16	>0.5 @ 500 - 770nm >5 @ 770 - 810nm >7 @ 810 - 1100nm >1.5 @ 1100 - 1800nm	26	Vented Fit Over	New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	₹17,835	Contact Us
------	---	----	--------------------	---	---------	------------

[#90-853 New](#)



LS18	>7 @ 190 - 534nm >5 @ 760 - 1090nm >7 @ 790 - 850nm >6 @ 851 - 960nm >7 @ 961 - 1070nm	22	Vented Fit Over	New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	₹21,750	1 In Stock
------	---	----	--------------------	---	---------	------------

[#90-854 New](#)



LS19	>5 @ 1025 - 1075nm >6 @ 1035 - 1070nm >7 @ 1045 - 1065nm >2 @ 1450 - 1650nm >3 @ 1651 - 1775nm >4 @ 1776 - 3000nm >5 @ 1980 - 2550nm >5 @ 5200 - 11,000nm >6 @ 9000 - 10,600nm	23	Vented Fit Over	New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	₹18,270	2 In Stock
------	--	----	--------------------	---	---------	------------

[#90-855 New](#)



New

Launched
on our
website
before
appearing
in our
latest print
catalogs.
Be the
first to buy
before
anyone
else!

LS20	>8 @ 190 - 532nm >5 @ 730 - 1110nm >7 @ 745 - 1100nm >9 @ 753 - 765nm >10 @ 765 - 865 -	13	Vented Fit Over	₹25,230	1 In Stock
------	---	----	--------------------	---------	------------



Copyright 2023, Edmund Optics India Private Limited, #287, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038
Phone: 1-800-363-1992 :
www.edmundoptics.com

[#90-856 New](#)



New

Launched
on our
website
before
appearing
in our
latest print
catalogs.
Be the
first to buy
before
anyone
else!

LS21	>6 @ 180 - 400nm >5 @ 720 - 1090nm >7 @ 750 - 1064nm	25	Vented Fit Over	₹16,965	1 In Stock
------	---	----	--------------------	---------	------------