

[All Products](#) / [Optics](#) / [Optical Mirrors](#) / [Focusing \(Concave\) Mirrors](#)

TECHSPEC® $\lambda/4$ Precision Spherical Mirrors



- Ideal for Multispectral Focusing Applications
- Variety of Coating Options Offered
- Multiple Sizes Available
- [\$\lambda/8\$ Precision Spherical Mirrors](#) Also Available

Common Specifications

Physical & Mechanical Properties

Back Surface:	Ground
---------------	--------


Optical Properties

Focal Length Tolerance (%)	± 2
----------------------------	---------

Surface Quality:	60-40
------------------	-------

Surface Accuracy:	$\lambda/4$
-------------------	-------------

Technical Information



Products

Surface Accuracy	Dia. (mm)	EFL (mm)	Aperture (f/#)	Coating	Stock Number	Price	Buy
$\lambda/4$	25.40	25.40	f/1	Uncoated	#43-335	₹8,174 Volume Pricing	14 In Stock
$\lambda/4$	25.40	25.40	f/1	Protected Aluminum (400-2000nm)	#43-336	₹9,031 Volume Pricing	1 In Stock
$\lambda/4$	25.40	25.40	f/1	Enhanced Aluminum (250-700nm)	#43-535	₹9,420 Volume Pricing	2 In Stock
$\lambda/4$	25.40	25.40	f/1	Enhanced Aluminum (450-650nm)	#43-536	₹9,420 Volume Pricing	1 In Stock
$\lambda/4$	25.40	25.40	f/1	Protected Gold (700-10000nm)	#43-337	₹10,276 Volume Pricing	6 In Stock
$\lambda/4$	25.40	25.40	f/1	Protected Silver (450-10000nm)	#71-794	₹9,420 Volume Pricing	2 In Stock
$\lambda/4$	25.40	50.80	f/2	Uncoated	#43-338	₹8,174 Volume Pricing	20+ In Stock
$\lambda/4$	25.40	50.80	f/2	Protected Aluminum (400-2000nm)	#43-339	₹9,031 Volume Pricing	1 In Stock
$\lambda/4$	25.40	50.80	f/2	Enhanced Aluminum (250-700nm)	#43-537	₹9,420 Volume Pricing	3 In Stock
$\lambda/4$	25.40	50.80	f/2	Enhanced Aluminum (450-650nm)	#43-538	₹9,420 Volume Pricing	2 In Stock

$\lambda/4$	25.40	50.80	f/2	Protected Gold (700-1000nm)	#43-340	₹10,276 Volume Pricing	Contact Us
$\lambda/4$	25.40	50.80	f/2	Protected Silver (450-1000nm)	#71-795	₹9,420 Volume Pricing	4 In Stock
$\lambda/4$	25.40	76.20	f/3	Uncoated	#43-341	₹8,174 Volume Pricing	20+ In Stock
$\lambda/4$	25.40	76.20	f/3	Protected Aluminum (400-2000nm)	#43-342	₹9,031 Volume Pricing	2 In Stock
$\lambda/4$	25.40	76.20	f/3	Enhanced Aluminum (250-700nm)	#43-539	₹9,420 Volume Pricing	2 In Stock
$\lambda/4$	25.40	76.20	f/3	Enhanced Aluminum (450-650nm)	#43-540	₹9,420 Volume Pricing	Contact Us
$\lambda/4$	25.40	76.20	f/3	Protected Gold (700-1000nm)	#43-343	₹10,276 Volume Pricing	5 In Stock
$\lambda/4$	25.40	76.20	f/3	Protected Silver (450-1000nm)	#71-796	₹9,420 Volume Pricing	3 In Stock
$\lambda/4$	25.40	101.60	f/4	Uncoated	#43-344	₹8,174 Volume Pricing	6 In Stock
$\lambda/4$	25.40	101.60	f/4	Protected Aluminum (400-2000nm)	#43-345	₹9,031 Volume Pricing	Contact Us
$\lambda/4$	25.40	101.60	f/4	Enhanced Aluminum (250-700nm)	#43-541	₹9,420 Volume Pricing	20+ In Stock
$\lambda/4$	25.40	101.60	f/4	Enhanced Aluminum (450-650nm)	#43-542	₹9,420 Volume Pricing	Contact Us

$\lambda/4$	25.40	101.60	f/4	Protected Gold (700-1000nm)	#43-346	₹10,276 Volume Pricing	Contact Us
$\lambda/4$	25.40	101.60	f/4	Protected Silver (450-1000nm)	#71-797	₹9,420 Volume Pricing	2 In Stock
$\lambda/4$	25.40	152.40	f/6	Uncoated	#49-595	₹8,174 Volume Pricing	20+ In Stock
$\lambda/4$	25.40	152.40	f/6	Protected Aluminum (400-2000nm)	#49-600	₹9,031 Volume Pricing	Contact Us
$\lambda/4$	25.40	152.40	f/6	Enhanced Aluminum (250-700nm)	#49-605	₹9,420 Volume Pricing	14 In Stock
$\lambda/4$	25.40	152.40	f/6	Enhanced Aluminum (450-650nm)	#49-610	₹9,420 Volume Pricing	2 In Stock
$\lambda/4$	25.40	152.40	f/6	Protected Gold (700-1000nm)	#49-615	₹10,276 Volume Pricing	3 In Stock
$\lambda/4$	25.40	152.40	f/6	Protected Silver (450-1000nm)	#71-798	₹9,420 Volume Pricing	3 In Stock
$\lambda/4$	25.40	203.20	f/8	Uncoated	#49-596	₹8,174 Volume Pricing	11 In Stock
$\lambda/4$	25.40	203.20	f/8	Protected Aluminum (400-2000nm)	#49-601	₹9,031 Volume Pricing	1 In Stock
$\lambda/4$	25.40	203.20	f/8	Enhanced Aluminum (250-700nm)	#49-606	₹9,420 Volume Pricing	Contact Us
$\lambda/4$	25.40	203.20	f/8	Enhanced Aluminum (450-650nm)	#49-611	₹9,420 Volume Pricing	2 In Stock

$\lambda/4$	25.40	203.20	f/8	Protected Gold (700-1000nm)	#49-616	₹10,276 Volume Pricing	2 In Stock
$\lambda/4$	25.40	203.20	f/8	Protected Silver (450-1000nm)	#71-799	₹9,420 Volume Pricing	1 In Stock
$\lambda/4$	50.80	50.80	f/1	Protected Silver (450-1000nm)	#71-800	₹15,103 Volume Pricing	2 In Stock
$\lambda/4$	50.80	50.80	f/1	Uncoated	#32-811	₹9,809 Volume Pricing	20+ In Stock
$\lambda/4$	50.80	50.80	f/1	Protected Aluminum (400-2000nm)	#32-812	₹11,989 Volume Pricing	5 In Stock
$\lambda/4$	50.80	50.80	f/1	Enhanced Aluminum (250-700nm)	#43-543	₹13,935 Volume Pricing	11 In Stock
$\lambda/4$	50.80	50.80	f/1	Enhanced Aluminum (450-650nm)	#43-544	₹13,935 Volume Pricing	1 In Stock
$\lambda/4$	50.80	50.80	f/1	Protected Gold (700-1000nm)	#32-813	₹18,061 Volume Pricing	4 In Stock
$\lambda/4$	50.80	101.60	f/2	Protected Silver (450-1000nm)	#71-801	₹15,103 Volume Pricing	3 In Stock
$\lambda/4$	50.80	152.40	f/3	Protected Silver (450-1000nm)	#71-802	₹15,103 Volume Pricing	2 In Stock
$\lambda/4$	50.80	101.60	f/2	Uncoated	#32-814	₹9,809 Volume Pricing	20+ In Stock
$\lambda/4$	50.80	101.60	f/2	Protected Aluminum (400-2000nm)	#32-815	₹11,989 Volume Pricing	2 In Stock

$\lambda/4$	50.80	101.60	f/2	Enhanced Aluminum (250-700nm)	#43-545	₹13,935 Volume Pricing	5 In Stock
$\lambda/4$	50.80	101.60	f/2	Enhanced Aluminum (450-650nm)	#43-546	₹13,935 Volume Pricing	1 In Stock
$\lambda/4$	50.80	101.60	f/2	Protected Gold (700-10000nm)	#32-816	₹18,061 Volume Pricing	2 In Stock
$\lambda/4$	50.80	203.20	f/4	Protected Silver (450-10000nm)	#71-803	₹15,103 Volume Pricing	3 In Stock
$\lambda/4$	50.80	152.40	f/3	Uncoated	#49-597	₹9,809 Volume Pricing	5 In Stock
$\lambda/4$	50.80	152.40	f/3	Protected Aluminum (400-2000nm)	#49-602	₹11,989 Volume Pricing	3 In Stock
$\lambda/4$	50.80	152.40	f/3	Enhanced Aluminum (250-700nm)	#49-607	₹13,935 Volume Pricing	3 In Stock
$\lambda/4$	50.80	152.40	f/3	Enhanced Aluminum (450-650nm)	#49-612	₹13,935 Volume Pricing	2 In Stock
$\lambda/4$	50.80	152.40	f/3	Protected Gold (700-10000nm)	#49-617	₹18,061 Volume Pricing	3 In Stock
$\lambda/4$	50.80	304.80	f/6	Protected Silver (450-10000nm)	#71-804	₹15,103 Volume Pricing	1 In Stock
$\lambda/4$	50.80	203.20	f/4	Uncoated	#49-598	₹9,809 Volume Pricing	5 In Stock
$\lambda/4$	50.80	203.20	f/4	Protected Aluminum (400-2000nm)	#49-603	₹11,989 Volume Pricing	Contact Us

$\lambda/4$	50.80	203.20	f/4	Enhanced Aluminum (250-700nm)	#49-608	₹13,935 Volume Pricing	1 In Stock
$\lambda/4$	50.80	203.20	f/4	Enhanced Aluminum (450-650nm)	#49-613	₹13,935 Volume Pricing	Contact Us
$\lambda/4$	50.80	203.20	f/4	Protected Gold (700-10000nm)	#49-618	₹18,061 Volume Pricing	3 In Stock
$\lambda/4$	50.80	508.00	f/10	Protected Silver (450-10000nm)	#71-805	₹15,103 Volume Pricing	4 In Stock
$\lambda/4$	50.80	304.80	f/6	Uncoated	#32-817	₹9,809 Volume Pricing	20+ In Stock
$\lambda/4$	50.80	304.80	f/6	Protected Aluminum (400-2000nm)	#32-818	₹11,989 Volume Pricing	11 In Stock
$\lambda/4$	50.80	304.80	f/6	Enhanced Aluminum (250-700nm)	#43-547	₹13,935 Volume Pricing	10 In Stock
$\lambda/4$	50.80	304.80	f/6	Enhanced Aluminum (450-650nm)	#43-548	₹13,935 Volume Pricing	3 In Stock
$\lambda/4$	50.80	304.80	f/6	Protected Gold (700-10000nm)	#32-819	₹18,061 Volume Pricing	8 In Stock
$\lambda/4$	50.80	508.00	f/10	Uncoated	#32-820	₹9,809 Volume Pricing	20+ In Stock
$\lambda/4$	50.80	508.00	f/10	Protected Aluminum (400-2000nm)	#32-821	₹11,989 Volume Pricing	5 In Stock
$\lambda/4$	50.80	508.00	f/10	Enhanced Aluminum (250-700nm)	#43-549	₹13,935 Volume Pricing	2 In Stock

$\lambda/4$	50.80	508.00	f/10	Enhanced Aluminum (450-650nm)	#43-550	₹13,935 Volume Pricing	4 In Stock
$\lambda/4$	50.80	508.00	f/10	Protected Gold (700-10000nm)	#32-822	₹18,061 Volume Pricing	2 In Stock
$\lambda/4$	50.80	1,016.00	f/20	Protected Silver (450-10000nm)	#71-806	₹15,103 Volume Pricing	2 In Stock
$\lambda/4$	50.80	1,016.00	f/20	Uncoated	#43-347	₹9,809 Volume Pricing	20+ In Stock
$\lambda/4$	50.80	1,016.00	f/20	Protected Aluminum (400-2000nm)	#43-348	₹11,989 Volume Pricing	3 In Stock
$\lambda/4$	50.80	1,016.00	f/20	Enhanced Aluminum (250-700nm)	#43-551	₹13,935 Volume Pricing	4 In Stock
$\lambda/4$	50.80	1,016.00	f/20	Enhanced Aluminum (450-650nm)	#43-552	₹13,935 Volume Pricing	5 In Stock
$\lambda/4$	50.80	1,016.00	f/20	Protected Gold (700-10000nm)	#43-349	₹18,061 Volume Pricing	2 In Stock
$\lambda/4$	76.20	76.20	f/1	Protected Silver (450-10000nm)	#71-807	₹23,277 Volume Pricing	1 In Stock
$\lambda/4$	76.20	152.40	f/2	Protected Silver (450-10000nm)	#71-808	₹23,277 Volume Pricing	3 In Stock
$\lambda/4$	76.20	203.20	f/2	Protected Silver (450-10000nm)	#71-809	₹23,277 Volume Pricing	Contact Us
$\lambda/4$	76.20	76.20	f/1	Uncoated	#32-823	₹15,648 Volume Pricing	10 In Stock

$\lambda/4$	76.20	76.20	f/1	Protected Aluminum (400-2000nm)	#32-824	₹18,840 Volume Pricing	Contact Us
$\lambda/4$	76.20	76.20	f/1	Enhanced Aluminum (250-700nm)	#43-553	₹22,109 Volume Pricing	2 In Stock
$\lambda/4$	76.20	76.20	f/1	Enhanced Aluminum (450-650nm)	#43-554	₹22,109 Volume Pricing	1 In Stock
$\lambda/4$	76.20	76.20	f/1	Protected Gold (700-10000nm)	#32-825	₹26,235 Volume Pricing	5 In Stock
$\lambda/4$	76.20	304.80	f/4	Protected Silver (450-10000nm)	#71-810	₹23,277 Volume Pricing	2 In Stock
$\lambda/4$	76.20	152.40	f/2	Uncoated	#32-826	₹15,648 Volume Pricing	7 In Stock
$\lambda/4$	76.20	152.40	f/2	Protected Aluminum (400-2000nm)	#32-827	₹18,840 Volume Pricing	2 In Stock
$\lambda/4$	76.20	152.40	f/2	Enhanced Aluminum (250-700nm)	#43-555	₹22,109 Volume Pricing	Contact Us
$\lambda/4$	76.20	152.40	f/2	Enhanced Aluminum (450-650nm)	#43-556	₹22,109 Volume Pricing	1 In Stock
$\lambda/4$	76.20	152.40	f/2	Protected Gold (700-10000nm)	#32-828	₹26,235 Volume Pricing	5 In Stock
$\lambda/4$	76.20	457.20	f/6	Protected Silver (450-10000nm)	#71-811	₹23,277 Volume Pricing	2 In Stock
$\lambda/4$	76.20	203.20	f/2.7	Uncoated	#43-582	₹15,648 Volume Pricing	20+ In Stock

$\lambda/4$	76.20	203.20	f/2.7	Protected Aluminum (400-2000nm)	#43-583	₹18,840 Volume Pricing	6 In Stock
$\lambda/4$	76.20	203.20	f/2.7	Enhanced Aluminum (250-700nm)	#43-584	₹22,109 Volume Pricing	1 In Stock
$\lambda/4$	76.20	203.20	f/2.7	Enhanced Aluminum (450-650nm)	#43-585	₹22,109 Volume Pricing	2 In Stock
$\lambda/4$	76.20	203.20	f/2.7	Protected Gold (700-10000nm)	#43-586	₹26,235 Volume Pricing	2 In Stock
$\lambda/4$	76.20	762.00	f/10	Protected Silver (450-10000nm)	#71-812	₹23,277 Volume Pricing	2 In Stock
$\lambda/4$	76.20	304.80	f/4	Uncoated	#49-599	₹15,648 Volume Pricing	15 In Stock
$\lambda/4$	76.20	304.80	f/4	Protected Aluminum (400-2000nm)	#49-604	₹18,840 Volume Pricing	3 In Stock
$\lambda/4$	76.20	304.80	f/4	Enhanced Aluminum (250-700nm)	#49-609	₹22,109 Volume Pricing	Contact Us
$\lambda/4$	76.20	304.80	f/4	Enhanced Aluminum (450-650nm)	#49-614	₹22,109 Volume Pricing	Contact Us
$\lambda/4$	76.20	304.80	f/4	Protected Gold (700-10000nm)	#49-619	₹26,235 Volume Pricing	Contact Us
$\lambda/4$	76.20	457.20	f/6	Uncoated	#32-829	₹15,648 Volume Pricing	10 In Stock
$\lambda/4$	76.20	457.20	f/6	Protected Aluminum (400-2000nm)	#32-830	₹18,840 Volume Pricing	2 In Stock

$\lambda/4$	76.20	457.20	f/6	Enhanced Aluminum (250-700nm)	#43-557	₹22,109 Volume Pricing	3 In Stock
$\lambda/4$	76.20	457.20	f/6	Enhanced Aluminum (450-650nm)	#43-558	₹22,109 Volume Pricing	Contact Us
$\lambda/4$	76.20	457.20	f/6	Protected Gold (700-10000nm)	#32-831	₹26,235 Volume Pricing	1 In Stock
$\lambda/4$	76.20	762.00	f/10	Uncoated	#32-832	₹15,648 Volume Pricing	20+ In Stock
$\lambda/4$	76.20	762.00	f/10	Protected Aluminum (400-2000nm)	#32-833	₹18,840 Volume Pricing	3 In Stock
$\lambda/4$	76.20	762.00	f/10	Enhanced Aluminum (250-700nm)	#43-559	₹22,109 Volume Pricing	1 In Stock
$\lambda/4$	76.20	762.00	f/10	Enhanced Aluminum (450-650nm)	#43-560	₹22,109 Volume Pricing	1 In Stock
$\lambda/4$	76.20	762.00	f/10	Protected Gold (700-10000nm)	#32-834	₹26,235 Volume Pricing	5 In Stock
$\lambda/4$	152.40	609.60	f/4	Protected Silver (450-10000nm)	#71-813	₹55,274 Volume Pricing	Contact Us
$\lambda/4$	152.40	609.60	f/4	Uncoated	#43-968	₹39,314 Volume Pricing	20+ In Stock
$\lambda/4$	152.40	609.60	f/4	Protected Aluminum (400-2000nm)	#43-969	₹45,542 Volume Pricing	1 In Stock
$\lambda/4$	152.40	609.60	f/4	Enhanced Aluminum (250-700nm)	#43-970	₹52,160 Volume Pricing	3 In Stock

$\lambda/4$	152.40	609.60	f/4	Enhanced Aluminum (450-650nm) #43-971	₹52,160 Volume Pricing	Contact Us
$\lambda/4$	152.40	609.60	f/4	Protected Gold (700-10000nm) #43-972	₹59,945 Volume Pricing	4 In Stock



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038

Phone: 1-800-363-1992 :

www.edmundoptics.com