


[All Products](#) / [Optics](#) / [Optical Lenses](#) / [Achromatic Lenses](#)

TECHSPEC® MgF₂ Coated Negative Achromatic Lenses



- Magnesium Fluoride (MgF₂) Coating
- Used to Extend Focal Length
- [Broadband AR Coated Negative Achromatic Lenses](#) Also Available

Common Specifications

Physical & Mechanical Properties



Bevel: Protective as needed

Optical Properties

Focal Length Tolerance (%) : ± 1

Focal Length Specification Wavelength (nm):	587.6	Surface Quality:	40-20
Coating:	MgF ₂ (400-700nm)	Coating Specification:	R _{avg} ≤ 1.75% @ 400 - 700nm
Power (P-V) @ 632.8nm:	1.5λ	Irregularity (P-V) @ 632.8nm:	λ/4
Wavelength Range (nm):	400 - 700		

Technical Information



Products

Dia. (mm)	EFL (mm)	BFL (mm)	Substrate	Coating	Stock Number	Price	Buy
6.25	-7.50	-9.90	N-BAF10 / N-SF10	MgF ₂ (400-700nm)	#62-472	₹5,333 Volume Pricing	13 In Stock
6.25	-10.00	-11.92	N-BAF10 / N-SF10	MgF ₂ (400-700nm)	#62-473	₹5,333 Volume Pricing	20+ In Stock
6.25	-12.50	-12.89	N-BAF10 / N-SF10	MgF ₂ (400-700nm)	#45-420	₹5,333 Volume Pricing	20+ In Stock
6.25	-25.00	-26.53	N-BAF10 / N-SF10	MgF ₂ (400-700nm)	#45-421	₹5,333 Volume Pricing	20+ In Stock
9.00	-12.00	-13.78	N-BK7 / N-SF5	MgF ₂ (400-700nm)	#62-474	₹5,644 Volume Pricing	20+ In Stock
9.00	-25.00	-27.33	N-BAF10 / N-SF10	MgF ₂ (400-700nm)	#45-828	₹5,644 Volume Pricing	20+ In Stock
12.50	-15.00	-18.08	N-BAF10 / N-SF10	MgF ₂ (400-700nm)	#48-350	₹6,539 Volume Pricing	16 In Stock
12.50	-20.00	-22.88	N-BAF10 / N-SF10	MgF ₂ (400-700nm)	#62-475	₹6,539 Volume Pricing	5 In Stock
12.50	-25.00	-27.33	N-BAF10 / N-SF10	MgF ₂ (400-700nm)	#45-219	₹6,539 Volume Pricing	20+ In Stock
12.50	-35.00	-36.51	N-BK7 / N-SF5	MgF ₂ (400-700nm)	#45-424	₹6,539 Volume Pricing	20+ In Stock
12.50	-50.00	-51.58	N-BK7 / N-SF5	MgF ₂ (400-700nm)	#45-220	₹6,539 Volume Pricing	20+ In Stock
12.50	-75.00	-77.47	N-BK7 / N-SF5	MgF ₂ (400-700nm)	#47-016	₹6,539 Volume Pricing	16 In Stock
25.00	-30.00	-36.15	N-BAF10 / N-SF10	MgF ₂ (400-700nm)	#48-351	₹8,719 Volume Pricing	20+ In Stock
25.00	-40.00	-44.40	N-BAF10 / N-SF10	MgF ₂ (400-700nm)	#62-476	₹8,719 Volume Pricing	20+ In Stock
25.00	-50.00	-53.33	N-BAF10 / N-SF10	MgF ₂ (400-700nm)	#45-221	₹8,719 Volume Pricing	20+ In Stock

25.00	-75.00	-77.65	N-BK7 / N-SF5	MgF ₂ (400-700nm)	#45-422	₹8,719 Volume Pricing	20+ In Stock
25.00	-	-	N-BAF10 / N-SF10	MgF ₂ (400-700nm)	#45-222	₹8,719 Volume Pricing	20+ In Stock
25.00	-	-	N-BK7 / N-SF5	MgF ₂ (400-700nm)	#45-423	₹8,719 Volume Pricing	20+ In Stock
40.00	-60.00	-67.12	N-BAF10 / N-SF10	MgF ₂ (400-700nm)	#63-763	₹13,935 Volume Pricing	20+ In Stock
40.00	-80.00	-84.47	N-BK7 / N-SF5	MgF ₂ (400-700nm)	#63-764	₹13,935 Volume Pricing	20+ In Stock
40.00	-	-	N-BK7 / N-SF5	MgF ₂ (400-700nm)	#63-765	₹13,935 Volume Pricing	20+ In Stock
40.00	-	-	N-BK7 / N-SF5	MgF ₂ (400-700nm)	#63-766	₹13,935 Volume Pricing	20+ In Stock
40.00	-	-	N-BK7 / N-SF5	MgF ₂ (400-700nm)	#63-767	₹13,935 Volume Pricing	9 In Stock



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038
 Phone: 1-800-363-1992 :
www.edmundoptics.com