

[All Products](#) / [Microscopy](#) / [Infinity Corrected Objectives](#)

Mitutoyo NIR, NUV, and UV Infinity Corrected Objectives [See More by Mitutoyo](#)



- Ideal for Bright Field Imaging in UV, Visible, and NIR Spectral Regions
- Excellent Performance at Nd:YAG Laser Lines
- Broad Spectral Ranges

Common Specifications

General

Compatible Tube Lens Focal Length (mm):	Focal Length: 200mm	Manufacturer:	Mitutoyo
--	---------------------	---------------	----------

Optical Properties

Compatible Cover Glass Thickness (mm):	N/A	Immersion Liquid:	N/A
---	-----	-------------------	-----


Threading & Mounting

Mounting Threads:	M26 x 36 TPI
-------------------	--------------

Environmental & Durability Factors

Operating Temperature (°C):	-5 to +45
Operating Humidity:	20 - 80%

Technical Information



Products

Magnification	NA	DWL (nm)	FL (mm)	Model Number	WD (mm)	Stock Number	Price	Buy
5X	0.14	532, 1064	40.00	378-822- 5	37.5	#46-402	₹1,75,740	9 In Stock
10X	0.26	532, 1064	20.00	378-823- 15	30.5	#46-403	₹2,01,840	5 In Stock
20X	0.40	532, 1064	10.00	378-824- 16	20.0	#46-404	₹3,54,090	5 In Stock
50X	0.42	532, 1064	4.00	378-825- 17	17.0	#46-405	₹4,04,550	3 In Stock
100X	0.50	532, 1064	2.00	378-826- 15	12.0	#46-406	₹5,89,860	5 In Stock
50X	0.65	532, 1064	4.00	378-863- 5	10.0	#56-982	₹9,83,100	1 In Stock
20X	0.40	532, 1064	10.00	378-867- 5	25.5	#89-350	₹4,75,890	1 In Stock
50X	0.42	532, 1064	4.00	378-868- 5	25.5	#89-351	₹6,27,270	2 In Stock
100X	0.70	532, 1064	2.00	378-864- 15	10.0	#56-983	₹9,74,400	2 In Stock
10X	0.28	355, 532	20.00	378-809- 5	30.5	#86-176	₹3,41,910	1 In Stock
20X	0.40	355, 532	10.00	378-817- 8	17.0	#46-407	₹6,99,480	17 In Stock
50X	0.42	355, 532	4.00	378-818- 8	15.0	#46-408	₹6,99,480	3 In Stock
100X	0.50	355, 532	2.00	378-819- 15	11.0	#46-409	₹8,90,100	Contact Us
50X	0.65	355, 532	4.00	378-888- 6	10.0	#86-177	₹14,26,800	Contact Us
10X	0.25	266, 355, 532	20.00	378-844- 15	20.0	#86-175	₹12,09,300	Contact Us
20X	0.36	266, 532	10.00	378-837- 8	15.0	#56-320	₹18,44,400	Contact Us
50X	0.40	266, 532	4.00	378-838- 8	12.0	#56-321	₹18,87,900	Contact Us

80X	0.55	266,532	2.50	378-839-5	10.0	#56-322	₹25,92,600	Contact Us
						#75-053 New		
								
						New		
						Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!		
100X	0.70	532,1064	2.00	378-864-5	10.00		₹11,11,425	2 In Stock