

[All Products](#) / [Optics](#) / [Optical Lenses](#) / [Plano-Concave \(PCV\) Lenses](#)

TECHSPEC® UV Fused Silica Plano-Concave (PCV) Lenses



- Negative Focal Lengths for Beam Expansion or Light Projection Applications
- Wavelength Range of 200 - 2200nm
- Popular UV-AR Coating Option Available

Common Specifications

General

Note:

Max. Flat Annulus is 0.3mm

Optical Properties



 Substrate: [Fused Silica](#) (Corning 7980)

Surface Quality: 40-20

Power (P-V) @ 632.8nm: 1.5λ

Irregularity (P-V) @ 632.8nm: λ/4

Technical Information



UV FS Transmission Curve

Products

Dia. (mm)	EFL (mm)	BFL (mm)	Coating	Substrate	Stock Number	Price	Buy
6.00	-9.00	-10.38	Uncoated	Fused Silica	#45-697	₹8,719 Volume Pricing	10 In Stock
6.00	-12.00	-13.38	Uncoated	Fused Silica	#45-698	₹8,719 Volume Pricing	20+ In Stock
6.00	-18.00	-19.37	Uncoated	Fused Silica	#45-699	₹8,719 Volume Pricing	20+ In Stock
6.00	-9.00	-10.38	UV-AR (250-425nm)	Fused Silica	#46-308	₹10,510 Volume Pricing	20+ In Stock
6.00	-9.00	-10.38	UV-VIS (250-700nm)	Fused Silica	#71-091	₹10,510 Volume Pricing	8 In Stock
6.00	-12.00	-13.38	UV-AR (250-425nm)	Fused Silica	#46-309	₹10,510 Volume Pricing	20+ In Stock
6.00	-12.00	-13.38	UV-VIS (250-700nm)	Fused Silica	#71-092	₹10,510 Volume Pricing	3 In Stock
6.00	-18.00	-19.37	UV-AR (250-425nm)	Fused Silica	#46-310	₹10,510 Volume Pricing	20+ In Stock
6.00	-18.00	-19.37	UV-VIS (250-700nm)	Fused Silica	#71-093	₹10,510 Volume Pricing	4 In Stock
6.00	-9.00	-10.38	VIS-NIR (400-1000nm)	Fused Silica	#21-043	₹10,510 Volume Pricing	8 In Stock
6.00	-12.00	-13.38	VIS-NIR (400-1000nm)	Fused Silica	#21-044	₹10,510 Volume Pricing	2 In Stock
6.00	-18.00	-19.37	VIS-NIR (400-1000nm)	Fused Silica	#21-045	₹10,510 Volume Pricing	9 In Stock
9.00	-13.00	-14.89	UV-VIS (250-700nm)	Fused Silica	#71-094	₹10,899 Volume Pricing	5 In Stock

9.00	-18.00	-19.37	UV-VIS (250-700nm)	Fused Silica	#71-095	₹10,899 Volume Pricing	5 In Stock
9.00	-13.50	-14.89	Uncoated	Fused Silica	#45-700	₹9,108 Volume Pricing	20+ In Stock
9.00	-18.00	-19.37	Uncoated	Fused Silica	#45-701	₹9,108 Volume Pricing	20+ In Stock
9.00	-27.00	-28.42	Uncoated	Fused Silica	#45-702	₹9,108 Volume Pricing	20+ In Stock
9.00	-13.50	-14.89	UV-AR (250-425nm)	Fused Silica	#46-311	₹10,899 Volume Pricing	12 In Stock
9.00	-18.00	-19.37	UV-AR (250-425nm)	Fused Silica	#46-312	₹10,899 Volume Pricing	20+ In Stock
9.00	-27.00	-28.42	UV-VIS (250-700nm)	Fused Silica	#71-096	₹10,899 Volume Pricing	5 In Stock
9.00	-27.00	-28.42	UV-AR (250-425nm)	Fused Silica	#46-313	₹10,899 Volume Pricing	8 In Stock
9.00	-13.50	-14.89	VIS-NIR (400-1000nm)	Fused Silica	#21-046	₹10,899 Volume Pricing	5 In Stock
9.00	-18.00	-19.37	VIS-NIR (400-1000nm)	Fused Silica	#21-047	₹10,899 Volume Pricing	1 In Stock
9.00	-27.00	-28.42	VIS-NIR (400-1000nm)	Fused Silica	#21-048	₹10,899 Volume Pricing	8 In Stock
12.00	-25.00	-26.37	Uncoated	Fused Silica	#48-046	₹9,576 Volume Pricing	8 In Stock
12.00	-30.00	-31.37	Uncoated	Fused Silica	#48-047	₹9,576 Volume Pricing	20+ In Stock
12.00	-40.00	-41.37	Uncoated	Fused Silica	#48-048	₹9,576 Volume Pricing	20+ In Stock
12.00	-50.00	-51.37	Uncoated	Fused Silica	#48-049	₹9,576 Volume Pricing	20+ In Stock
12.00	-	-	Uncoated	Fused Silica	#85-879	₹9,576 Volume Pricing	20+ In Stock

12.00	-25.00	-26.37	UV-AR (250-425nm)	Fused Silica	#48-050	₹11,366 Volume Pricing	5 In Stock
12.00	-25.00	-26.37	UV-VIS (250-700nm)	Fused Silica	#71-097	₹11,366 Volume Pricing	1 In Stock
12.00	-30.00	-31.37	UV-AR (250-425nm)	Fused Silica	#48-051	₹11,366 Volume Pricing	5 In Stock
12.00	-30.00	-31.37	UV-VIS (250-700nm)	Fused Silica	#71-098	₹11,366 Volume Pricing	4 In Stock
12.00	-40.00	-41.37	UV-AR (250-425nm)	Fused Silica	#48-052	₹11,366 Volume Pricing	4 In Stock
12.00	-40.00	-41.37	UV-VIS (250-700nm)	Fused Silica	#71-099	₹11,366 Volume Pricing	2 In Stock
12.00	-50.00	-51.37	UV-AR (250-425nm)	Fused Silica	#48-053	₹11,366 Volume Pricing	2 In Stock
12.00	-50.00	-51.37	UV-VIS (250-700nm)	Fused Silica	#71-100	₹11,366 Volume Pricing	8 In Stock
12.00	-	-	UV-AR (250-425nm)	Fused Silica	#88-037	₹11,366 Volume Pricing	20+ In Stock
12.00	-	-	UV-VIS (250-700nm)	Fused Silica	#71-101	₹11,366 Volume Pricing	Contact Us
12.00	-25.00	-26.37	VIS-NIR (400-1000nm)	Fused Silica	#21-049	₹11,366 Volume Pricing	8 In Stock
12.00	-30.00	-31.37	VIS-NIR (400-1000nm)	Fused Silica	#21-050	₹11,366 Volume Pricing	1 In Stock
12.00	-40.00	-41.37	VIS-NIR (400-1000nm)	Fused Silica	#21-051	₹11,366 Volume Pricing	17 In Stock
12.00	-50.00	-51.37	VIS-NIR (400-1000nm)	Fused Silica	#21-052	₹11,366 Volume Pricing	3 In Stock

12.00	- 100.00	- 101.37	VIS-NIR (400- 1000nm)	Fused Silica	#21-053	₹11,366 Volume Pricing	4 In Stock
25.00	-50.00	-51.37	Uncoated	Fused Silica	#48-315	₹10,121 Volume Pricing	20+ In Stock
25.00	-75.00	-76.71	Uncoated	Fused Silica	#48-316	₹10,121 Volume Pricing	20+ In Stock
25.00	- 100.00	- 101.71	Uncoated	Fused Silica	#48-317	₹10,121 Volume Pricing	6 In Stock
25.00	- 150.00	- 151.71	Uncoated	Fused Silica	#48-318	₹10,121 Volume Pricing	5 In Stock
25.00	- 200.00	- 201.71	Uncoated	Fused Silica	#48-319	₹10,121 Volume Pricing	3 In Stock
25.00	- 250.00	- 251.71	Uncoated	Fused Silica	#48-320	₹10,121 Volume Pricing	Contact Us
25.00	-50.00	-51.37	UV-AR (250- 425nm)	Fused Silica	#48-321	₹11,833 Volume Pricing	15 In Stock
25.00	-50.00	-51.37	UV-VIS (250- 700nm)	Fused Silica	#71-102	₹11,833 Volume Pricing	4 In Stock
25.00	-75.00	-76.71	UV-AR (250- 425nm)	Fused Silica	#48-322	₹11,833 Volume Pricing	6 In Stock
25.00	-75.00	-76.71	UV-VIS (250- 700nm)	Fused Silica	#71-103	₹11,833 Volume Pricing	2 In Stock
25.00	- 100.00	- 101.71	UV-AR (250- 425nm)	Fused Silica	#48-323	₹11,833 Volume Pricing	Contact Us
25.00	- 100.00	- 101.71	UV-VIS (250- 700nm)	Fused Silica	#71-104	₹11,833 Volume Pricing	Contact Us
25.00	- 150.00	- 151.71	UV-AR (250- 425nm)	Fused Silica	#48-324	₹11,833 Volume Pricing	8 In Stock
25.00	- 150.00	- 151.71	UV-VIS (250- 700nm)	Fused Silica	#71-105	₹11,833 Volume Pricing	3 In Stock

25.00	-	-	UV-AR (250-425nm)	Fused Silica	#48-325	₹11,833 Volume Pricing	5 In Stock
25.00	-	-	UV-VIS (250-700nm)	Fused Silica	#71-106	₹11,833 Volume Pricing	6 In Stock
25.00	-	-	UV-AR (250-425nm)	Fused Silica	#48-326	₹11,833 Volume Pricing	5 In Stock
25.00	-	-	UV-VIS (250-700nm)	Fused Silica	#71-107	₹11,833 Volume Pricing	4 In Stock
25.00	-50.00	-51.37	VIS-NIR (400-1000nm)	Fused Silica	#21-054	₹11,911 Volume Pricing	5 In Stock
25.00	-75.00	-76.71	VIS-NIR (400-1000nm)	Fused Silica	#21-055	₹11,911 Volume Pricing	2 In Stock
25.00	-	-	VIS-NIR (400-1000nm)	Fused Silica	#21-056	₹11,911 Volume Pricing	3 In Stock
25.00	-	-	VIS-NIR (400-1000nm)	Fused Silica	#21-057	₹11,911 Volume Pricing	13 In Stock
25.00	-	-	VIS-NIR (400-1000nm)	Fused Silica	#21-058	₹11,911 Volume Pricing	4 In Stock
25.00	-	-	VIS-NIR (400-1000nm)	Fused Silica	#21-059	₹11,911 Volume Pricing	8 In Stock



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038

Phone: 1-800-363-1992 :

www.edmundoptics.com