

[All Products](#) / [Lab and Production](#) / [Optical Adhesives](#)

## Norland Optical Adhesives

See More by [Norland](#)



- Excellent Optical Qualities
- Adhesives for Glass, Metal, and Plastic Bonding
- Cure Quickly when Exposed to UV Light
- [Preloaded Norland Optical Adhesive Syringes](#) Also Available

**Technical Information**

## Products

| Norland Number | Size (oz) | Bonding Type             | Glass Bonding | Metal Bonding | Index of Refraction (n <sub>d</sub> ) | Stock Number            | Price                                     | Buy          |
|----------------|-----------|--------------------------|---------------|---------------|---------------------------------------|-------------------------|-------------------------------------------|--------------|
| 61             | 16        | Glass to Glass/Metal     | Excellent     | Excellent     | 1.56                                  | <a href="#">#15-697</a> | ₹28,620<br><a href="#">Volume Pricing</a> | Contact Us   |
| 63             | 16        | Glass to Glass           | Good          | Good          | 1.56                                  | <a href="#">#16-778</a> | ₹28,620<br><a href="#">Volume Pricing</a> | Contact Us   |
| 65             | 16        | Glass to Glass/Metal     | Good          | Good          | 1.52                                  | <a href="#">#16-779</a> | ₹28,620<br><a href="#">Volume Pricing</a> | 8 In Stock   |
| 68             | 16        | Plastic to Plastic/Glass | Excellent     | Good          | 1.54                                  | <a href="#">#16-780</a> | ₹28,620<br><a href="#">Volume Pricing</a> | 4 In Stock   |
| 81             | 16        | Glass to Glass/Metal     | Excellent     | Excellent     | 1.56                                  | <a href="#">#16-781</a> | ₹28,620<br><a href="#">Volume Pricing</a> | Contact Us   |
| 60             | 1         | Glass to Glass           | Good          | Good          | 1.56                                  | <a href="#">#42-192</a> | ₹3,488<br><a href="#">Volume Pricing</a>  | Contact Us   |
| 61             | 1         | Glass to Glass/Metal     | Excellent     | Excellent     | 1.56                                  | <a href="#">#37-322</a> | ₹3,668<br><a href="#">Volume Pricing</a>  | 20+ In Stock |
| 63             | 1         | Glass to Glass           | Good          | Good          | 1.56                                  | <a href="#">#36-425</a> | ₹3,668<br><a href="#">Volume Pricing</a>  | 20+ In Stock |
| 65             | 1         | Glass to Glass/Metal     | Good          | Good          | 1.52                                  | <a href="#">#36-426</a> | ₹3,668<br><a href="#">Volume Pricing</a>  | 20+ In Stock |
| 68             | 1         | Plastic to Plastic/Glass | Excellent     | Good          | 1.54                                  | <a href="#">#36-427</a> | ₹3,668<br><a href="#">Volume Pricing</a>  | 20+ In Stock |
| 68T            | 1         | Plastic to Plastic/Glass | Excellent     | Good          | 1.54                                  | <a href="#">#14-392</a> | ₹3,803<br><a href="#">Volume Pricing</a>  | 6 In Stock   |
| 68TH           | 1         | Plastic to Plastic/Glass | Excellent     | Good          | 1.54                                  | <a href="#">#14-791</a> | ₹7,965<br><a href="#">Volume Pricing</a>  | 3 In Stock   |
| 72             | 3.52      | Plastic to Plastic/Glass | Excellent     | Good          | 1.56                                  | <a href="#">#17-344</a> | ₹10,890<br><a href="#">Volume Pricing</a> | 4 In Stock   |
| 73             | 3.52      | Glass to Glass           | Excellent     | Good          | 1.56                                  | <a href="#">#17-345</a> | ₹10,890<br><a href="#">Volume Pricing</a> | 9 In Stock   |
| 74             | 3.52      | Plastic to Plastic/Glass | Excellent     | Good          | 1.52                                  | <a href="#">#17-346</a> | ₹10,890<br><a href="#">Volume Pricing</a> | 4 In Stock   |
| 76             | 3.52      | Glass to Plastic         | Excellent     | Good          | 1.51                                  | <a href="#">#17-347</a> | ₹10,890<br><a href="#">Volume Pricing</a> | 5 In Stock   |
| 78             | 3.52      | Plastic to Plastic/Glass | Excellent     | Good          | 1.50                                  | <a href="#">#17-348</a> | ₹10,890<br><a href="#">Volume Pricing</a> | 3 In Stock   |

|        |      |                          |           |           |      |                         |                                           |              |
|--------|------|--------------------------|-----------|-----------|------|-------------------------|-------------------------------------------|--------------|
| 81     | 1    | Glass to Glass/Metal     | Excellent | Excellent | 1.56 | <a href="#">#36-428</a> | ₹3,668<br><a href="#">Volume Pricing</a>  | 20+ In Stock |
| 83H    | 1    | Glass to Glass/Metal     | Excellent | Excellent | 1.56 | <a href="#">#55-583</a> | ₹7,965<br><a href="#">Volume Pricing</a>  | 2 In Stock   |
| 85     | 1    | Plastic to Plastic/Glass | Excellent | Fair      | 1.46 | <a href="#">#88-140</a> | ₹7,965<br><a href="#">Volume Pricing</a>  | 5 In Stock   |
| 86H    | 1    | Glass to Glass/Plastic   | Excellent | Good      | 1.55 | <a href="#">#12-848</a> | ₹7,965<br><a href="#">Volume Pricing</a>  | Contact Us   |
| 86TH   | 1    | Glass to Glass/Plastic   | Excellent | Good      | 1.54 | <a href="#">#17-349</a> | ₹7,965<br><a href="#">Volume Pricing</a>  | Contact Us   |
| 86TLH  | 1    | Glass to Glass/Metal     | Excellent | Excellent | 1.55 | <a href="#">#14-797</a> | ₹7,965<br><a href="#">Volume Pricing</a>  | Contact Us   |
| 87     | 1    | Glass to Glass/Plastic   | Excellent | Good      | 1.52 | <a href="#">#17-350</a> | ₹7,965<br><a href="#">Volume Pricing</a>  | 4 In Stock   |
| 88     | 1    | Glass to Glass/Metal     | Excellent | Excellent | 1.56 | <a href="#">#14-841</a> | ₹7,965<br><a href="#">Volume Pricing</a>  | 6 In Stock   |
| 89H    | 1    | Glass to Glass           | Excellent | Good      | 1.51 | <a href="#">#17-351</a> | ₹7,965<br><a href="#">Volume Pricing</a>  | 5 In Stock   |
| UVS 91 | 1    | Liquid Crystal Displays  | Excellent | Good      | N/A  | <a href="#">#17-364</a> | ₹5,580<br><a href="#">Volume Pricing</a>  | 2 In Stock   |
| 107    | 4    | Glass to Metal           | Excellent | Excellent | 1.51 | <a href="#">#62-048</a> | ₹8,505<br><a href="#">Volume Pricing</a>  | 6 In Stock   |
| 108H   | 3.52 | Glass to Metal           | Excellent | Excellent | 1.51 | <a href="#">#17-363</a> | ₹9,540<br><a href="#">Volume Pricing</a>  | 5 In Stock   |
| 139    | 1    | Glass to Glass           | Excellent | Good      | 1.39 | <a href="#">#15-696</a> | ₹15,660<br><a href="#">Volume Pricing</a> | 2 In Stock   |
| 144    | 1    | Glass to Glass           | Excellent | Good      | 1.44 | <a href="#">#17-358</a> | ₹10,620<br><a href="#">Volume Pricing</a> | 2 In Stock   |
| 146H   | 1    | Plastic to Plastic/Glass | Excellent | Good      | 1.46 | <a href="#">#12-866</a> | ₹7,965<br><a href="#">Volume Pricing</a>  | 3 In Stock   |
| 148    | 1    | Glass to Glass           | Excellent | Good      | 1.48 | <a href="#">#17-359</a> | ₹7,965<br><a href="#">Volume Pricing</a>  | 1 In Stock   |
| 160    | 1    | Glass to Glass           | Excellent | Good      | 1.60 | <a href="#">#12-860</a> | ₹7,965<br><a href="#">Volume Pricing</a>  | 3 In Stock   |
| 165H   | 1    | Glass to Glass           | Excellent | Excellent | 1.65 | <a href="#">#17-362</a> | ₹7,965<br><a href="#">Volume Pricing</a>  | 4 In Stock   |
| 170    | 1    | Glass to Glass           | Excellent | Good      | 1.70 | <a href="#">#12-851</a> | ₹23,850<br><a href="#">Volume Pricing</a> | 2 In Stock   |
| 170F   | 1    | Glass to Glass           | Excellent | Good      | 1.70 | <a href="#">#14-794</a> | ₹23,850<br><a href="#">Volume Pricing</a> | Contact Us   |

|       |   |                |           |           |        |                         |                                           |            |
|-------|---|----------------|-----------|-----------|--------|-------------------------|-------------------------------------------|------------|
| 1348  | 1 | Glass to Glass | Good      | Good      | 1.348  | <a href="#">#12-857</a> | ₹15,930<br><a href="#">Volume Pricing</a> | 2 In Stock |
| 1369  | 1 | Glass to Glass | Good      | Good      | 1.369  | <a href="#">#17-352</a> | ₹18,270<br><a href="#">Volume Pricing</a> | 1 In Stock |
| 1375  | 1 | Glass to Glass | Excellent | Good      | 1.375  | <a href="#">#17-353</a> | ₹10,620<br><a href="#">Volume Pricing</a> | 2 In Stock |
| 1422  | 1 | Glass to Glass | Excellent | Good      | 1.422  | <a href="#">#17-357</a> | ₹18,270<br><a href="#">Volume Pricing</a> | 1 In Stock |
| 13775 | 1 | Glass to Glass | Excellent | Excellent | 1.3775 | <a href="#">#17-354</a> | ₹18,270<br><a href="#">Volume Pricing</a> | 3 In Stock |
| 13825 | 1 | Glass to Glass | Good      | Good      | 1.3825 | <a href="#">#17-355</a> | ₹18,270<br><a href="#">Volume Pricing</a> | Contact Us |
| 1622H | 1 | Glass to Glass | Excellent | Excellent | 1.622  | <a href="#">#17-360</a> | ₹10,620<br><a href="#">Volume Pricing</a> | Contact Us |
| 1639H | 1 | Glass to Glass | Excellent | Excellent | 1.639  | <a href="#">#17-361</a> | ₹10,620<br><a href="#">Volume Pricing</a> | 1 In Stock |
| 1665  | 1 | Glass to Glass | Excellent | Good      | 1.665  | <a href="#">#12-863</a> | ₹10,620<br><a href="#">Volume Pricing</a> | 3 In Stock |
| 13685 | 1 | Glass to Glass | Excellent | Good      | 1.3685 | <a href="#">#12-854</a> | ₹10,620<br><a href="#">Volume Pricing</a> | 3 In Stock |



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038  
Phone: 1-800-363-1992 :  
[www.edmundoptics.com](http://www.edmundoptics.com)