

[All Products](#) / [Optics](#) / [Optical Lenses](#) / [Double-Convex \(DCX\) Lenses](#)

TECHSPEC® VIS-NIR Coated Double-Convex (DCX) Lenses



- AR Coated to Provide <1.25% Reflectance per Surface for 400 - 1000nm
- Minimize Aberrations Including Spherical and Coma
- [UV Fused Silica DCX Lenses](#) Available
- Other Coating Options Available: [Uncoated](#), [MgF₂](#), [VIS 0°](#), [NIR I](#), [NIR II](#), [VIS-EXT](#), and [YAG-BBAR](#)

Common Specifications

Physical & Mechanical Properties

Bevel: Protective as needed

Optical Properties

Coating: VIS-NIR (400-1000nm)

Coating Specification:

$R_{\text{abs}} \leq 0.25\% @ 880\text{nm}$
 $R_{\text{avg}} \leq 1.25\% @ 400 - 870\text{nm}$
 $R_{\text{avg}} \leq 1.25\% @ 890 - 1000\text{nm}$

Focal Length Tolerance (%): ± 1



Wavelength Range (nm): 400 - 1000

Technical Information

VIS-NIR Coating

$R_{avg} \leq 0.25\%$ @ 880nm, $R_{avg} \leq 1.25\%$ @ 400 - 1000nm

Typ. Energy Density Limit: 5 J/cm² @ 532nm, 10ns



Products

Dia. (mm)	BFL (mm)	EFL (mm)	Coating	Substrate	Stock Number	Price	Buy
3.00	2.21	3.00	VIS-NIR (400-1000nm)	N-SF5	#49-447	₹5,216 Volume Pricing	7 In Stock
3.00	3.78	4.50	VIS-NIR (400-1000nm)	N-BK7	#49-448	₹5,216 Volume Pricing	1 In Stock
3.00	5.37	6.00	VIS-NIR (400-1000nm)	N-BK7	#49-449	₹5,216 Volume Pricing	10 In Stock
3.00	8.46	9.00	VIS-NIR (400-1000nm)	N-BK7	#49-450	₹5,216 Volume Pricing	2 In Stock
4.50	3.70	4.50	VIS-NIR (400-1000nm)	N-LASF44	#47-893	₹5,216 Volume Pricing	20+ In Stock
4.50	8.16	9.00	VIS-NIR (400-1000nm)	N-BK7	#47-894	₹5,216 Volume Pricing	8 In Stock
5.00	4.19	5.00	VIS-NIR (400-1000nm)	N-SF5	#63-658	₹4,204 Volume Pricing	20+ In Stock
5.00	9.31	10.00	VIS-NIR (400-1000nm)	N-BK7	#63-659	₹4,204 Volume Pricing	6 In Stock
5.00	14.33	15.00	VIS-NIR (400-1000nm)	N-BK7	#63-660	₹4,204 Volume Pricing	20+ In Stock
5.00	19.50	20.00	VIS-NIR (400-1000nm)	N-BK7	#63-661	₹4,204 Volume Pricing	Contact Us
5.00	24.50	25.00	VIS-NIR (400-1000nm)	N-BK7	#63-662	₹4,204 Volume Pricing	Contact Us
6.00	5.19	6.00	VIS-NIR (400-1000nm)	N-SF5	#45-859	₹3,386 Volume Pricing	6 In Stock

6.00	8.22	9.00	VIS-NIR (400-1000nm)	N-BK7	#45-860	₹3,386 Volume Pricing	9 In Stock
6.00	11.18	12.00	VIS-NIR (400-1000nm)	N-BK7	#45-861	₹3,386 Volume Pricing	20+ In Stock
6.00	17.26	18.00	VIS-NIR (400-1000nm)	N-BK7	#45-862	₹3,386 Volume Pricing	Contact Us
6.00	23.13	24.00	VIS-NIR (400-1000nm)	N-BK7	#45-863	₹3,386 Volume Pricing	2 In Stock
6.00	29.23	30.00	VIS-NIR (400-1000nm)	N-BK7	#45-864	₹3,386 Volume Pricing	5 In Stock
6.00	35.33	36.00	VIS-NIR (400-1000nm)	N-BK7	#45-865	₹3,386 Volume Pricing	4 In Stock
9.00	7.90	9.00	VIS-NIR (400-1000nm)	N-SF5	#45-866	₹3,464 Volume Pricing	20+ In Stock
9.00	12.56	13.50	VIS-NIR (400-1000nm)	N-BK7	#45-867	₹3,464 Volume Pricing	Contact Us
9.00	17.12	18.00	VIS-NIR (400-1000nm)	N-BK7	#45-868	₹3,464 Volume Pricing	2 In Stock
9.00	26.08	27.00	VIS-NIR (400-1000nm)	N-BK7	#45-869	₹3,464 Volume Pricing	20+ In Stock
9.00	35.15	36.00	VIS-NIR (400-1000nm)	N-BK7	#45-870	₹3,464 Volume Pricing	Contact Us
9.00	44.17	45.00	VIS-NIR (400-1000nm)	N-BK7	#45-871	₹3,464 Volume Pricing	2 In Stock
10.00	8.89	10.00	VIS-NIR (400-1000nm)	N-SF5	#63-663	₹3,464 Volume Pricing	20+ In Stock
10.00	13.80	15.00	VIS-NIR (400-1000nm)	N-BK7	#63-664	₹3,464 Volume Pricing	4 In Stock

10.00	19.16	20.00	VIS-NIR (400-1000nm)	N-BK7	#63-665	₹3,464 Volume Pricing	20+ In Stock
10.00	24.16	25.00	VIS-NIR (400-1000nm)	N-BK7	#63-666	₹3,464 Volume Pricing	5 In Stock
10.00	29.17	30.00	VIS-NIR (400-1000nm)	N-BK7	#63-667	₹3,464 Volume Pricing	1 In Stock
10.00	39.16	40.00	VIS-NIR (400-1000nm)	N-BK7	#63-668	₹3,464 Volume Pricing	1 In Stock
10.00	49.17	50.00	VIS-NIR (400-1000nm)	N-BK7	#63-669	₹3,464 Volume Pricing	5 In Stock
10.00	99.17	100.00	VIS-NIR (400-1000nm)	N-BK7	#63-670	₹3,464 Volume Pricing	6 In Stock
12.00	10.79	12.00	VIS-NIR (400-1000nm)	N-SF5	#45-872	₹3,698 Volume Pricing	20+ In Stock
12.00	16.81	18.00	VIS-NIR (400-1000nm)	N-BK7	#45-873	₹3,620 Volume Pricing	20+ In Stock
12.00	22.65	24.00	VIS-NIR (400-1000nm)	N-BK7	#33-391	₹3,620 Volume Pricing	4 In Stock
12.00	28.75	30.00	VIS-NIR (400-1000nm)	N-BK7	#45-875	₹3,620 Volume Pricing	6 In Stock
12.00	34.90	36.00	VIS-NIR (400-1000nm)	N-BK7	#45-876	₹3,620 Volume Pricing	3 In Stock
12.00	47.09	48.00	VIS-NIR (400-1000nm)	N-BK7	#45-877	₹3,620 Volume Pricing	2 In Stock
12.00	71.07	72.00	VIS-NIR (400-1000nm)	N-BK7	#45-878	₹3,620 Volume Pricing	11 In Stock
15.00	13.68	15.00	VIS-NIR (400-1000nm)	N-SF11	#45-879	₹3,698 Volume Pricing	20+ In Stock

15.00	18.99	20.00	VIS-NIR (400-1000nm)	N-SF11	#63-671	₹3,620 Volume Pricing	5 In Stock
15.00	21.29	22.50	VIS-NIR (400-1000nm)	N-SF11	#45-880	₹3,620 Volume Pricing	14 In Stock
15.00	23.82	25.00	VIS-NIR (400-1000nm)	N-BK7	#63-672	₹3,620 Volume Pricing	2 In Stock
15.00	28.82	30.00	VIS-NIR (400-1000nm)	N-BK7	#45-881	₹3,620 Volume Pricing	8 In Stock
15.00	44.00	45.00	VIS-NIR (400-1000nm)	N-BK7	#63-673	₹3,620 Volume Pricing	14 In Stock
15.00	49.00	50.00	VIS-NIR (400-1000nm)	N-BK7	#45-882	₹3,620 Volume Pricing	Contact Us
15.00	59.00	60.00	VIS-NIR (400-1000nm)	N-BK7	#63-674	₹3,620 Volume Pricing	2 In Stock
18.00	16.69	18.00	VIS-NIR (400-1000nm)	N-SF11	#63-675	₹3,776 Volume Pricing	10 In Stock
18.00	25.25	27.00	VIS-NIR (400-1000nm)	N-BK7	#45-883	₹3,776 Volume Pricing	20+ In Stock
18.00	34.59	36.00	VIS-NIR (400-1000nm)	N-BK7	#45-884	₹3,776 Volume Pricing	11 In Stock
20.00	18.55	20.00	VIS-NIR (400-1000nm)	N-SF11	#63-678	₹3,834 Volume Pricing	11 In Stock
20.00	23.86	25.00	VIS-NIR (400-1000nm)	N-SF11	#63-679	₹3,834 Volume Pricing	20+ In Stock
20.00	28.20	30.00	VIS-NIR (400-1000nm)	N-BK7	#45-885	₹3,834 Volume Pricing	20+ In Stock
20.00	38.44	40.00	VIS-NIR (400-1000nm)	N-BK7	#45-886	₹3,834 Volume Pricing	20+ In Stock

20.00	48.84	50.00	VIS-NIR (400-1000nm)	N-BK7	#63-680	₹3,834 Volume Pricing	14 In Stock
20.00	58.67	60.00	VIS-NIR (400-1000nm)	N-BK7	#63-681	₹3,834 Volume Pricing	2 In Stock
20.00	78.67	80.00	VIS-NIR (400-1000nm)	N-BK7	#63-682	₹3,834 Volume Pricing	4 In Stock
25.00	22.47	25.00	VIS-NIR (400-1000nm)	N-SF5	#45-887	₹4,048 Volume Pricing	20+ In Stock
25.00	28.31	30.00	VIS-NIR (400-1000nm)	N-SF5	#63-683	₹4,009 Volume Pricing	20+ In Stock
25.00	32.81	35.00	VIS-NIR (400-1000nm)	N-BK7	#45-888	₹4,009 Volume Pricing	20+ In Stock
25.00	38.21	40.00	VIS-NIR (400-1000nm)	N-BK7	#45-889	₹4,009 Volume Pricing	3 In Stock
25.00	48.29	50.00	VIS-NIR (400-1000nm)	N-BK7	#45-890	₹4,009 Volume Pricing	9 In Stock
25.00	73.84	75.00	VIS-NIR (400-1000nm)	N-BK7	#45-891	₹4,009 Volume Pricing	4 In Stock
25.00	98.95	100.00	VIS-NIR (400-1000nm)	N-BK7	#45-892	₹4,009 Volume Pricing	5 In Stock
25.00	123.84	125.00	VIS-NIR (400-1000nm)	N-BK7	#45-893	₹4,009 Volume Pricing	8 In Stock
25.00	148.88	150.00	VIS-NIR (400-1000nm)	N-BK7	#45-894	₹4,009 Volume Pricing	5 In Stock
25.00	173.94	175.00	VIS-NIR (400-1000nm)	N-BK7	#45-895	₹4,009 Volume Pricing	9 In Stock
25.00	198.35	200.00	VIS-NIR (400-1000nm)	N-BK7	#33-397	₹4,009 Volume Pricing	13 In Stock

30.00	28.12	30.00	VIS-NIR (400-1000nm)	N-SF11	#63-684	₹4,749 Volume Pricing	20+ In Stock
30.00	47.82	50.00	VIS-NIR (400-1000nm)	N-BK7	#45-898	₹4,671 Volume Pricing	Contact Us
30.00	58.33	60.00	VIS-NIR (400-1000nm)	N-BK7	#63-685	₹4,671 Volume Pricing	1 In Stock
30.00	73.35	75.00	VIS-NIR (400-1000nm)	N-BK7	#45-899	₹4,671 Volume Pricing	20+ In Stock
30.00	98.34	100.00	VIS-NIR (400-1000nm)	N-BK7	#63-686	₹4,671 Volume Pricing	5 In Stock
30.00	118.34	120.00	VIS-NIR (400-1000nm)	N-BK7	#63-687	₹4,671 Volume Pricing	Contact Us
40.00	37.54	40.00	VIS-NIR (400-1000nm)	N-SF11	#63-688	₹5,605 Volume Pricing	13 In Stock
40.00	57.10	60.00	VIS-NIR (400-1000nm)	N-BK7	#45-900	₹5,605 Volume Pricing	Contact Us
40.00	77.32	80.00	VIS-NIR (400-1000nm)	N-BK7	#33-422	₹5,605 Volume Pricing	17 In Stock
40.00	97.33	100.00	VIS-NIR (400-1000nm)	N-BK7	#33-409	₹5,605 Volume Pricing	Contact Us
40.00	117.67	120.00	VIS-NIR (400-1000nm)	N-BK7	#63-689	₹5,605 Volume Pricing	8 In Stock
40.00	197.35	200.00	VIS-NIR (400-1000nm)	N-BK7	#33-416	₹5,605 Volume Pricing	1 In Stock
50.00	45.30	50.00	VIS-NIR (400-1000nm)	N-SF11	#45-905	₹5,800 Volume Pricing	8 In Stock
50.00	96.65	100.00	VIS-NIR (400-1000nm)	N-BK7	#45-906	₹5,800 Volume Pricing	5 In Stock

50.00	147.00	150.00	VIS-NIR (400-1000nm)	N-BK7	#45-907	₹5,800 Volume Pricing	3 In Stock
50.00	198.33	200.00	VIS-NIR (400-1000nm)	N-BK7	#45-908	₹5,800 Volume Pricing	13 In Stock
50.00	248.37	250.00	VIS-NIR (400-1000nm)	N-BK7	#45-909	₹5,800 Volume Pricing	5 In Stock



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038

Phone: 1-800-363-1992 :

www.edmundoptics.com