

[All Products](#) / [Optics](#) / [Prisms](#) / [Right Angle Prisms](#)
TECHSPEC® N-SF11 Right Angle Prisms


- Ray Deviation of 90°
- Left Handed Image
- High Refractive Index Material
- Additional [Right Angle Prism](#) Options Available

Common Specifications

Physical & Mechanical Properties



Bevel: Protective as needed


Optical Properties

Substrate: [N-SF11](#)


Surface Quality:	20-10	Angle Tolerance (arcmin):	±2
Image Orientation:	Left-Handed	Ray Deviation (°):	90
Power (fringes) @ 632.8nm:	1.25	Irregularity (fringes) @ 632.8nm:	0.25

Technical Information







Right Angle Prism Ray Path



Right Angle Prism Ray Path



Right Angle Prism Tunnel Diagram



Right Angle Prism Tunnel Diagram

Products

Length of Legs (mm)	Length of Hypotenuse (mm)	Coating	Stock Number	Price	Buy
2.00	2.80	Uncoated	#45-524	₹11,790 Volume Pricing	4 In Stock
3.00	4.20	Uncoated	#45-525	₹11,340 Volume Pricing	20+ In Stock
4.00	5.70	Uncoated	#45-526	₹8,235 Volume Pricing	20+ In Stock
5.00	7.10	Uncoated	#45-527	₹8,235 Volume Pricing	20+ In Stock
10.00	14.10	Uncoated	#45-949	₹13,500 Volume Pricing	20+ In Stock
15.00	21.20	Uncoated	#45-950	₹14,940 Volume Pricing	20+ In Stock
2.00	2.80	MgF ₂ & Aluminized	#47-922	₹14,490 Volume Pricing	Contact Us
3.00	4.20	MgF ₂ & Aluminized	#47-923	₹13,950 Volume Pricing	Contact Us
4.00	5.70	MgF ₂ & Aluminized	#47-924	₹10,890 Volume Pricing	20+ In Stock
5.00	7.10	MgF ₂ & Aluminized	#47-925	₹10,890 Volume Pricing	9 In Stock
10.00	14.10	MgF ₂ & Aluminized	#47-926	₹15,930 Volume Pricing	1 In Stock
15.00	21.20	MgF ₂ & Aluminized	#47-927	₹17,280 Volume Pricing	11 In Stock



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038

Phone: 1-800-363-1992 :

www.edmundoptics.com