

[All Products](#) / [Optics](#) / [Optical Assemblies](#) / [Laser Optic Assemblies](#)

LightPath® Fiber Optic Collimators

See More by [Lightpath®](#)





- Easy to Integrate
- Models for FC/PC, FC/APC, and SMA Connections Available
- Four Wavelength Ranges Covering 350-1600nm


Common Specifications

Physical & Mechanical Properties			
Bevel:	Protective as needed	Construction:	304L Stainless Steel Housing
Optical Properties			
Surface Quality:	40-20	Conjugate Distance:	Infinite

Technical Information



FC/APC Connectors



Products

EFL (mm)	NA	Coating	Alignment Wavelength (nm)	Connector	Lens Included	Stock Number	Price	Buy
15.29	0.16	BBAR (350-700nm)	543	FC/PC	#37-098	#47-224	₹16,830 Volume Pricing	11 In Stock
15.29	0.16	BBAR (350-700nm)	543	SMA	#37-098	#47-227	₹16,830 Volume Pricing	20+ In Stock
15.29	0.16	BBAR (350-700nm)	543	FC/APC	#37-098	#13-555	₹25,290 Volume Pricing	20+ In Stock
15.29	0.16	BBAR (600-1050nm)	633	FC/APC	#37-099	#13-556	₹25,290 Volume Pricing	8 In Stock
15.29	0.16	BBAR (600-1050nm)	633	FC/PC	#37-099	#67-719	₹16,830 Volume Pricing	5 In Stock
15.29	0.16	BBAR (600-1050nm)	633	SMA	#37-099	#67-724	₹16,830 Volume Pricing	5 In Stock
15.29	0.16	BBAR (600-1050nm)	780	FC/PC	#37-099	#47-225	₹16,830 Volume Pricing	11 In Stock
15.29	0.16	BBAR (600-1050nm)	780	SMA	#37-099	#47-228	₹16,830 Volume Pricing	3 In Stock
15.29	0.16	BBAR (1050-1600nm)	1064	FC/PC	#37-100	#64-765	₹16,830 Volume Pricing	20+ In Stock

[#64-766 Clearance](#)



Clearance

Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.

15.29	0.16	BBAR (1050-1600nm)	1064	SMA	#37-100	₹10,262	20+ In Stock
-------	------	-----------------------	------	-----	-------------------------	---------	--------------

[#47-226 Clearance](#)



Clearance

Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.

15.29	0.16	BBAR (1050-1600nm)	1310	FC/PC	#37-100	₹10,262	20+ In Stock
-------	------	-----------------------	------	-------	-------------------------	---------	--------------

[#47-229 Clearance](#)



Clearance

Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.

15.29	0.16	BBAR (1050-1600nm)	1310	SMA	#37-100	₹10,262	2 In Stock
-------	------	-----------------------	------	-----	-------------------------	---------	------------

15.29	0.16	BBAR (1050-1600nm)	1550	FC/PC	#37-100	#83-724	₹16,830 Volume Pricing	5 In Stock
-------	------	-----------------------	------	-------	-------------------------	-------------------------	---	------------

15.29	0.16	BBAR (1050-1600nm)	1550	SMA	#37-100	#83-729	₹16,830 Volume Pricing	8 In Stock
-------	------	-----------------------	------	-----	-------------------------	-------------------------	---	------------

11.00	0.25	BBAR (350-700nm)	543	FC/PC	#87-117	#47-218	₹16,830 Volume Pricing	7 In Stock
-------	------	---------------------	-----	-------	-------------------------	-------------------------	---	------------

11.00	0.25	BBAR (350-700nm)	543	SMA	#87-117	#47-221	₹16,830 Volume Pricing	15 In Stock
-------	------	---------------------	-----	-----	-------------------------	-------------------------	---	-------------

11.00	0.25	BBAR (350-700nm)	543	FC/APC	-	#16-705	₹25,290 Volume Pricing	5 In Stock
-------	------	---------------------	-----	--------	---	-------------------------	---	------------

11.00	0.25	BBAR (600-1050nm)	633	FC/PC	#87-118	#67-720	₹16,830 Volume Pricing	17 In Stock
-------	------	----------------------	-----	-------	-------------------------	-------------------------	---	-------------

11.00	0.25	BBAR (600-1050nm)	633	SMA	#87-118	#67-725	₹16,830 Volume Pricing	5 In Stock
-------	------	----------------------	-----	-----	-------------------------	-------------------------	---	------------

11.00	0.25	BBAR (600-1050nm)	633	FC/APC	-	#16-706	₹25,290 Volume Pricing	6 In Stock
-------	------	----------------------	-----	--------	---	-------------------------	---	------------

11.00	0.25	BBAR (600-1050nm)	780	FC/PC	#87-118	#47-219	₹16,830 Volume Pricing	20+ In Stock
-------	------	----------------------	-----	-------	-------------------------	-------------------------	---	--------------

11.00	0.25	BBAR (600-1050nm)	780	SMA	#87-118	#47-222	₹16,830 Volume Pricing	20+ In Stock
-------	------	----------------------	-----	-----	-------------------------	-------------------------	---	--------------

11.00	0.25	BBAR (1050-1600nm)	1064	FC/PC	#87-119	#64-767	₹16,830 Volume Pricing	20+ In Stock
11.00	0.25	BBAR (1050-1600nm)	1064	SMA	#87-119	#64-768	₹16,830 Volume Pricing	8 In Stock
11.00	0.25	BBAR (1050-1600nm)	1310	FC/PC	#87-119	#47-220	₹16,830 Volume Pricing	20+ In Stock
11.00	0.25	BBAR (1050-1600nm)	1310	SMA	#87-119	#47-223	₹16,830 Volume Pricing	20+ In Stock
11.00	0.25	BBAR (1050-1600nm)	1550	FC/PC	#87-119	#83-725	₹16,830 Volume Pricing	6 In Stock
11.00	0.25	BBAR (1050-1600nm)	1550	SMA	#87-119	#83-730	₹16,830 Volume Pricing	20+ In Stock
6.24	0.40	BBAR (350-700nm)	543	FC/APC	#87-125	#13-553	₹25,290 Volume Pricing	5 In Stock
6.24	0.40	BBAR (350-700nm)	543	FC/PC	#87-125	#64-769	₹16,830 Volume Pricing	20+ In Stock
6.24	0.40	BBAR (350-700nm)	543	SMA	#87-125	#64-770	₹16,830 Volume Pricing	7 In Stock
6.24	0.40	BBAR (600-1050nm)	633	FC/APC	#87-126	#13-554	₹25,290 Volume Pricing	7 In Stock
6.24	0.40	BBAR (600-1050nm)	633	FC/PC	#87-126	#67-721	₹16,830 Volume Pricing	20+ In Stock
6.24	0.40	BBAR (600-1050nm)	633	SMA	#87-126	#67-726	₹16,830 Volume Pricing	11 In Stock
6.24	0.40	BBAR (600-1050nm)	780	FC/PC	#87-126	#64-771	₹16,830 Volume Pricing	20+ In Stock
6.24	0.40	BBAR (600-1050nm)	780	SMA	#87-126	#64-772	₹16,830 Volume Pricing	8 In Stock

[#64-773 Clearance](#)



Clearance

Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.

6.24	0.40	BBAR (1050-1600nm)	1064	FC/PC	#87-127	₹10,262	20+ In Stock
------	------	-----------------------	------	-------	-------------------------	---------	--------------

[#64-775 Clearance](#)



Clearance

Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.

6.24	0.40	BBAR (1050-1600nm)	1310	FC/PC	#87-127	₹10,262	20+ In Stock
------	------	-----------------------	------	-------	-------------------------	---------	--------------

6.24	0.40	BBAR (1050-1600nm)	1550	SMA	#87-127	#83-731	₹16,830 Volume Pricing	20+ In Stock
------	------	-----------------------	------	-----	-------------------------	-------------------------	---	--------------

8.00	0.50	BBAR (350-700nm)	543	FC/PC	#37-102	#64-777	₹19,170 Volume Pricing	20+ In Stock
------	------	---------------------	-----	-------	-------------------------	-------------------------	---	--------------

8.00	0.50	BBAR (350-700nm)	543	FC/APC	-	#16-709	₹25,290 Volume Pricing	Contact Us
------	------	---------------------	-----	--------	---	-------------------------	---	------------

8.00	0.50	BBAR (350-700nm)	543	SMA	#37-102	#64-778	₹19,170 Volume Pricing	7 In Stock
8.00	0.50	BBAR (600-1050nm)	633	FC/PC	#37-103	#67-722	₹16,830 Volume Pricing	20+ In Stock
8.00	0.50	BBAR (600-1050nm)	633	SMA	#37-103	#67-727	₹19,170 Volume Pricing	8 In Stock
8.00	0.50	BBAR (600-1050nm)	633	FC/APC	-	#16-710	₹25,290 Volume Pricing	9 In Stock
8.00	0.50	BBAR (600-1050nm)	780	FC/PC	#37-103	#64-779	₹19,170 Volume Pricing	20+ In Stock
8.00	0.50	BBAR (600-1050nm)	780	SMA	#37-103	#64-780	₹19,170 Volume Pricing	4 In Stock
8.00	0.50	BBAR (1050-1600nm)	1064	FC/PC	#37-104	#64-781	₹19,170 Volume Pricing	15 In Stock
8.00	0.50	BBAR (1050-1600nm)	1064	SMA	#37-104	#64-782	₹19,170 Volume Pricing	3 In Stock
8.00	0.50	BBAR (1050-1600nm)	1310	FC/PC	#37-104	#64-783	₹19,170 Volume Pricing	Contact Us
8.00	0.50	BBAR (1050-1600nm)	1310	SMA	#37-104	#64-784	₹19,170 Volume Pricing	9 In Stock
8.00	0.50	BBAR (1050-1600nm)	1550	FC/PC	#37-104	#83-727	₹19,170 Volume Pricing	10 In Stock

[#83-732 Clearance](#)



Clearance

Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.

8.00	0.50	BBAR (1050-1600nm)	1550	SMA	#37-104		₹11,654	5 In Stock
------	------	-----------------------	------	-----	-------------------------	--	---------	------------

4.51	0.55	BBAR (350-700nm)	543	FC/APC	#87-153	#13-551	₹25,290 Volume Pricing	20+ In Stock
------	------	---------------------	-----	--------	-------------------------	-------------------------	---	--------------

4.51	0.55	BBAR (350-700nm)	543	FC/PC	#87-153	#64-785	₹16,830 Volume Pricing	20+ In Stock
------	------	---------------------	-----	-------	-------------------------	-------------------------	---	--------------

4.51	0.55	BBAR (350-700nm)	543	SMA	#87-153	#64-786	₹16,830 Volume Pricing	20+ In Stock
------	------	---------------------	-----	-----	-------------------------	-------------------------	---	--------------

4.51	0.55	BBAR (600-1050nm)	633	FC/APC	#87-154	#13-552	₹25,290 Volume Pricing	7 In Stock
------	------	----------------------	-----	--------	-------------------------	-------------------------	---	------------

4.51	0.55	BBAR (600-1050nm)	633	FC/PC	#87-154	#67-723	₹16,830 Volume Pricing	20+ In Stock
------	------	----------------------	-----	-------	-------------------------	-------------------------	---	--------------

4.51	0.55	BBAR (600-1050nm)	633	SMA	#87-154	#67-728	₹16,830 Volume Pricing	5 In Stock
------	------	----------------------	-----	-----	-------------------------	-------------------------	---	------------

4.51	0.55	BBAR (600-1050nm)	780	FC/PC	#87-154	#64-787	₹16,830 Volume Pricing	20+ In Stock
------	------	----------------------	-----	-------	-------------------------	-------------------------	---	--------------

4.51	0.55	BBAR (600-1050nm)	780	SMA	#87-154	#64-788	₹16,830 Volume Pricing	5 In Stock
------	------	----------------------	-----	-----	-------------------------	-------------------------	---	------------

[#64-791 Clearance](#)



Clearance

Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.

4.51	0.55	BBAR (1050-1600nm)	1310	FC/PC	#87-155	₹10,262	5 In Stock
------	------	-----------------------	------	-------	-------------------------	---------	------------

[#64-792 Clearance](#)



Clearance

Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.

4.51	0.55	BBAR (1050-1600nm)	1310	SMA	#87-155	₹10,262	9 In Stock
------	------	-----------------------	------	-----	-------------------------	---------	------------

[#83-733 Clearance](#)



Clearance

Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.



BBAR
Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038
Phone: 1-800-363-1992 : [www.edmundoptics.com](#)

4.00	0.60	BBAR (350-500nm)	405	FC/APC	#83-990	#13-550	₹25,290 Volume Pricing	20+ In Stock
4.02	0.60	BBAR (350-500nm)	405	FC/PC	#83-990	#88-067	₹16,830 Volume Pricing	20+ In Stock
4.02	0.60	BBAR (350-500nm)	405	SMA	#83-990	#88-068	₹16,830 Volume Pricing	16 In Stock