

[All Products](#) / [Optics](#) / [Polarization Optics](#) / [Retarders \(Waveplates\)](#) / [Achromatic Waveplates](#)

Achromatic Waveplates (Retarders)





- Multiple Wavelength Ranges Available
- Flat Response Over Each Broad Spectral Range
- $\lambda/4$ and $\lambda/2$ Retardance
- Mounted in Black Anodized Aluminum Housing



Common Specifications




Physical & Mechanical Properties				
Dimensional Tolerance (mm):		+0/-0.25	Construction: Crystalline	
Housing Tolerance (mm):		+0/-0.25		
Optical Properties				
Substrate:		Crystal Quartz and MgF ₂		

Technical Information




25.4mm Diameter Waveplates





30.0mm Diameter Waveplates



Products

Retardance	Wavelength Range (nm)	CA (mm)	Dia. (mm)	Type	Surface Quality	Stock Number	Price	Buy
$\lambda/4$	465 - 610	11.5	25.40	Achromatic Waveplate	20-10	#46-558	₹72,790 Volume Pricing	2 In Stock
$\lambda/2$	465 - 610	11.5	25.40	Achromatic Waveplate	20-10	#46-559	₹72,790 Volume Pricing	5 In Stock
$\lambda/4$	610 - 850	11.5	25.40	Achromatic Waveplate	20-10	#63-935	₹72,790 Volume Pricing	Contact Us
$\lambda/2$	610 - 850	11.5	25.40	Achromatic Waveplate	20-10	#63-936	₹72,790 Volume Pricing	2 In Stock
$\lambda/4$	700 - 1000	11.5	25.40	Achromatic Waveplate	20-10	#46-560	₹72,790 Volume Pricing	3 In Stock
$\lambda/2$	700 - 1000	11.5	25.40	Achromatic Waveplate	20-10	#46-561	₹72,790 Volume Pricing	3 In Stock
$\lambda/4$	1200 - 1650	11.5	25.40	Achromatic Waveplate	20-10	#46-562	₹72,790 Volume Pricing	2 In Stock
$\lambda/2$	1200 - 1650	11.5	25.40	Achromatic Waveplate	20-10	#46-563	₹72,790 Volume Pricing	2 In Stock
$\lambda/4$	465 - 610	23	30.00	Achromatic Waveplate	20-10	#48-497	₹81,743 Volume Pricing	3 In Stock
$\lambda/2$	465 - 610	23	30.00	Achromatic Waveplate	20-10	#48-498	₹81,743 Volume Pricing	3 In Stock
$\lambda/4$	610 - 850	23	30.00	Achromatic Waveplate	20-10	#65-919	₹81,743 Volume Pricing	5 In Stock
$\lambda/2$	610 - 850	23	30.00	Achromatic Waveplate	20-10	#65-920	₹81,743 Volume Pricing	4 In Stock
$\lambda/4$	700 - 1000	23	30.00	Achromatic Waveplate	20-10	#48-499	₹81,743 Volume Pricing	5 In Stock
$\lambda/2$	700 - 1000	23	30.00	Achromatic Waveplate	20-10	#48-500	₹81,743 Volume Pricing	4 In Stock
$\lambda/4$	1200 - 1650	23	30.00	Achromatic Waveplate	20-10	#48-501	₹81,743 Volume Pricing	3 In Stock
$\lambda/2$	1200 - 1650	23	30.00	Achromatic Waveplate	20-10	#48-502	₹81,743 Volume Pricing	1 In Stock
$\lambda/4$	340 - 560	>8.0	12.70	Achromatic Waveplate	40-20	#39-024	₹61,891 Volume Pricing	4 In Stock
$\lambda/2$	340 - 560	>8.0	12.70	Achromatic Waveplate	40-20	#39-025	₹61,891 Volume Pricing	1 In Stock

$\lambda/4$	340 - 560	>20.0	25.40	Achromatic Waveplate	40-20	#39-026	₹79,018 Volume Pricing	Contact Us
$\lambda/2$	340 - 560	>20.0	25.40	Achromatic Waveplate	40-20	#39-027	₹79,018 Volume Pricing	3 In Stock
$\lambda/4$	340 - 560	>27.0	50.80	Achromatic Waveplate	40-20	#39-028	₹2,50,288 Volume Pricing	1 In Stock
$\lambda/2$	340 - 560	>34.0	50.80	Achromatic Waveplate	40-20	#39-029	₹2,50,288 Volume Pricing	1 In Stock
$\lambda/4$	450 - 650	>8.0	12.70	Achromatic Waveplate	40-20	#39-030	₹61,891 Volume Pricing	2 In Stock
$\lambda/2$	450 - 650	>8.0	12.70	Achromatic Waveplate	40-20	#39-031	₹61,891 Volume Pricing	8 In Stock
$\lambda/4$	450 - 650	>20.0	25.40	Achromatic Waveplate	40-20	#39-032	₹79,018 Volume Pricing	2 In Stock
$\lambda/2$	450 - 650	>20.0	25.40	Achromatic Waveplate	40-20	#39-033	₹79,018 Volume Pricing	1 In Stock
$\lambda/4$	450 - 650	>34.0	50.80	Achromatic Waveplate	40-20	#39-034	₹2,50,288 Volume Pricing	2 In Stock
$\lambda/2$	450 - 650	>34.0	50.80	Achromatic Waveplate	40-20	#39-035	₹2,50,288 Volume Pricing	2 In Stock
$\lambda/4$	550 - 750	>8.0	12.70	Achromatic Waveplate	40-20	#39-036	₹61,891 Volume Pricing	1 In Stock
$\lambda/2$	550 - 750	>8.0	12.70	Achromatic Waveplate	40-20	#39-037	₹61,891 Volume Pricing	3 In Stock
$\lambda/4$	550 - 750	>20.0	25.40	Achromatic Waveplate	40-20	#39-038	₹79,018 Volume Pricing	4 In Stock
$\lambda/2$	550 - 750	>20.0	25.40	Achromatic Waveplate	40-20	#39-039	₹79,018 Volume Pricing	1 In Stock
$\lambda/4$	550 - 750	>34.0	50.80	Achromatic Waveplate	40-20	#39-040	₹2,50,288 Volume Pricing	1 In Stock
$\lambda/2$	550 - 750	>34.0	50.80	Achromatic Waveplate	40-20	#39-041	₹2,50,288 Volume Pricing	1 In Stock
$\lambda/4$	650 - 1100	>8.0	12.70	Achromatic Waveplate	40-20	#39-042	₹61,891 Volume Pricing	Contact Us
$\lambda/2$	650 - 1100	>8.0	12.70	Achromatic Waveplate	40-20	#39-043	₹61,891 Volume Pricing	5 In Stock
$\lambda/4$	650 - 1100	>20.0	25.40	Achromatic Waveplate	40-20	#39-044	₹79,018 Volume Pricing	8 In Stock
$\lambda/2$	650 - 1100	>20.0	25.40	Achromatic Waveplate	40-20	#39-045	₹79,018 Volume Pricing	3 In Stock

$\lambda/4$	650 - 1100	>34.0	50.80	Achromatic Waveplate	40-20	#39-046	₹2,50,288 Volume Pricing	Contact Us
$\lambda/2$	650 - 1100	>34.0	50.80	Achromatic Waveplate	40-20	#39-047	₹2,50,288 Volume Pricing	1 In Stock
$\lambda/4$	900 - 2100	>8.0	12.70	Achromatic Waveplate	40-20	#39-048	₹61,891 Volume Pricing	3 In Stock
$\lambda/2$	900 - 2100	>8.0	12.70	Achromatic Waveplate	40-20	#39-049	₹61,891 Volume Pricing	4 In Stock
$\lambda/4$	900 - 2100	>20.0	25.40	Achromatic Waveplate	40-20	#39-050	₹79,018 Volume Pricing	4 In Stock
$\lambda/2$	900 - 2100	>20.0	25.40	Achromatic Waveplate	40-20	#39-051	₹79,018 Volume Pricing	1 In Stock
$\lambda/4$	900 - 2100	>34.0	50.80	Achromatic Waveplate	40-20	#39-052	₹2,50,288 Volume Pricing	1 In Stock
$\lambda/2$	900 - 2100	>34.0	50.80	Achromatic Waveplate	40-20	#39-053	₹2,50,288 Volume Pricing	1 In Stock



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038
 Phone: 1-800-363-1992 :
www.edmundoptics.com