

[All Products](#) / [Optics](#) / [Optical Lenses](#) / [Ball and Condenser Lenses](#)

Molded Aspheric Condenser Lenses



- Hardened for Improved Durability
- High Numerical Apertures
- Ideal for Illumination Applications

Common Specifications

Physical & Mechanical Properties

Bevel:


Protective as needed

Optical Properties

Conjugate Distance:

Infinite

Technical Information



Products

Dia. (mm)	EFL (mm)	NA	Coating	Stock Number	Price	Buy
5.00	3.10	0.81	Uncoated	#15-172	₹2,491 Volume Pricing	20+ In Stock
5.00	3.10	0.81	MgF ₂ (400-700nm)	#15-677	₹3,348 Volume Pricing	20+ In Stock
5.00	3.70	0.68	Uncoated	#88-282	₹2,491 Volume Pricing	20+ In Stock
5.00	3.70	0.68	MgF ₂ (400-700nm)	#35-031	₹3,348 Volume Pricing	Contact Us
5.00	3.70	0.68	NIR I (600-1050nm)	#15-877	₹4,437 Volume Pricing	Contact Us
5.00	3.70	0.68	VIS-EXT (350-700nm)	#71-481	₹4,437 Volume Pricing	5 In Stock
6.30	9.00	0.35	Uncoated	#34-455	₹2,491 Volume Pricing	20+ In Stock
6.30	9.00	0.35	MgF ₂ (400-700nm)	#35-033	₹3,348 Volume Pricing	15 In Stock
6.30	9.00	0.35	NIR I (600-1050nm)	#15-878	₹4,437 Volume Pricing	20+ In Stock
6.30	9.00	0.35	VIS-EXT (350-700nm)	#71-482	₹4,437 Volume Pricing	5 In Stock
6.80	6.00	0.56	Uncoated	#34-456	₹2,491 Volume Pricing	20+ In Stock
6.80	6.00	0.56	MgF ₂ (400-700nm)	#35-036	₹3,348 Volume Pricing	9 In Stock
6.80	6.00	0.56	NIR I (600-1050nm)	#15-879	₹4,437 Volume Pricing	3 In Stock

6.80	6.00	0.56	VIS-EXT (350-700nm)	#71-483	₹4,437 Volume Pricing	Contact Us
8.50	7.40	0.57	Uncoated	#34-457	₹2,491 Volume Pricing	20+ In Stock
8.50	7.40	0.57	MgF ₂ (400-700nm)	#35-037	₹3,348 Volume Pricing	Contact Us
8.50	7.40	0.57	NIR I (600-1050nm)	#15-880	₹4,437 Volume Pricing	4 In Stock
8.50	7.40	0.57	VIS-EXT (350-700nm)	#71-484	₹4,437 Volume Pricing	5 In Stock
10.00	6.60	0.76	VIS-EXT (350-700nm)	#71-485	₹4,437 Volume Pricing	2 In Stock
#88-283 Clearance						
 Clearance Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.						
10.00	6.60	0.76	Uncoated		₹2,491 Volume Pricing	20+ In Stock
10.00	6.60	0.76	MgF ₂ (400-700nm)	#35-038	₹3,348 Volume Pricing	20+ In Stock
10.00	6.60	0.76	NIR I (600-1050nm)	#15-881	₹4,437 Volume Pricing	4 In Stock
12.00	7.50	0.8	Uncoated	#88-284	₹2,491 Volume Pricing	20+ In Stock
12.00	7.50	0.8	MgF ₂ (400-700nm)	#35-039	₹3,348 Volume Pricing	12 In Stock

12.00	7.50	0.8	NIR I (600-1050nm)	#15-882	₹4,437 Volume Pricing	9 In Stock
12.00	7.50	0.8	VIS-EXT (350-700nm)	#71-486	₹4,437 Volume Pricing	6 In Stock
12.00	10.50	0.57	VIS-EXT (350-700nm)	#71-487	₹4,437 Volume Pricing	4 In Stock
12.00	10.50	0.57	Uncoated	#88-285	₹2,491 Volume Pricing	20+ In Stock
12.00	10.50	0.57	MgF ₂ (400-700nm)	#35-040	₹3,348 Volume Pricing	12 In Stock
12.00	10.50	0.57	NIR I (600-1050nm)	#15-883	₹4,437 Volume Pricing	6 In Stock
12.00	10.40	0.57	Uncoated	#88-286	₹2,491 Volume Pricing	20+ In Stock
12.00	10.40	0.57	MgF ₂ (400-700nm)	#35-041	₹3,348 Volume Pricing	7 In Stock
12.00	10.40	0.57	NIR I (600-1050nm)	#15-884	₹4,437 Volume Pricing	5 In Stock
12.00	10.40	0.57	VIS-EXT (350-700nm)	#71-488	₹4,437 Volume Pricing	5 In Stock
12.00	12.50	0.48	VIS-EXT (350-700nm)	#71-489	₹4,437 Volume Pricing	5 In Stock
12.00	12.50	0.48	Uncoated	#88-287	₹2,491 Volume Pricing	20+ In Stock
12.00	12.50	0.48	MgF ₂ (400-700nm)	#35-065	₹3,348 Volume Pricing	20+ In Stock
12.00	12.50	0.48	NIR I (600-1050nm)	#15-885	₹4,437 Volume Pricing	10 In Stock
13.00	7.70	0.85	VIS-EXT (350-700nm)	#71-490	₹4,437 Volume Pricing	5 In Stock

13.00	7.70	0.85	Uncoated	#34-458	₹2,491 Volume Pricing	Contact Us
13.00	7.70	0.85	MgF ₂ (400-700nm)	#35-044	₹3,348 Volume Pricing	20+ In Stock
13.00	7.70	0.85	NIR I (600-1050nm)	#15-886	₹4,437 Volume Pricing	Contact Us
15.00	8.25	0.91	Uncoated	#15-173	₹2,491 Volume Pricing	20+ In Stock
15.00	8.25	0.91	MgF ₂ (400-700nm)	#15-678	₹3,348 Volume Pricing	5 In Stock
15.00	8.25	0.91	NIR I (600-1050nm)	#15-887	₹4,437 Volume Pricing	2 In Stock
15.00	8.25	0.91	VIS-EXT (350-700nm)	#71-491	₹4,437 Volume Pricing	1 In Stock
16.00	10.80	0.74	Uncoated	#34-459	₹2,491 Volume Pricing	20+ In Stock
16.00	10.80	0.74	MgF ₂ (400-700nm)	#35-047	₹3,348 Volume Pricing	7 In Stock
18.00	8.40	1.06	Uncoated	#34-460	₹2,491 Volume Pricing	20+ In Stock
18.00	8.40	1.06	MgF ₂ (400-700nm)	#35-048	₹3,348 Volume Pricing	5 In Stock
18.00	13.50	0.67	Uncoated	#34-461	₹2,491 Volume Pricing	20+ In Stock
18.00	13.50	0.67	MgF ₂ (400-700nm)	#35-049	₹3,348 Volume Pricing	6 In Stock
18.00	13.50	0.67	NIR I (600-1050nm)	#15-888	₹4,437 Volume Pricing	2 In Stock
18.00	13.50	0.67	VIS-EXT (350-700nm)	#71-492	₹4,437 Volume Pricing	1 In Stock

20.00	11.00	0.89	VIS-EXT (350-700nm)	#71-493	₹5,060 Volume Pricing	Contact Us
20.00	11.10	0.89	Uncoated	#88-288	₹3,114 Volume Pricing	20+ In Stock
20.00	11.10	0.89	MgF ₂ (400-700nm)	#35-052	₹3,970 Volume Pricing	Contact Us
20.00	11.10	0.89	NIR I (600-1050nm)	#15-889	₹5,060 Volume Pricing	Contact Us
20.00	16.00	0.63	Uncoated	#88-289	₹3,114 Volume Pricing	20+ In Stock
20.00	16.00	0.63	MgF ₂ (400-700nm)	#35-062	₹3,970 Volume Pricing	20+ In Stock
20.00	16.00	0.63	NIR I (600-1050nm)	#15-890	₹5,060 Volume Pricing	4 In Stock
20.00	16.00	0.63	VIS-EXT (350-700nm)	#71-494	₹5,060 Volume Pricing	2 In Stock
20.00	16.40	0.61	Uncoated	#15-174	₹3,114 Volume Pricing	6 In Stock
20.00	16.40	0.61	MgF ₂ (400-700nm)	#15-679	₹3,970 Volume Pricing	Contact Us
20.00	16.40	0.61	NIR I (600-1050nm)	#15-892	₹5,060 Volume Pricing	4 In Stock
20.00	17.50	0.57	Uncoated	#88-290	₹3,114 Volume Pricing	20+ In Stock
20.00	17.50	0.57	MgF ₂ (400-700nm)	#35-063	₹3,970 Volume Pricing	4 In Stock
20.00	17.50	0.57	NIR I (600-1050nm)	#15-891	₹5,060 Volume Pricing	7 In Stock
20.00	17.50	0.57	VIS-EXT (350-700nm)	#71-495	₹5,060 Volume Pricing	4 In Stock

24.00	16.40	0.61	VIS-EXT (350-700nm)	#71-496	₹5,060 Volume Pricing	4 In Stock
24.00	15.40	0.78	Uncoated	#15-175	₹3,348 Volume Pricing	20+ In Stock
24.00	15.40	0.78	MgF ₂ (400-700nm)	#15-680	₹4,204 Volume Pricing	20+ In Stock
24.00	18.00	0.67	Uncoated	#15-176	₹3,348 Volume Pricing	20+ In Stock
24.00	18.00	0.67	MgF ₂ (400-700nm)	#15-681	₹4,204 Volume Pricing	12 In Stock
24.00	18.00	0.67	NIR I (600-1050nm)	#15-893	₹5,060 Volume Pricing	13 In Stock
24.00	18.00	0.67	VIS-EXT (350-700nm)	#71-497	₹5,060 Volume Pricing	5 In Stock
26.00	19.50	0.67	Uncoated	#34-462	₹3,348 Volume Pricing	2 In Stock
26.00	19.50	0.67	MgF ₂ (400-700nm)	#35-064	₹4,204 Volume Pricing	20+ In Stock
26.00	19.50	0.67	NIR I (600-1050nm)	#15-894	₹5,060 Volume Pricing	7 In Stock
26.00	19.50	0.67	VIS-EXT (350-700nm)	#71-498	₹5,060 Volume Pricing	8 In Stock
30.00	17.50	0.86	Uncoated	#88-291	₹3,581 Volume Pricing	9 In Stock
30.00	17.50	0.86	MgF ₂ (400-700nm)	#15-683	₹4,360 Volume Pricing	20+ In Stock
30.00	17.50	0.86	NIR I (600-1050nm)	#15-895	₹5,527 Volume Pricing	20+ In Stock
30.00	17.50	0.86	VIS-EXT (350-700nm)	#71-499	₹5,527 Volume Pricing	2 In Stock

30.00	26.90	0.56	Uncoated	#15-177	₹3,581 Volume Pricing	20+ In Stock
30.00	26.90	0.56	MgF ₂ (400-700nm)	#15-682	₹4,360 Volume Pricing	Contact Us
30.00	26.90	0.56	NIR I (600-1050nm)	#15-896	₹5,527 Volume Pricing	11 In Stock
30.00	26.90	0.56	VIS-EXT (350-700nm)	#71-500	₹5,527 Volume Pricing	3 In Stock



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038

Phone: 1-800-363-1992 :

www.edmundoptics.com