

[All Products](#) / [Optics](#) / [Optical Lenses](#) / [Achromatic Lenses](#)

TECHSPEC® Near-UV (NUV) Achromatic Lenses



- Excellent Transmission in 345 – 700nm Range
- Ideal for use with NUV LEDs and Mercury Lamps
- Low-Cost, Cemented Design

Common Specifications

Physical & Mechanical Properties



Centering (arcmin): <1

Bevel: Protective as needed

Optical Properties

Focal Length Tolerance (%)	±1	Focal Length Specification Wavelength (nm):	405.00
Substrate:	N-FK5 / F2HT	Surface Quality:	40-20
Coating:	UV-VIS (345-700nm)	Power (P-V) @ 632.8nm:	1.5λ
Irregularity (P-V) @ 632.8nm:	λ/4	Wavelength Range (nm):	345 - 700

Technical Information



Products

Dia. (mm)	EFL (mm)	BFL (mm)	Substrate	Coating	Stock Number	Price	Buy
6.25	12.50	10.22	N-FK5 / F2HT	UV-VIS (345-700nm)	#84-327	₹10,121 Volume Pricing	20+ In Stock
6.25	15.00	13.05	N-FK5 / F2HT	UV-VIS (345-700nm)	#84-328	₹10,121 Volume Pricing	20+ In Stock
#84-331 Clearance							
 Clearance Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.							
6.25	30.00	28.39	N-FK5 / F2HT	UV-VIS (345-700nm)		₹9,131	20+ In Stock
9.00	18.00	15.05	N-FK5 / F2HT	UV-VIS (345-700nm)	#35-993	₹10,743 Volume Pricing	20+ In Stock
9.00	27.00	24.13	N-FK5 / F2HT	UV-VIS (345-700nm)	#35-994	₹10,743 Volume Pricing	20+ In Stock
9.00	36.00	33.56	N-FK5 / F2HT	UV-VIS (345-700nm)	#35-995	₹10,743 Volume Pricing	20+ In Stock
12.50	25.00	21.59	N-FK5 / F2HT	UV-VIS (345-700nm)	#65-971	₹11,055 Volume Pricing	20+ In Stock

12.50	30.00	27.22	N-FK5 / F2HT	UV-VIS (345-700nm)	#65-972	₹11,055 Volume Pricing	11 In Stock
12.50	40.00	37.48	N-FK5 / F2HT	UV-VIS (345-700nm)	#65-973	₹11,055 Volume Pricing	20+ In Stock
12.50	50.00	47.31	N-FK5 / F2HT	UV-VIS (345-700nm)	#65-974	₹11,055 Volume Pricing	20+ In Stock
25.00	50.00	44.74	N-FK5 / F2HT	UV-VIS (345-700nm)	#65-976	₹12,845 Volume Pricing	20+ In Stock
25.00	60.00	55.63	N-FK5 / F2HT	UV-VIS (345-700nm)	#65-977	₹12,845 Volume Pricing	20+ In Stock
25.00	75.00	71.09	N-FK5 / F2HT	UV-VIS (345-700nm)	#65-978	₹12,845 Volume Pricing	5 In Stock
25.00	100.00	96.32	N-FK5 / F2HT	UV-VIS (345-700nm)	#65-979	₹12,845 Volume Pricing	20+ In Stock
25.00	125.00	121.29	N-FK5 / F2HT	UV-VIS (345-700nm)	#65-980	₹12,845 Volume Pricing	20+ In Stock
50.00	100.00	87.39	N-FK5 / F2HT	UV-VIS (345-700nm)	#85-878	₹19,307 Volume Pricing	4 In Stock
50.00	150.00	141.28	N-FK5 / F2HT	UV-VIS (345-700nm)	#35-996	₹19,307 Volume Pricing	20+ In Stock
50.00	200.00	192.01	N-FK5 / F2HT	UV-VIS (345-700nm)	#35-997	₹19,307 Volume Pricing	20+ In Stock



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038

Phone: 1-800-363-1992 :

www.edmundoptics.com