

[All Products](#) / [Optics](#) / [Optical Lenses](#) / [Aspheric Lenses](#) / [Plastic Molded](#)

TECHSPEC®

Plastic Aspheric Lenses




- Full Prescription Data Available
- Standard 25mm Diameter for Easy System Integration
- High Numerical Aperture Designs for Superior Light Collection

Common Specifications

Physical & Mechanical Properties			
Clear Aperture CA (mm):	21.5	Bevel:	Protective as needed
Shape of Back Surface:	Convex		
Optical Properties			
Aspheric Design Wavelength (nm):	587.6		
Surface Quality:	80-50	Conjugate Distance:	Infinite
Environmental & Durability Factors			
Operating Temperature (°C):	-30 to 70		

Technical Information



Products

Dia. (mm)	EFL (mm)	NA	Coating	Stock Number	Price	Buy
25.00	17.50	0.71	Uncoated	#21-204	₹3,970 Volume Pricing	20+ In Stock
25.00	20.00	0.63	Uncoated	#21-205	₹3,970 Volume Pricing	6 In Stock
25.00	25.00	0.50	Uncoated	#21-206	₹3,970 Volume Pricing	20+ In Stock
25.00	30.00	0.42	Uncoated	#21-207	₹3,970 Volume Pricing	20+ In Stock
25.00	40.00	0.31	Uncoated	#21-208	₹3,970 Volume Pricing	20+ In Stock
25.00	50.00	0.25	Uncoated	#21-209	₹3,970 Volume Pricing	20+ In Stock
25.00	17.50	0.71	BBAR (425-675nm)	#21-210	₹5,177 Volume Pricing	20+ In Stock
25.00	20.00	0.63	BBAR (425-675nm)	#21-211	₹5,177 Volume Pricing	Contact Us
25.00	25.00	0.50	BBAR (425-675nm)	#21-212	₹5,177 Volume Pricing	20+ In Stock
25.00	30.00	0.42	BBAR (425-675nm)	#21-213	₹5,177 Volume Pricing	20+ In Stock
25.00	17.50	0.71	BBAR (600-1000nm)	#21-216	₹5,177 Volume Pricing	20+ In Stock
25.00	20.00	0.63	BBAR (600-1000nm)	#21-217	₹5,177 Volume Pricing	20+ In Stock
25.00	25.00	0.50	BBAR (600-1000nm)	#21-218	₹5,177 Volume Pricing	20+ In Stock
25.00	30.00	0.42	BBAR (600-1000nm)	#21-219	₹5,177 Volume Pricing	20+ In Stock

25.00	40.00	0.31	BBAR (600-1000nm)	#21-220	₹5,177 Volume Pricing	3 In Stock
25.00	50.00	0.25	BBAR (600-1000nm)	#21-221	₹5,177 Volume Pricing	20+ In Stock
25.00	40.00	0.31	BBAR (425-675nm)	#21-214	₹5,177 Volume Pricing	20+ In Stock
25.00	50.00	0.25	BBAR (425-675nm)	#21-215	₹5,177 Volume Pricing	20+ In Stock

[#66-006 Clearance](#)



Clearance

25.00	17.50	0.71	Uncoated	Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.	₹3,041	20+ In Stock
-------	-------	------	----------	--	--------	--------------

[#66-007 Clearance](#)



Clearance

25.00	20.00	0.63	Uncoated	Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.	₹3,041	20+ In Stock
-------	-------	------	----------	--	--------	--------------

[#66-008 Clearance](#)



Clearance

25.00 25.00 0.50 Uncoated

Availability is limited,
so buy before these
products disappear.
Sorry, we cannot
accept returns. Receive
up to 80% off select
products.

₹3,041

20+ In Stock

[#66-009 Clearance](#)



Clearance

25.00 30.00 0.42 Uncoated

Availability is limited,
so buy before these
products disappear.
Sorry, we cannot
accept returns. Receive
up to 80% off select
products.

₹3,041

20+ In Stock

[#66-010 Clearance](#)



Clearance

25.00 40.00 0.31 Uncoated

Availability is limited,
so buy before these
products disappear.
Sorry, we cannot
accept returns. Receive
up to 80% off select
products.

₹3,041

20+ In Stock

[#66-011 Clearance](#)



Clearance

25.00 50.00 0.25 Uncoated

Availability is limited,
so buy before these
products disappear.
Sorry, we cannot
accept returns. Receive
up to 80% off select
products.

₹3,041

20+ In Stock

[#66-013 Clearance](#)



Clearance

25.00 17.50 0.71

BBAR
(425-
675nm)

Availability is limited,
so buy before these
products disappear.
Sorry, we cannot
accept returns. Receive
up to 80% off select
products.

₹3,998

20+ In Stock

[#66-014 Clearance](#)



Clearance

25.00 20.00 0.63

BBAR
(425-
675nm)

Availability is limited,
so buy before these
products disappear.
Sorry, we cannot
accept returns. Receive
up to 80% off select
products.

₹3,998

20+ In Stock

[#66-015 Clearance](#)



Clearance

25.00	25.00	0.50	BBAR (425-675nm)	Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.	₹3,998	20+ In Stock
-------	-------	------	---------------------	--	--------	--------------

[#66-016 Clearance](#)



Clearance

25.00	30.00	0.42	BBAR (425-675nm)	Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.	₹3,998	20+ In Stock
-------	-------	------	---------------------	--	--------	--------------

[#66-017 Clearance](#)



Clearance

25.00	40.00	0.31	BBAR (425-675nm)	Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.	₹3,998	20+ In Stock
-------	-------	------	---------------------	--	--------	--------------

[#66-018 Clearance](#)



Clearance

25.00	50.00	0.25	BBAR (425- 675nm)	Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.	₹3,998	Contact Us
-------	-------	------	-------------------------	--	--------	------------

[#66-021 Clearance](#)



Clearance

25.00	20.00	0.63	BBAR (600- 1000nm)	Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.	₹3,998	20+ In Stock
-------	-------	------	--------------------------	--	--------	--------------

[#66-022 Clearance](#)



Clearance

25.00	25.00	0.50	BBAR (600- 1000nm)	Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.	₹3,998	20+ In Stock
-------	-------	------	--------------------------	--	--------	--------------

[#66-023 Clearance](#)



Clearance

25.00	30.00	0.42	BBAR (600- 1000nm)	Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.	₹3,998	20+ In Stock
-------	-------	------	--------------------------	--	--------	--------------

[#66-024 Clearance](#)



Clearance

25.00	40.00	0.31	BBAR (600- 1000nm)	Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.	₹3,998	20+ In Stock
-------	-------	------	--------------------------	--	--------	--------------

[#66-025 Clearance](#)



Clearance

25.00	50.00	0.25	BBAR (600- 1000nm)	Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.	₹3,998	20+ In Stock
-------	-------	------	--------------------------	--	--------	--------------



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038

Phone: 1-800-363-1992 :

www.edmundoptics.com