


[All Products](#) / [Optics](#) / [Optical Lenses](#) / [Aspheric Lenses](#) / [Glass Polished](#)

TECHSPEC® Near-Infrared (NIR) Aspheric Lenses



- Optimized for Applications in the NIR
- Uncoated or AR coated versions available
- Multiple Design Wavelengths Available

Common Specifications

Physical & Mechanical Properties

Bevel:

Protective as needed

Technical Information

Products

Dia. (mm)	EFL (mm)	Aspheric DWL (nm)	NA	Coating	Stock Number	Price	Buy
10.00	8.00	780	0.63	Uncoated	#13-496	₹13,390 Volume Pricing	20+ In Stock
10.00	8.00	780	0.63	VIS+ (350-700nm)	#16-266	₹14,947 Volume Pricing	2 In Stock
10.00	8.00	780	0.63	NIR+ (600-1050nm)	#16-278	₹14,947 Volume Pricing	20+ In Stock
10.00	8.00	780	0.63	SWIR+ (900-1700nm)	#16-290	₹14,947 Volume Pricing	9 In Stock
12.50	25.00	780	0.25	Uncoated	#13-498	₹15,414 Volume Pricing	20+ In Stock
12.50	25.00	780	0.25	VIS+ (350-700nm)	#16-268	₹16,971 Volume Pricing	15 In Stock
12.50	25.00	780	0.25	NIR+ (600-1050nm)	#16-280	₹16,971 Volume Pricing	11 In Stock
12.50	25.00	780	0.25	SWIR+ (900-1700nm)	#16-292	₹16,971 Volume Pricing	12 In Stock
12.50	10.00	780	0.63	Uncoated	#13-497	₹15,414 Volume Pricing	20+ In Stock
12.50	10.00	780	0.63	VIS+ (350-700nm)	#16-267	₹16,971 Volume Pricing	17 In Stock
12.50	10.00	780	0.63	NIR+ (600-1050nm)	#16-279	₹16,971 Volume Pricing	13 In Stock
12.50	10.00	780	0.63	SWIR+ (900-1700nm)	#16-291	₹16,971 Volume Pricing	7 In Stock
15.00	30.00	1550	0.25	Uncoated	#17-417	₹24,289 Volume Pricing	20+ In Stock
15.00	30.00	1550	0.25	SWIR+	#29-987	₹25,924 Volume Pricing	Contact Us
15.00	30.00	1550	0.25	1550nm V-Coat	#22-937	₹25,924 Volume Pricing	1 In Stock
15.00	15.00	2000	0.5	Uncoated	#18-749	₹46,710 Volume Pricing	5 In Stock

15.00	15.00	1550	0.5	Uncoated	#17-416	₹24,289 Volume Pricing	14 In Stock
15.00	15.00	1550	0.5	SWIR+	#29-986	₹25,924 Volume Pricing	8 In Stock
15.00	15.00	1550	0.5	1550nm V-Coat	#22-936	₹25,924 Volume Pricing	10 In Stock
15.00	12.00	780	0.63	Uncoated	#13-499	₹16,582 Volume Pricing	20+ In Stock
15.00	12.00	780	0.63	VIS+ (350-700nm)	#16-269	₹18,217 Volume Pricing	15 In Stock
15.00	12.00	780	0.63	NIR+ (600-1050nm)	#16-281	₹18,217 Volume Pricing	8 In Stock
15.00	12.00	780	0.63	SWIR+ (900-1700nm)	#16-293	₹18,217 Volume Pricing	11 In Stock
15.00	11.25	1550	0.67	Uncoated	#17-415	₹25,924 Volume Pricing	6 In Stock
15.00	11.25	1550	0.67	SWIR+	#29-985	₹27,559 Volume Pricing	5 In Stock
15.00	11.25	1550	0.67	1550nm V-Coat	#22-935	₹27,559 Volume Pricing	3 In Stock
18.00	15.00	780	0.60	Uncoated	#13-500	₹18,217 Volume Pricing	16 In Stock
18.00	15.00	780	0.60	VIS+ (350-700nm)	#16-270	₹19,852 Volume Pricing	11 In Stock
18.00	15.00	780	0.60	NIR+ (600-1050nm)	#16-282	₹19,852 Volume Pricing	20+ In Stock
18.00	15.00	780	0.60	SWIR+ (900-1700nm)	#16-294	₹19,852 Volume Pricing	Contact Us
20.00	17.99	780	0.56	Uncoated	#13-501	₹18,995 Volume Pricing	20+ In Stock
20.00	17.99	780	0.56	VIS+ (350-700nm)	#16-271	₹20,630 Volume Pricing	20+ In Stock
20.00	17.99	780	0.56	NIR+ (600-1050nm)	#16-283	₹20,630 Volume Pricing	4 In Stock
20.00	17.99	780	0.56	SWIR+ (900-1700nm)	#16-295	₹20,630 Volume Pricing	20+ In Stock
25.00	50.00	780	0.25	Uncoated	#13-503	₹19,463 Volume Pricing	10 In Stock

25.00	50.00	1550	0.25	Uncoated	#17-421	₹28,337 Volume Pricing	6 In Stock
25.00	50.00	780	0.25	VIS+ (350-700nm)	#16-273	₹21,876 Volume Pricing	14 In Stock
25.00	50.00	780	0.25	NIR+ (600-1050nm)	#16-285	₹21,876 Volume Pricing	10 In Stock
25.00	50.00	780	0.25	SWIR+ (900-1700nm)	#16-297	₹21,876 Volume Pricing	13 In Stock
25.00	50.00	1550	0.25	SWIR+	#29-990	₹30,751 Volume Pricing	3 In Stock
25.00	50.00	1550	0.25	1550nm V-Coat	#22-940	₹30,751 Volume Pricing	Contact Us
25.00	25.00	1550	0.5	Uncoated	#17-419	₹28,337 Volume Pricing	15 In Stock
25.00	25.00	1550	0.5	SWIR+	#29-989	₹30,751 Volume Pricing	5 In Stock
25.00	25.00	1550	0.5	1550nm V-Coat	#22-939	₹30,751 Volume Pricing	4 In Stock
25.00	20.00	780	0.63	Uncoated	#13-502	₹19,463 Volume Pricing	12 In Stock
25.00	20.00	780	0.63	VIS+ (350-700nm)	#16-272	₹21,876 Volume Pricing	12 In Stock
25.00	20.00	780	0.63	NIR+ (600-1050nm)	#16-284	₹21,876 Volume Pricing	20+ In Stock
25.00	20.00	780	0.63	SWIR+ (900-1700nm)	#16-296	₹21,876 Volume Pricing	20+ In Stock
25.00	15.00	1550	0.83	Uncoated	#17-418	₹30,362 Volume Pricing	2 In Stock
25.00	15.00	1550	0.83	SWIR+	#29-988	₹32,775 Volume Pricing	20+ In Stock
25.00	15.00	1550	0.83	1550nm V-Coat	#22-938	₹32,775 Volume Pricing	14 In Stock
30.00	26.00	780	0.58	Uncoated	#13-504	₹25,535 Volume Pricing	20+ In Stock
30.00	26.00	780	0.58	VIS+ (350-700nm)	#16-274	₹27,948 Volume Pricing	20+ In Stock
30.00	26.00	780	0.58	NIR+ (600-1050nm)	#16-286	₹27,948 Volume Pricing	20+ In Stock

30.00	26.00	780	0.58	SWIR+ (900-1700nm)	#16-298	₹27,948 Volume Pricing	5 In Stock
45.00	32.00	780	0.70	Uncoated	#13-505	₹35,655 Volume Pricing	13 In Stock
45.00	32.00	780	0.70	VIS+ (350-700nm)	#16-275	₹38,458 Volume Pricing	Contact Us
45.00	32.00	780	0.70	NIR+ (600-1050nm)	#16-287	₹38,458 Volume Pricing	5 In Stock
45.00	32.00	780	0.70	SWIR+ (900-1700nm)	#16-299	₹38,458 Volume Pricing	4 In Stock
50.00	100.00	780	0.25	Uncoated	#13-507	₹41,261 Volume Pricing	20+ In Stock
50.00	100.00	780	0.25	VIS+ (350-700nm)	#16-277	₹45,153 Volume Pricing	4 In Stock
50.00	100.00	780	0.25	NIR+ (600-1050nm)	#16-289	₹45,153 Volume Pricing	20+ In Stock
50.00	100.00	780	0.25	SWIR+ (900-1700nm)	#16-301	₹45,153 Volume Pricing	20+ In Stock
50.00	40.00	780	0.63	Uncoated	#13-506	₹41,261 Volume Pricing	20+ In Stock
50.00	40.00	780	0.63	VIS+ (350-700nm)	#16-276	₹45,153 Volume Pricing	20+ In Stock
50.00	40.00	780	0.63	NIR+ (600-1050nm)	#16-288	₹45,153 Volume Pricing	12 In Stock
50.00	40.00	780	0.63	SWIR+ (900-1700nm)	#16-300	₹45,153 Volume Pricing	20+ In Stock
75.00	150.00	780	0.25	Uncoated	#13-509	₹64,616 Volume Pricing	5 In Stock
75.00	150.00	780	0.25	NIR+ (600-1050nm)	#28-916	₹72,790 Volume Pricing	4 In Stock
100.00	100.00	780	0.50	NIR+ (600-1050nm)	#28-917	₹94,977 Volume Pricing	1 In Stock
75.00	60.00	780	0.63	Uncoated	#13-508	₹64,616 Volume Pricing	14 In Stock
75.00	60.00	780	0.63	NIR+ (600-1050nm)	#28-915	₹72,790 Volume Pricing	5 In Stock
100.00	200.00	780	0.25	Uncoated	#13-511	₹87,192 Volume Pricing	5 In Stock

100.00	200.00	780	0.25	NIR+ (600-1050nm)	#28-918	₹94,977 Volume Pricing	4 In Stock
100.00	100.00	780	0.50	Uncoated	#13-510	₹87,192 Volume Pricing	20+ In Stock



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038

Phone: 1-800-363-1992 :

www.edmundoptics.com