

[All Products](#) / [Cameras](#) / [Gigabit Ethernet Cameras](#)

IDS Imaging uEye Warp10 10GigE Cameras See More by [IDS Imaging Development Systems](#)





- 10GBASE-T (10GigE) Ethernet Interface, 10X Faster than GigE
- Up to 12.3MP Resolution with Framrates up to 98fps
- Compatible with 1GigE, 2.5GigE and 5GigE Interfaces

Common Specifications

General				
Manufacturer:		IDS Imaging Development Systems	Camera Series:	uEye+ WP
Physical & Mechanical Properties				
Dimensions (mm):		60 x 75 x 94.5 (excludes connectors and lens mount)	Housing:	Full
Sensor				
Image Buffer:		2032	Type of Sensor:	Progressive Scan CMOS
Shutter Type:		Global	Pixel Depth:	12 bit
Machine Vision Standard:		GigE Vision		
Hardware & Interface Connectivity				
Interface:		10GigE (PoE)		
Power Supply:		Power over Ethernet (PoE) or via GPIO	GPIOs:	1 Trigger Input, 1 Flash Output, 2 Fast Output
Interface Port Orientation:		Back Panel	GPIO Connector Type:	12-pin M12 connector (Attend 216A-12MSR)
Threading & Mounting				
Mounting Threads:			1/4-20 with Tripod Mount Adapter #16-017	
Environmental & Durability Factors				
Operating Temperature (°C):			0 to +55	
Storage Temperature (°C):			-20 to +60	

Technical Information

Products

Type	Sensor Format	Resolution (Megapixels)	Model Number	Mount	Stock Number	Price	Buy
Monochrome Camera	1.3"	20.32	GV-77Q5WP-M-GL	TFL-Mount	#78-297 New	₹6,45,000	Contact Us
							
					New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!		
Color Camera	1.3"	20.32	GV-77Q5WP-C-HQ	TFL-Mount	#78-296 New	₹6,45,000	Contact Us
							
					New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!		

[#78-299 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

Monochrome
Camera

1.5"

29.90

GV-
77S5WP-
M-GL

TFL-
Mount

₹6,78,500

Contact Us

[#78-298 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

Color
Camera

1.5"

29.90

GV-
77S5WP-
C-HQ

TFL-
Mount

₹6,78,500

Contact Us

[#73-555 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

Monochrome Camera

2"

44.84

GV-77U5WP-M-GL

TFL-Mount

₹7,82,000

Contact Us

[#73-556 New](#)



New

Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!

Color Camera

2"

44.84

GV-77U5WP-C-HQ

TFL-Mount

₹7,93,000

Contact Us

Color Camera

1.1"

12.30

GV-7000WP-C-HQ

C-Mount

[#24-071](#)

₹3,45,500

1 In Stock

Monochrome Camera

1.1"

12.30

GV-7000WP-M-GL

C-Mount

[#24-072](#)

₹3,45,500

Contact Us

Color Camera

2/3"

5.00

GV-7080WP-C-HQ

C-Mount

[#24-073](#)

₹2,32,000

1 In Stock

Monochrome Camera

2/3"

5.00

GV-7080WP-M-GL

C-Mount

[#24-074](#)

₹2,32,000

1 In Stock

Color Camera	1"	8.80	GV-7090WP-C-HQ	C-Mount	#24-075	₹3,17,000	1 In Stock
Monochrome Camera	1"	8.80	GV-7090WP-M-GL	C-Mount	#24-076	₹3,17,000	2 In Stock
Color Camera	1/1.8"	5.10	GV-79F0WP-C-HQ	C-Mount	#28-721	₹2,26,500	1 In Stock
Monochrome Camera	1/1.8"	5.10	GV-79F0WP-M-GL	C-Mount	#28-722	₹2,26,500	Contact Us
Color Camera	2/3"	8.13	GV-79J0WP-C-HQ	C-Mount	#28-723	₹2,49,000	1 In Stock
Monochrome Camera	2/3"	8.13	GV-79J0WP-M-GL	C-Mount	#28-724	₹2,49,000	1 In Stock
Color Camera	1"	12.42	GV-79L0WP-C-HQ	C-Mount	#28-725	₹2,84,000	Contact Us
Monochrome Camera	1"	12.42	GV-79L0WP-M-GL	C-Mount	#28-726	₹2,83,000	1 In Stock



Edmund
optics | worldwide

Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038
Phone: 1-800-363-1992 :
www.edmundoptics.com