

[All Products](#) /
 [Laser Optics](#) /
 [Laser Mirrors](#) /
 [Laser Line Mirrors](#)

TECHSPEC® Concave Laser Line Mirrors



- Ideal for Focusing Laser Light
- >99.8% Reflectivity at Center Wavelength
- High Thermal Stability Fused Silica Substrates

Common Specifications

Physical & Mechanical Properties

Back Surface: Fine Grind

Clear Aperture (%): 90


Optical Properties

Substrate: [Fused Silica](#) (Corning 7980)


Surface Quality: 20-10

Technical Information

266nm and 355nm



532nm and 1064nm



Products

DWL (nm)	Dia. (mm)	EFL (mm)	Coating	Stock Number	Price	Buy
266	25.40	25.00	Laser Mirror (266nm)	#39-947	₹12,845 Volume Pricing	10 In Stock
266	25.40	50.00	Laser Mirror (266nm)	#39-948	₹12,845 Volume Pricing	10 In Stock
266	25.40	75.00	Laser Mirror (266nm)	#39-949	₹12,845 Volume Pricing	12 In Stock
266	25.40	100.00	Laser Mirror (266nm)	#39-950	₹12,845 Volume Pricing	3 In Stock
266	25.40	200.00	Laser Mirror (266nm)	#39-951	₹12,845 Volume Pricing	1 In Stock
266	25.40	500.00	Laser Mirror (266nm)	#39-952	₹12,845 Volume Pricing	8 In Stock
355	25.40	25.00	Laser Mirror (355nm)	#39-954	₹12,845 Volume Pricing	13 In Stock
355	25.40	50.00	Laser Mirror (355nm)	#39-955	₹12,845 Volume Pricing	20+ In Stock
355	25.40	75.00	Laser Mirror (355nm)	#39-956	₹12,845 Volume Pricing	17 In Stock
355	25.40	100.00	Laser Mirror (355nm)	#39-957	₹12,845 Volume Pricing	14 In Stock
355	25.40	200.00	Laser Mirror (355nm)	#39-958	₹12,845 Volume Pricing	20+ In Stock
355	25.40	500.00	Laser Mirror (355nm)	#39-959	₹12,845 Volume Pricing	10 In Stock
532	25.40	25.00	Laser Mirror (532nm)	#39-960	₹12,845 Volume Pricing	Contact Us
532	25.40	50.00	Laser Mirror (532nm)	#39-961	₹12,845 Volume Pricing	4 In Stock
532	25.40	75.00	Laser Mirror (532nm)	#39-962	₹12,845 Volume Pricing	3 In Stock
532	25.40	100.00	Laser Mirror (532nm)	#39-963	₹12,845 Volume Pricing	5 In Stock

532	25.40	200.00	Laser Mirror (532nm)	#39-964	₹12,845 Volume Pricing	3 In Stock
532	25.40	500.00	Laser Mirror (532nm)	#39-965	₹12,845 Volume Pricing	3 In Stock
1064	25.40	25.00	Laser Mirror (1064nm)	#39-966	₹12,845 Volume Pricing	11 In Stock
1064	25.40	50.00	Laser Mirror (1064nm)	#39-967	₹12,845 Volume Pricing	4 In Stock
1064	25.40	75.00	Laser Mirror (1064nm)	#39-968	₹12,845 Volume Pricing	10 In Stock
1064	25.40	100.00	Laser Mirror (1064nm)	#39-969	₹12,845 Volume Pricing	Contact Us
1064	25.40	200.00	Laser Mirror (1064nm)	#39-970	₹12,845 Volume Pricing	1 In Stock
1064	25.40	500.00	Laser Mirror (1064nm)	#39-971	₹12,845 Volume Pricing	1 In Stock
266	50.80	50.00	Laser Mirror (266nm)	#11-327	₹18,684 Volume Pricing	1 In Stock
266	50.80	100.00	Laser Mirror (266nm)	#11-328	₹18,684 Volume Pricing	4 In Stock
266	50.80	150.00	Laser Mirror (266nm)	#11-329	₹18,684 Volume Pricing	5 In Stock
266	50.80	250.00	Laser Mirror (266nm)	#11-330	₹18,684 Volume Pricing	5 In Stock
266	50.80	500.00	Laser Mirror (266nm)	#11-331	₹18,684 Volume Pricing	4 In Stock
355	50.80	50.00	Laser Mirror (355nm)	#11-332	₹18,684 Volume Pricing	2 In Stock
355	50.80	100.00	Laser Mirror (355nm)	#11-333	₹18,684 Volume Pricing	6 In Stock
355	50.80	150.00	Laser Mirror (355nm)	#11-334	₹18,684 Volume Pricing	9 In Stock
355	50.80	250.00	Laser Mirror (355nm)	#11-335	₹18,684 Volume Pricing	5 In Stock
355	50.80	500.00	Laser Mirror (355nm)	#11-336	₹18,684 Volume Pricing	14 In Stock
532	50.80	50.00	Laser Mirror (532nm)	#11-337	₹18,684 Volume Pricing	3 In Stock

532	50.80	100.00	Laser Mirror (532nm)	#11-338	₹18,684 Volume Pricing	1 In Stock
532	50.80	150.00	Laser Mirror (532nm)	#11-339	₹18,684 Volume Pricing	1 In Stock
532	50.80	250.00	Laser Mirror (532nm)	#11-340	₹18,684 Volume Pricing	5 In Stock
532	50.80	500.00	Laser Mirror (532nm)	#11-341	₹18,684 Volume Pricing	5 In Stock
1064	50.80	50.00	Laser Mirror (1064nm)	#11-342	₹18,684 Volume Pricing	2 In Stock
1064	50.80	100.00	Laser Mirror (1064nm)	#11-343	₹18,684 Volume Pricing	Contact Us
1064	50.80	150.00	Laser Mirror (1064nm)	#11-344	₹18,684 Volume Pricing	6 In Stock
1064	50.80	250.00	Laser Mirror (1064nm)	#11-345	₹18,684 Volume Pricing	8 In Stock
1064	50.80	500.00	Laser Mirror (1064nm)	#11-346	₹18,684 Volume Pricing	4 In Stock
-	25.40	25.00	Uncoated	#39-973	₹8,641 Volume Pricing	5 In Stock
-	25.40	50.00	Uncoated	#39-974	₹8,641 Volume Pricing	16 In Stock
-	25.40	100.00	Uncoated	#39-977	₹8,641 Volume Pricing	20+ In Stock
-	25.40	75.00	Uncoated	#39-975	₹8,641 Volume Pricing	15 In Stock
-	25.40	200.00	Uncoated	#39-978	₹8,641 Volume Pricing	20+ In Stock
-	25.40	500.00	Uncoated	#39-979	₹8,641 Volume Pricing	20+ In Stock
-	50.80	50.00	Uncoated	#11-347	₹16,037 Volume Pricing	20+ In Stock
-	50.80	100.00	Uncoated	#11-348	₹15,959 Volume Pricing	7 In Stock
-	50.80	150.00	Uncoated	#11-349	₹16,037 Volume Pricing	20+ In Stock
-	50.80	250.00	Uncoated	#11-350	₹16,037 Volume Pricing	20+ In Stock

-	50.80	500.00	Uncoated	#11-352	₹16,037 Volume Pricing	20+ In Stock
---	-------	--------	----------	-------------------------	---	--------------



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038

Phone: 1-800-363-1992 :

www.edmundoptics.com