

[All Products](#) / [Optomechanics](#) / [Benchtop Optical Mounts](#) / [Optical Lens and Filter Mounts](#)

Multi-Axis Adjustable Optic Mounts



- 2-Axis, 3-Axis, and 5-Axis Adjustable Mounts Available
- Options for 12.5mm (0.5"), 25mm (1"), and 50mm (2") Dia. Optics
- M6 Mounting Threads

Common Specifications

Physical & Mechanical Properties

Construction:



Black Anodized Aluminum

Threading & Mounting

Compatible Post:

M6 x 1.0

Technical Information



Products

Type	Size of Compatible Optics (mm)	CA (mm)	Travel (mm)	Stock Number	Price	Buy
Adjustable - Linear (XY)	12.5 - 12.7	10.0	±1.5 in X and Y	#62-955	₹17,897 Volume Pricing	10 In Stock
Adjustable - Linear (XY)	25.0 - 25.4	22.0	±1.5 in X and Y	#62-956	₹18,924 Volume Pricing	14 In Stock
Adjustable - Linear (XY)	50.0 - 50.8	46.0	±2.0 in X and Y	#62-957	₹21,125 Volume Pricing	3 In Stock
Adjustable - Linear (XY)	-	1" x 32 TPI	±1.5 in X and Y	#87-209	₹25,379 Volume Pricing	4 In Stock
Adjustable - Linear (XYZ)	12.5 - 12.7	10.0	±2.0 in X and Y, ±1.5 in Z	#62-958	₹29,413 Volume Pricing	4 In Stock
Adjustable - Linear (XYZ)	25.0 - 25.4	22.0	±2.0 in X and Y, ±1.5 in Z	#62-959	₹37,042 Volume Pricing	7 In Stock
Adjustable - Linear (XYZ)	50.0 - 50.8	46.0	±1.5 in X and Y, ±1.5 in Z	#62-960	₹41,443 Volume Pricing	5 In Stock
Adjustable - Linear (XYZ)	-	1" x 32 TPI	±2.0 in X and Y, ±1.5 in Z	#87-210	₹33,154 Volume Pricing	2 In Stock
Adjustable - Linear (XYZ) & Tip-Tilt	25.0 - 25.4	22.0	±2.0 in X and Y, ±1.5 in Z	#13-776	₹51,712 Volume Pricing	2 In Stock
Adjustable - Linear (XYZ) & Tip-Tilt	50.0 - 50.8	46.0	±2.0 in X and Y, ±1.5 in Z	#13-778	₹57,580 Volume Pricing	1 In Stock



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038

Phone: 1-800-363-1992 :

www.edmundoptics.com