

[All Products](#) / [Cameras](#) / [Gigabit Ethernet Cameras](#)

## Teledyne FLIR IIS Oryx®10GigE Cameras

See More by [Teledyne FLIR](#)

- 10GBASE-T (10GigE) Ethernet Interface
- 3.2 to 31 Megapixel Sony 4th Gen Pregius S Sensors
- Supports 4K60, 12-bit System Integration
- Tripod Adapter Built into Larger Oryx® Models



  
Teledyne  
Authorized  
Distributor

### Common Specifications

#### General

Manufacturer:	FLIR	Camera Series:	Oryx®
---------------	------	----------------	-------

#### Physical & Mechanical Properties

Housing:	Full
----------	------

#### Sensor

Image Buffer:	240MB
---------------	-------

Type of Sensor:	Progressive Scan CMOS	Shutter Type:	Global
-----------------	-----------------------	---------------	--------

Machine Vision Standard:	GigE Vision
--------------------------	-------------

#### Hardware & Interface Connectivity

Interface:	10GigE
------------	--------

Connector:	GigE interface with Screw Locks	Power Supply:	Power Supply Required and Sold Separately: USA: <a href="#">#19-803</a> Europe: <a href="#">#19-803</a> Japan: <a href="#">#19-803</a> Korea: Not Available China: <a href="#">#19-803</a>
------------	---------------------------------	---------------	---

Synchronization:	Hardware Trigger (GPIO) or Software Trigger	Interface Port Orientation:	Back Panel
------------------	---	-----------------------------	------------

GPIO Connector Type:	12-pin Hirose (HR10)
----------------------	----------------------

#### Environmental & Durability Factors

Storage Temperature (°C):	-30 to +60
---------------------------	------------

## Technical Information

## Products

Type	Model Number	Sensor Format	Resolution (Megapixels)	Connector	Mount	Stock Number	Price	Buy
Monochrome Camera	ORX-10GS-89S6M-C	1"	8.90	GigE interface with Screw Locks	C-Mount	<a href="#">#19-792</a>	₹4,31,000	1 In Stock



Recertified

Stock No.: 19-792-RCD-05P  
Recertified Code: 05P (All Original  
Parts Included, Perfect)

## Recertified Products

*Typically 1-2 Recertified Products are  
in stock at a time. Please contact our  
sales team if you would like exact  
availability of an item.*

Recertified products are those  
identified with the recertified logo  
indicating they were returned to  
Edmund Optics® and cannot be sold  
as new for the following reasons:

- Open Box – Missing original  
packaging
- Cosmetic Blemishes –  
Scratches, rub marks or other  
minor cosmetic imperfections
- Service/Repair – Product has  
been serviced to the factory  
original specification
- Factory Returns – Product has  
been returned in its original  
condition

Monochrome Camera	ORX-10GS-89S6MC	1"	8.90	GigE interface with Screw Locks	C-Mount	Recertified products are inspected for damage and any necessary repairs are made. Products are then certified by Edmund Optics® to be in good working order. Since quantity is low, recertified products are sold on a first come, first serve basis. Any imperfections will be listed in the description, indicated in the stock number, and categorized by the table below. When purchasing recertified products, the Edmund Optics® standard <a href="#">return policy</a> applies.	₹3,90,957	1 In Stock
-------------------	-----------------	----	------	---------------------------------	---------	--	-----------	------------

View all our [recertified products](#) in the  
Web Specials section of our website.

	Parts		Cosmetic	
	05	All Original Parts Included	P	Perfect
04	Missing Manual	N	Minor Defect/Scratches	
03	Missing Manual and Small Accessory	J	Major Defect/Scratches	
02	Missing Manual and Large Accessory			



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038  
Phone: 1-800-363-1992 :  
[www.edmundoptics.com](http://www.edmundoptics.com)