

[All Products](#) / [Imaging Lenses](#) / [Fixed Focal Length Lenses](#)

TECHSPEC® C Series Fixed Focal Length SWIR Lenses



- Up to 2/3", C-Mount Lens
- Up to 7.5 MegaPixels, 2.8µm Pixel Size Sensors
- Compact (C) SWIR Lens for 900-1700nm Wavelength Range
- 3.5mm to 100mm Focal Length

Common Specifications

Physical & Mechanical Properties

Iris Option: Variable

Optical Properties

Coating: 900 - 1700nm BBAR

Coating Specification: 900 - 1700nm BBAR

Threading & Mounting

Mount: C-Mount

Environmental & Durability Factors

Storage Temperature (°C): -20 to +60 For questions regarding operating temperature please contact our support team

Technical Information

Products

FL (mm)	Max. Sensor Format	Aperture (f/#)	WD (mm)	Mount	Stock Number	Price	Buy
3.50	1/1.8"	f/2 - f/11	0 - ∞	C-Mount	#23-216	₹55,800	Contact Us
4.50	1/1.8"	f/2 - f/11	25 - ∞	C-Mount	#23-217	₹55,800	Contact Us
6.00	1/1.8"	f/1.4 - f/16	75 - ∞	C-Mount	#23-218	₹32,886	5 In Stock
8.50	2/3"	f/1.3 - f/16	100 - ∞	C-Mount	#23-219	₹32,886	2 In Stock
12.00	2/3"	f/1.8 - f/16	100 - ∞	C-Mount	#23-220	₹32,886	5 In Stock
16.00	2/3"	f/1.6 - f/16	100 - ∞	C-Mount	#23-221	₹28,710	2 In Stock
25.00	2/3"	f/1.4 - f/16	100 - ∞	C-Mount	#23-222	₹28,710	5 In Stock
35.00	2/3"	f/1.65 - f/22	165 - ∞	C-Mount	#23-223	₹28,710	2 In Stock
50.00	2/3"	f/2 - f/22	250 - ∞	C-Mount	#23-224	₹31,581	3 In Stock
#74-055 New							
 New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!							
75.00	2/3"	f/2.0 - f/16.0	500 - ∞	C-Mount		₹52,200	1 In Stock
100.00	4/3"	f/2.8 - f/22	750 - ∞	C-Mount	#23-225	₹53,550	Contact Us



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038

Phone: 1-800-363-1992 :

www.edmundoptics.com