

FOCAL LENGTH (EFL):  $10 \pm 0,1$   
 BACK FOCAL LENGTH (BFL):  $8,18$

1 AR COATING: NONE

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	$7,85 \pm 0,008$ CX	GLASS N-SF11 785/258	R	$\infty$ PL
$\varnothing_e$	9		$\varnothing_e$	9
3/	3 (0,5) $\lambda=632,8$ nm		3/	3 (0,5) $\lambda=632,8$ nm
4/	-		4/	$3,82'$
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED


ROHS: COMPLIANT  
 SCALE: NONE  
 $\lambda = 587,6$  nm

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm

**EO**® Edmund Optics®

TITLE 10,0mm Dia, x 10,0mm FL, Uncoated, Plano-Convex Lens

DWG NO 63471

SHEET SIZE A4 SHEET 1 OF 1