



FOCAL LENGTH (EFL): $75 \pm 0,75$
 BACK FOCAL LENGTH (BFL): $72,31$

LEFT SURFACE	MATERIAL	RIGHT SURFACE
R 35,707 CX Øe 11,7 (λ) - 3/ 2 (0,2) λ=632,8 nm 4/ - 5/ 10 - 5 6/ -	GLASS Fused Silica 458/678	R ∞ PL Øe 11,7 (λ) - 3/ 2 (0,2) λ=632,8 nm 4/ 2,18' 5/ 10 - 5 6/ -

PROTECTIVE CHAMFERS AS NEEDED		FIRST ANGLE PROJECTION			
ROHS: COMPLIANT	SCALE: NONE				λ = 355nm
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY			TITLE	12,7mm Dia x 75mm FL, Uncoated, Plano-Convex Lens	
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING			ALL DIMS IN: mm	DWG NO	38637
INDICATIONS IN ACCORDANCE WITH ISO 10110					SHEET 1 OF 1