



KG2

Optical properties	Mechanical properties	Colorimetric properties
Reflection factor	Reference thickness	1 mm 2 mm 3 mm
$P_d = 0,921$	$d = 2,00 \text{ mm}$	Illuminant D65 x 0,312 0,311 0,310 y 0,330 0,331 0,331 Y 89,5 87,1 84,7 λ_d 501 nm 501 nm 501 nm P _e 0,003 0,007 0,010
Spectral values guaranteed	Density	
τ_i (365 nm) $\geq 0,93$	$\rho = 2,52 \text{ g/cm}^3$	
τ_i (500 nm) $\geq 0,94$	Knoop hardness	
τ_i (600 nm) $\geq 0,92$	HK[0.1/20] = 444	
τ_i (700 nm) $\leq 0,83$	Thermal properties	Illuminant A x 0,446 0,444 0,442 y 0,409 0,410 0,411 Y 89,3 86,7 84,2 λ_d 506 nm 507 nm 507 nm P _e 0,004 0,008 0,012
τ_i (800 nm) $\leq 0,55$	Transformation temperature	
τ_i (900 nm) $\leq 0,28$	$T_g = 605 \text{ }^\circ\text{C}$	
τ_i (1060 nm) $\leq 0,12$	Thermal expansion in $10^{-6}/\text{K}$	
τ_i (2200 nm) $\leq 0,2$	$\alpha_{(-30^\circ\text{C}/+70^\circ\text{C})} = 5,4$	
Refractive indices	$\alpha_{(20^\circ\text{C}/300^\circ\text{C})} = 6,3$	Notes
		UV
n_d (587,6 nm) = 1,51		Transmission changes are possible under the action of intense ultraviolet radiation.
Sellmeier coefficients	Chemical properties	Ionically colored glass
on request	Chemical resistance	Shortpass filter
	FR class = 0	Heat protection filter
	SR class = 2	DIN 58131
	AR class = 3	
	Resistance against humidity	Disclaimer
	Delicate glass	All data without tolerances are to be understood to be reference values.
Internal quality	see pocket catalogue "Optical Filter Glass 2020", chapter 5.5	
Bubble class 3		



KG2



Internal transmittance τ_i at reference thickness
 The internal transmittance values, tabulated and graphically represented, are reference values only

λ /nm	τ_i	λ /nm	τ_i	λ /nm	τ_i	λ /nm	τ_i	λ /nm	τ_i	λ /nm	τ_i
200	< 1,0E-05	500	9,569E-01	800	5,237E-01	1100	9,099E-02	2200	1,647E-01	3700	7,376E-03
210	< 1,0E-05	510	9,564E-01	810	4,940E-01	1110	8,975E-02	2250	1,671E-01	3750	5,454E-03
220	< 1,0E-05	520	9,538E-01	820	4,640E-01	1120	8,844E-02	2300	1,764E-01	3800	3,463E-03
230	< 1,0E-05	530	9,516E-01	830	4,342E-01	1130	8,715E-02	2350	1,885E-01	3850	1,917E-03
240	< 1,0E-05	540	9,531E-01	840	4,080E-01	1140	8,600E-02	2400	1,997E-01	3900	8,350E-04
250	< 1,0E-05	550	9,554E-01	850	3,822E-01	1150	8,470E-02	2450	2,114E-01	3950	3,360E-04
260	1,0E-03	560	9,541E-01	860	3,557E-01	1160	8,350E-02	2500	2,227E-01	4000	1,525E-04
270	2,0E-02	570	9,518E-01	870	3,300E-01	1170	8,252E-02	2550	2,311E-01	4050	7,328E-05
280	8,8E-02	580	9,489E-01	880	3,054E-01	1180	8,150E-02	2600	2,370E-01	4100	4,198E-05
290	2,5E-01	590	9,440E-01	890	2,840E-01	1190	8,070E-02	2650	2,404E-01	4150	2,924E-05
300	4,4E-01	600	9,380E-01	900	2,652E-01	1200	8,005E-02	2700	2,327E-01	4200	2,239E-05
310	6,4E-01	610	9,314E-01	910	2,457E-01	1250	7,868E-02	2750	1,493E-01	4250	2,065E-05
320	7,690E-01	620	9,230E-01	920	2,280E-01	1300	8,103E-02	2800	2,260E-02	4300	2,344E-05
330	8,522E-01	630	9,132E-01	930	2,130E-01	1350	8,550E-02	2850	6,823E-03	4350	3,020E-05
340	9,020E-01	640	9,020E-01	940	2,001E-01	1400	9,250E-02	2900	4,519E-03	4400	4,162E-05
350	9,310E-01	650	8,891E-01	950	1,850E-01	1450	1,028E-01	2950	3,811E-03	4450	4,823E-05
360	9,492E-01	660	8,750E-01	960	1,726E-01	1500	1,157E-01	3000	3,483E-03	4500	4,508E-05
370	9,593E-01	670	8,590E-01	970	1,611E-01	1550	1,305E-01	3050	3,357E-03	4550	4,009E-05
380	9,651E-01	680	8,407E-01	980	1,510E-01	1600	1,471E-01	3100	3,334E-03	4600	3,556E-05
390	9,615E-01	690	8,199E-01	990	1,415E-01	1650	1,651E-01	3150	3,357E-03	4650	2,884E-05
400	9,549E-01	700	7,980E-01	1000	1,333E-01	1700	1,835E-01	3200	3,420E-03	4700	2,143E-05
410	9,482E-01	710	7,740E-01	1010	1,259E-01	1750	1,951E-01	3250	3,491E-03	4750	1,346E-05
420	9,423E-01	720	7,499E-01	1020	1,189E-01	1800	2,007E-01	3300	3,614E-03	4800	< 1,000E-05
430	9,388E-01	730	7,250E-01	1030	1,133E-01	1850	2,011E-01	3350	3,793E-03	4850	< 1,000E-05
440	9,382E-01	740	6,990E-01	1040	1,089E-01	1900	1,971E-01	3400	4,130E-03	4900	< 1,000E-05
450	9,393E-01	750	6,710E-01	1050	1,047E-01	1950	1,905E-01	3450	4,645E-03	4950	< 1,000E-05
460	9,416E-01	760	6,428E-01	1060	1,009E-01	2000	1,834E-01	3500	5,333E-03	5000	< 1,000E-05
470	9,461E-01	770	6,130E-01	1070	9,748E-02	2050	1,776E-01	3550	6,109E-03	5050	< 1,000E-05
480	9,506E-01	780	5,840E-01	1080	9,478E-02	2100	1,724E-01	3600	7,119E-03	5100	< 1,000E-05
490	9,542E-01	790	5,530E-01	1090	9,283E-02	2150	1,676E-01	3650	7,893E-03	5150	< 1,000E-05