



FOCAL LENGTH (EFL):  $12 \pm 0,12$   
 BACK FOCAL LENGTH (BFL):  $9,26$

- 1 1550nm V-COAT  
 $R(\text{ABS}) < 0,25\% @ 1550\text{nm} @ 0^\circ \text{AOI}$

LEFT SURFACE	MATERIAL	RIGHT SURFACE
R 5,502 CX $\varnothing_e$ 8,1 $\lambda$ SEE NOTE 1 3/ 3 (0,5) $\lambda=632,8$ nm 4/ - 5/ 40 - 20 6/ -	GLASS Fused Silica 458/678 Nd: 1,458	R $\infty$ PL $\varnothing_e$ 8,1 $\lambda$ SEE NOTE 1 3/ 3 (0,5) $\lambda=632,8$ nm 4/ 2,18' 5/ 40 - 20 6/ -

PROTECTIVE CHAMFERS AS NEEDED		FIRST ANGLE PROJECTION	Edmund Optics®	
ROHS: COMPLIANT	SCALE: NONE			
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY. DO NOT MANUFACTURE PARTS TO THIS DRAWING			TITLE	9mm Dia x 12mm FL, 1550NM V-COAT Coated, Plano-Convex Lens
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN: mm	DWG NO
			SHEET SIZE	A4
			SHEET	1 OF 1