


[All Products](#) / [Optics](#) / [Optical Filters](#) / [Neutral Density \(ND\) Filters](#)

Continuously Variable Neutral Density Filters



- Continuous Linear Adjustment of Optical Density
- Use in Pairs to Control Beam Transmission
- Ideal for 400 - 700nm

Common Specifications


Physical & Mechanical Properties

Dimensions (mm):	25.4 x 76.2	Length (inches):	3.00
Length (mm):	76.20	Thickness (inches):	0.063 ±0.01
Thickness (mm):	1.60 ±0.25	Width (inches):	1.00
Width (mm):	25.40	Construction:	Plate

Optical Properties

Angle of Incidence (°):	0.00	Substrate:	Float Glass
Coating:	Surface 1: Inconel	Blocking Wavelength Range (nm):	400 - 700

Technical Information



Products

Dimensions (mm)	Optical Density OD (Average)	Thickness (inches)	Thickness (mm)	Stock Number	Price	Buy
25.4 x 76.2	0.04 - 1.0	0.063	1.60	#64-381	₹7,941 Volume Pricing	1 In Stock
25.4 x 76.2	0.04 - 2.0	0.063	1.60	#41-960	₹9,186 Volume Pricing	20+ In Stock
25.4 x 76.2	0.04 - 3.0	0.063	1.60	#64-382	₹11,678 Volume Pricing	1 In Stock
25.4 x 76.2	0.04 - 4.0	0.063	1.60	#63-048	₹13,312 Volume Pricing	3 In Stock



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038

Phone: 1-800-363-1992 :

www.edmundoptics.com