

Miniature Diode Laser Modules

Circular and elliptical miniature diode laser modules provide the smallest package size and best value. Included inside every module are complete electronics to manage the constant power laser drive with a closed-light loop based on an internal photodiode. Also included in the electronics are protection circuits to provide a robust system in even the smallest of packages.

Miniature diode laser modules use the patented AlignLock technology to guarantee beam-pointing alignment of <4.3 mrad. This allows for simpler and easier integration, as you can trust the unit-to-unit consistency of each beam.

FEATURES

- VLM2 and VLM3-style packages
- High visibility 635 nm, 650 nm, and 670 nm
- Circular or elliptical beams

APPLICATIONS

- Industrial
- Alignment
- Scanning
- Machine Vision
- Inspection
- Medical
- Life Sciences




SPECIFICATIONS	VLM2-3RL, 2mW, 670nm	VMB2.3-4L, 4mW, 635nm	VHK2.3-1L, 1mW, 635nm	VHK2-1L, 1mW, 670nm	VLM2-8L, 7.5mW, 670nm
Module Type	VLM2	VLM2	VLM2	VLM2	VLM2
Wavelength (nm)	670 ±5	635 +7/-2	635 +7/-2	670 ±5	670 ±5
Power (mW)	2.3	4.2	0.95	0.95	7.5
CDRH Class	Illa	Illa		ll, Non-Conforming	IIIb, Non-Conforming
Spot Size (mm)	3	1.3	1.1	1.3	3.4 x 1.3
Beam Type	Circular	Circular	Circular	Ellipical	Elliptical
Divergence (mrad)	0.4	0.7	0.7	0.7	0.3 × 0.8
Laser Drive	Continuous- Wave (CW)				
Power Supply (VDC)	5 to 10				
Recommended Power Supply Voltage (V)	5	5	5	5	5
Body Diameter (mm)	14.8	14.8	14.8	14.8	14.8
Body Length (mm)	45	34	34	34	28
Lead Length (mm)	914	914	914	914	305
Connector	none	none	none	none	none
Part Number	0221-005-00	0222-200-00	0221-698-01	0222-152-01	0223-038-00

SPECIFICATIONS	VLM3.5-2, 1.6mW, 650nm	VLM3-1L, 1mW, 670nm	VLM3-5L, 5mW, 670nm
Module Type	VLM3	VLM3	VLM3
Wavelength (nm)	650 ±5	670 ±5	670 ±5
Power (mW)	1.6	0.95	4.2
CDRH Class	Illa, Non-Conforming	II	Illa
Spot Size (mm)	1.3	1.3 x 4.6	4.6 x 1.3
Beam Type	Circular	Elliptical	Elliptical
Divergence (mrad)	0.8	0.7 × 0.2	0.2 × 0.7
Laser Drive	Continuous- Wave (CW)	Continuous- Wave (CW)	Continuous- Wave (CW)
Power Supply (VDC)	3 to 6	3 to 6	3 to 6
Recommended Power Supply Voltage (V)	3.3	3.3	3.3
Body Diameter (mm)	9.5	9.5	9.5
Body Length (mm)	26	19	19
Lead Length (mm)	914	914	914
Connector	none	none	none
Part Number	0222-002-01	0220-970-00	0220-968-00



MECHANICAL SPECIFICATIONS





Diode LabLaser Universal Power Supply			
31-1001-000	VLM Power Supply	Power Supply, 90-264VAC In, 5VDC Out, 3.5mm Jack	
1057734	Plug, 3.5 mm Stereo	Phono Plug to take Laser Diode Module with leads and add a Power Supply Plug	

VLM Power Supply

The Universal Diode Laser Module Power Supply uses the latest switchmode technology to provide a 5 VDC output suitable for driving any of the Coherent laser diode modules. The supply is CE-marked and meets appropriate UL, CSA, TUV, GS, and FCC requirements.

This compact (75 x 50 x 41 mm) autoranging power module can be connected to any 90-260 VAC 50/60 Hz supply. There is an IEC 320 input socket and a 1.8 m detachable line cord with plug provided. The 1.8 m output cable is terminated with an easy connect/disconnect jack socket

Purchase separately the 3.5 mm Plug to then add to your laser power leads to be compatible with the power supply jack.

FEATURES

- Well-regulated 5VDC output
- Autoranging 90 to 260 VAC IEC input
- Output cable with easy connect/ disconnect jack



3.5 mm Jack Plug for VLM





Variable Angle Diode Laser Mount			
0221-437-00	Mount for VLM2 or LG2	Variable Angle, 1/4-20 inch Base, 14.8 mm Bore	
0221-448-00	Mount for VLM3 or LG3	Variable Angle, 1/4-20 inch Base, 9.5 mm Bore	

Variable Angle Diode Laser Mount

Coherent's variable angle laser diode module mounts are designed to accept three different sizes of diode laser module namely VLM3, VLM2 (9.5 mm and14.8 mm diameter).


This simple mount acts as combined heat sink, electrical insulator and variable angle mount for 9.5 or 14.8 mm diameter diode modules and 19.0 mm Diode LabLasers. The lasers are held firmly in a spherical-surface brass ring by two small set screws. This ring is clamped between two insulating blocks forming a "ball and socket" arrangement. Two socket-head screws can be loosened to allow easy angular adjustment of the module (±15° range) and quick, rigid locking in position.

FEATURES

- Simple tip/tilt and lock in place mechanism
- Adjustable angle through about ±15 degrees

MECHANICAL SPECIFICATIONS

VLM Mount





Coherent, Inc., 5100 Patrick Henry Drive Santa Clara, CA 95054 p. (800) 527-3786 | (408) 764-4983 f. (408) 764-4646

tech.sales@Coherent.com www.Coherent.com

Coherent follows a policy of continuous product improvement. Specifications are subject to change without notice. Coherent's scientific and industrial lasers are certified to comply with the Federal Regulations (21 CFR Subchapter J) as administered by the Center for Devices and Radiological Health on all systems ordered for shipment after August 2, 1976.

LASER REJURITOR-AVOID DIRECT LASER REJURITOR-AVOID DIRECT LASE REALERE PRODUCT LASE REALERE PRODUCT

Coherent offers a limited warranty for all ULN Diode Laser Modules. For full details of this warranty coverage, please refer to the Service section at www.Coherent.com or contact your local Sales or Service Representative. Printed in the U.S.A. MC-XXX-17-0M0917 Copyright ©2017 Coherent, Inc.