

[All Products](#) / [Optics](#) / [Beamsplitters](#) / [Plate Beamsplitters](#)

Broadband Polarizing Plate Beamsplitters





- Wire Grid Technology
- Reflects S-Polarized Light, Transmits P-Polarized Light
- Ideal for High Temperature Environments

Common Specifications

Physical & Mechanical Properties			
Thickness (mm):		0.70 ±0.07	Dimensional Tolerance (mm): ±0.2
Construction:		Wire Grid	
Optical Properties			
Angle of Incidence (°):		45 ±15	
Substrate:		Corning Eagle XG	Surface Quality: 80-50
Coating Specification:		Surface 2: R _{abs} <2.0% @ 420 - 670nm	Wavelength Range (nm): 420 - 700
Transmission Axis Tolerance (°):		±1	
Material Properties			
Thermal Expansion:		31.7 x 10 ⁻⁷ /°C	
Environmental & Durability Factors			
Operating Temperature (°C):		-40 to +200	

Technical Information



Products

Coating Specification	Operating Temperature (°C)	Substrate	Thickness (mm)	CA (mm)	Dimensions (mm)	Stock Number	Price	Buy
Surface 2: R _{abs} <2.0% @ 420 - 670nm	-40 to +200	Corning Eagle XG	0.70	8.5 x 8.5	12.5 x 12.5	#48-544	₹14,169 Volume Pricing	11 In Stock
Surface 2: R _{abs} <2.0% @ 420 - 670nm	-40 to +200	Corning Eagle XG	0.70	21.0 x 21.0	25.0 x 25.0	#48-545	₹18,995 Volume Pricing	17 In Stock



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038
Phone: 1-800-363-1992 : www.edmundoptics.com