


[All Products](#) / [Optics](#) / [Windows and Diffusers](#) / [UV and IR Windows](#)

Sodium Chloride (NaCl) Windows




- Excellent Transmission from 250nm – 16μm
- Low Cost
- Ideal for FTIR Spectroscopy
- [Potassium Bromide \(KBr\) Windows](#) Also Available



Common Specifications

Physical & Mechanical Properties			
Bevel:	Protective as needed	Edges:	Fine Ground
Knoop Hardness (kg/mm ²):	18.20	Poisson's Ratio:	0.25
Young's Modulus (GPa):	39.98		
Optical Properties			
Abbe Number (v _d):	42.89		
Coating:	Uncoated	Index of Refraction (n _d):	1.544
Substrate:	Sodium Chloride (NaCl)	Surface Quality:	60-40
Wavelength Range (nm):	250 - 16000		
Material Properties			
Coefficient of Thermal Expansion CTE (10 ⁻⁶ /°C):	44		
Density (g/cm ³):	2.17	Solubility, in 100g of H ₂ O @ 273K (g):	35.70

Technical Information



Products

Dia. (mm)	Thickness (mm)	Coating	Stock Number	Price	Buy
13.00	1.00	Uncoated	#68-812	₹4,328 Volume Pricing	5 In Stock
13.00	2.00	Uncoated	#68-813	₹4,328 Volume Pricing	Contact Us
20.00	2.00	Uncoated	#68-814	₹4,694 Volume Pricing	13 In Stock
25.00	2.00	Uncoated	#68-815	₹5,208 Volume Pricing	7 In Stock
25.00	4.00	Uncoated	#68-816	₹5,208 Volume Pricing	6 In Stock
25.00	5.00	Uncoated	#68-817	₹5,208 Volume Pricing	2 In Stock
32.00	3.00	Uncoated	#68-818	₹5,721 Volume Pricing	7 In Stock
50.00	3.00	Uncoated	#68-819	₹14,523 Volume Pricing	8 In Stock



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038

Phone: 1-800-363-1992 :

www.edmundoptics.com