





FOCAL LENGTH (EFL): 300 ±3

BACK FOCAL LENGTH (BFL): 296,7

- 1 405nm V-COAT
R(ABS) < 0,25% @ 405nm @ 0° AOI

LEFT SURFACE	MATERIAL	RIGHT SURFACE
R 155,04 CX Øe 39 (λ) SEE NOTE 1 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 6/ -	GLASS N-BK7 517/642 Nd: 1,517 Vd: 64,17	R ∞ PL Øe 39 (λ) SEE NOTE 1 3/ 3 (0,5) λ=632,8 nm 4/ 1,93' 5/ 40 - 20 6/ -

PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION		 Edmund Optics®			
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm			TITLE 40mm Dia x 300mm FL, 405nm V-Coat Coated, Plano-Convex Lens			
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY								DWG NO 26130
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING					SHEET T SIZE A4			
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN: mm					SHEET 1 OF 1