





FOCAL LENGTH (EFL): 400 ± 4

BACK FOCAL LENGTH (BFL): 396,7

- 1 785nm V-COAT
R(ABS) < 0,25% @ 785nm @ 0° AOI

LEFT SURFACE	MATERIAL	RIGHT SURFACE
R 206,72 CX Øe 39 λ SEE NOTE 1 3/ 3 (0,5) $\lambda=632,8$ nm 4/ - 5/ 40 - 20 6/ -	GLASS N-BK7 517/642 Nd: 1,517 Vd: 64,17	R ∞ PL Øe 39 λ SEE NOTE 1 3/ 3 (0,5) $\lambda=632,8$ nm 4/ 1,93' 5/ 40 - 20 6/ -

PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION		 Edmund Optics®				
ROHS: COMPLIANT	SCALE: NONE	$\lambda = 587,6\text{nm}$							
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY					TITLE	40mm Dia x 400mm FL, 785nm V-Coat Coated, Plano-Convex Lens			
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING									
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN:	mm	DWG NO	26158	SHEET T SIZE	A4	SHEET 1 OF 1